

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520943

Luminaire Tested: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520943
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4639.6 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520943
CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

Luminous Intensity Polar Plot



TEST NUMBER: P520943

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520943

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	340.3	7.3
100°-110°	968.4	20.9
110°-120°	927.8	20.0
120°-130°	734.4	15.8
130°-140°	589.4	12.7
140°-150°	461.5	9.9
150°-160°	337.6	7.3
160°-170°	209.1	4.5
170°-180°	71.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2236.6	48.2
90°-150°	4021.8	86.7
90°-180°	4640.0	100.0
0°-180°	4639.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	37	147	659	228	141	42
105°	150	228	987	1743	1657	159
115°	280	338	748	1585	1862	275
125°	395	438	714	1185	1417	353
135°	483	523	706	1001	1132	373
145°	569	599	711	866	944	356
155°	650	666	728	783	815	301
165°	718	721	737	753	764	202
175°	753	748	746	741	736	71
180°	747	747	747	747	747	

TEST NUMBER: P520943

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.4	60.2	139.7	40.7	30.7
95°	36.9	146.6	658.9	228.0	140.6
97.5°	67.9	171.7	1014.7	726.1	497.6
100°	89.5	186.6	1092.0	1106.1	852.0
102.5°	113.3	202.7	1074.9	1415.8	1193.9
105°	150.5	228.3	986.9	1743.2	1657.1
107.5°	188.3	258.0	884.1	1835.5	1912.1
110°	214.4	279.7	825.0	1800.2	1972.3

TEST NUMBER: P520943

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.4	301.3	785.2	1716.7	1962.1
115°	279.7	338.0	748.3	1585.3	1861.6
117.5°	315.2	369.9	726.5	1441.7	1734.4
120°	343.6	389.5	724.2	1359.6	1640.1
122.5°	366.4	412.2	718.5	1287.6	1548.1
125°	394.8	437.8	714.2	1185.3	1417.1
127.5°	425.7	466.0	712.0	1124.1	1315.2
130°	441.6	481.9	708.6	1081.5	1248.2
132.5°	458.7	497.8	708.6	1048.3	1201.6
135°	482.8	523.1	705.7	1001.2	1131.7
137.5°	505.5	544.7	705.4	961.3	1074.1
140°	522.6	562.8	704.3	928.3	1036.6
142.5°	541.9	575.5	707.7	901.9	999.1
145°	569.4	598.6	711.4	866.5	944.3
147.5°	593.0	621.3	717.7	830.8	898.0
150°	613.4	632.9	719.9	819.0	866.2
152.5°	629.3	649.9	722.2	803.0	846.9
155°	650.3	665.6	728.4	783.1	815.1
157.5°	676.5	685.6	729.9	774.1	796.9
160°	690.1	697.1	735.5	767.2	786.7
162.5°	698.1	706.1	736.7	761.4	776.4
165°	718.5	721.3	737.0	752.8	763.9
167.5°	732.4	729.9	743.5	750.7	755.1
170°	737.0	735.6	741.2	742.8	748.3
172.5°	747.2	742.5	744.6	740.5	744.9
175°	752.6	748.4	745.5	741.1	735.5
177.5°	754.9	748.2	744.6	740.1	741.2
180°	746.9	746.9	746.9	746.9	746.9

(END OF REPORT)