

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520963

Luminaire Tested: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520963  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6332.1 lumens  
Efficiency: N/A  
Efficacy: 124.2 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 51  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520963

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P520963

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520963

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	464.5	7.3
100°-110°	1321.7	20.9
110°-120°	1266.3	20.0
120°-130°	1002.2	15.8
130°-140°	804.5	12.7
140°-150°	629.8	9.9
150°-160°	460.8	7.3
160°-170°	285.4	4.5
170°-180°	96.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3052.5	48.2
90°-150°	5489.0	86.7
90°-180°	6332.0	100.0
0°-180°	6332.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P520963

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9

TEST NUMBER: P520963

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)