

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520965

Luminaire Tested: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520965
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6618.5 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 51.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520965
CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P520965

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520965

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	485.5	7.3
100°-110°	1381.5	20.9
110°-120°	1323.6	20.0
120°-130°	1047.6	15.8
130°-140°	840.8	12.7
140°-150°	658.3	9.9
150°-160°	481.7	7.3
160°-170°	298.3	4.5
170°-180°	101.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3190.6	48.2
90°-150°	5737.2	86.7
90°-180°	6618.0	100.0
0°-180°	6618.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	53	209	940	325	200	60
105°	215	326	1408	2487	2364	227
115°	399	482	1068	2262	2656	393
125°	563	624	1019	1691	2022	504
135°	689	746	1007	1428	1614	531
145°	812	854	1015	1236	1347	507
155°	928	950	1039	1117	1163	429
165°	1025	1029	1051	1074	1090	288
175°	1074	1068	1064	1057	1049	102
180°	1066	1066	1066	1066	1066	

TEST NUMBER: P520965

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	85.9	199.3	58.0	43.8
95°	52.7	209.1	939.9	325.3	200.5
97.5°	96.8	245.0	1447.5	1035.8	709.8
100°	127.6	266.3	1557.7	1577.8	1215.4
102.5°	161.6	289.2	1533.4	2019.7	1703.2
105°	214.7	325.6	1407.8	2486.7	2363.9
107.5°	268.6	368.0	1261.2	2618.4	2727.7
110°	305.9	399.0	1176.9	2568.0	2813.6

TEST NUMBER: P520965

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	341.5	429.9	1120.2	2448.9	2799.0
115°	399.1	482.2	1067.5	2261.5	2655.6
117.5°	449.7	527.7	1036.3	2056.6	2474.1
120°	490.2	555.6	1033.1	1939.5	2339.6
122.5°	522.6	588.0	1025.0	1836.8	2208.4
125°	563.1	624.5	1018.9	1690.8	2021.6
127.5°	607.3	664.7	1015.7	1603.6	1876.1
130°	630.0	687.4	1010.8	1542.9	1780.5
132.5°	654.3	710.1	1010.8	1495.4	1714.1
135°	688.7	746.2	1006.7	1428.3	1614.4
137.5°	721.1	777.0	1006.3	1371.4	1532.2
140°	745.4	802.9	1004.7	1324.2	1478.7
142.5°	773.0	820.9	1009.6	1286.6	1425.2
145°	812.3	853.9	1014.8	1236.1	1347.0
147.5°	845.9	886.3	1023.8	1185.2	1281.0
150°	875.1	902.8	1027.0	1168.3	1235.6
152.5°	897.8	927.1	1030.2	1145.5	1208.1
155°	927.7	949.5	1039.2	1117.2	1162.7
157.5°	965.0	978.1	1041.2	1104.3	1136.8
160°	984.5	994.4	1049.3	1094.5	1122.2
162.5°	995.8	1007.3	1050.9	1086.2	1107.6
165°	1025.0	1028.9	1051.3	1073.9	1089.8
167.5°	1044.8	1041.3	1060.6	1070.9	1077.2
170°	1051.3	1049.3	1057.4	1059.6	1067.5
172.5°	1065.9	1059.2	1062.2	1056.3	1062.6
175°	1073.6	1067.6	1063.5	1057.2	1049.3
177.5°	1076.8	1067.3	1062.2	1055.8	1057.4
180°	1065.5	1065.5	1065.5	1065.5	1065.5

(END OF REPORT)