

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520967

Luminaire Tested: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520967
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6848.3 lumens
Efficiency: N/A
Efficacy: 134.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 51.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520967

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P520967

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520967

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	502.4	7.3
100°-110°	1429.4	20.9
110°-120°	1369.6	20.0
120°-130°	1083.9	15.8
130°-140°	870.0	12.7
140°-150°	681.1	9.9
150°-160°	498.4	7.3
160°-170°	308.7	4.5
170°-180°	104.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3301.4	48.2
90°-150°	5936.5	86.7
90°-180°	6848.0	100.0
0°-180°	6848.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	54	216	972	337	208	62
105°	222	337	1457	2573	2446	235
115°	413	499	1105	2340	2748	407
125°	583	646	1054	1750	2092	522
135°	713	772	1042	1478	1670	550
145°	840	884	1050	1279	1394	525
155°	960	982	1075	1156	1203	444
165°	1061	1065	1088	1111	1128	298
175°	1111	1105	1100	1094	1086	105
180°	1102	1102	1102	1102	1102	

TEST NUMBER: P520967

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.8	88.9	206.2	60.0	45.3
95°	54.5	216.4	972.5	336.6	207.5
97.5°	100.2	253.5	1497.8	1071.8	734.4
100°	132.0	275.5	1611.8	1632.6	1257.6
102.5°	167.3	299.2	1586.6	2089.8	1762.3
105°	222.2	336.9	1456.7	2573.1	2446.0
107.5°	277.9	380.8	1305.0	2709.3	2822.4
110°	316.5	412.8	1217.8	2657.2	2911.3

TEST NUMBER: P520967

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	353.4	444.8	1159.1	2533.9	2896.2
115°	412.9	499.0	1104.6	2340.0	2747.8
117.5°	465.3	546.1	1072.3	2128.0	2560.0
120°	507.2	574.9	1068.9	2006.9	2420.8
122.5°	540.8	608.4	1060.6	1900.6	2285.0
125°	582.7	646.2	1054.3	1749.5	2091.8
127.5°	628.4	687.8	1050.9	1659.3	1941.3
130°	651.8	711.3	1045.9	1596.4	1842.4
132.5°	677.0	734.8	1045.9	1547.4	1773.6
135°	712.6	772.1	1041.7	1477.8	1670.5
137.5°	746.2	804.0	1041.3	1419.0	1585.4
140°	771.3	830.7	1039.6	1370.2	1530.1
142.5°	799.8	849.4	1044.6	1331.3	1474.7
145°	840.5	883.5	1050.1	1279.1	1393.8
147.5°	875.3	917.1	1059.3	1226.3	1325.5
150°	905.5	934.2	1062.7	1208.9	1278.5
152.5°	928.9	959.3	1066.0	1185.3	1250.0
155°	960.0	982.5	1075.2	1156.0	1203.1
157.5°	998.5	1012.0	1077.3	1142.6	1176.3
160°	1018.6	1028.9	1085.7	1132.5	1161.2
162.5°	1030.4	1042.3	1087.4	1123.9	1146.1
165°	1060.6	1064.7	1087.8	1111.2	1127.6
167.5°	1081.1	1077.4	1097.4	1108.1	1114.6
170°	1087.8	1085.8	1094.1	1096.4	1104.6
172.5°	1102.9	1095.9	1099.1	1093.0	1099.5
175°	1110.9	1104.7	1100.4	1093.9	1085.7
177.5°	1114.2	1104.4	1099.1	1092.5	1094.1
180°	1102.5	1102.5	1102.5	1102.5	1102.5

(END OF REPORT)