

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521424

Luminaire Tested: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521424
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-38)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6672.1 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 58.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521424

CATALOG NUMBER: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

Luminous Intensity Polar Plot



TEST NUMBER: P521424

CATALOG NUMBER: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92		81	81	81		70	70	70	65
1	101	97	92	89	95	91	87	84	80	78	75		71	69	67		62	60	59	55
2	92	84	78	72	86	79	74	69	70	66	62		62	58	55		54	52	49	45
3	84	74	66	60	78	70	63	57	62	56	52		54	50	47		48	44	42	38
4	76	65	57	51	72	62	54	48	55	49	44		48	44	40		43	39	36	33
5	70	58	50	43	66	55	47	41	49	43	38		43	38	34		38	34	31	28
6	65	52	44	38	61	49	42	36	44	38	33		39	34	30		35	30	27	25
7	60	47	39	33	56	45	37	32	40	34	29		36	30	27		32	27	24	22
8	56	43	35	29	52	41	33	28	36	30	26		33	27	24		29	25	22	19
9	52	39	31	26	49	37	30	25	33	27	23		30	25	21		27	22	19	17
10	48	36	28	23	45	34	27	23	31	25	21		28	23	19		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14097	14097	14097
5°	14210	14122	14082
10°	14195	14096	14057
15°	14128	14047	14017
20°	14064	14002	13918
25°	13956	13902	13750
30°	13836	13803	13633
35°	13696	13648	13504
40°	13559	13508	13342
45°	13401	13291	13139
50°	13174	13083	12930
55°	12989	12801	12648
60°	12688	12433	12256
65°	12278	11931	11745
70°	11564	11192	10993
75°	10441	10174	10024
80°	8623	8623	8512
85°	6066	6966	7188

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13401 cd/sqm

TEST NUMBER: P521424

CATALOG NUMBER: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	2.2
10°-20°	414.4	6.2
20°-30°	626.6	9.4
30°-40°	754.6	11.3
40°-50°	783.7	11.7
50°-60°	710.4	10.6
60°-70°	541.0	8.1
70°-80°	302.3	4.5
80°-90°	78.4	1.2
90°-100°	169.9	2.5
100°-110°	483.4	7.2
110°-120°	463.2	6.9
120°-130°	366.6	5.5
130°-140°	294.2	4.4
140°-150°	230.4	3.5
150°-160°	168.5	2.5
160°-170°	104.4	1.6
170°-180°	35.4	0.5
0°-30°	1185.7	17.8
0°-40°	1940.3	29.1
0°-60°	3434.3	51.5
0°-90°	4356.0	65.3
90°-120°	1116.5	16.7
90°-150°	2007.7	30.1
90°-180°	2316.0	34.7
0°-180°	6672.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1528	1528	1528	1528	1528	
5°	1534	1520	1525	1520	1520	146
15°	1479	1466	1471	1468	1468	417
25°	1371	1360	1366	1355	1351	631
35°	1216	1209	1212	1200	1199	761
45°	1027	1021	1019	1008	1007	791
55°	808	804	796	786	786	720
65°	562	556	546	539	538	554
75°	293	289	285	281	281	310
85°	57	61	66	67	68	71
90°	0	0	0	0	0	3
95°	18	73	329	114	70	21
105°	75	114	493	870	827	79
115°	140	169	374	791	929	137
125°	197	218	356	592	707	176
135°	241	261	352	500	565	186
145°	284	299	355	433	471	178
155°	325	332	364	391	407	150
165°	359	360	368	376	381	101
175°	376	374	372	370	367	36
180°	373	373	373	373	373	

TEST NUMBER: P521424

CATALOG NUMBER: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1527.9	1527.9	1527.9	1527.9	1527.9
2.5°	1537.3	1524.8	1528.8	1526.1	1521.1
5°	1534.3	1519.8	1524.8	1520.5	1520.5
7.5°	1523.7	1509.8	1513.1	1510.5	1510.5
10°	1515.2	1499.6	1504.6	1500.4	1500.4
12.5°	1501.6	1487.7	1492.7	1488.5	1487.6
15°	1479.1	1465.6	1470.6	1467.5	1467.5
17.5°	1452.0	1439.1	1445.6	1440.5	1438.8
20°	1432.4	1417.9	1426.1	1417.6	1417.6
22.5°	1408.7	1395.8	1403.2	1392.9	1391.3
25°	1370.9	1359.5	1365.6	1354.9	1350.7
27.5°	1328.5	1316.2	1325.3	1313.3	1311.1
30°	1298.7	1287.3	1295.6	1282.8	1279.7
32.5°	1266.5	1256.7	1262.5	1250.5	1248.2
35°	1216.0	1208.7	1211.7	1200.0	1199.0
37.5°	1162.3	1155.2	1158.1	1145.1	1144.3
40°	1125.8	1119.6	1121.6	1107.8	1107.8
42.5°	1088.4	1081.4	1081.7	1068.7	1067.9
45°	1027.1	1020.9	1018.6	1008.0	1007.0
47.5°	962.0	959.1	955.6	945.0	945.0
50°	917.8	915.8	911.5	900.8	900.8
52.5°	872.8	871.6	865.6	856.7	855.0
55°	807.5	804.4	795.8	786.3	786.3
57.5°	736.0	733.5	723.9	716.2	714.3
60°	687.6	683.4	673.8	665.3	664.2
62.5°	637.5	634.2	623.7	616.0	614.1
65°	562.4	556.1	546.5	539.0	538.0
67.5°	483.0	475.9	467.5	461.3	459.2
70°	428.7	422.4	414.9	409.5	407.5
72.5°	375.2	369.0	362.2	358.6	358.2
75°	292.9	288.7	285.4	281.2	281.2
77.5°	212.4	209.9	208.2	206.1	206.1
80°	162.3	162.3	162.3	160.2	160.2
82.5°	116.5	119.0	120.7	119.5	119.5
85°	57.3	61.4	65.8	66.9	67.9
87.5°	16.1	21.1	26.3	27.2	28.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.1	69.8	20.3	15.3
95°	18.4	73.2	328.9	113.8	70.2
97.5°	33.9	85.7	506.5	362.5	248.4
100°	44.7	93.2	545.1	552.1	425.3
102.5°	56.6	101.2	536.6	706.7	596.0
105°	75.1	114.0	492.6	870.2	827.2
107.5°	94.0	128.8	441.3	916.3	954.5
110°	107.0	139.6	411.8	898.6	984.6

TEST NUMBER: P521424

CATALOG NUMBER: SQ4-F-050U-100D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	119.5	150.4	392.0	856.9	979.5
115°	139.6	168.8	373.6	791.4	929.3
117.5°	157.4	184.7	362.6	719.7	865.8
120°	171.5	194.4	361.5	678.7	818.7
122.5°	182.9	205.8	358.7	642.8	772.8
125°	197.1	218.5	356.5	591.7	707.4
127.5°	212.5	232.6	355.4	561.2	656.5
130°	220.4	240.5	353.7	539.9	623.1
132.5°	229.0	248.5	353.7	523.3	599.8
135°	241.0	261.1	352.3	499.8	564.9
137.5°	252.3	271.9	352.2	479.9	536.2
140°	260.9	281.0	351.6	463.4	517.5
142.5°	270.5	287.3	353.3	450.2	498.7
145°	284.2	298.8	355.1	432.6	471.4
147.5°	296.0	310.2	358.2	414.7	448.3
150°	306.2	315.9	359.4	408.8	432.4
152.5°	314.2	324.4	360.5	400.9	422.8
155°	324.6	332.3	363.6	390.9	406.9
157.5°	337.7	342.3	364.3	386.4	397.8
160°	344.5	348.0	367.2	383.0	392.7
162.5°	348.5	352.5	367.7	380.1	387.6
165°	358.7	360.1	367.9	375.8	381.4
167.5°	365.6	364.4	371.1	374.7	377.0
170°	367.9	367.2	370.0	370.8	373.6
172.5°	373.0	370.6	371.7	369.6	371.9
175°	375.7	373.6	372.1	370.0	367.2
177.5°	376.8	373.5	371.7	369.5	370.0
180°	372.9	372.9	372.9	372.9	372.9

(END OF REPORT)