

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520970

Luminaire Tested: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520970  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7089.3 lumens  
Efficiency: N/A  
Efficacy: 139.6 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 50.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520970  
CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

### Luminous Intensity Polar Plot



TEST NUMBER: P520970

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520970

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	520.1	7.3
100°-110°	1479.7	20.9
110°-120°	1417.7	20.0
120°-130°	1122.1	15.8
130°-140°	900.6	12.7
140°-150°	705.1	9.9
150°-160°	515.9	7.3
160°-170°	319.6	4.5
170°-180°	108.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3417.5	48.2
90°-150°	6145.3	86.7
90°-180°	7089.0	100.0
0°-180°	7089.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	56	224	1007	348	215	64
105°	230	349	1508	2664	2532	243
115°	427	516	1143	2422	2844	421
125°	603	669	1091	1811	2165	540
135°	738	799	1078	1530	1729	569
145°	870	915	1087	1324	1443	544
155°	994	1017	1113	1197	1245	459
165°	1098	1102	1126	1150	1167	309
175°	1150	1144	1139	1132	1124	109
180°	1141	1141	1141	1141	1141	

TEST NUMBER: P520970

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.4	92.0	213.5	62.1	46.9
95°	56.4	224.0	1006.8	348.5	214.8
97.5°	103.7	262.4	1550.5	1109.5	760.3
100°	136.7	285.2	1668.5	1690.1	1301.8
102.5°	173.1	309.8	1642.5	2163.3	1824.3
105°	230.0	348.8	1508.0	2663.6	2532.1
107.5°	287.7	394.2	1350.9	2804.6	2921.8
110°	327.6	427.3	1260.6	2750.7	3013.7

TEST NUMBER: P520970

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4\_6500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	365.8	460.4	1199.9	2623.0	2998.1
115°	427.4	516.5	1143.4	2422.3	2844.5
117.5°	481.7	565.3	1110.0	2202.9	2650.1
120°	525.1	595.1	1106.6	2077.5	2506.0
122.5°	559.8	629.8	1097.9	1967.4	2365.4
125°	603.2	669.0	1091.4	1811.1	2165.4
127.5°	650.5	712.0	1087.9	1717.7	2009.6
130°	674.8	736.3	1082.7	1652.6	1907.2
132.5°	700.8	760.6	1082.7	1601.8	1836.0
135°	737.7	799.2	1078.4	1529.8	1729.3
137.5°	772.4	832.2	1077.9	1468.9	1641.2
140°	798.5	860.0	1076.2	1418.4	1583.9
142.5°	828.0	879.3	1081.4	1378.1	1526.6
145°	870.1	914.6	1087.0	1324.1	1442.9
147.5°	906.1	949.4	1096.6	1269.5	1372.1
150°	937.3	967.0	1100.1	1251.4	1323.5
152.5°	961.6	993.0	1103.5	1227.0	1294.0
155°	993.7	1017.1	1113.1	1196.6	1245.4
157.5°	1033.7	1047.7	1115.2	1182.9	1217.7
160°	1054.5	1065.1	1123.9	1172.3	1202.0
162.5°	1066.6	1078.9	1125.7	1163.5	1186.4
165°	1097.9	1102.1	1126.1	1150.3	1167.3
167.5°	1119.1	1115.3	1136.1	1147.1	1153.9
170°	1126.1	1124.0	1132.6	1135.0	1143.4
172.5°	1141.7	1134.5	1137.8	1131.4	1138.2
175°	1150.0	1143.6	1139.1	1132.4	1123.9
177.5°	1153.4	1143.2	1137.8	1130.9	1132.6
180°	1141.3	1141.3	1141.3	1141.3	1141.3

(END OF REPORT)