

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520978

Luminaire Tested: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520978
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3230.9 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 34.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520978

CATALOG NUMBER: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P520978

CATALOG NUMBER: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78		62	62	62		47	47	47	40
1	97	93	90	87	88	85	83	80	70	68	67		56	55	54		44	43	42	37
2	89	83	78	73	82	76	72	68	63	60	58		51	49	48		40	39	38	33
3	83	74	68	63	75	68	63	59	57	53	50		47	44	42		37	35	34	30
4	76	67	60	55	70	62	56	51	52	48	44		43	40	37		34	32	31	27
5	71	60	53	48	65	56	50	45	47	43	39		39	36	33		32	29	28	25
6	66	55	47	42	60	51	44	40	43	38	35		36	33	30		29	27	25	22
7	61	50	43	38	56	46	40	36	40	35	31		33	30	27		27	25	23	21
8	57	46	39	34	52	42	36	32	36	32	28		31	27	25		25	23	21	19
9	53	42	35	31	49	39	33	29	34	29	26		29	25	23		24	21	20	17
10	50	39	32	28	46	36	30	26	31	27	24		27	23	21		22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10010	10010	10010
5°	9849	9825	9897
10°	9215	9338	9599
15°	8378	8643	9125
20°	7436	7823	8509
25°	6475	6989	7817
30°	5547	6157	7163
35°	4600	5226	6373
40°	3534	4178	5431
45°	2555	3164	4370
50°	1740	2358	3465
55°	1131	1705	2693
60°	650	1201	1947
65°	172	734	985
70°	84	227	283
75°	36	18	0
80°	27	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4370 cd/sqm

TEST NUMBER: P520978

CATALOG NUMBER: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	3.1
10°-20°	253.2	7.8
20°-30°	317.0	9.8
30°-40°	292.8	9.1
40°-50°	196.7	6.1
50°-60°	101.6	3.1
60°-70°	31.8	1.0
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	142.1	4.4
100°-110°	404.2	12.5
110°-120°	387.3	12.0
120°-130°	306.6	9.5
130°-140°	246.0	7.6
140°-150°	192.6	6.0
150°-160°	140.9	4.4
160°-170°	87.3	2.7
170°-180°	29.6	0.9
0°-30°	669.2	20.7
0°-40°	962.0	29.8
0°-60°	1260.3	39.0
0°-90°	1294.2	40.1
90°-120°	933.6	28.9
90°-150°	1678.9	52.0
90°-180°	1937.0	60.0
0°-180°	3230.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1085	1085	1085	1085	1085	
5°	1063	1053	1061	1064	1069	99
15°	877	874	905	935	955	244
25°	636	641	686	734	768	292
35°	408	419	464	519	566	253
45°	196	208	242	290	335	154
55°	70	82	106	136	167	66
65°	8	15	34	40	45	13
75°	1	1	0	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P520978

CATALOG NUMBER: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1084.9	1084.9	1084.9	1084.9	1084.9
2.5°	1087.4	1077.2	1079.9	1079.8	1076.9
5°	1063.4	1052.6	1060.8	1064.5	1068.6
7.5°	1018.5	1010.1	1025.7	1037.5	1046.0
10°	983.6	976.4	996.7	1012.8	1024.6
12.5°	943.3	937.8	962.3	984.3	999.4
15°	877.1	874.0	904.9	935.3	955.3
17.5°	806.1	806.0	841.3	879.0	903.1
20°	757.4	758.9	796.8	838.3	866.6
22.5°	708.7	712.3	752.7	796.0	828.4
25°	636.1	641.3	686.5	733.5	767.9
27.5°	566.4	573.9	621.6	670.4	712.3
30°	520.7	529.4	577.9	629.3	672.4
32.5°	475.7	486.1	533.4	587.7	631.6
35°	408.4	418.6	464.0	518.6	565.8
37.5°	338.8	348.8	393.1	446.9	497.9
40°	293.4	304.7	346.9	399.0	450.9
42.5°	252.3	263.5	303.3	354.5	403.4
45°	195.8	207.6	242.5	289.7	334.9
47.5°	149.0	161.8	192.4	235.1	276.3
50°	121.2	134.1	164.3	201.9	241.4
52.5°	99.0	111.4	138.7	174.1	210.4
55°	70.3	82.1	106.0	136.1	167.4
57.5°	48.6	58.8	80.2	105.3	129.9
60°	35.2	44.9	65.1	85.5	105.5
62.5°	23.4	32.3	52.1	67.7	81.1
65°	7.9	15.1	33.6	40.5	45.1
67.5°	4.0	4.8	17.6	18.6	20.2
70°	3.1	3.1	8.4	9.0	10.5
72.5°	2.3	2.3	3.4	4.3	4.6
75°	1.0	1.0	0.5	0.0	0.0
77.5°	0.5	0.5	0.4	0.0	0.0
80°	0.5	0.5	0.0	0.0	0.0
82.5°	0.1	0.1	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P520978

CATALOG NUMBER: SQ4-BB-025U-050D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)