

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521604

Luminaire Tested: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521604
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-36)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7840.1 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.26 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521604

CATALOG NUMBER: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P521604

CATALOG NUMBER: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	28				
1	93	88	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23				
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16				
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	20	18	14				
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16	12				
6	59	47	39	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10				
7	54	43	35	29	48	38	32	27	30	25	22	23	19	17	16	14	12	9				
8	50	38	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8				
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7				
10	44	32	25	20	39	29	23	19	23	18	15	18	14	12	12	10	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6997	6997	6997
5°	7043	6995	7005
10°	7009	7028	6941
15°	7027	6957	6987
20°	6999	6969	6898
25°	6920	6879	6836
30°	6900	6857	6791
35°	6794	6794	6689
40°	6742	6680	6593
45°	6615	6615	6521
50°	6535	6491	6402
55°	6425	6359	6259
60°	6281	6167	6071
65°	6032	5897	5783
70°	5751	5554	5414
75°	5126	4980	4905
80°	4235	4176	4123
85°	3070	3398	3398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6615 cd/sqm

TEST NUMBER: P521604

CATALOG NUMBER: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	0.9
10°-20°	205.7	2.6
20°-30°	310.8	4.0
30°-40°	374.4	4.8
40°-50°	388.1	5.0
50°-60°	351.9	4.5
60°-70°	267.5	3.4
70°-80°	149.0	1.9
80°-90°	38.4	0.5
90°-100°	416.8	5.3
100°-110°	1186.1	15.1
110°-120°	1136.4	14.5
120°-130°	899.4	11.5
130°-140°	721.9	9.2
140°-150°	565.2	7.2
150°-160°	413.5	5.3
160°-170°	256.2	3.3
170°-180°	86.9	1.1
0°-30°	588.3	7.5
0°-40°	962.7	12.3
0°-60°	1702.8	21.7
0°-90°	2157.6	27.5
90°-120°	2739.4	34.9
90°-150°	4925.9	62.8
90°-180°	5682.0	72.5
0°-180°	7840.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	758	758	758	758	758	
5°	760	751	755	756	756	72
15°	736	729	728	728	732	207
25°	680	675	676	672	672	315
35°	603	597	603	596	594	378
45°	507	504	507	498	500	392
55°	399	398	395	391	389	356
65°	276	275	270	267	265	274
75°	144	142	140	138	138	153
85°	29	31	32	33	32	35
90°	0	0	0	0	0	3
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P521604

CATALOG NUMBER: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	758.4	758.4	758.4	758.4	758.4
2.5°	764.2	756.1	757.6	758.3	752.7
5°	760.5	751.4	755.3	756.4	756.4
7.5°	757.2	750.1	752.7	749.5	749.1
10°	748.1	745.1	750.2	742.9	740.9
12.5°	744.0	739.3	740.2	738.8	740.9
15°	735.7	728.6	728.4	728.5	731.5
17.5°	722.9	713.7	719.7	713.3	712.5
20°	712.9	703.8	709.8	702.6	702.6
22.5°	703.0	692.3	698.2	688.4	686.0
25°	679.8	674.8	675.7	671.5	671.5
27.5°	663.5	652.3	656.0	650.2	650.6
30°	647.7	636.6	643.6	635.4	637.4
32.5°	632.0	624.9	628.7	619.7	623.3
35°	603.2	597.2	603.2	596.0	593.9
37.5°	578.0	571.7	573.6	569.0	563.9
40°	559.8	552.7	554.6	548.4	547.4
42.5°	539.9	535.3	535.6	530.2	530.8
45°	507.0	504.0	507.0	497.7	499.8
47.5°	477.6	474.0	473.7	467.5	470.0
50°	455.3	453.3	452.2	446.0	446.0
52.5°	432.1	430.1	429.0	424.4	423.6
55°	399.4	398.4	395.3	391.1	389.1
57.5°	363.6	361.6	359.9	355.5	353.9
60°	340.4	338.4	334.2	329.0	329.0
62.5°	314.8	312.7	307.7	305.8	302.6
65°	276.3	275.3	270.1	266.9	264.9
67.5°	238.0	234.7	232.4	228.4	226.4
70°	213.2	209.1	205.9	202.8	200.7
72.5°	185.8	182.6	179.4	177.9	175.1
75°	143.8	141.8	139.7	137.6	137.6
77.5°	104.5	103.9	101.8	101.8	100.8
80°	79.7	80.7	78.6	78.6	77.6
82.5°	57.3	58.3	57.9	58.7	57.7
85°	29.0	31.0	32.1	33.1	32.1
87.5°	8.3	10.7	12.4	13.2	13.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P521604

CATALOG NUMBER: SQ4-F-125U-050D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)