

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521666

Luminaire Tested: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521666
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-37)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9513.2 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521666

CATALOG NUMBER: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P521666

CATALOG NUMBER: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32																				
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27																				
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	31	29	28	22																				
3	78	68	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24	19																				
4	71	60	53	47	63	55	48	43	44	39	35	33	30	27	24	22	20	16																				
5	65	54	46	40	58	48	42	36	39	34	30	30	26	24	22	19	17	14																				
6	60	48	40	34	53	43	37	31	35	30	26	27	23	21	19	17	15	12																				
7	55	43	35	30	49	39	32	27	31	26	23	24	21	18	18	15	14	11																				
8	51	39	31	26	46	35	29	24	29	24	20	22	19	16	16	14	12	10																				
9	47	35	28	23	43	32	26	21	26	21	18	20	17	14	15	13	11	9																				
10	44	32	25	21	40	29	23	19	24	19	16	19	15	13	14	11	10	8																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9893	9893	9893
5°	9967	9931	9876
10°	9991	9918	9872
15°	9888	9851	9804
20°	9866	9800	9790
25°	9782	9763	9653
30°	9717	9655	9582
35°	9580	9569	9449
40°	9492	9445	9386
45°	9379	9327	9225
50°	9251	9182	9056
55°	9080	8969	8844
60°	8866	8722	8560
65°	8571	8379	8230
70°	8036	7850	7666
75°	7240	7033	6926
80°	5914	5967	5866
85°	4234	4859	4859

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9379 cd/sqm

TEST NUMBER: P521666

CATALOG NUMBER: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	1.1
10°-20°	290.6	3.1
20°-30°	439.7	4.6
30°-40°	528.8	5.6
40°-50°	549.0	5.8
50°-60°	497.4	5.2
60°-70°	378.4	4.0
70°-80°	210.3	2.2
80°-90°	54.2	0.6
90°-100°	474.1	5.0
100°-110°	1349.1	14.2
110°-120°	1292.6	13.6
120°-130°	1023.0	10.8
130°-140°	821.1	8.6
140°-150°	642.8	6.8
150°-160°	470.4	4.9
160°-170°	291.4	3.1
170°-180°	98.9	1.0
0°-30°	831.8	8.7
0°-40°	1360.6	14.3
0°-60°	2407.0	25.3
0°-90°	3049.8	32.1
90°-120°	3115.8	32.8
90°-150°	5602.8	58.9
90°-180°	6463.0	67.9
0°-180°	9513.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1076	1067	1072	1067	1066	102
15°	1035	1027	1031	1030	1026	293
25°	961	952	959	949	948	443
35°	851	847	850	840	839	533
45°	719	714	715	707	707	555
55°	564	564	558	553	550	504
65°	393	387	384	378	377	386
75°	203	200	197	195	194	215
85°	40	43	46	46	46	49
90°	0	0	0	0	0	4
95°	51	204	918	318	196	59
105°	210	318	1375	2428	2308	222
115°	390	471	1042	2208	2593	384
125°	550	610	995	1651	1974	492
135°	673	729	983	1395	1577	519
145°	793	834	991	1207	1316	496
155°	906	927	1015	1091	1136	419
165°	1001	1005	1027	1049	1064	281
175°	1048	1043	1038	1032	1025	99
180°	1040	1040	1040	1040	1040	

TEST NUMBER: P521666

CATALOG NUMBER: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1072.3	1072.3	1072.3	1072.3	1072.3
2.5°	1079.3	1070.1	1073.1	1070.7	1068.4
5°	1076.2	1066.6	1072.3	1067.4	1066.4
7.5°	1071.1	1059.8	1062.5	1061.5	1061.5
10°	1066.4	1052.1	1058.6	1053.7	1053.7
12.5°	1053.9	1041.9	1046.9	1044.4	1045.9
15°	1035.2	1026.6	1031.3	1030.2	1026.4
17.5°	1019.0	1008.6	1012.1	1010.3	1008.8
20°	1004.9	995.3	998.1	993.3	997.1
22.5°	989.3	979.7	984.8	976.8	976.8
25°	960.9	952.3	959.0	949.2	948.2
27.5°	930.9	925.3	929.7	922.4	919.7
30°	912.1	903.5	906.3	901.3	899.4
32.5°	890.2	881.6	884.4	875.6	876.8
35°	850.6	846.8	849.6	839.8	838.9
37.5°	814.7	807.0	811.5	803.5	802.7
40°	788.1	780.5	784.2	779.3	779.3
42.5°	763.9	755.5	757.6	751.1	748.8
45°	718.8	714.0	714.8	707.0	707.0
47.5°	674.2	670.8	669.3	661.4	662.9
50°	644.5	638.8	639.7	630.9	630.9
52.5°	610.2	610.5	606.8	601.1	596.5
55°	564.5	563.5	557.6	552.7	549.8
57.5°	515.6	511.2	507.0	500.4	499.8
60°	480.5	477.6	472.7	466.7	463.9
62.5°	444.5	441.7	436.7	431.6	431.1
65°	392.6	386.9	383.8	377.9	377.0
67.5°	336.1	331.6	327.7	323.0	322.5
70°	297.9	294.0	291.0	287.0	284.2
72.5°	262.7	256.6	253.5	250.3	248.2
75°	203.1	200.3	197.3	195.3	194.3
77.5°	145.7	145.9	145.9	143.3	142.4
80°	111.3	112.3	112.3	111.3	110.4
82.5°	80.9	82.6	83.4	82.4	82.2
85°	40.0	42.9	45.9	45.9	45.9
87.5°	10.9	14.8	18.0	18.7	18.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.8	83.9	194.7	56.7	42.7
95°	51.4	204.2	917.9	317.7	195.8
97.5°	94.6	239.2	1413.6	1011.5	693.2
100°	124.6	260.0	1521.2	1540.9	1186.9
102.5°	157.9	282.4	1497.5	1972.3	1663.2
105°	209.7	318.0	1374.8	2428.4	2308.5
107.5°	262.3	359.4	1231.6	2557.0	2663.8
110°	298.7	389.6	1149.3	2507.8	2747.7

TEST NUMBER: P521666

CATALOG NUMBER: SQ4-F-150U-075D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	333.5	419.8	1093.9	2391.5	2733.4
115°	389.7	470.9	1042.5	2208.5	2593.4
117.5°	439.2	515.4	1012.0	2008.4	2416.1
120°	478.7	542.5	1008.9	1894.1	2284.8
122.5°	510.4	574.2	1001.0	1793.7	2156.6
125°	549.9	609.9	995.0	1651.2	1974.2
127.5°	593.1	649.1	991.9	1566.0	1832.2
130°	615.2	671.3	987.1	1506.7	1738.8
132.5°	638.9	693.5	987.1	1460.4	1673.9
135°	672.6	728.7	983.2	1394.8	1576.6
137.5°	704.2	758.8	982.8	1339.2	1496.3
140°	728.0	784.1	981.2	1293.2	1444.1
142.5°	754.9	801.7	985.9	1256.4	1391.8
145°	793.2	833.9	991.1	1207.2	1315.5
147.5°	826.1	865.5	999.8	1157.4	1251.0
150°	854.6	881.6	1002.9	1140.9	1206.7
152.5°	876.7	905.4	1006.1	1118.7	1179.8
155°	906.0	927.3	1014.8	1091.0	1135.5
157.5°	942.4	955.2	1016.8	1078.4	1110.1
160°	961.4	971.1	1024.7	1068.8	1095.9
162.5°	972.5	983.7	1026.3	1060.8	1081.7
165°	1001.0	1004.8	1026.7	1048.8	1064.3
167.5°	1020.3	1016.9	1035.8	1045.8	1052.0
170°	1026.7	1024.7	1032.6	1034.8	1042.5
172.5°	1040.9	1034.3	1037.4	1031.6	1037.7
175°	1048.4	1042.6	1038.5	1032.4	1024.7
177.5°	1051.6	1042.3	1037.4	1031.1	1032.6
180°	1040.5	1040.5	1040.5	1040.5	1040.5

(END OF REPORT)