

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936238

Luminaire Tested: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936238  
REPORT IS A COMBINATION OF REPORTS P933445 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3376.5 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 33  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936238  
CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1688	1688	1688
5°	1648	1950	2268
10°	1494	2842	3760
15°	1269	3711	4541
20°	1033	4300	4628
25°	862	4499	4534
30°	726	4526	4525
35°	642	4450	4642
40°	559	4351	4763
45°	506	4278	4781
50°	463	4212	4702
55°	444	4116	4494
60°	455	3934	4165
65°	471	3657	3713
70°	502	3188	3136
75°	554	2597	2448
80°	599	1799	1649
85°	525	954	845

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 4781 cd/sqm



TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.3	1.0
10°-20°	156.4	4.6
20°-30°	273.6	8.1
30°-40°	352.2	10.4
40°-50°	393.3	11.6
50°-60°	376.7	11.2
60°-70°	298.6	8.8
70°-80°	175.6	5.2
80°-90°	49.5	1.5
90°-100°	95.1	2.8
100°-110°	250.2	7.4
110°-120°	259.4	7.7
120°-130°	208.1	6.2
130°-140°	163.3	4.8
140°-150°	125.3	3.7
150°-160°	90.2	2.7
160°-170°	55.2	1.6
170°-180°	18.7	0.6
<b>0°-30°</b>	<b>465.2</b>	<b>13.8</b>
<b>0°-40°</b>	<b>817.4</b>	<b>24.2</b>
<b>0°-60°</b>	<b>1587.4</b>	<b>47.0</b>
<b>0°-90°</b>	<b>2111.1</b>	<b>62.5</b>
<b>90°-120°</b>	<b>604.7</b>	<b>17.9</b>
<b>90°-150°</b>	<b>1101.3</b>	<b>32.6</b>
<b>90°-180°</b>	<b>1265.0</b>	<b>37.5</b>
<b>0°-180°</b>	<b>3376.5</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	273	273	273	273	273	
5°	266	285	321	363	376	25
15°	199	368	619	751	774	55
25°	127	417	738	770	771	59
35°	86	398	695	734	763	54
45°	59	318	614	704	735	45
55°	42	202	521	605	622	38
65°	33	107	387	435	441	33
75°	25	66	212	233	234	26
85°	9	20	53	58	59	9
90°	1	4	10	5	5	2
95°	13	49	164	84	58	14
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	202	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	197	197	19
180°	195	195	195	195	195	



TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	272.8	272.8	272.8	272.8	272.8	272.8	272.8	272.8	272.8	272.8	272.8
2.5°	272.8	272.8	274.5	275.4	277.2	278.1	279.8	281.6	286.8	287.7	289.4
5°	265.8	269.3	280.7	285.1	297.4	314.0	321.0	332.4	356.1	363.1	367.6
7.5°	255.2	263.2	291.2	298.2	328.9	372.8	391.2	415.8	453.5	471.9	486.9
10°	238.6	255.2	305.2	322.0	371.9	438.5	472.8	507.0	564.0	589.4	599.1
12.5°	220.2	247.4	320.1	343.0	414.9	512.2	553.5	591.2	656.1	690.3	695.5
15°	199.1	236.0	334.2	367.6	460.5	573.6	619.2	665.8	726.3	750.8	757.0
17.5°	180.7	227.2	347.3	382.5	495.6	628.9	675.4	714.0	763.1	779.8	784.1
20°	157.9	213.1	356.1	401.7	532.5	669.3	714.0	743.8	777.2	787.7	789.5
22.5°	141.2	198.2	361.4	408.7	557.0	693.8	731.5	755.2	778.0	781.5	782.4
25°	127.2	181.6	360.5	416.7	578.1	708.7	737.7	755.2	768.3	770.1	770.1
27.5°	114.1	163.2	357.0	418.4	593.9	712.3	735.0	747.3	753.4	757.0	757.0
30°	102.6	145.6	348.2	414.9	600.8	708.7	727.2	733.3	739.4	744.7	747.3
32.5°	93.8	129.0	335.0	407.9	601.7	700.0	713.1	716.6	725.4	737.7	742.1
35°	86.0	112.3	320.1	398.3	596.5	685.9	694.7	698.2	715.8	734.2	740.3
37.5°	78.0	100.0	300.9	381.6	588.5	669.3	675.4	681.6	708.7	730.7	737.7
40°	70.2	89.5	278.1	363.1	576.3	649.1	654.4	664.0	700.0	725.4	732.4
42.5°	64.0	80.7	253.5	343.8	560.5	626.3	634.1	648.2	689.4	716.6	724.5
45°	58.8	71.9	227.2	317.5	540.3	602.6	614.0	633.3	677.1	703.5	710.4
47.5°	53.5	65.8	200.0	290.3	518.4	578.9	593.9	615.7	660.5	685.9	692.0
50°	49.1	59.6	172.8	261.3	494.7	553.5	571.0	593.9	639.5	663.1	671.0
52.5°	45.6	54.4	147.4	232.5	467.5	527.1	547.4	571.0	614.0	636.8	642.1
55°	42.1	50.0	125.4	201.7	439.4	499.1	521.0	543.8	585.9	605.2	608.8
57.5°	40.4	46.5	107.0	172.8	409.6	467.5	492.1	513.1	552.6	567.5	571.0
60°	37.8	43.9	93.0	148.2	377.2	437.7	458.8	479.8	513.1	525.4	528.0
62.5°	35.1	42.1	82.5	124.5	343.8	402.6	423.6	443.0	471.0	479.8	483.3
65°	33.3	40.4	74.6	107.0	309.7	365.7	386.8	403.5	426.3	435.1	436.8
67.5°	31.6	38.6	68.5	92.1	275.4	328.9	344.7	360.5	378.0	386.8	387.7
70°	29.0	36.8	63.1	81.5	240.3	286.8	300.0	316.6	330.7	335.0	337.7
72.5°	27.2	34.2	59.6	73.7	204.4	246.4	258.7	268.4	280.7	285.1	285.1
75°	24.6	30.7	56.2	65.8	167.5	201.7	212.3	221.9	231.5	233.4	230.7
77.5°	21.9	27.2	48.2	55.3	130.7	159.7	168.4	173.7	181.6	183.3	184.2
80°	18.4	23.7	37.8	43.0	94.7	117.6	123.7	128.1	135.1	135.1	136.8
82.5°	14.0	18.4	27.2	30.7	64.0	80.7	86.0	88.6	93.0	93.0	93.0
85°	8.8	11.4	17.5	20.1	38.6	49.1	52.7	53.5	57.0	57.9	57.9
87.5°	4.4	6.1	11.4	12.3	20.1	25.5	25.5	27.2	27.2	26.3	25.5
90°	1.3	2.4	3.4	3.7	5.8	8.5	9.9	8.8	6.6	5.0	5.0
92.5°	5.2	14.1	23.0	25.3	35.6	49.3	56.1	49.1	35.2	24.9	23.9
95°	12.6	28.9	45.2	49.3	87.5	138.4	163.9	146.2	110.9	84.5	81.5
97.5°	21.7	36.1	50.5	54.1	117.8	202.7	245.2	234.1	211.8	195.1	189.4
100°	28.9	41.9	54.9	58.2	128.9	223.2	270.2	271.0	272.7	273.9	267.1
102.5°	34.9	47.1	59.2	62.3	133.9	229.5	277.3	291.5	319.9	341.3	335.5
105°	45.1	55.4	65.7	68.3	137.7	230.2	276.5	308.4	372.1	419.9	416.7
107.5°	55.5	65.1	74.7	77.2	138.4	220.0	260.8	305.3	394.2	460.8	461.6
110°	62.6	71.3	80.0	82.1	137.3	210.9	247.7	297.5	396.8	471.2	474.5



TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	69.6	77.9	86.1	88.2	137.3	203.0	235.8	286.6	388.3	464.5	469.5
115°	80.1	87.7	95.3	97.2	138.7	193.9	221.5	270.5	368.4	441.9	448.8
117.5°	90.4	97.3	104.2	106.0	141.2	188.2	211.7	255.9	344.3	410.6	418.2
120°	96.4	103.0	109.4	111.1	143.4	186.4	207.8	248.2	328.9	389.5	397.0
122.5°	102.3	108.9	115.5	117.1	146.3	185.3	204.8	241.1	313.8	368.4	375.8
125°	111.4	117.4	123.4	124.9	150.4	184.5	201.5	232.4	294.2	340.5	347.3
127.5°	118.7	124.7	130.8	132.3	154.4	184.0	198.7	225.2	278.4	318.1	323.9
130°	122.6	129.1	135.6	137.3	157.4	184.3	197.7	221.3	268.5	303.9	309.2
132.5°	126.7	133.2	139.7	141.4	159.8	184.5	196.8	217.9	260.2	291.9	296.6
135°	132.7	138.7	144.6	146.1	162.5	184.3	195.2	213.0	248.4	274.9	279.0
137.5°	138.9	144.8	150.6	152.1	166.4	185.5	195.0	210.0	239.9	262.3	265.6
140°	144.0	149.4	154.8	156.2	168.8	185.7	194.0	206.9	232.8	252.2	255.3
142.5°	147.9	152.9	157.9	159.1	170.7	186.3	194.0	205.4	228.1	245.1	247.8
145°	153.9	158.3	162.6	163.8	173.4	186.3	192.7	202.0	220.5	234.5	236.5
147.5°	159.9	164.2	168.5	169.5	177.3	187.6	192.7	200.0	214.6	225.6	227.3
150°	163.9	167.7	171.6	172.6	179.3	188.3	192.7	198.9	211.2	220.5	221.8
152.5°	168.0	170.8	173.8	174.5	180.6	188.7	192.7	198.0	208.5	216.4	217.5
155°	174.0	176.2	178.3	178.9	183.5	189.7	192.7	196.9	205.3	211.6	212.3
157.5°	178.4	180.5	182.6	183.1	186.4	190.6	192.7	195.9	202.5	207.4	207.9
160°	181.5	183.1	184.7	185.1	187.7	191.1	192.7	195.5	201.1	205.3	205.5
162.5°	184.4	185.7	186.9	187.2	189.1	191.5	192.7	195.1	199.8	203.4	203.6
165°	187.7	188.8	189.9	190.2	191.1	192.2	192.7	194.4	197.8	200.3	200.6
167.5°	190.7	191.2	191.8	191.9	192.6	193.6	194.0	195.2	197.3	199.0	199.1
170°	192.7	193.2	193.8	193.9	193.9	194.0	194.0	195.2	197.3	199.0	199.0
172.5°	193.8	193.9	194.0	194.0	194.0	194.0	194.0	194.9	196.6	198.0	197.9
175°	195.2	195.2	195.2	195.2	194.8	194.3	194.0	194.6	195.7	196.6	196.6
177.5°	195.2	195.2	195.2	195.2	194.9	194.5	194.3	194.7	195.6	196.3	196.2
180°	195.2	195.2	195.2	195.2	195.2	195.2	195.2	195.2	195.2	195.2	195.2



TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	272.8	272.8
2.5°	291.2	289.4
5°	374.5	376.3
7.5°	504.4	503.5
10°	627.2	635.0
12.5°	716.6	718.4
15°	771.1	774.5
17.5°	792.1	792.9
20°	792.9	791.2
22.5°	783.3	781.5
25°	771.9	771.1
27.5°	761.4	762.2
30°	757.0	759.6
32.5°	757.0	761.4
35°	758.8	763.1
37.5°	757.9	763.1
40°	754.3	760.5
42.5°	744.7	749.1
45°	729.8	735.0
47.5°	710.4	714.0
50°	685.9	689.4
52.5°	655.2	656.1
55°	618.4	621.9
57.5°	578.9	579.8
60°	535.1	537.7
62.5°	488.6	488.6
65°	439.4	441.2
67.5°	388.6	392.9
70°	336.9	337.7
72.5°	285.9	285.9
75°	233.4	234.2
77.5°	183.3	183.3
80°	136.0	136.8
82.5°	93.8	95.6
85°	58.8	58.8
87.5°	27.2	24.6
90°	5.0	5.0
92.5°	19.9	16.0
95°	69.5	57.6
97.5°	166.6	143.7
100°	240.0	212.8
102.5°	312.2	288.9
105°	404.3	391.7
107.5°	464.5	467.6
110°	487.6	500.6





TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	489.6	509.6
115°	476.6	504.4
117.5°	449.1	479.9
120°	426.9	456.9
122.5°	405.3	434.8
125°	374.5	401.7
127.5°	346.8	369.7
130°	330.4	351.6
132.5°	315.6	334.6
135°	295.3	311.7
137.5°	279.1	292.4
140°	267.8	280.4
142.5°	258.6	269.4
145°	244.7	252.9
147.5°	234.1	240.8
150°	227.3	232.8
152.5°	221.6	225.8
155°	215.0	217.7
157.5°	209.8	211.7
160°	206.7	207.8
162.5°	204.7	205.7
165°	201.7	202.8
167.5°	199.6	200.0
170°	199.0	199.0
172.5°	197.4	197.1
175°	196.6	196.6
177.5°	195.7	195.2
180°	195.2	195.2



TEST NUMBER: P936238

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-6-3000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.88	4.92	4.72	5.78	6.86	17.05	18.09	17.88	18.95	20.02
	3H	4.60	5.54	5.45	6.41	7.51	18.90	19.83	19.74	20.70	21.81
	4H	4.91	5.79	5.77	6.67	7.78	19.55	20.43	20.41	21.31	22.42
	6H	5.17	5.99	6.04	6.87	8.00	19.98	20.80	20.86	21.68	22.81
	8H	5.24	6.02	6.12	6.92	8.05	20.11	20.89	20.99	21.79	22.92
	12H	5.26	6.01	6.15	6.91	8.06	20.18	20.92	21.07	21.82	22.97
4H	2H	11.11	12.00	11.98	12.87	13.99	17.34	18.23	18.21	19.11	20.22
	3H	12.70	13.44	13.57	14.35	15.48	19.40	20.14	20.28	21.05	22.18
	4H	12.80	13.48	13.69	14.38	15.54	20.17	20.85	21.06	21.76	22.91
	6H	12.82	13.41	13.73	14.34	15.49	20.72	21.31	21.62	22.24	23.39
	8H	12.80	13.35	13.71	14.28	15.45	20.88	21.43	21.79	22.36	23.53
	12H	12.77	13.26	13.70	14.21	15.38	20.98	21.48	21.91	22.42	23.60
8H	4H	14.26	14.80	15.16	15.73	16.90	20.25	20.80	21.16	21.72	22.89
	6H	14.51	14.96	15.44	15.93	17.10	20.88	21.34	21.82	22.30	23.47
	8H	14.53	14.93	15.47	15.89	17.08	21.10	21.51	22.05	22.46	23.65
	12H	14.50	14.86	15.45	15.81	17.05	21.25	21.61	22.20	22.56	23.80
12H	4H	14.41	14.90	15.34	15.85	17.02	20.21	20.71	21.14	21.65	22.83
	6H	14.77	15.17	15.71	16.13	17.32	20.87	21.27	21.81	22.23	23.42
	8H	14.84	15.20	15.79	16.15	17.39	21.10	21.46	22.05	22.41	23.65