

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521111

Luminaire Tested: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521111
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6083.8 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521111

CATALOG NUMBER: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P521111

CATALOG NUMBER: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		50	50	50	44
1	98	94	91	88	90	87	84	81	72	70	69		59	58	57		47	46	46	40
2	91	84	79	75	83	78	73	69	65	62	59		54	52	50		43	42	41	36
3	84	75	69	64	77	70	64	60	59	55	52		49	46	44		40	38	37	33
4	77	68	61	56	71	63	57	52	54	49	46		45	42	39		37	35	33	30
5	72	61	54	49	66	57	51	46	49	44	41		41	38	35		34	32	30	27
6	67	56	49	43	61	52	46	41	45	40	36		38	34	32		32	29	27	24
7	62	51	44	39	57	48	41	37	41	36	33		35	31	29		29	27	25	22
8	58	47	40	35	53	44	37	33	38	33	30		32	29	26		27	25	23	21
9	54	43	36	32	50	40	34	30	35	30	27		30	27	24		26	23	21	19
10	51	40	33	29	47	37	31	27	33	28	25		28	25	22		24	21	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20616	20616	20616
5°	20284	20234	20384
10°	18980	19233	19769
15°	17254	17801	18793
20°	15317	16112	17524
25°	13338	14395	16101
30°	11425	12680	14753
35°	9473	10763	13126
40°	7278	8607	11184
45°	5261	6516	8999
50°	3584	4857	7138
55°	2331	3513	5548
60°	1336	2474	4010
65°	354	1511	2030
70°	175	467	583
75°	78	39	0
80°	58	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8999 cd/sqm

TEST NUMBER: P521111

CATALOG NUMBER: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.9	3.4
10°-20°	521.5	8.6
20°-30°	652.9	10.7
30°-40°	603.0	9.9
40°-50°	405.2	6.7
50°-60°	209.3	3.4
60°-70°	65.5	1.1
70°-80°	4.2	0.1
80°-90°	0.1	0.0
90°-100°	250.8	4.1
100°-110°	713.5	11.7
110°-120°	683.6	11.2
120°-130°	541.0	8.9
130°-140°	434.3	7.1
140°-150°	340.0	5.6
150°-160°	248.8	4.1
160°-170°	154.1	2.5
170°-180°	52.3	0.9
0°-30°	1378.3	22.7
0°-40°	1981.3	32.6
0°-60°	2595.8	42.7
0°-90°	2665.6	43.8
90°-120°	1647.8	27.1
90°-150°	2963.1	48.7
90°-180°	3418.0	56.2
0°-180°	6083.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2234	2234	2234	2234	2234	
5°	2190	2168	2185	2193	2201	203
15°	1806	1800	1864	1926	1968	503
25°	1310	1321	1414	1511	1582	601
35°	841	862	956	1068	1165	521
45°	403	428	499	597	690	317
55°	145	169	218	280	345	135
65°	16	31	69	84	93	27
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	27	108	485	168	104	31
105°	111	168	727	1284	1221	117
115°	206	249	551	1168	1372	203
125°	291	322	526	873	1044	260
135°	356	385	520	738	834	274
145°	420	441	524	638	696	262
155°	479	490	537	577	600	221
165°	529	531	543	555	563	149
175°	554	551	549	546	542	53
180°	550	550	550	550	550	

TEST NUMBER: P521111

CATALOG NUMBER: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2234.5	2234.5	2234.5	2234.5	2234.5
2.5°	2239.7	2218.6	2224.2	2224.0	2218.1
5°	2190.2	2168.0	2184.8	2192.6	2201.0
7.5°	2097.7	2080.3	2112.6	2136.8	2154.3
10°	2025.9	2011.1	2052.9	2085.9	2110.2
12.5°	1942.9	1931.4	1982.0	2027.2	2058.3
15°	1806.4	1800.1	1863.7	1926.3	1967.5
17.5°	1660.3	1660.1	1732.7	1810.4	1860.1
20°	1560.0	1563.1	1641.0	1726.7	1784.8
22.5°	1459.6	1467.0	1550.2	1639.5	1706.1
25°	1310.2	1320.8	1414.0	1510.8	1581.6
27.5°	1166.7	1182.1	1280.2	1380.7	1467.0
30°	1072.4	1090.4	1190.2	1296.0	1384.8
32.5°	979.9	1001.2	1098.6	1210.5	1300.9
35°	841.1	862.2	955.6	1068.1	1165.4
37.5°	697.7	718.4	809.7	920.4	1025.5
40°	604.3	627.6	714.6	821.9	928.6
42.5°	519.6	542.8	624.6	730.1	830.9
45°	403.2	427.5	499.4	596.7	689.7
47.5°	306.8	333.2	396.3	484.3	569.1
50°	249.7	276.1	338.4	415.9	497.3
52.5°	203.9	229.5	285.6	358.7	433.3
55°	144.9	169.2	218.4	280.4	344.9
57.5°	100.1	121.0	165.2	216.9	267.5
60°	72.4	92.5	134.1	176.1	217.3
62.5°	48.2	66.6	107.2	139.4	167.1
65°	16.2	31.0	69.2	83.5	93.0
67.5°	8.2	9.9	36.3	38.3	41.5
70°	6.5	6.5	17.3	18.4	21.6
72.5°	4.8	4.8	6.9	8.9	9.5
75°	2.2	2.2	1.1	0.0	0.0
77.5°	1.1	1.1	0.9	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.4	44.4	102.9	30.0	22.6
95°	27.2	108.0	485.4	168.0	103.6
97.5°	50.0	126.5	747.6	535.0	366.6
100°	65.9	137.5	804.5	814.9	627.7
102.5°	83.5	149.4	792.0	1043.1	879.6
105°	110.9	168.2	727.1	1284.3	1220.9
107.5°	138.7	190.1	651.3	1352.3	1408.8
110°	158.0	206.0	607.8	1326.3	1453.1

TEST NUMBER: P521111

CATALOG NUMBER: SQ4-BB-075U-100D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	222.0	578.5	1264.7	1445.6
115°	206.1	249.1	551.3	1168.0	1371.5
117.5°	232.2	272.6	535.2	1062.2	1277.8
120°	253.2	286.9	533.5	1001.7	1208.3
122.5°	269.9	303.7	529.4	948.6	1140.5
125°	290.8	322.5	526.2	873.2	1044.1
127.5°	313.6	343.3	524.5	828.2	969.0
130°	325.4	355.0	522.0	796.8	919.6
132.5°	337.9	366.8	522.0	772.3	885.3
135°	355.7	385.4	519.9	737.6	833.8
137.5°	372.4	401.3	519.7	708.3	791.3
140°	385.0	414.7	518.9	683.9	763.7
142.5°	399.2	424.0	521.4	664.5	736.1
145°	419.5	441.0	524.1	638.4	695.7
147.5°	436.9	457.7	528.7	612.1	661.6
150°	451.9	466.3	530.4	603.4	638.2
152.5°	463.7	478.8	532.1	591.6	623.9
155°	479.1	490.4	536.7	577.0	600.5
157.5°	498.4	505.1	537.7	570.3	587.1
160°	508.4	513.6	541.9	565.3	579.6
162.5°	514.3	520.2	542.8	561.0	572.0
165°	529.4	531.4	543.0	554.7	562.8
167.5°	539.6	537.8	547.8	553.1	556.4
170°	543.0	541.9	546.1	547.2	551.3
172.5°	550.5	547.0	548.6	545.5	548.8
175°	554.5	551.4	549.2	546.0	541.9
177.5°	556.1	551.2	548.6	545.3	546.1
180°	550.3	550.3	550.3	550.3	550.3

(END OF REPORT)