

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521217

Luminaire Tested: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521217
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7412.7 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 74.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521217

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P521217

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		44	44	44	37
1	96	92	89	86	87	84	81	79	68	67	65		54	53	52		41	40	40	34
2	89	82	77	73	80	75	71	67	62	59	56		49	47	45		38	37	36	30
3	82	74	67	62	74	67	62	58	56	52	49		45	42	40		35	33	32	27
4	75	66	59	54	69	61	55	50	50	46	43		41	38	36		32	30	29	25
5	70	59	52	47	63	55	48	44	46	41	38		37	34	32		29	27	26	23
6	65	54	47	41	59	50	43	39	42	37	34		34	31	29		27	25	24	21
7	60	49	42	37	55	45	39	35	38	34	30		32	28	26		25	23	22	19
8	56	45	38	33	51	42	35	31	35	31	27		29	26	23		24	21	20	17
9	52	41	34	30	48	38	32	28	33	28	25		27	24	21		22	20	18	16
10	49	38	31	27	45	35	29	26	30	26	23		25	22	20		21	18	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21109	21109	21109
5°	20769	20717	20871
10°	19432	19692	20242
15°	17666	18226	19242
20°	15682	16497	17942
25°	13656	14739	16484
30°	11698	12982	15106
35°	9699	11021	13439
40°	7452	8811	11451
45°	5387	6673	9214
50°	3670	4972	7307
55°	2385	3597	5680
60°	1369	2532	4106
65°	362	1546	2078
70°	178	477	596
75°	78	39	0
80°	58	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9214 cd/sqm

TEST NUMBER: P521217

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.8	2.8
10°-20°	533.9	7.2
20°-30°	668.4	9.0
30°-40°	617.4	8.3
40°-50°	414.9	5.6
50°-60°	214.3	2.9
60°-70°	67.1	0.9
70°-80°	4.2	0.1
80°-90°	0.1	0.0
90°-100°	343.6	4.6
100°-110°	977.6	13.2
110°-120°	936.6	12.6
120°-130°	741.3	10.0
130°-140°	595.0	8.0
140°-150°	465.8	6.3
150°-160°	340.8	4.6
160°-170°	211.1	2.8
170°-180°	71.6	1.0
0°-30°	1411.2	19.0
0°-40°	2028.6	27.4
0°-60°	2657.8	35.9
0°-90°	2729.2	36.8
90°-120°	2257.8	30.5
90°-150°	4059.9	54.8
90°-180°	4684.0	63.2
0°-180°	7412.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2288	2288	2288	2288	2288	
5°	2242	2220	2237	2245	2254	208
15°	1850	1843	1908	1972	2014	515
25°	1342	1352	1448	1547	1619	615
35°	861	883	978	1094	1193	533
45°	413	438	511	611	706	324
55°	148	173	224	287	353	138
65°	17	32	71	85	95	28
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	37	148	665	230	142	43
105°	152	230	996	1760	1673	161
115°	282	341	755	1600	1879	278
125°	398	442	721	1196	1431	357
135°	487	528	712	1011	1142	376
145°	575	604	718	875	953	359
155°	656	672	735	791	823	303
165°	725	728	744	760	771	204
175°	760	756	753	748	742	72
180°	754	754	754	754	754	

TEST NUMBER: P521217

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2287.9	2287.9	2287.9	2287.9	2287.9
2.5°	2293.2	2271.5	2277.2	2277.1	2271.0
5°	2242.5	2219.7	2236.9	2244.9	2253.5
7.5°	2147.7	2130.0	2163.0	2187.8	2205.7
10°	2074.2	2059.1	2101.9	2135.7	2160.6
12.5°	1989.2	1977.5	2029.3	2075.6	2107.4
15°	1849.5	1843.0	1908.2	1972.3	2014.5
17.5°	1699.9	1699.7	1774.1	1853.6	1904.4
20°	1597.2	1600.4	1680.2	1767.9	1827.4
22.5°	1494.5	1502.0	1587.2	1678.6	1746.8
25°	1341.5	1352.3	1447.8	1546.8	1619.3
27.5°	1194.5	1210.3	1310.7	1413.7	1502.0
30°	1098.0	1116.4	1218.6	1327.0	1417.9
32.5°	1003.2	1025.1	1124.8	1239.3	1332.0
35°	861.1	882.8	978.5	1093.6	1193.2
37.5°	714.4	735.6	829.0	942.4	1050.0
40°	618.7	642.5	731.6	841.5	950.8
42.5°	532.0	555.8	639.5	747.5	850.7
45°	412.9	437.7	511.4	610.9	706.2
47.5°	314.1	341.2	405.8	495.8	582.6
50°	255.7	282.7	346.4	425.8	509.1
52.5°	208.8	234.9	292.4	367.2	443.6
55°	148.3	173.2	223.6	287.1	353.1
57.5°	102.5	123.9	169.1	222.1	273.8
60°	74.2	94.7	137.2	180.3	222.5
62.5°	49.4	68.2	109.8	142.8	171.1
65°	16.6	31.8	70.8	85.4	95.2
67.5°	8.4	10.1	37.2	39.3	42.5
70°	6.6	6.6	17.7	18.9	22.1
72.5°	4.9	4.9	7.1	9.1	9.7
75°	2.2	2.2	1.1	0.0	0.0
77.5°	1.1	1.1	0.9	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.5	60.8	141.1	41.1	31.0
95°	37.3	148.0	665.1	230.2	141.9
97.5°	68.5	173.4	1024.3	733.0	502.3
100°	90.3	188.4	1102.3	1116.6	860.1
102.5°	114.4	204.7	1085.1	1429.2	1205.2
105°	151.9	230.4	996.2	1759.7	1672.8
107.5°	190.1	260.4	892.5	1852.9	1930.3
110°	216.4	282.3	832.8	1817.3	1991.1

TEST NUMBER: P521217

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	241.7	304.2	792.7	1732.9	1980.7
115°	282.4	341.3	755.4	1600.3	1879.2
117.5°	318.2	373.4	733.3	1455.4	1750.8
120°	346.9	393.1	731.1	1372.5	1655.6
122.5°	369.8	416.1	725.3	1299.8	1562.7
125°	398.5	441.9	721.0	1196.5	1430.6
127.5°	429.7	470.4	718.7	1134.8	1327.7
130°	445.8	486.4	715.3	1091.8	1260.0
132.5°	463.0	502.5	715.3	1058.2	1213.0
135°	487.4	528.0	712.4	1010.7	1142.5
137.5°	510.3	549.8	712.1	970.4	1084.3
140°	527.5	568.2	711.0	937.1	1046.4
142.5°	547.0	580.9	714.4	910.5	1008.6
145°	574.8	604.2	718.2	874.7	953.2
147.5°	598.6	627.2	724.5	838.7	906.5
150°	619.2	638.9	726.8	826.7	874.4
152.5°	635.3	656.0	729.0	810.6	854.9
155°	656.5	671.9	735.4	790.6	822.8
157.5°	682.9	692.1	736.8	781.5	804.4
160°	696.7	703.7	742.5	774.5	794.1
162.5°	704.7	712.8	743.7	768.7	783.8
165°	725.3	728.1	744.0	760.0	771.2
167.5°	739.4	736.8	750.6	757.8	762.3
170°	744.0	742.6	748.3	749.8	755.4
172.5°	754.3	749.5	751.7	747.5	752.0
175°	759.7	755.5	752.6	748.1	742.5
177.5°	762.0	755.3	751.7	747.1	748.3
180°	754.0	754.0	754.0	754.0	754.0

(END OF REPORT)