

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936348

Luminaire Tested: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936348
REPORT IS A COMBINATION OF REPORTS P933454 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6452.4 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936348
CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2760	2760	2760
5°	2696	3189	3709
10°	2445	4649	6150
15°	2078	6074	7425
20°	1692	7039	7568
25°	1411	7366	7414
30°	1190	7413	7400
35°	1052	7289	7591
40°	917	7129	7789
45°	830	7013	7820
50°	762	6907	7690
55°	730	6753	7349
60°	747	6456	6811
65°	777	6005	6071
70°	828	5237	5129
75°	916	4270	4002
80°	1003	2961	2697
85°	890	1570	1380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7820 cd/sqm



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	1.2
10°-20°	341.0	5.3
20°-30°	596.4	9.2
30°-40°	767.8	11.9
40°-50°	857.6	13.3
50°-60°	821.4	12.7
60°-70°	650.9	10.1
70°-80°	382.8	5.9
80°-90°	107.4	1.7
90°-100°	139.1	2.2
100°-110°	365.7	5.7
110°-120°	379.2	5.9
120°-130°	304.2	4.7
130°-140°	238.7	3.7
140°-150°	183.2	2.8
150°-160°	131.9	2.0
160°-170°	80.7	1.3
170°-180°	27.3	0.4
0°-30°	1014.4	15.7
0°-40°	1782.2	27.6
0°-60°	3461.2	53.6
0°-90°	4602.3	71.3
90°-120°	884.1	13.7
90°-150°	1610.2	25.0
90°-180°	1850.0	28.7
0°-180°	6452.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	595	595	595	595	595	
5°	580	622	700	792	820	53
15°	434	801	1350	1637	1689	121
25°	277	908	1608	1679	1681	128
35°	187	868	1515	1601	1664	117
45°	128	692	1339	1534	1603	99
55°	92	440	1136	1320	1356	84
65°	73	233	843	948	962	72
75°	54	143	463	509	511	56
85°	19	44	115	126	128	20
90°	2	5	14	7	7	3
95°	18	72	240	124	84	20
105°	66	100	404	614	573	70
115°	117	142	324	646	737	116
125°	163	182	295	498	587	145
135°	194	214	285	402	456	150
145°	225	239	282	343	370	141
155°	254	261	282	309	318	117
165°	274	278	282	293	296	77
175°	285	285	284	287	287	27
180°	285	285	285	285	285	



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	594.8	594.8	594.8	594.8	594.8	594.8	594.8	594.8	594.8	594.8	594.8
2.5°	594.8	594.8	598.6	600.5	604.3	606.2	610.1	613.9	625.4	627.3	631.1
5°	579.5	587.1	612.0	621.5	648.3	684.6	699.9	724.8	776.4	791.7	801.3
7.5°	556.5	573.7	634.9	650.2	717.1	812.8	852.9	906.5	988.7	1028.9	1061.4
10°	520.2	556.5	665.5	701.8	810.9	956.2	1030.8	1105.5	1229.8	1285.2	1306.3
12.5°	480.0	539.3	698.0	747.7	904.6	1116.9	1206.8	1289.0	1430.6	1505.1	1516.6
15°	434.1	514.4	728.6	801.3	1004.0	1250.8	1350.2	1451.6	1583.6	1637.1	1650.5
17.5°	394.0	495.3	757.3	833.8	1080.5	1371.3	1472.6	1556.8	1663.9	1700.2	1709.8
20°	344.2	464.7	776.4	875.9	1160.9	1459.2	1556.8	1621.8	1694.5	1717.4	1721.2
22.5°	307.9	432.2	787.9	891.2	1214.5	1512.8	1595.0	1646.7	1696.4	1704.0	1705.9
25°	277.3	395.9	786.0	908.4	1260.4	1545.3	1608.4	1646.7	1675.3	1679.2	1679.2
27.5°	248.6	355.7	778.3	912.2	1294.8	1553.0	1602.7	1629.4	1642.8	1650.5	1650.5
30°	223.7	317.5	759.2	904.6	1310.1	1545.3	1585.5	1598.9	1612.2	1623.7	1629.4
32.5°	204.6	281.1	730.5	889.3	1312.0	1526.2	1554.9	1562.5	1581.6	1608.4	1618.0
35°	187.4	244.8	698.0	868.2	1300.5	1495.6	1514.7	1522.4	1560.6	1600.8	1614.1
37.5°	170.2	218.0	655.9	831.9	1283.3	1459.2	1472.6	1486.0	1545.3	1593.1	1608.4
40°	153.0	195.1	606.2	791.7	1256.5	1415.3	1426.7	1447.8	1526.2	1581.6	1596.9
42.5°	139.6	175.9	552.7	749.7	1222.1	1365.5	1382.8	1413.3	1503.2	1562.5	1579.7
45°	128.1	156.8	495.3	692.3	1178.1	1313.9	1338.8	1380.8	1476.5	1533.8	1549.1
47.5°	116.7	143.4	436.0	633.0	1130.3	1262.3	1294.8	1342.6	1440.1	1495.6	1509.0
50°	107.1	130.0	376.7	569.9	1078.6	1206.8	1245.1	1294.8	1394.2	1445.9	1463.1
52.5°	99.4	118.6	321.3	506.8	1019.3	1149.4	1193.4	1245.1	1338.8	1388.5	1400.0
55°	91.8	109.0	273.5	439.8	958.1	1088.2	1136.1	1185.8	1277.6	1319.6	1327.3
57.5°	88.0	101.4	233.3	376.7	893.1	1019.3	1072.8	1118.8	1204.9	1237.4	1245.1
60°	82.2	95.6	202.7	323.2	822.3	954.3	1000.2	1046.1	1118.8	1145.6	1151.4
62.5°	76.5	91.8	179.8	271.6	749.7	877.8	923.7	965.8	1027.0	1046.1	1053.7
65°	72.7	88.0	162.6	233.3	675.1	797.5	843.4	879.7	929.4	948.5	952.4
67.5°	68.8	84.1	149.2	200.8	600.5	717.1	751.6	786.0	824.2	843.4	845.3
70°	63.1	80.3	137.7	177.9	524.0	625.4	654.0	690.4	721.0	730.5	736.3
72.5°	59.3	74.6	130.0	160.6	445.6	537.4	564.2	585.2	612.0	621.5	621.5
75°	53.5	66.9	122.4	143.4	365.3	439.8	462.8	483.8	504.9	508.7	503.0
77.5°	47.8	59.3	105.2	120.5	284.9	348.1	367.2	378.7	395.9	399.7	401.6
80°	40.2	51.6	82.2	93.7	206.5	256.3	269.6	279.2	294.5	294.5	298.3
82.5°	30.6	40.2	59.3	66.9	139.6	175.9	187.4	193.2	202.7	202.7	202.7
85°	19.1	24.9	38.2	44.0	84.1	107.1	114.7	116.7	124.3	126.2	126.2
87.5°	9.6	13.4	24.9	26.8	44.0	55.5	55.5	59.3	59.3	57.4	55.5
90°	1.9	3.4	5.0	5.4	8.4	12.5	14.5	12.9	9.7	7.3	7.3
92.5°	7.6	20.7	33.8	37.0	52.0	72.0	81.9	71.8	51.6	36.4	35.0
95°	18.4	42.2	66.1	72.0	127.8	202.3	239.6	213.8	162.3	123.5	119.1
97.5°	31.8	52.9	73.8	79.1	172.2	296.4	358.6	342.3	309.7	285.2	276.9
100°	42.2	61.2	80.2	85.0	188.4	326.2	395.1	396.3	398.7	400.5	390.6
102.5°	51.0	68.8	86.5	90.9	195.8	335.6	405.5	426.3	467.8	498.9	490.4
105°	65.9	81.0	96.1	99.8	201.4	336.7	404.4	450.9	544.1	613.9	609.3
107.5°	81.2	95.2	109.3	112.8	202.3	321.7	381.3	446.3	576.2	673.6	674.8
110°	91.6	104.2	116.9	120.1	200.8	308.4	362.2	434.8	580.0	688.9	693.7



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	101.7	113.8	125.8	128.9	200.9	296.8	344.8	419.1	567.7	679.2	686.5
115°	117.0	128.1	139.3	142.1	202.7	283.5	323.9	395.5	538.7	646.1	656.2
117.5°	132.1	142.3	152.4	155.0	206.5	275.2	309.5	374.2	503.3	600.3	611.6
120°	140.9	150.5	160.1	162.5	209.6	272.4	303.8	362.8	480.9	569.4	580.3
122.5°	149.5	159.2	168.9	171.3	214.0	270.9	299.4	352.5	458.9	538.6	549.4
125°	162.8	171.6	180.3	182.5	219.9	269.7	294.6	339.7	430.1	497.8	507.7
127.5°	173.5	182.3	191.2	193.4	225.9	269.0	290.6	329.4	407.0	465.1	473.5
130°	179.3	188.8	198.3	200.7	230.2	269.5	289.1	323.6	392.6	444.3	452.1
132.5°	185.2	194.8	204.2	206.6	233.7	269.7	287.7	318.6	380.4	426.7	433.7
135°	194.0	202.7	211.4	213.6	237.5	269.5	285.4	311.3	363.1	401.9	407.8
137.5°	203.0	211.6	220.2	222.4	243.3	271.1	285.0	306.9	350.6	383.4	388.3
140°	210.5	218.4	226.3	228.3	246.8	271.4	283.7	302.6	340.4	368.7	373.3
142.5°	216.3	223.6	230.9	232.7	249.8	272.4	283.7	300.3	333.5	358.4	362.3
145°	225.1	231.5	237.8	239.4	253.6	272.4	281.8	295.4	322.5	342.9	345.9
147.5°	233.9	240.1	246.3	247.8	259.1	274.2	281.8	292.5	313.8	329.8	332.3
150°	239.6	245.3	250.8	252.2	262.1	275.2	281.8	290.8	308.9	322.3	324.3
152.5°	245.6	249.8	254.1	255.1	264.0	275.9	281.8	289.4	304.8	316.4	317.9
155°	254.3	257.5	260.7	261.4	268.2	277.3	281.8	287.9	300.1	309.3	310.3
157.5°	260.8	263.9	267.0	267.7	272.4	278.6	281.8	286.6	296.0	303.2	303.9
160°	265.2	267.6	270.0	270.6	274.3	279.3	281.8	285.9	294.0	300.1	300.5
162.5°	269.6	271.5	273.2	273.7	276.3	280.0	281.8	285.2	292.1	297.3	297.7
165°	274.5	276.1	277.8	278.2	279.4	281.0	281.8	284.3	289.2	292.9	293.3
167.5°	278.9	279.7	280.5	280.6	281.7	283.0	283.7	285.3	288.6	291.0	291.2
170°	281.8	282.6	283.3	283.5	283.6	283.7	283.7	285.3	288.6	291.0	291.0
172.5°	283.3	283.5	283.7	283.7	283.7	283.7	283.7	284.9	287.5	289.4	289.2
175°	285.4	285.4	285.4	285.4	284.8	284.1	283.7	284.5	286.1	287.3	287.3
177.5°	285.4	285.4	285.4	285.4	284.9	284.4	284.1	284.8	286.0	287.0	286.8
180°	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	594.8	594.8
2.5°	634.9	631.1
5°	816.6	820.4
7.5°	1099.7	1097.8
10°	1367.5	1384.7
12.5°	1562.5	1566.3
15°	1681.1	1688.7
17.5°	1727.0	1728.9
20°	1728.9	1725.1
22.5°	1707.9	1704.0
25°	1683.0	1681.1
27.5°	1660.0	1662.0
30°	1650.5	1656.2
32.5°	1650.5	1660.0
35°	1654.3	1663.9
37.5°	1652.4	1663.9
40°	1644.7	1658.1
42.5°	1623.7	1633.3
45°	1591.2	1602.7
47.5°	1549.1	1556.8
50°	1495.6	1503.2
52.5°	1428.6	1430.6
55°	1348.3	1356.0
57.5°	1262.3	1264.2
60°	1166.7	1172.4
62.5°	1065.2	1065.2
65°	958.1	961.9
67.5°	847.2	856.7
70°	734.4	736.3
72.5°	623.4	623.4
75°	508.7	510.6
77.5°	399.7	399.7
80°	296.4	298.3
82.5°	204.6	208.5
85°	128.1	128.1
87.5°	59.3	53.5
90°	7.3	7.3
92.5°	29.2	23.3
95°	101.6	84.0
97.5°	243.4	210.1
100°	350.8	311.0
102.5°	456.4	422.4
105°	591.0	572.7
107.5°	679.2	683.6
110°	712.7	731.9



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	715.8	745.1
115°	696.9	737.4
117.5°	656.6	701.7
120°	624.1	667.9
122.5°	592.6	635.7
125°	547.5	587.3
127.5°	507.0	540.5
130°	483.1	514.0
132.5°	461.5	489.2
135°	431.7	455.6
137.5°	407.9	427.5
140°	391.6	409.9
142.5°	378.1	393.8
145°	357.8	369.7
147.5°	342.1	352.1
150°	332.4	340.4
152.5°	324.0	330.0
155°	314.3	318.3
157.5°	306.7	309.5
160°	302.2	303.8
162.5°	299.2	300.7
165°	294.9	296.5
167.5°	291.8	292.5
170°	291.0	291.0
172.5°	288.7	288.1
175°	287.3	287.3
177.5°	286.1	285.4
180°	285.4	285.4



TEST NUMBER: P936348

CATALOG NUMBER: SQ4-FB-025U-075D-92765-1D-UNV-STD-W-8-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.27	7.43	7.01	8.20	9.12	19.45	20.61	20.19	21.38	22.30
	3H	7.00	8.04	7.75	8.82	9.78	21.31	22.35	22.07	23.13	24.09
	4H	7.31	8.29	8.08	9.08	10.05	21.97	22.95	22.74	23.74	24.71
	6H	7.58	8.49	8.36	9.28	10.27	22.42	23.33	23.20	24.12	25.11
	8H	7.65	8.52	8.45	9.34	10.32	22.55	23.41	23.34	24.23	25.22
	12H	7.68	8.51	8.48	9.32	10.33	22.62	23.45	23.43	24.26	25.28
4H	2H	13.52	14.51	14.30	15.29	16.26	19.76	20.74	20.54	21.53	22.50
	3H	15.12	15.94	15.90	16.76	17.75	21.83	22.66	22.62	23.48	24.47
	4H	15.22	15.98	16.03	16.80	17.81	22.61	23.36	23.41	24.19	25.20
	6H	15.25	15.91	16.07	16.75	17.77	23.17	23.82	23.99	24.67	25.69
	8H	15.24	15.85	16.06	16.69	17.72	23.34	23.95	24.16	24.79	25.82
	12H	15.21	15.76	16.05	16.62	17.66	23.45	24.00	24.29	24.86	25.90
8H	4H	16.69	17.31	17.52	18.15	19.18	22.70	23.31	23.52	24.15	25.18
	6H	16.95	17.46	17.80	18.34	19.37	23.34	23.85	24.19	24.73	25.77
	8H	16.97	17.42	17.84	18.30	19.35	23.56	24.02	24.43	24.90	25.95
	12H	16.95	17.35	17.82	18.22	19.33	23.72	24.12	24.59	24.99	26.10
12H	4H	16.85	17.40	17.70	18.27	19.31	22.66	23.22	23.51	24.08	25.12
	6H	17.21	17.67	18.08	18.54	19.59	23.33	23.78	24.19	24.66	25.71
	8H	17.30	17.70	18.16	18.57	19.67	23.57	23.97	24.44	24.84	25.95