

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521236

Luminaire Tested: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521236
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6492.5 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 62
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521236

CATALOG NUMBER: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P521236

CATALOG NUMBER: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	92	88	84	81	81	78	75	72	59	57	55	41	40	40	25	25	25	17				
2	84	77	72	67	74	69	64	60	52	49	47	37	36	34	23	23	22	16				
3	77	69	62	57	68	61	56	51	47	43	40	34	31	30	21	20	19	14				
4	71	61	54	49	62	54	48	44	42	38	35	30	28	26	19	18	17	13				
5	65	55	47	42	57	49	43	38	38	34	30	27	25	23	18	17	16	12				
6	60	49	42	36	53	44	38	33	34	30	27	25	22	20	16	15	14	11				
7	55	44	37	32	49	40	34	29	31	27	24	23	20	18	15	14	13	10				
8	51	40	33	28	46	36	30	26	28	24	21	21	18	16	14	13	12	9				
9	48	37	30	25	42	33	27	23	26	22	19	19	17	15	13	12	11	8				
10	45	34	27	23	40	30	25	21	24	20	17	18	15	13	12	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9577	9577	9577
5°	9423	9399	9469
10°	8817	8934	9183
15°	8015	8269	8729
20°	7114	7485	8140
25°	6196	6686	7479
30°	5308	5890	6853
35°	4400	5000	6097
40°	3381	3997	5196
45°	2444	3027	4181
50°	1665	2256	3316
55°	1083	1631	2577
60°	620	1150	1862
65°	164	701	943
70°	81	216	270
75°	36	18	0
80°	27	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4181 cd/sqm

TEST NUMBER: P521236

CATALOG NUMBER: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.5
10°-20°	242.2	3.7
20°-30°	303.3	4.7
30°-40°	280.1	4.3
40°-50°	188.2	2.9
50°-60°	97.2	1.5
60°-70°	30.4	0.5
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	385.4	5.9
100°-110°	1096.7	16.9
110°-120°	1050.8	16.2
120°-130°	831.6	12.8
130°-140°	667.5	10.3
140°-150°	522.6	8.0
150°-160°	382.4	5.9
160°-170°	236.8	3.6
170°-180°	80.4	1.2
0°-30°	640.2	9.9
0°-40°	920.4	14.2
0°-60°	1205.8	18.6
0°-90°	1238.2	19.1
90°-120°	2532.9	39.0
90°-150°	4554.7	70.2
90°-180°	5254.0	80.9
0°-180°	6492.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1038	1038	1038	1038	1038	
5°	1017	1007	1015	1018	1022	94
15°	839	836	866	895	914	234
25°	609	614	657	702	735	279
35°	391	400	444	496	541	242
45°	187	199	232	277	320	147
55°	67	79	101	130	160	63
65°	8	14	32	39	43	13
75°	1	1	0	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P521236

CATALOG NUMBER: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1038.0	1038.0	1038.0	1038.0	1038.0
2.5°	1040.4	1030.6	1033.2	1033.1	1030.3
5°	1017.4	1007.1	1014.9	1018.5	1022.4
7.5°	974.4	966.4	981.3	992.6	1000.7
10°	941.1	934.2	953.6	968.9	980.2
12.5°	902.5	897.2	920.7	941.7	956.1
15°	839.1	836.2	865.7	894.8	913.9
17.5°	771.2	771.1	804.9	841.0	864.0
20°	724.6	726.1	762.3	802.1	829.1
22.5°	678.0	681.5	720.1	761.6	792.5
25°	608.6	613.5	656.8	701.8	734.7
27.5°	541.9	549.1	594.7	641.4	681.4
30°	498.2	506.5	552.9	602.0	643.3
32.5°	455.2	465.1	510.3	562.3	604.3
35°	390.7	400.5	443.9	496.2	541.3
37.5°	324.1	333.7	376.1	427.5	476.4
40°	280.7	291.5	331.9	381.8	431.4
42.5°	241.3	252.1	290.2	339.1	386.0
45°	187.3	198.6	232.0	277.2	320.4
47.5°	142.5	154.8	184.1	225.0	264.3
50°	116.0	128.3	157.2	193.2	231.0
52.5°	94.7	106.6	132.7	166.6	201.3
55°	67.3	78.6	101.4	130.2	160.2
57.5°	46.5	56.2	76.7	100.8	124.2
60°	33.6	43.0	62.3	81.8	100.9
62.5°	22.4	30.9	49.8	64.8	77.6
65°	7.5	14.4	32.1	38.8	43.2
67.5°	3.8	4.6	16.9	17.8	19.3
70°	3.0	3.0	8.0	8.6	10.0
72.5°	2.2	2.2	3.2	4.1	4.4
75°	1.0	1.0	0.5	0.0	0.0
77.5°	0.5	0.5	0.4	0.0	0.0
80°	0.5	0.5	0.0	0.0	0.0
82.5°	0.1	0.1	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P521236

CATALOG NUMBER: SQ4-BB-125U-050D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)