

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521249

Luminaire Tested: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521249  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7108.7 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 73.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521249

CATALOG NUMBER: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P521249

CATALOG NUMBER: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	90	86	83	83	80	77	75	63	61	59	46	45	44	32	31	31	24
2	86	79	74	69	76	71	67	63	56	53	50	42	40	39	29	28	27	22
3	79	70	64	59	70	63	58	54	50	47	44	38	36	34	27	25	24	19
4	73	63	56	51	65	57	51	46	45	41	38	34	32	30	24	23	22	18
5	67	56	49	44	60	51	45	40	41	37	33	31	29	26	22	21	20	16
6	62	51	44	38	55	46	40	35	37	33	29	29	26	24	21	19	18	15
7	57	46	39	34	51	42	36	31	34	29	26	26	23	21	19	18	16	13
8	53	42	35	30	48	38	32	28	31	27	24	24	21	19	18	16	15	12
9	50	38	32	27	45	35	29	25	29	24	21	22	20	17	17	15	14	11
10	46	35	29	24	42	32	27	23	26	22	19	21	18	16	16	14	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14342	14342	14342
5°	14112	14076	14181
10°	13204	13380	13753
15°	12004	12385	13074
20°	10655	11209	12191
25°	9279	10014	11201
30°	7948	8821	10264
35°	6590	7488	9131
40°	5063	5987	7780
45°	3660	4534	6260
50°	2493	3379	4965
55°	1621	2443	3859
60°	930	1722	2790
65°	247	1050	1412
70°	121	324	405
75°	53	29	0
80°	43	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 6260 cd/sqm

TEST NUMBER: P521249

CATALOG NUMBER: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.9	2.0
10°-20°	362.8	5.1
20°-30°	454.2	6.4
30°-40°	419.5	5.9
40°-50°	281.9	4.0
50°-60°	145.6	2.0
60°-70°	45.6	0.6
70°-80°	2.9	0.0
80°-90°	0.1	0.0
90°-100°	385.4	5.4
100°-110°	1096.7	15.4
110°-120°	1050.8	14.8
120°-130°	831.6	11.7
130°-140°	667.5	9.4
140°-150°	522.6	7.4
150°-160°	382.4	5.4
160°-170°	236.8	3.3
170°-180°	80.4	1.1
0°-30°	958.8	13.5
0°-40°	1378.4	19.4
0°-60°	1805.8	25.4
0°-90°	1854.4	26.1
90°-120°	2532.9	35.6
90°-150°	4554.7	64.1
90°-180°	5254.0	73.9
0°-180°	7108.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1554	1554	1554	1554	1554	
5°	1524	1508	1520	1525	1531	141
15°	1257	1252	1297	1340	1369	350
25°	912	919	984	1051	1100	418
35°	585	600	665	743	811	362
45°	280	297	348	415	480	220
55°	101	118	152	195	240	94
65°	11	22	48	58	65	19
75°	2	2	1	0	0	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P521249

CATALOG NUMBER: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1554.5	1554.5	1554.5	1554.5	1554.5
2.5°	1558.1	1543.4	1547.3	1547.2	1543.1
5°	1523.7	1508.2	1519.9	1525.3	1531.2
7.5°	1459.3	1447.2	1469.7	1486.5	1498.7
10°	1409.4	1399.1	1428.2	1451.1	1468.0
12.5°	1351.6	1343.7	1378.8	1410.3	1431.9
15°	1256.7	1252.3	1296.6	1340.1	1368.8
17.5°	1155.0	1154.9	1205.4	1259.4	1294.0
20°	1085.2	1087.4	1141.6	1201.2	1241.7
22.5°	1015.4	1020.6	1078.5	1140.6	1186.9
25°	911.5	918.9	983.7	1051.0	1100.3
27.5°	811.6	822.4	890.6	960.5	1020.5
30°	746.0	758.5	828.0	901.6	963.4
32.5°	681.7	696.5	764.2	842.1	905.0
35°	585.1	599.8	664.8	743.1	810.7
37.5°	485.4	499.8	563.3	640.3	713.4
40°	420.4	436.6	497.1	571.8	646.0
42.5°	361.4	377.6	434.5	507.9	578.0
45°	280.5	297.4	347.5	415.1	479.8
47.5°	213.4	231.8	275.7	336.9	395.9
50°	173.7	192.1	235.4	289.3	345.9
52.5°	141.8	159.6	198.7	249.5	301.4
55°	100.8	117.7	151.9	195.1	239.9
57.5°	69.6	84.2	114.9	150.9	186.1
60°	50.4	64.4	93.3	122.5	151.2
62.5°	33.5	46.3	74.6	97.0	116.3
65°	11.3	21.6	48.1	58.1	64.7
67.5°	5.7	6.9	25.3	26.7	28.9
70°	4.5	4.5	12.0	12.8	15.0
72.5°	3.3	3.3	4.8	6.2	6.6
75°	1.5	1.5	0.8	0.0	0.0
77.5°	0.8	0.8	0.6	0.0	0.0
80°	0.8	0.8	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P521249

CATALOG NUMBER: SQ4-BB-125U-075D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)