

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936632

Luminaire Tested: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936632
REPORT IS A COMBINATION OF REPORTS P933469 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3144.5 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936632
CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	43	42				37	
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	39	37	35				30	
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29				25	
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25				21	
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21				18	
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18				15	
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16				13	
8	51	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14				12	
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12				10	
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11				9	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1688	1688	1688
5°	1648	1950	2270
10°	1493	2840	3762
15°	1267	3708	4543
20°	1030	4294	4630
25°	858	4490	4535
30°	724	4514	4528
35°	638	4436	4644
40°	555	4336	4765
45°	502	4260	4784
50°	460	4191	4704
55°	439	4093	4495
60°	446	3909	4167
65°	463	3628	3714
70°	490	3158	3137
75°	538	2567	2449
80°	576	1775	1651
85°	480	937	845

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4784 cd/sqm



TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.5	0.7
10°-20°	104.3	3.3
20°-30°	182.4	5.8
30°-40°	234.9	7.5
40°-50°	262.3	8.3
50°-60°	251.3	8.0
60°-70°	199.1	6.3
70°-80°	117.1	3.7
80°-90°	33.5	1.1
90°-100°	130.5	4.2
100°-110°	343.2	10.9
110°-120°	355.9	11.3
120°-130°	285.4	9.1
130°-140°	224.0	7.1
140°-150°	171.9	5.5
150°-160°	123.8	3.9
160°-170°	75.7	2.4
170°-180°	25.6	0.8
0°-30°	310.3	9.9
0°-40°	545.1	17.3
0°-60°	1058.7	33.7
0°-90°	1408.5	44.8
90°-120°	829.6	26.4
90°-150°	1510.9	48.0
90°-180°	1736.0	55.2
0°-180°	3144.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	182	182	182	182	182	
5°	177	190	214	242	251	16
15°	133	245	413	501	517	37
25°	85	278	492	514	514	39
35°	57	266	463	490	509	36
45°	39	212	410	469	490	30
55°	28	135	348	404	415	26
65°	22	71	258	290	294	22
75°	16	44	142	156	156	17
85°	6	13	35	39	39	6
90°	2	5	14	7	7	2
95°	17	68	225	116	79	19
105°	62	94	379	576	537	66
115°	110	133	304	606	692	108
125°	153	171	276	467	551	136
135°	182	200	268	377	428	141
145°	211	225	264	322	347	132
155°	239	245	264	290	299	110
165°	258	261	264	275	278	73
175°	268	268	266	270	270	25
180°	268	268	268	268	268	



TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9
2.5°	181.9	181.9	183.1	183.7	184.9	185.5	186.6	187.7	191.3	191.8	193.1
5°	177.3	179.6	187.2	190.1	198.3	209.5	214.1	221.8	237.5	242.2	245.1
7.5°	170.2	175.5	194.2	198.9	219.4	248.6	260.9	277.3	302.4	314.7	324.7
10°	159.1	170.2	203.6	214.7	248.0	292.5	315.3	338.2	376.2	393.1	399.6
12.5°	146.9	165.0	213.6	228.7	276.7	341.7	369.1	394.3	437.6	460.4	463.9
15°	132.8	157.4	222.9	245.1	307.1	382.6	413.0	444.0	484.4	500.7	504.8
17.5°	120.5	151.6	231.7	255.1	330.5	419.4	450.5	476.2	508.9	520.1	523.0
20°	105.3	142.1	237.5	268.0	355.1	446.4	476.2	496.1	518.3	525.3	526.5
22.5°	94.2	132.2	241.0	272.6	371.5	462.7	487.9	503.7	518.9	521.2	521.8
25°	84.8	121.1	240.4	277.9	385.5	472.6	492.0	503.7	512.5	513.6	513.6
27.5°	76.0	108.8	238.1	279.1	396.1	475.0	490.3	498.5	502.6	504.8	504.8
30°	68.5	97.1	232.2	276.7	400.7	472.6	484.9	489.0	493.1	496.7	498.5
32.5°	62.6	86.0	223.5	272.0	401.3	466.8	475.6	478.0	483.8	492.0	494.9
35°	57.3	74.9	213.6	265.6	397.8	457.5	463.3	465.7	477.4	489.6	493.7
37.5°	52.1	66.7	200.7	254.5	392.5	446.4	450.5	454.6	472.6	487.3	492.0
40°	46.8	59.6	185.5	242.2	384.4	432.9	436.5	442.8	466.8	483.8	488.5
42.5°	42.7	53.8	169.1	229.3	373.8	417.7	422.9	432.4	459.8	478.0	483.2
45°	39.2	48.0	151.6	211.7	360.3	401.9	409.5	422.4	451.6	469.2	473.9
47.5°	35.7	43.9	133.4	193.7	345.8	386.1	396.1	410.6	440.6	457.5	461.6
50°	32.8	39.8	115.3	174.3	330.0	369.1	380.8	396.1	426.5	442.3	447.5
52.5°	30.4	36.3	98.3	155.0	311.8	351.6	365.0	380.8	409.5	424.7	428.3
55°	28.1	33.3	83.6	134.6	293.1	332.9	347.5	362.7	390.8	403.7	406.0
57.5°	26.9	31.0	71.3	115.3	273.2	311.8	328.1	342.2	368.5	378.5	380.8
60°	25.1	29.2	62.0	98.9	251.6	292.0	306.0	320.0	342.2	350.4	352.2
62.5°	23.4	28.1	55.0	83.1	229.3	268.5	282.5	295.4	314.1	320.0	322.3
65°	22.2	26.9	49.7	71.3	206.5	243.9	257.9	269.1	284.3	290.1	291.3
67.5°	21.1	25.7	45.6	61.4	183.7	219.4	229.9	240.4	252.1	257.9	258.6
70°	19.3	24.6	42.1	54.4	160.3	191.3	200.0	211.2	220.5	223.5	225.2
72.5°	18.1	22.8	39.8	49.2	136.3	164.4	172.6	179.0	187.2	190.1	190.1
75°	16.4	20.5	37.4	43.9	111.7	134.6	141.5	148.0	154.4	155.6	153.8
77.5°	14.7	18.1	32.2	36.9	87.2	106.5	112.3	115.8	121.1	122.3	122.9
80°	12.3	15.8	25.1	28.7	63.2	78.4	82.5	85.4	90.1	90.1	91.3
82.5°	9.3	12.3	18.1	20.5	42.7	53.8	57.3	59.1	62.0	62.0	62.0
85°	5.8	7.6	11.7	13.4	25.7	32.8	35.1	35.7	38.0	38.6	38.6
87.5°	3.0	4.1	7.6	8.2	13.4	17.0	17.0	18.1	18.1	17.5	17.0
90°	1.8	3.2	4.7	5.1	7.9	11.8	13.7	12.1	9.1	6.8	6.8
92.5°	7.2	19.4	31.7	34.7	48.7	67.5	76.9	67.4	48.4	34.2	32.8
95°	17.3	39.6	62.0	67.6	120.0	189.8	224.8	200.6	152.2	115.9	111.8
97.5°	29.8	49.5	69.2	74.2	161.6	278.2	336.4	321.2	290.6	267.6	259.8
100°	39.5	57.4	75.3	79.8	176.8	306.1	370.8	371.9	374.2	375.8	366.5
102.5°	47.8	64.5	81.2	85.4	183.7	314.9	380.5	400.0	439.0	468.2	460.2
105°	61.8	76.0	90.1	93.7	188.9	315.9	379.4	423.1	510.5	576.1	571.8
107.5°	76.2	89.4	102.6	105.9	189.8	301.9	357.9	418.8	540.7	632.1	633.2
110°	85.9	97.8	109.7	112.7	188.4	289.4	339.9	408.0	544.3	646.5	651.0



TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	95.4	106.7	118.1	121.0	188.4	278.5	323.5	393.3	532.7	637.4	644.3
115°	109.8	120.3	130.7	133.3	190.2	266.0	303.9	371.1	505.4	606.2	615.7
117.5°	124.0	133.5	143.0	145.4	193.8	258.2	290.5	351.1	472.3	563.2	573.8
120°	132.3	141.3	150.2	152.4	196.6	255.6	285.1	340.4	451.3	534.4	544.7
122.5°	140.4	149.5	158.4	160.7	200.7	254.2	280.9	330.8	430.6	505.4	515.5
125°	152.8	161.0	169.2	171.3	206.3	253.1	276.4	318.8	403.6	467.1	476.5
127.5°	162.8	171.2	179.5	181.6	211.9	252.5	272.7	309.0	381.8	436.4	444.2
130°	168.2	177.2	186.1	188.4	216.0	252.8	271.2	303.6	368.4	417.0	424.2
132.5°	173.8	182.8	191.7	193.9	219.3	253.1	270.0	298.9	356.9	400.4	407.0
135°	182.1	190.2	198.4	200.4	222.9	252.8	267.8	292.0	340.6	377.1	382.6
137.5°	190.5	198.6	206.7	208.7	228.3	254.4	267.5	287.9	329.0	359.8	364.4
140°	197.5	204.9	212.4	214.3	231.5	254.6	266.1	283.9	319.4	346.0	350.3
142.5°	202.9	209.8	216.6	218.4	234.3	255.5	266.1	281.8	312.9	336.3	339.9
145°	211.2	217.1	223.2	224.6	237.9	255.6	264.4	277.1	302.6	321.7	324.5
147.5°	219.5	225.3	231.1	232.6	243.2	257.3	264.4	274.4	294.5	309.5	311.8
150°	224.8	230.0	235.4	236.7	245.9	258.2	264.4	272.9	289.8	302.5	304.4
152.5°	230.4	234.4	238.4	239.4	247.7	258.8	264.4	271.6	286.1	296.9	298.3
155°	238.7	241.6	244.6	245.3	251.7	260.1	264.4	270.2	281.7	290.3	291.3
157.5°	244.8	247.7	250.5	251.2	255.6	261.4	264.4	268.8	277.8	284.5	285.2
160°	249.0	251.1	253.4	253.9	257.4	262.0	264.4	268.2	275.9	281.7	282.0
162.5°	253.1	254.7	256.4	256.8	259.3	262.7	264.4	267.6	274.1	279.0	279.3
165°	257.6	259.1	260.7	261.0	262.1	263.6	264.4	266.7	271.3	274.8	275.1
167.5°	261.7	262.4	263.1	263.3	264.2	265.5	266.1	267.7	270.8	273.0	273.2
170°	264.4	265.1	265.8	266.0	266.1	266.1	266.1	267.7	270.8	273.0	273.0
172.5°	265.8	266.0	266.1	266.1	266.1	266.1	266.1	267.4	269.7	271.6	271.4
175°	267.8	267.8	267.8	267.8	267.3	266.5	266.1	266.9	268.5	269.6	269.6
177.5°	267.8	267.8	267.8	267.8	267.4	266.8	266.6	267.2	268.4	269.3	269.1
180°	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8



TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	181.9	181.9
2.5°	194.2	193.1
5°	249.8	251.0
7.5°	336.3	335.8
10°	418.3	423.5
12.5°	478.0	479.1
15°	514.2	516.6
17.5°	528.3	528.9
20°	528.9	527.7
22.5°	522.4	521.2
25°	514.8	514.2
27.5°	507.8	508.4
30°	504.8	506.7
32.5°	504.8	507.8
35°	506.0	508.9
37.5°	505.4	508.9
40°	503.1	507.2
42.5°	496.7	499.6
45°	486.7	490.3
47.5°	473.9	476.2
50°	457.5	459.8
52.5°	437.0	437.6
55°	412.5	414.7
57.5°	386.1	386.7
60°	356.8	358.6
62.5°	325.9	325.9
65°	293.1	294.2
67.5°	259.2	262.0
70°	224.6	225.2
72.5°	190.7	190.7
75°	155.6	156.2
77.5°	122.3	122.3
80°	90.7	91.3
82.5°	62.6	63.7
85°	39.2	39.2
87.5°	18.1	16.4
90°	6.8	6.8
92.5°	27.4	21.9
95°	95.3	78.9
97.5°	228.5	197.2
100°	329.2	291.9
102.5°	428.3	396.3
105°	554.6	537.4
107.5°	637.3	641.5
110°	668.9	686.7



TEST NUMBER: P936632

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	671.7	699.2
115°	653.9	692.0
117.5°	616.1	658.4
120°	585.7	626.7
122.5°	556.1	596.6
125°	513.7	551.0
127.5°	475.7	507.2
130°	453.4	482.4
132.5°	433.0	459.0
135°	405.1	427.6
137.5°	382.7	401.1
140°	367.5	384.7
142.5°	354.7	369.6
145°	335.7	346.9
147.5°	321.1	330.3
150°	311.9	319.4
152.5°	304.0	309.7
155°	295.0	298.8
157.5°	287.9	290.5
160°	283.6	285.1
162.5°	280.8	282.2
165°	276.7	278.3
167.5°	273.8	274.4
170°	273.0	273.0
172.5°	270.9	270.3
175°	269.6	269.6
177.5°	268.5	267.8
180°	267.8	267.8



TEST NUMBER: P936632
 CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.31	3.16	3.30	4.17	5.51	15.45	16.30	16.45	17.31	18.65
	3H	3.02	3.78	4.02	4.80	6.16	17.28	18.04	18.28	19.06	20.42
	4H	3.31	4.04	4.33	5.06	6.43	17.91	18.64	18.93	19.66	21.03
	6H	3.57	4.23	4.59	5.26	6.64	18.33	19.00	19.36	20.02	21.41
	8H	3.63	4.27	4.67	5.31	6.69	18.44	19.08	19.48	20.12	21.50
	12H	3.65	4.25	4.69	5.29	6.69	18.50	19.11	19.54	20.15	21.55
4H	2H	9.50	10.23	10.52	11.25	12.62	15.73	16.45	16.75	17.47	18.84
	3H	11.07	11.68	12.10	12.73	14.11	17.76	18.36	18.79	19.41	20.80
	4H	11.17	11.72	12.21	12.76	14.17	18.51	19.07	19.55	20.11	21.52
	6H	11.18	11.66	12.23	12.72	14.12	19.04	19.52	20.09	20.58	21.98
	8H	11.15	11.60	12.20	12.66	14.08	19.20	19.64	20.25	20.70	22.12
	12H	11.11	11.52	12.18	12.59	14.01	19.28	19.69	20.35	20.76	22.18
8H	4H	12.60	13.05	13.65	14.11	15.52	18.57	19.02	19.62	20.08	21.50
	6H	12.84	13.21	13.92	14.31	15.73	19.19	19.56	20.27	20.66	22.07
	8H	12.86	13.19	13.94	14.27	15.70	19.40	19.73	20.48	20.81	22.24
	12H	12.83	13.12	13.91	14.19	15.67	19.54	19.83	20.62	20.90	22.38
12H	4H	12.74	13.15	13.81	14.22	15.64	18.53	18.93	19.60	20.00	21.43
	6H	13.10	13.42	14.18	14.51	15.94	19.17	19.50	20.26	20.58	22.02
	8H	13.17	13.45	14.25	14.53	16.01	19.40	19.68	20.48	20.76	22.23