

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521306

Luminaire Tested: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521306
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8951.8 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521306

CATALOG NUMBER: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P521306

CATALOG NUMBER: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23				
1	92	89	85	82	82	79	76	74	61	59	57	44	43	42	29	28	28	21				
2	85	78	73	68	75	70	65	62	54	51	49	40	38	36	26	25	25	19				
3	78	70	63	58	69	62	57	52	48	45	42	36	34	32	24	23	22	17				
4	72	62	55	50	64	56	50	45	44	40	36	32	30	28	22	21	20	15				
5	66	56	48	43	59	50	44	39	39	35	32	29	27	25	20	19	18	14				
6	61	50	43	37	54	45	39	34	36	31	28	27	24	22	19	17	16	13				
7	56	45	38	33	50	41	35	30	32	28	25	25	22	20	17	16	14	12				
8	52	41	34	29	47	37	31	27	30	25	22	23	20	18	16	14	13	11				
9	49	38	31	26	44	34	28	24	27	23	20	21	18	16	15	13	12	10				
10	46	35	28	24	41	31	26	22	25	21	18	19	17	15	14	12	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15683	15683	15683
5°	15430	15393	15506
10°	14438	14631	15038
15°	13126	13542	14296
20°	11651	12256	13330
25°	10146	10950	12248
30°	8691	9646	11222
35°	7206	8188	9985
40°	5537	6547	8508
45°	4002	4957	6846
50°	2727	3695	5430
55°	1773	2672	4219
60°	1017	1882	3050
65°	269	1148	1543
70°	132	356	442
75°	57	29	0
80°	43	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6846 cd/sqm

TEST NUMBER: P521306

CATALOG NUMBER: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	1.7
10°-20°	396.7	4.4
20°-30°	496.6	5.5
30°-40°	458.7	5.1
40°-50°	308.2	3.4
50°-60°	159.2	1.8
60°-70°	49.9	0.6
70°-80°	3.1	0.0
80°-90°	0.1	0.0
90°-100°	507.9	5.7
100°-110°	1445.2	16.1
110°-120°	1384.7	15.5
120°-130°	1095.9	12.2
130°-140°	879.7	9.8
140°-150°	688.7	7.7
150°-160°	503.9	5.6
160°-170°	312.1	3.5
170°-180°	105.9	1.2
0°-30°	1048.5	11.7
0°-40°	1507.2	16.8
0°-60°	1974.7	22.1
0°-90°	2027.7	22.7
90°-120°	3337.9	37.3
90°-150°	6002.1	67.0
90°-180°	6924.0	77.3
0°-180°	8951.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1666	1649	1662	1668	1674	154
15°	1374	1369	1418	1465	1497	383
25°	997	1005	1076	1149	1203	457
35°	640	656	727	812	886	396
45°	307	325	380	454	525	241
55°	110	129	166	213	262	103
65°	12	24	53	64	71	21
75°	2	2	1	0	0	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	55	219	983	340	210	63
105°	225	341	1473	2602	2473	238
115°	418	504	1117	2366	2778	411
125°	589	653	1066	1769	2115	527
135°	720	781	1053	1494	1689	556
145°	850	893	1062	1293	1409	531
155°	971	993	1087	1169	1216	449
165°	1072	1076	1100	1124	1140	302
175°	1123	1117	1113	1106	1098	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P521306

CATALOG NUMBER: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1699.8	1699.8	1699.8	1699.8	1699.8
2.5°	1703.8	1687.7	1691.9	1691.8	1687.3
5°	1666.1	1649.2	1662.0	1667.9	1674.3
7.5°	1595.7	1582.5	1607.1	1625.5	1638.8
10°	1541.1	1529.8	1561.7	1586.8	1605.2
12.5°	1477.9	1469.3	1507.7	1542.1	1565.8
15°	1374.2	1369.3	1417.8	1465.3	1496.7
17.5°	1263.0	1262.8	1318.1	1377.2	1415.0
20°	1186.7	1189.1	1248.3	1313.5	1357.7
22.5°	1110.4	1116.0	1179.3	1247.2	1297.9
25°	996.7	1004.7	1075.6	1149.2	1203.1
27.5°	887.5	899.2	973.8	1050.3	1115.9
30°	815.8	829.5	905.4	985.9	1053.4
32.5°	745.4	761.6	835.7	920.8	989.6
35°	639.8	655.9	727.0	812.5	886.5
37.5°	530.8	546.5	615.9	700.2	780.1
40°	459.7	477.4	543.6	625.2	706.4
42.5°	395.2	412.9	475.2	555.4	632.1
45°	306.7	325.2	379.9	453.9	524.7
47.5°	233.4	253.5	301.5	368.4	432.9
50°	190.0	210.1	257.4	316.4	378.3
52.5°	155.1	174.6	217.3	272.8	329.6
55°	110.2	128.7	166.1	213.3	262.3
57.5°	76.2	92.1	125.7	165.0	203.5
60°	55.1	70.4	102.0	133.9	165.3
62.5°	36.7	50.7	81.6	106.1	127.1
65°	12.3	23.6	52.6	63.5	70.7
67.5°	6.2	7.5	27.6	29.2	31.6
70°	4.9	4.9	13.2	14.0	16.4
72.5°	3.6	3.6	5.3	6.8	7.2
75°	1.6	1.6	0.8	0.0	0.0
77.5°	0.8	0.8	0.7	0.0	0.0
80°	0.8	0.8	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.0	89.9	208.5	60.7	45.8
95°	55.1	218.8	983.3	340.3	209.8
97.5°	101.3	256.3	1514.4	1083.6	742.6
100°	133.5	278.6	1629.6	1650.7	1271.5
102.5°	169.1	302.6	1604.2	2112.9	1781.8
105°	224.6	340.7	1472.8	2601.5	2473.1
107.5°	281.0	385.0	1319.4	2739.3	2853.7
110°	320.0	417.4	1231.2	2686.6	2943.5

TEST NUMBER: P521306

CATALOG NUMBER: SQ4-BB-150U-075D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.3	449.7	1171.9	2561.9	2928.3
115°	417.5	504.5	1116.8	2365.9	2778.2
117.5°	470.5	552.1	1084.2	2151.6	2588.3
120°	512.8	581.2	1080.8	2029.1	2447.6
122.5°	546.7	615.1	1072.3	1921.6	2310.3
125°	589.1	653.4	1065.9	1768.9	2114.9
127.5°	635.3	695.4	1062.5	1677.6	1962.8
130°	659.1	719.1	1057.5	1614.1	1862.7
132.5°	684.5	742.9	1057.5	1564.5	1793.2
135°	720.5	780.6	1053.2	1494.2	1689.0
137.5°	754.4	812.9	1052.8	1434.7	1602.9
140°	779.9	839.9	1051.1	1385.4	1547.0
142.5°	808.7	858.8	1056.2	1346.0	1491.0
145°	849.8	893.3	1061.7	1293.2	1409.2
147.5°	885.0	927.2	1071.0	1239.9	1340.2
150°	915.5	944.5	1074.4	1222.2	1292.7
152.5°	939.2	969.9	1077.8	1198.4	1263.9
155°	970.6	993.4	1087.1	1168.7	1216.4
157.5°	1009.6	1023.2	1089.2	1155.3	1189.3
160°	1029.9	1040.3	1097.7	1145.0	1174.0
162.5°	1041.8	1053.8	1099.4	1136.4	1158.8
165°	1072.3	1076.4	1099.8	1123.5	1140.1
167.5°	1093.1	1089.3	1109.6	1120.3	1127.0
170°	1099.8	1097.8	1106.2	1108.5	1116.8
172.5°	1115.1	1108.1	1111.3	1105.1	1111.7
175°	1123.2	1116.9	1112.6	1106.0	1097.7
177.5°	1126.5	1116.6	1111.3	1104.5	1106.2
180°	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)