

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521353

Luminaire Tested: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-37)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4840.8 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 45.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521353

CATALOG NUMBER: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P521353

CATALOG NUMBER: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																										
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																																				
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	58	56	52																																				
2	91	83	77	72	85	78	73	68	69	64	61	60	57	54	52	49	47	43																																				
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	46	42	40	36																																				
4	76	65	56	50	71	61	53	48	54	48	43	47	42	39	41	37	34	31																																				
5	70	58	49	43	65	54	47	41	48	42	37	42	37	33	36	33	30	27																																				
6	64	52	43	37	60	49	41	36	43	37	32	38	33	29	33	29	26	23																																				
7	59	47	38	33	55	44	37	31	39	33	28	34	29	26	30	26	23	21																																				
8	55	42	34	29	51	40	33	28	36	30	25	31	27	23	28	24	21	18																																				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16																																				
10	48	35	28	23	45	34	27	22	30	24	20	27	22	19	24	20	17	15																																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9692	9692	9692
5°	9764	9729	9676
10°	9788	9716	9671
15°	9686	9650	9604
20°	9666	9600	9591
25°	9583	9564	9457
30°	9520	9459	9388
35°	9386	9375	9256
40°	9299	9253	9196
45°	9188	9137	9038
50°	9063	8995	8872
55°	8895	8787	8664
60°	8686	8545	8387
65°	8396	8208	8062
70°	7871	7691	7510
75°	7094	6891	6787
80°	5797	5844	5744
85°	4150	4764	4764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9188 cd/sqm

TEST NUMBER: P521353

CATALOG NUMBER: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	2.1
10°-20°	284.7	5.9
20°-30°	430.7	8.9
30°-40°	518.0	10.7
40°-50°	537.9	11.1
50°-60°	487.3	10.1
60°-70°	370.7	7.7
70°-80°	206.0	4.3
80°-90°	53.1	1.1
90°-100°	135.9	2.8
100°-110°	386.8	8.0
110°-120°	370.6	7.7
120°-130°	293.3	6.1
130°-140°	235.4	4.9
140°-150°	184.3	3.8
150°-160°	134.8	2.8
160°-170°	83.5	1.7
170°-180°	28.3	0.6
0°-30°	814.9	16.8
0°-40°	1333.0	27.5
0°-60°	2358.1	48.7
0°-90°	2987.9	61.7
90°-120°	893.2	18.5
90°-150°	1606.2	33.2
90°-180°	1853.0	38.3
0°-180°	4840.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1050	1050	1050	1050	1050	
5°	1054	1045	1050	1046	1045	100
15°	1014	1006	1010	1009	1006	287
25°	941	933	940	930	929	434
35°	833	830	832	823	822	522
45°	704	700	700	693	693	543
55°	553	552	546	542	539	494
65°	385	379	376	370	369	379
75°	199	196	193	191	190	211
85°	39	42	45	45	45	48
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P521353

CATALOG NUMBER: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.5	1050.5	1050.5	1050.5	1050.5
2.5°	1057.4	1048.4	1051.3	1048.9	1046.7
5°	1054.3	1045.0	1050.5	1045.7	1044.8
7.5°	1049.4	1038.3	1040.9	1040.0	1040.0
10°	1044.8	1030.7	1037.1	1032.3	1032.3
12.5°	1032.5	1020.7	1025.6	1023.2	1024.7
15°	1014.1	1005.7	1010.3	1009.3	1005.5
17.5°	998.3	988.2	991.6	989.8	988.3
20°	984.5	975.1	977.8	973.1	976.8
22.5°	969.2	959.8	964.8	956.9	956.9
25°	941.4	933.0	939.5	929.9	929.0
27.5°	912.0	906.5	910.8	903.7	901.1
30°	893.6	885.2	887.9	883.0	881.2
32.5°	872.2	863.7	866.4	857.8	859.0
35°	833.3	829.6	832.4	822.8	821.8
37.5°	798.1	790.6	795.0	787.2	786.4
40°	772.1	764.6	768.3	763.5	763.5
42.5°	748.4	740.1	742.2	735.9	733.6
45°	704.2	699.5	700.3	692.7	692.7
47.5°	660.5	657.2	655.7	647.9	649.4
50°	631.4	625.8	626.7	618.1	618.1
52.5°	597.8	598.1	594.5	588.9	584.4
55°	553.0	552.1	546.3	541.5	538.6
57.5°	505.2	500.9	496.7	490.2	489.7
60°	470.7	467.9	463.1	457.3	454.5
62.5°	435.5	432.7	427.9	422.9	422.3
65°	384.6	379.0	376.0	370.2	369.3
67.5°	329.3	324.8	321.1	316.5	315.9
70°	291.8	288.1	285.1	281.2	278.4
72.5°	257.4	251.4	248.4	245.3	243.2
75°	199.0	196.2	193.3	191.3	190.4
77.5°	142.7	142.9	142.9	140.4	139.5
80°	109.1	110.0	110.0	109.0	108.1
82.5°	79.2	80.9	81.7	80.7	80.6
85°	39.2	42.0	45.0	45.0	45.0
87.5°	10.7	14.5	17.6	18.4	17.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P521353

CATALOG NUMBER: SQ4-F-025U-075D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)