

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521384

Luminaire Tested: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521384
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-39)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7463.7 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521384

CATALOG NUMBER: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P521384

CATALOG NUMBER: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	90	97	93	90	86	84	81	79	76	74	72	68	66	65
2	93	85	79	73	88	81	75	71	73	69	65	66	63	59	59	57	54
3	85	75	67	61	80	71	64	59	65	59	54	58	54	50	52	49	46
4	78	66	58	51	73	63	56	50	57	51	46	52	47	43	47	43	39
5	71	59	50	44	67	56	48	43	51	45	40	46	41	37	42	38	34
6	66	53	44	38	62	51	43	37	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	35	30	27
8	57	44	35	30	53	42	34	29	38	32	27	35	29	25	32	27	24
9	53	40	32	27	50	38	31	26	35	29	24	32	27	23	29	25	21
10	49	37	29	24	47	35	28	23	32	26	22	30	24	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17596	17596	17596
5°	17740	17625	17557
10°	17691	17583	17514
15°	17637	17527	17478
20°	17554	17441	17359
25°	17423	17327	17210
30°	17286	17231	17052
35°	17109	17050	16838
40°	16910	16846	16645
45°	16722	16612	16353
50°	16458	16323	16128
55°	16155	16003	15751
60°	15849	15559	15290
65°	15234	14913	14616
70°	14478	13971	13801
75°	13090	12715	12494
80°	10786	10786	10616
85°	7643	8744	9189

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16722 cd/sqm

TEST NUMBER: P521384

CATALOG NUMBER: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.5	2.4
10°-20°	516.9	6.9
20°-30°	781.8	10.5
30°-40°	941.7	12.6
40°-50°	977.7	13.1
50°-60°	886.3	11.9
60°-70°	676.1	9.1
70°-80°	378.2	5.1
80°-90°	98.3	1.3
90°-100°	148.6	2.0
100°-110°	422.9	5.7
110°-120°	405.2	5.4
120°-130°	320.7	4.3
130°-140°	257.4	3.4
140°-150°	201.5	2.7
150°-160°	147.4	2.0
160°-170°	91.3	1.2
170°-180°	31.0	0.4
0°-30°	1479.2	19.8
0°-40°	2420.9	32.4
0°-60°	4284.9	57.4
0°-90°	5437.5	72.9
90°-120°	976.8	13.1
90°-150°	1756.4	23.5
90°-180°	2026.0	27.1
0°-180°	7463.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1907	1907	1907	1907	1907	
5°	1916	1896	1903	1898	1896	182
15°	1846	1828	1835	1833	1830	521
25°	1712	1694	1702	1690	1691	789
35°	1519	1507	1514	1497	1495	950
45°	1282	1274	1273	1257	1253	987
55°	1004	1002	995	982	979	897
65°	698	694	683	675	670	692
75°	367	361	357	352	350	388
85°	72	79	83	83	87	90
90°	0	0	0	0	0	3
95°	16	64	288	100	61	18
105°	66	100	431	761	724	70
115°	122	148	327	692	813	120
125°	172	191	312	518	619	154
135°	211	228	308	437	494	163
145°	249	261	311	378	412	155
155°	284	291	318	342	356	131
165°	314	315	322	329	334	88
175°	329	327	326	324	321	31
180°	326	326	326	326	326	

TEST NUMBER: P521384

CATALOG NUMBER: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1907.2	1907.2	1907.2	1907.2	1907.2
2.5°	1918.9	1903.3	1908.0	1904.5	1898.0
5°	1915.5	1896.1	1903.0	1897.7	1895.7
7.5°	1900.9	1882.7	1888.5	1885.4	1882.9
10°	1888.3	1870.9	1876.8	1873.6	1869.5
12.5°	1874.1	1855.9	1862.6	1857.8	1856.1
15°	1846.5	1828.1	1835.0	1832.8	1829.8
17.5°	1813.0	1794.4	1801.5	1797.3	1794.8
20°	1787.9	1768.5	1776.4	1768.0	1768.0
22.5°	1759.4	1740.0	1749.6	1737.1	1739.6
25°	1711.5	1694.1	1702.1	1689.6	1690.6
27.5°	1659.4	1643.1	1653.4	1637.2	1636.6
30°	1622.6	1606.2	1617.4	1599.6	1600.6
32.5°	1581.6	1567.7	1577.2	1560.2	1559.6
35°	1519.0	1506.8	1513.8	1497.0	1495.0
37.5°	1450.8	1441.8	1444.8	1428.8	1428.0
40°	1404.0	1395.8	1398.7	1382.0	1382.0
42.5°	1356.3	1348.9	1351.0	1332.6	1332.6
45°	1281.6	1274.4	1273.2	1257.4	1253.3
47.5°	1201.8	1196.1	1192.4	1178.2	1176.3
50°	1146.6	1142.5	1137.2	1124.6	1123.6
52.5°	1088.9	1087.2	1081.1	1067.7	1066.7
55°	1004.3	1002.3	994.9	982.3	979.2
57.5°	915.8	913.8	905.1	892.7	889.7
60°	858.9	852.8	843.2	831.6	828.6
62.5°	797.0	790.0	780.4	769.8	769.1
65°	697.8	693.7	683.1	674.7	669.5
67.5°	604.5	595.3	584.8	577.9	576.9
70°	536.7	527.5	517.9	512.6	511.6
72.5°	468.9	461.3	452.6	447.3	447.1
75°	367.2	361.1	356.7	351.5	350.5
77.5°	266.6	264.9	263.2	257.6	257.6
80°	203.0	203.0	203.0	199.8	199.8
82.5°	146.0	150.1	150.2	148.8	148.8
85°	72.2	79.3	82.6	82.7	86.8
87.5°	20.1	27.5	32.6	33.5	36.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.3	61.0	17.8	13.4
95°	16.1	64.0	287.7	99.6	61.4
97.5°	29.6	75.0	443.1	317.1	217.3
100°	39.1	81.5	476.9	483.0	372.1
102.5°	49.5	88.5	469.4	618.3	521.4
105°	65.7	99.7	431.0	761.3	723.7
107.5°	82.2	112.7	386.1	801.6	835.1
110°	93.6	122.1	360.3	786.2	861.3

TEST NUMBER: P521384

CATALOG NUMBER: SQ4-F-025U-125D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.6	131.6	342.9	749.7	856.9
115°	122.2	147.6	326.8	692.3	813.0
117.5°	137.7	161.6	317.3	629.6	757.4
120°	150.1	170.1	316.3	593.8	716.2
122.5°	160.0	180.0	313.8	562.3	676.1
125°	172.4	191.2	311.9	517.6	618.9
127.5°	185.9	203.5	310.9	490.9	574.4
130°	192.9	210.4	309.4	472.3	545.1
132.5°	200.3	217.4	309.4	457.8	524.7
135°	210.8	228.4	308.2	437.2	494.2
137.5°	220.8	237.9	308.1	419.8	469.1
140°	228.2	245.8	307.6	405.4	452.7
142.5°	236.6	251.3	309.1	393.9	436.3
145°	248.7	261.4	310.7	378.4	412.4
147.5°	259.0	271.3	313.4	362.8	392.2
150°	267.9	276.4	314.4	357.7	378.3
152.5°	274.8	283.8	315.4	350.7	369.8
155°	284.0	290.7	318.1	342.0	355.9
157.5°	295.4	299.4	318.7	338.1	348.0
160°	301.4	304.4	321.2	335.1	343.5
162.5°	304.9	308.4	321.7	332.5	339.1
165°	313.8	315.0	321.8	328.8	333.6
167.5°	319.9	318.8	324.7	327.8	329.8
170°	321.8	321.2	323.7	324.4	326.8
172.5°	326.3	324.2	325.2	323.4	325.3
175°	328.7	326.8	325.6	323.6	321.2
177.5°	329.7	326.7	325.2	323.2	323.7
180°	326.2	326.2	326.2	326.2	326.2

(END OF REPORT)