

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936932

Luminaire Tested: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936932
REPORT IS A COMBINATION OF REPORTS P933472 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5287.1 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936932
CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4258	4258	4258
5°	4156	4918	5724
10°	3765	7163	9489
15°	3196	9352	11458
20°	2599	10830	11678
25°	2166	11325	11441
30°	1824	11387	11419
35°	1610	11189	11713
40°	1401	10935	12019
45°	1266	10745	12066
50°	1159	10572	11866
55°	1106	10324	11340
60°	1130	9858	10511
65°	1169	9154	9368
70°	1236	7966	7915
75°	1354	6479	6177
80°	1451	4478	4162
85°	1217	2362	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12066 cd/sqm



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	1.1
10°-20°	263.1	5.0
20°-30°	460.2	8.7
30°-40°	592.4	11.2
40°-50°	661.7	12.5
50°-60°	633.7	12.0
60°-70°	502.2	9.5
70°-80°	295.3	5.6
80°-90°	83.1	1.6
90°-100°	130.5	2.5
100°-110°	343.2	6.5
110°-120°	355.9	6.7
120°-130°	285.4	5.4
130°-140°	224.0	4.2
140°-150°	171.9	3.3
150°-160°	123.8	2.3
160°-170°	75.7	1.4
170°-180°	25.6	0.5
0°-30°	782.6	14.8
0°-40°	1375.0	26.0
0°-60°	2670.4	50.5
0°-90°	3551.1	67.2
90°-120°	829.6	15.7
90°-150°	1510.9	28.6
90°-180°	1736.0	32.8
0°-180°	5287.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	459	459	459	459	459	
5°	447	480	540	611	633	41
15°	335	618	1042	1263	1303	93
25°	214	701	1241	1296	1297	99
35°	145	670	1169	1235	1284	90
45°	99	534	1033	1183	1236	76
55°	71	339	876	1018	1046	65
65°	56	180	651	732	742	56
75°	41	111	357	392	394	43
85°	15	34	88	97	99	16
90°	2	5	14	7	7	2
95°	17	68	225	116	79	19
105°	62	94	379	576	537	66
115°	110	133	304	606	692	108
125°	153	171	276	467	551	136
135°	182	200	268	377	428	141
145°	211	225	264	322	347	132
155°	239	245	264	290	299	110
165°	258	261	264	275	278	73
175°	268	268	266	270	270	25
180°	268	268	268	268	268	



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	458.9	458.9	461.8	463.3	466.3	467.8	470.7	473.7	482.5	484.0	486.9
5°	447.1	453.0	472.2	479.5	500.2	528.3	540.1	559.2	599.1	610.9	618.3
7.5°	429.4	442.6	489.9	501.7	553.3	627.1	658.1	699.5	762.9	793.8	818.9
10°	401.3	429.4	513.5	541.5	625.6	737.7	795.3	852.8	948.8	991.6	1007.8
12.5°	370.4	416.1	538.6	576.9	698.0	861.7	931.1	994.6	1103.7	1161.3	1170.1
15°	334.9	396.9	562.2	618.3	774.6	965.0	1041.7	1120.0	1221.8	1263.1	1273.4
17.5°	304.0	382.2	584.3	643.4	833.7	1058.0	1136.2	1201.1	1283.7	1311.8	1319.1
20°	265.6	358.6	599.1	675.8	895.7	1125.9	1201.1	1251.3	1307.4	1325.1	1328.0
22.5°	237.5	333.5	607.9	687.6	937.0	1167.1	1230.6	1270.5	1308.8	1314.8	1316.2
25°	214.0	305.5	606.5	700.9	972.4	1192.2	1241.0	1270.5	1292.6	1295.6	1295.6
27.5°	191.8	274.4	600.6	703.8	998.9	1198.2	1236.5	1257.2	1267.5	1273.4	1273.4
30°	172.7	245.0	585.8	698.0	1010.8	1192.2	1223.2	1233.6	1243.9	1252.8	1257.2
32.5°	157.9	216.9	563.7	686.1	1012.3	1177.5	1199.7	1205.5	1220.3	1241.0	1248.3
35°	144.6	188.9	538.6	669.9	1003.4	1153.9	1168.6	1174.5	1204.0	1235.1	1245.4
37.5°	131.3	168.2	506.1	641.9	990.1	1125.9	1136.2	1146.6	1192.2	1229.1	1241.0
40°	118.1	150.5	467.8	610.9	969.4	1091.9	1100.8	1117.0	1177.5	1220.3	1232.1
42.5°	107.7	135.8	426.4	578.4	942.8	1053.6	1066.8	1090.5	1159.8	1205.5	1218.8
45°	98.9	121.0	382.2	534.1	908.9	1013.7	1032.9	1065.4	1139.1	1183.4	1195.2
47.5°	90.0	110.7	336.4	488.4	872.0	973.9	998.9	1035.9	1111.1	1153.9	1164.3
50°	82.7	100.4	290.6	439.7	832.2	931.1	960.6	998.9	1075.7	1115.5	1128.8
52.5°	76.7	91.5	247.9	391.0	786.5	886.8	920.8	960.6	1032.9	1071.3	1080.1
55°	70.8	84.1	211.0	339.4	739.2	839.6	876.5	914.9	985.7	1018.1	1024.0
57.5°	67.8	78.2	180.0	290.6	689.1	786.5	827.8	863.2	929.6	954.7	960.6
60°	63.5	73.8	156.4	249.4	634.5	736.3	771.8	807.2	863.2	883.9	888.3
62.5°	59.0	70.8	138.7	209.5	578.4	677.3	712.7	745.2	792.4	807.2	813.0
65°	56.1	67.8	125.4	180.0	520.9	615.3	650.7	678.8	717.2	731.9	734.9
67.5°	53.1	65.0	115.1	155.0	463.3	553.3	579.9	606.5	636.0	650.7	652.2
70°	48.7	62.0	106.2	137.3	404.3	482.5	504.6	532.6	556.3	563.7	568.1
72.5°	45.8	57.6	100.4	123.9	343.8	414.7	435.3	451.5	472.2	479.5	479.5
75°	41.3	51.6	94.4	110.7	281.8	339.4	357.1	373.3	389.5	392.5	388.1
77.5°	36.9	45.8	81.2	93.0	219.8	268.6	283.3	292.1	305.5	308.4	309.8
80°	31.0	39.9	63.5	72.3	159.3	197.7	208.1	215.4	227.3	227.3	230.2
82.5°	23.6	31.0	45.8	51.6	107.7	135.8	144.6	149.0	156.4	156.4	156.4
85°	14.7	19.2	29.5	33.9	65.0	82.7	88.5	90.0	95.9	97.4	97.4
87.5°	7.4	10.3	19.2	20.7	33.9	42.8	42.8	45.8	45.8	44.3	42.8
90°	1.8	3.2	4.7	5.1	7.9	11.8	13.7	12.1	9.1	6.8	6.8
92.5°	7.2	19.4	31.7	34.7	48.7	67.5	76.9	67.4	48.4	34.2	32.8
95°	17.3	39.6	62.0	67.6	120.0	189.8	224.8	200.6	152.2	115.9	111.8
97.5°	29.8	49.5	69.2	74.2	161.6	278.2	336.4	321.2	290.6	267.6	259.8
100°	39.5	57.4	75.3	79.8	176.8	306.1	370.8	371.9	374.2	375.8	366.5
102.5°	47.8	64.5	81.2	85.4	183.7	314.9	380.5	400.0	439.0	468.2	460.2
105°	61.8	76.0	90.1	93.7	188.9	315.9	379.4	423.1	510.5	576.1	571.8
107.5°	76.2	89.4	102.6	105.9	189.8	301.9	357.9	418.8	540.7	632.1	633.2
110°	85.9	97.8	109.7	112.7	188.4	289.4	339.9	408.0	544.3	646.5	651.0



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	95.4	106.7	118.1	121.0	188.4	278.5	323.5	393.3	532.7	637.4	644.3
115°	109.8	120.3	130.7	133.3	190.2	266.0	303.9	371.1	505.4	606.2	615.7
117.5°	124.0	133.5	143.0	145.4	193.8	258.2	290.5	351.1	472.3	563.2	573.8
120°	132.3	141.3	150.2	152.4	196.6	255.6	285.1	340.4	451.3	534.4	544.7
122.5°	140.4	149.5	158.4	160.7	200.7	254.2	280.9	330.8	430.6	505.4	515.5
125°	152.8	161.0	169.2	171.3	206.3	253.1	276.4	318.8	403.6	467.1	476.5
127.5°	162.8	171.2	179.5	181.6	211.9	252.5	272.7	309.0	381.8	436.4	444.2
130°	168.2	177.2	186.1	188.4	216.0	252.8	271.2	303.6	368.4	417.0	424.2
132.5°	173.8	182.8	191.7	193.9	219.3	253.1	270.0	298.9	356.9	400.4	407.0
135°	182.1	190.2	198.4	200.4	222.9	252.8	267.8	292.0	340.6	377.1	382.6
137.5°	190.5	198.6	206.7	208.7	228.3	254.4	267.5	287.9	329.0	359.8	364.4
140°	197.5	204.9	212.4	214.3	231.5	254.6	266.1	283.9	319.4	346.0	350.3
142.5°	202.9	209.8	216.6	218.4	234.3	255.5	266.1	281.8	312.9	336.3	339.9
145°	211.2	217.1	223.2	224.6	237.9	255.6	264.4	277.1	302.6	321.7	324.5
147.5°	219.5	225.3	231.1	232.6	243.2	257.3	264.4	274.4	294.5	309.5	311.8
150°	224.8	230.0	235.4	236.7	245.9	258.2	264.4	272.9	289.8	302.5	304.4
152.5°	230.4	234.4	238.4	239.4	247.7	258.8	264.4	271.6	286.1	296.9	298.3
155°	238.7	241.6	244.6	245.3	251.7	260.1	264.4	270.2	281.7	290.3	291.3
157.5°	244.8	247.7	250.5	251.2	255.6	261.4	264.4	268.8	277.8	284.5	285.2
160°	249.0	251.1	253.4	253.9	257.4	262.0	264.4	268.2	275.9	281.7	282.0
162.5°	253.1	254.7	256.4	256.8	259.3	262.7	264.4	267.6	274.1	279.0	279.3
165°	257.6	259.1	260.7	261.0	262.1	263.6	264.4	266.7	271.3	274.8	275.1
167.5°	261.7	262.4	263.1	263.3	264.2	265.5	266.1	267.7	270.8	273.0	273.2
170°	264.4	265.1	265.8	266.0	266.1	266.1	266.1	267.7	270.8	273.0	273.0
172.5°	265.8	266.0	266.1	266.1	266.1	266.1	266.1	267.4	269.7	271.6	271.4
175°	267.8	267.8	267.8	267.8	267.3	266.5	266.1	266.9	268.5	269.6	269.6
177.5°	267.8	267.8	267.8	267.8	267.4	266.8	266.6	267.2	268.4	269.3	269.1
180°	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8	267.8



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	458.9	458.9
2.5°	489.9	486.9
5°	630.0	633.0
7.5°	848.5	847.0
10°	1055.0	1068.3
12.5°	1205.5	1208.5
15°	1297.1	1302.9
17.5°	1332.5	1334.0
20°	1334.0	1331.0
22.5°	1317.6	1314.8
25°	1298.5	1297.1
27.5°	1280.8	1282.2
30°	1273.4	1277.9
32.5°	1273.4	1280.8
35°	1276.4	1283.7
37.5°	1274.9	1283.7
40°	1269.0	1279.3
42.5°	1252.8	1260.1
45°	1227.6	1236.5
47.5°	1195.2	1201.1
50°	1153.9	1159.8
52.5°	1102.3	1103.7
55°	1040.2	1046.2
57.5°	973.9	975.4
60°	900.1	904.6
62.5°	821.9	821.9
65°	739.2	742.2
67.5°	653.7	661.1
70°	566.6	568.1
72.5°	481.0	481.0
75°	392.5	394.0
77.5°	308.4	308.4
80°	228.7	230.2
82.5°	157.9	160.8
85°	98.9	98.9
87.5°	45.8	41.3
90°	6.8	6.8
92.5°	27.4	21.9
95°	95.3	78.9
97.5°	228.5	197.2
100°	329.2	291.9
102.5°	428.3	396.3
105°	554.6	537.4
107.5°	637.3	641.5
110°	668.9	686.7



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	671.7	699.2
115°	653.9	692.0
117.5°	616.1	658.4
120°	585.7	626.7
122.5°	556.1	596.6
125°	513.7	551.0
127.5°	475.7	507.2
130°	453.4	482.4
132.5°	433.0	459.0
135°	405.1	427.6
137.5°	382.7	401.1
140°	367.5	384.7
142.5°	354.7	369.6
145°	335.7	346.9
147.5°	321.1	330.3
150°	311.9	319.4
152.5°	304.0	309.7
155°	295.0	298.8
157.5°	287.9	290.5
160°	283.6	285.1
162.5°	280.8	282.2
165°	276.7	278.3
167.5°	273.8	274.4
170°	273.0	273.0
172.5°	270.9	270.3
175°	269.6	269.6
177.5°	268.5	267.8
180°	267.8	267.8



TEST NUMBER: P936932

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.45	8.55	8.24	9.36	10.36	20.59	21.69	21.38	22.50	23.50
	3H	8.18	9.16	8.97	9.99	11.02	22.43	23.42	23.23	24.24	25.27
	4H	8.48	9.42	9.30	10.25	11.29	23.08	24.01	23.89	24.85	25.88
	6H	8.75	9.61	9.58	10.45	11.51	23.51	24.37	24.34	25.21	26.27
	8H	8.82	9.65	9.66	10.51	11.56	23.63	24.45	24.47	25.31	26.37
	12H	8.85	9.64	9.69	10.49	11.57	23.70	24.49	24.54	25.34	26.42
4H	2H	14.67	15.61	15.49	16.44	17.48	20.89	21.83	21.71	22.66	23.70
	3H	16.26	17.05	17.09	17.91	18.97	22.95	23.73	23.78	24.60	25.65
	4H	16.37	17.08	17.21	17.95	19.03	23.71	24.43	24.56	25.29	26.37
	6H	16.39	17.01	17.25	17.90	18.99	24.25	24.88	25.12	25.76	26.85
	8H	16.38	16.96	17.24	17.84	18.94	24.42	25.00	25.28	25.88	26.98
	12H	16.34	16.87	17.23	17.77	18.88	24.51	25.04	25.40	25.94	27.05
8H	4H	17.82	18.40	18.69	19.29	20.39	23.79	24.38	24.66	25.26	26.36
	6H	18.08	18.56	18.97	19.48	20.58	24.42	24.91	25.32	25.83	26.93
	8H	18.10	18.53	19.00	19.44	20.56	24.64	25.07	25.54	25.98	27.10
	12H	18.08	18.46	18.99	19.37	20.53	24.79	25.16	25.69	26.07	27.24
12H	4H	17.97	18.50	18.86	19.40	20.51	23.76	24.28	24.65	25.19	26.29
	6H	18.33	18.76	19.24	19.68	20.80	24.41	24.84	25.31	25.76	26.87
	8H	18.41	18.79	19.32	19.70	20.87	24.64	25.02	25.55	25.93	27.10