

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936935

Luminaire Tested: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936935
REPORT IS A COMBINATION OF REPORTS P933472 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5667.1 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936935
CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4564	4564	4564
5°	4454	5272	6135
10°	4036	7679	10171
15°	3426	10024	12281
20°	2786	11609	12516
25°	2322	12139	12263
30°	1955	12205	12239
35°	1726	11993	12556
40°	1502	11721	12882
45°	1357	11518	12933
50°	1242	11333	12720
55°	1186	11066	12156
60°	1210	10566	11266
65°	1252	9812	10041
70°	1325	8539	8484
75°	1453	6946	6620
80°	1554	4799	4462
85°	1308	2533	2284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12933 cd/sqm



TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.6	1.1
10°-20°	282.0	5.0
20°-30°	493.3	8.7
30°-40°	635.0	11.2
40°-50°	709.2	12.5
50°-60°	679.3	12.0
60°-70°	538.3	9.5
70°-80°	316.6	5.6
80°-90°	89.1	1.6
90°-100°	139.9	2.5
100°-110°	367.9	6.5
110°-120°	381.4	6.7
120°-130°	306.0	5.4
130°-140°	240.1	4.2
140°-150°	184.3	3.3
150°-160°	132.7	2.3
160°-170°	81.2	1.4
170°-180°	27.4	0.5
0°-30°	838.9	14.8
0°-40°	1473.9	26.0
0°-60°	2862.4	50.5
0°-90°	3806.3	67.2
90°-120°	889.2	15.7
90°-150°	1619.5	28.6
90°-180°	1861.0	32.8
0°-180°	5667.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	492	492	492	492	492	
5°	479	514	579	655	678	44
15°	359	663	1117	1354	1396	100
25°	229	751	1330	1389	1390	106
35°	155	718	1253	1324	1376	97
45°	106	572	1107	1268	1325	82
55°	76	364	940	1091	1121	69
65°	60	193	698	784	796	60
75°	44	119	383	421	422	46
85°	16	36	95	104	106	17
90°	2	5	15	7	7	3
95°	18	72	241	124	85	21
105°	66	100	407	618	576	70
115°	118	143	326	650	742	116
125°	164	184	296	501	591	145
135°	195	215	287	404	458	151
145°	226	241	283	345	372	142
155°	256	263	283	311	320	118
165°	276	280	283	294	298	78
175°	287	287	285	289	289	27
180°	287	287	287	287	287	



TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8
2.5°	491.8	491.8	495.0	496.6	499.8	501.4	504.6	507.7	517.2	518.8	521.9
5°	479.2	485.6	506.1	514.0	536.1	566.2	578.9	599.4	642.1	654.8	662.7
7.5°	460.2	474.5	525.1	537.7	593.1	672.1	705.4	749.7	817.7	850.9	877.8
10°	430.2	460.2	550.4	580.5	670.6	790.8	852.5	914.1	1017.0	1062.9	1080.2
12.5°	397.0	446.0	577.3	618.4	748.1	923.7	998.0	1066.0	1183.1	1244.7	1254.2
15°	359.0	425.5	602.6	662.7	830.3	1034.3	1116.6	1200.4	1309.6	1353.8	1365.0
17.5°	325.8	409.7	626.3	689.6	893.6	1134.0	1217.8	1287.5	1376.0	1406.1	1413.9
20°	284.7	384.4	642.1	724.4	960.0	1206.8	1287.5	1341.2	1401.3	1420.3	1423.5
22.5°	254.6	357.4	651.6	737.0	1004.3	1251.0	1319.1	1361.8	1402.9	1409.3	1410.8
25°	229.4	327.4	650.1	751.2	1042.3	1277.9	1330.2	1361.8	1385.5	1388.7	1388.7
27.5°	205.6	294.2	643.7	754.4	1070.7	1284.3	1325.4	1347.6	1358.6	1365.0	1365.0
30°	185.1	262.6	627.9	748.1	1083.4	1277.9	1311.1	1322.2	1333.3	1342.8	1347.6
32.5°	169.3	232.5	604.2	735.4	1085.0	1262.1	1285.9	1292.1	1308.0	1330.2	1338.0
35°	155.0	202.5	577.3	718.0	1075.5	1236.8	1252.6	1259.0	1290.5	1323.8	1334.9
37.5°	140.8	180.3	542.5	688.0	1061.3	1206.8	1217.8	1229.0	1277.9	1317.5	1330.2
40°	126.6	161.3	501.4	654.8	1039.1	1170.3	1179.9	1197.3	1262.1	1308.0	1320.6
42.5°	115.4	145.5	457.1	620.0	1010.6	1129.3	1143.5	1168.8	1243.2	1292.1	1306.4
45°	106.0	129.7	409.7	572.5	974.2	1086.6	1107.2	1141.9	1221.0	1268.5	1281.1
47.5°	96.5	118.6	360.6	523.5	934.7	1043.9	1070.7	1110.3	1190.9	1236.8	1247.9
50°	88.6	107.6	311.5	471.3	892.0	998.0	1029.7	1070.7	1153.0	1195.7	1210.0
52.5°	82.3	98.1	265.7	419.1	843.0	950.5	987.0	1029.7	1107.2	1148.3	1157.7
55°	75.9	90.1	226.2	363.8	792.4	899.9	939.5	980.6	1056.5	1091.3	1097.6
57.5°	72.7	83.8	192.9	311.5	738.6	843.0	887.3	925.3	996.4	1023.3	1029.7
60°	68.0	79.1	167.7	267.3	680.1	789.3	827.2	865.2	925.3	947.4	952.1
62.5°	63.3	75.9	148.7	224.6	620.0	726.0	763.9	798.7	849.4	865.2	871.4
65°	60.1	72.7	134.4	192.9	558.3	659.5	697.5	727.6	768.7	784.5	787.7
67.5°	56.9	69.6	123.4	166.1	496.6	593.1	621.6	650.1	681.7	697.5	699.1
70°	52.2	66.5	113.8	147.1	433.3	517.2	540.9	570.9	596.2	604.2	609.0
72.5°	49.1	61.7	107.6	132.8	368.6	444.5	466.6	484.0	506.1	514.0	514.0
75°	44.3	55.3	101.2	118.6	302.1	363.8	382.8	400.1	417.5	420.7	415.9
77.5°	39.5	49.1	87.0	99.6	235.6	287.9	303.7	313.1	327.4	330.5	332.1
80°	33.2	42.7	68.0	77.5	170.8	211.9	223.0	230.9	243.6	243.6	246.8
82.5°	25.3	33.2	49.1	55.3	115.4	145.5	155.0	159.7	167.7	167.7	167.7
85°	15.8	20.6	31.6	36.4	69.6	88.6	94.9	96.5	102.8	104.4	104.4
87.5°	7.9	11.0	20.6	22.2	36.4	45.9	45.9	49.1	49.1	47.5	45.9
90°	2.0	3.5	5.0	5.4	8.5	12.6	14.7	13.0	9.7	7.3	7.3
92.5°	7.7	20.8	33.9	37.2	52.3	72.3	82.4	72.3	51.9	36.6	35.1
95°	18.5	42.4	66.5	72.4	128.6	203.5	241.0	215.0	163.1	124.2	119.8
97.5°	32.0	53.1	74.2	79.5	173.2	298.2	360.6	344.3	311.4	286.9	278.4
100°	42.3	61.5	80.8	85.5	189.5	328.1	397.4	398.7	401.1	402.9	392.9
102.5°	51.2	69.2	87.0	91.5	196.9	337.5	407.8	428.7	470.5	501.8	493.2
105°	66.3	81.4	96.6	100.4	202.5	338.6	406.7	453.5	547.2	617.5	612.9
107.5°	81.7	95.8	109.9	113.5	203.5	323.6	383.6	448.9	579.6	677.6	678.7
110°	92.1	104.8	117.6	120.8	202.0	310.2	364.3	437.3	583.4	693.0	697.8



TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	102.3	114.4	126.6	129.6	202.0	298.5	346.8	421.6	571.0	683.2	690.6
115°	117.7	128.9	140.1	142.9	203.9	285.1	325.7	397.7	541.8	649.8	660.0
117.5°	132.9	143.1	153.3	155.8	207.7	276.8	311.4	376.3	506.2	603.7	615.0
120°	141.8	151.4	161.0	163.4	210.8	274.0	305.6	364.9	483.7	572.8	583.8
122.5°	150.5	160.2	169.8	172.3	215.2	272.5	301.1	354.5	461.6	541.8	552.6
125°	163.8	172.5	181.3	183.6	221.2	271.3	296.3	341.7	432.6	500.7	510.7
127.5°	174.5	183.5	192.4	194.6	227.1	270.6	292.3	331.3	409.2	467.7	476.1
130°	180.3	189.9	199.5	201.9	231.5	271.0	290.7	325.5	394.9	447.0	454.7
132.5°	186.3	195.9	205.4	207.9	235.1	271.3	289.4	320.4	382.6	429.2	436.2
135°	195.2	203.9	212.6	214.8	238.9	271.0	287.0	313.0	365.1	404.2	410.1
137.5°	204.2	212.8	221.5	223.7	244.7	272.7	286.7	308.6	352.7	385.7	390.6
140°	211.7	219.7	227.7	229.7	248.2	272.9	285.3	304.3	342.4	370.9	375.5
142.5°	217.5	224.9	232.2	234.1	251.2	273.9	285.3	302.0	335.4	360.4	364.3
145°	226.4	232.7	239.2	240.8	255.0	274.0	283.4	297.0	324.3	344.8	347.8
147.5°	235.3	241.5	247.7	249.3	260.7	275.8	283.4	294.2	315.7	331.7	334.3
150°	241.0	246.6	252.3	253.7	263.6	276.8	283.4	292.5	310.6	324.2	326.3
152.5°	246.9	251.2	255.5	256.6	265.5	277.4	283.4	291.2	306.7	318.3	319.8
155°	255.8	259.0	262.2	262.9	269.8	278.8	283.4	289.6	301.9	311.2	312.2
157.5°	262.4	265.5	268.5	269.3	274.0	280.2	283.4	288.2	297.8	305.0	305.7
160°	266.9	269.2	271.6	272.2	275.9	280.9	283.4	287.5	295.7	301.9	302.3
162.5°	271.3	273.0	274.8	275.3	278.0	281.6	283.4	286.9	293.8	299.0	299.4
165°	276.1	277.7	279.4	279.8	281.0	282.6	283.4	285.8	290.8	294.5	294.9
167.5°	280.5	281.3	282.0	282.2	283.2	284.6	285.3	287.0	290.2	292.7	292.8
170°	283.4	284.2	284.9	285.1	285.2	285.3	285.3	287.0	290.2	292.7	292.7
172.5°	284.9	285.1	285.3	285.3	285.3	285.3	285.3	286.6	289.1	291.1	290.9
175°	287.0	287.0	287.0	287.0	286.5	285.6	285.3	286.1	287.8	289.0	289.0
177.5°	287.0	287.0	287.0	287.0	286.6	286.0	285.7	286.4	287.7	288.6	288.5
180°	287.0	287.0	287.0	287.0	287.0	287.0	287.0	287.0	287.0	287.0	287.0



TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	491.8	491.8
2.5°	525.1	521.9
5°	675.3	678.5
7.5°	909.5	907.9
10°	1130.8	1145.1
12.5°	1292.1	1295.3
15°	1390.3	1396.5
17.5°	1428.2	1429.8
20°	1429.8	1426.6
22.5°	1412.3	1409.3
25°	1391.8	1390.3
27.5°	1372.8	1374.4
30°	1365.0	1369.7
32.5°	1365.0	1372.8
35°	1368.1	1376.0
37.5°	1366.5	1376.0
40°	1360.2	1371.2
42.5°	1342.8	1350.7
45°	1315.9	1325.4
47.5°	1281.1	1287.5
50°	1236.8	1243.2
52.5°	1181.5	1183.1
55°	1115.0	1121.4
57.5°	1043.9	1045.5
60°	964.8	969.6
62.5°	881.0	881.0
65°	792.4	795.5
67.5°	700.7	708.6
70°	607.4	609.0
72.5°	515.6	515.6
75°	420.7	422.3
77.5°	330.5	330.5
80°	245.2	246.8
82.5°	169.3	172.4
85°	106.0	106.0
87.5°	49.1	44.3
90°	7.3	7.3
92.5°	29.3	23.5
95°	102.2	84.6
97.5°	244.9	211.3
100°	352.9	312.8
102.5°	459.0	424.8
105°	594.5	576.1
107.5°	683.1	687.6
110°	716.9	736.1



TEST NUMBER: P936935

CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	720.0	749.4
115°	700.8	741.7
117.5°	660.4	705.7
120°	627.7	671.8
122.5°	596.1	639.4
125°	550.6	590.6
127.5°	509.9	543.6
130°	486.0	517.1
132.5°	464.1	492.0
135°	434.3	458.3
137.5°	410.2	430.0
140°	393.9	412.3
142.5°	380.2	396.1
145°	359.9	371.8
147.5°	344.2	354.1
150°	334.3	342.4
152.5°	325.8	331.9
155°	316.2	320.2
157.5°	308.5	311.4
160°	304.0	305.6
162.5°	301.0	302.5
165°	296.6	298.3
167.5°	293.5	294.2
170°	292.7	292.7
172.5°	290.3	289.8
175°	289.0	289.0
177.5°	287.8	287.0
180°	287.0	287.0



TEST NUMBER: P936935
 CATALOG NUMBER: SQ4-FB-050U-125D-92765-1D-UNV-STD-W-4-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.69	8.79	8.48	9.60	10.60	20.83	21.93	21.62	22.74	23.74
	3H	8.42	9.40	9.21	10.23	11.26	22.67	23.66	23.47	24.49	25.51
	4H	8.72	9.66	9.54	10.49	11.53	23.32	24.25	24.13	25.09	26.13
	6H	8.99	9.85	9.82	10.69	11.75	23.75	24.61	24.58	25.45	26.51
	8H	9.06	9.89	9.90	10.75	11.80	23.87	24.70	24.71	25.56	26.61
	12H	9.09	9.88	9.93	10.73	11.81	23.94	24.73	24.78	25.58	26.66
4H	2H	14.91	15.85	15.73	16.68	17.72	21.14	22.07	21.96	22.90	23.94
	3H	16.50	17.29	17.34	18.15	19.21	23.19	23.97	24.02	24.84	25.89
	4H	16.61	17.32	17.45	18.19	19.27	23.95	24.67	24.80	25.53	26.62
	6H	16.63	17.26	17.50	18.14	19.23	24.50	25.12	25.36	26.00	27.09
	8H	16.62	17.20	17.48	18.08	19.18	24.66	25.24	25.52	26.12	27.22
	12H	16.59	17.11	17.47	18.01	19.12	24.75	25.28	25.64	26.18	27.29
8H	4H	18.06	18.64	18.93	19.53	20.63	24.04	24.62	24.90	25.50	26.60
	6H	18.32	18.80	19.21	19.72	20.82	24.66	25.15	25.56	26.07	27.17
	8H	18.34	18.77	19.24	19.68	20.80	24.88	25.31	25.78	26.23	27.34
	12H	18.32	18.70	19.23	19.61	20.77	25.03	25.41	25.94	26.32	27.48
12H	4H	18.22	18.74	19.10	19.64	20.75	24.00	24.53	24.89	25.43	26.53
	6H	18.57	19.00	19.48	19.92	21.04	24.65	25.08	25.55	26.00	27.11
	8H	18.66	19.03	19.56	19.94	21.11	24.88	25.26	25.79	26.17	27.34