

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521435

Luminaire Tested: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521435
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-39)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7636.5 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 71.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521435

CATALOG NUMBER: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P521435

CATALOG NUMBER: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	96	92	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	73	88	81	75	70	72	68	64	65	61	58	58	55	53	49
3	85	75	67	61	80	71	64	58	64	58	53	57	53	49	51	47	45	41
4	77	66	58	51	73	63	55	49	56	50	45	51	46	42	45	41	38	35
5	71	59	50	44	67	56	48	42	50	44	39	45	40	36	41	37	33	30
6	65	53	44	38	62	50	42	37	45	39	34	41	36	32	37	33	29	26
7	61	48	39	33	57	45	38	32	41	35	30	37	32	28	34	29	26	23
8	56	43	35	30	53	41	34	29	38	31	27	34	29	25	31	26	23	21
9	52	40	32	26	49	38	31	26	35	28	24	31	26	22	28	24	21	19
10	49	36	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17403	17403	17403
5°	17547	17432	17364
10°	17498	17391	17322
15°	17444	17335	17286
20°	17362	17251	17169
25°	17233	17138	17022
30°	17098	17042	16866
35°	16922	16863	16654
40°	16724	16662	16463
45°	16538	16431	16174
50°	16278	16143	15951
55°	15978	15828	15579
60°	15675	15389	15122
65°	15068	14751	14457
70°	14319	13817	13650
75°	12947	12576	12355
80°	10664	10664	10499
85°	7558	8649	9093

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16538 cd/sqm

TEST NUMBER: P521435

CATALOG NUMBER: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.5	2.3
10°-20°	511.3	6.7
20°-30°	773.2	10.1
30°-40°	931.4	12.2
40°-50°	967.0	12.7
50°-60°	876.6	11.5
60°-70°	668.7	8.8
70°-80°	374.0	4.9
80°-90°	97.2	1.3
90°-100°	165.7	2.2
100°-110°	471.4	6.2
110°-120°	451.7	5.9
120°-130°	357.5	4.7
130°-140°	286.9	3.8
140°-150°	224.6	2.9
150°-160°	164.4	2.2
160°-170°	101.8	1.3
170°-180°	34.5	0.5
0°-30°	1463.1	19.2
0°-40°	2394.4	31.4
0°-60°	4238.0	55.5
0°-90°	5378.0	70.4
90°-120°	1088.8	14.3
90°-150°	1957.8	25.6
90°-180°	2259.0	29.6
0°-180°	7636.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1886	1886	1886	1886	1886	
5°	1895	1875	1882	1877	1875	180
15°	1826	1808	1815	1813	1810	515
25°	1693	1676	1684	1671	1672	780
35°	1502	1490	1497	1481	1479	939
45°	1268	1260	1259	1244	1240	977
55°	993	991	984	972	968	887
65°	690	686	676	667	662	684
75°	363	357	353	348	347	384
85°	71	78	82	82	86	89
90°	0	0	0	0	0	3
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	

TEST NUMBER: P521435

CATALOG NUMBER: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1886.3	1886.3	1886.3	1886.3	1886.3
2.5°	1897.9	1882.5	1887.1	1883.7	1877.2
5°	1894.6	1875.4	1882.2	1876.9	1874.9
7.5°	1880.1	1862.1	1867.9	1864.7	1862.3
10°	1867.7	1850.5	1856.3	1853.1	1849.0
12.5°	1853.6	1835.6	1842.2	1837.4	1835.8
15°	1826.3	1808.1	1814.9	1812.8	1809.7
17.5°	1793.2	1774.8	1781.8	1777.6	1775.2
20°	1768.3	1749.1	1757.0	1748.7	1748.7
22.5°	1740.2	1721.0	1730.5	1718.1	1720.5
25°	1692.8	1675.6	1683.5	1671.1	1672.1
27.5°	1641.3	1625.1	1635.3	1619.3	1618.7
30°	1604.9	1588.7	1599.7	1582.1	1583.1
32.5°	1564.3	1550.5	1559.9	1543.2	1542.6
35°	1502.4	1490.3	1497.2	1480.6	1478.6
37.5°	1435.0	1426.0	1429.0	1413.2	1412.4
40°	1388.6	1380.5	1383.4	1366.9	1366.9
42.5°	1341.4	1334.1	1336.2	1318.0	1318.0
45°	1267.5	1260.5	1259.3	1243.6	1239.6
47.5°	1188.7	1183.0	1179.4	1165.3	1163.4
50°	1134.1	1130.0	1124.7	1112.3	1111.3
52.5°	1076.9	1075.3	1069.3	1056.0	1055.0
55°	993.3	991.3	984.0	971.5	968.5
57.5°	905.8	903.8	895.2	883.0	879.9
60°	849.5	843.4	834.0	822.5	819.5
62.5°	788.3	781.4	771.9	761.3	760.7
65°	690.2	686.1	675.7	667.3	662.2
67.5°	597.9	588.8	578.4	571.6	570.5
70°	530.8	521.7	512.2	507.0	506.0
72.5°	463.8	456.3	447.6	442.4	442.2
75°	363.2	357.1	352.8	347.6	346.6
77.5°	263.6	262.0	260.3	254.7	254.7
80°	200.7	200.7	200.7	197.6	197.6
82.5°	144.4	148.5	148.6	147.1	147.1
85°	71.4	78.5	81.7	81.8	85.9
87.5°	19.9	27.2	32.3	33.2	35.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P521435

CATALOG NUMBER: SQ4-F-050U-125D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	116.5	146.7	382.3	835.7	955.2
115°	136.2	164.6	364.3	771.7	906.2
117.5°	153.5	180.1	353.6	701.8	844.3
120°	167.3	189.6	352.5	661.9	798.4
122.5°	178.3	200.6	349.8	626.8	753.6
125°	192.2	213.1	347.7	577.0	689.9
127.5°	207.2	226.8	346.6	547.2	640.2
130°	215.0	234.6	344.9	526.5	607.6
132.5°	223.3	242.3	344.9	510.3	584.9
135°	235.0	254.6	343.5	487.4	550.9
137.5°	246.1	265.1	343.4	468.0	522.9
140°	254.4	274.0	342.9	451.9	504.6
142.5°	263.8	280.1	344.5	439.0	486.4
145°	277.2	291.4	346.3	421.8	459.7
147.5°	288.7	302.4	349.4	404.4	437.1
150°	298.6	308.1	350.5	398.7	421.7
152.5°	306.4	316.4	351.6	390.9	412.3
155°	316.6	324.0	354.6	381.2	396.8
157.5°	329.3	333.8	355.3	376.8	387.9
160°	335.9	339.3	358.1	373.5	382.9
162.5°	339.8	343.7	358.6	370.7	378.0
165°	349.8	351.1	358.8	366.5	371.9
167.5°	356.5	355.3	361.9	365.4	367.6
170°	358.8	358.1	360.8	361.6	364.3
172.5°	363.7	361.4	362.5	360.5	362.6
175°	366.4	364.3	362.9	360.8	358.1
177.5°	367.5	364.2	362.5	360.3	360.8
180°	363.6	363.6	363.6	363.6	363.6

(END OF REPORT)