

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937131

Luminaire Tested: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937131
REPORT IS A COMBINATION OF REPORTS P933502 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4613.9 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937131
CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2465	2465	2465
5°	2405	2847	3313
10°	2179	4147	5493
15°	1850	5413	6632
20°	1504	6269	6759
25°	1253	6555	6622
30°	1055	6592	6610
35°	932	6477	6781
40°	810	6330	6957
45°	732	6220	6985
50°	670	6119	6868
55°	640	5977	6565
60°	653	5706	6084
65°	677	5299	5423
70°	716	4612	4581
75°	784	3750	3576
80°	838	2591	2408
85°	704	1367	1232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6985 cd/sqm



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.4	0.7
10°-20°	152.3	3.3
20°-30°	266.4	5.8
30°-40°	342.9	7.4
40°-50°	383.0	8.3
50°-60°	366.8	8.0
60°-70°	290.7	6.3
70°-80°	170.9	3.7
80°-90°	49.0	1.1
90°-100°	192.3	4.2
100°-110°	505.6	11.0
110°-120°	524.2	11.4
120°-130°	420.5	9.1
130°-140°	329.9	7.2
140°-150°	253.2	5.5
150°-160°	182.4	4.0
160°-170°	111.6	2.4
170°-180°	37.7	0.8
0°-30°	453.0	9.8
0°-40°	795.9	17.3
0°-60°	1545.8	33.5
0°-90°	2056.4	44.6
90°-120°	1222.1	26.5
90°-150°	2225.8	48.2
90°-180°	2557.0	55.4
0°-180°	4613.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	266	266	266	266	266	
5°	259	278	313	354	366	24
15°	194	358	603	731	754	54
25°	124	406	718	750	751	57
35°	84	388	676	715	743	52
45°	57	309	598	685	716	44
55°	41	196	507	589	606	37
65°	32	104	377	424	430	32
75°	24	64	207	227	228	25
85°	8	20	51	56	57	9
90°	3	7	20	10	10	3
95°	26	100	331	171	116	28
105°	91	138	559	849	792	97
115°	162	196	448	893	1019	160
125°	225	252	407	688	812	200
135°	268	295	394	556	630	208
145°	311	331	390	474	511	195
155°	352	361	390	428	440	162
165°	379	384	390	405	410	107
175°	394	394	392	397	397	37
180°	394	394	394	394	394	



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6
2.5°	265.6	265.6	267.3	268.2	269.9	270.8	272.5	274.2	279.3	280.2	281.9
5°	258.8	262.2	273.3	277.6	289.5	305.8	312.6	323.7	346.8	353.6	357.9
7.5°	248.6	256.2	283.6	290.4	320.3	363.0	380.9	404.9	441.6	459.5	474.0
10°	232.3	248.6	297.2	313.5	362.2	427.1	460.4	493.7	549.2	574.0	583.4
12.5°	214.4	240.9	311.8	334.0	404.0	498.8	539.0	575.7	638.9	672.2	677.3
15°	193.9	229.8	325.4	357.9	448.4	558.6	603.0	648.3	707.2	731.1	737.1
17.5°	176.0	221.2	338.2	372.4	482.6	612.4	657.7	695.3	743.1	759.3	763.6
20°	153.7	207.6	346.8	391.2	518.5	651.7	695.3	724.3	756.8	767.0	768.7
22.5°	137.5	193.0	351.9	398.0	542.4	675.6	712.3	735.4	757.6	761.0	761.9
25°	123.8	176.8	351.0	405.7	562.9	690.1	718.3	735.4	748.2	749.9	749.9
27.5°	111.0	158.9	347.6	407.4	578.2	693.6	715.8	727.7	733.7	737.1	737.1
30°	99.9	141.8	339.1	404.0	585.1	690.1	708.1	714.1	720.0	725.2	727.7
32.5°	91.4	125.6	326.3	397.2	585.9	681.6	694.4	697.8	706.4	718.3	722.6
35°	83.7	109.3	311.8	387.8	580.8	667.9	676.5	679.9	697.0	714.9	720.9
37.5°	76.0	97.4	293.0	371.5	573.1	651.7	657.7	663.7	690.1	711.5	718.3
40°	68.3	87.1	270.8	353.6	561.2	632.1	637.2	646.6	681.6	706.4	713.2
42.5°	62.4	78.6	246.8	334.8	545.8	609.8	617.5	631.2	671.3	697.8	705.5
45°	57.2	70.0	221.2	309.2	526.1	586.8	597.9	616.7	659.4	685.0	691.8
47.5°	52.1	64.1	194.7	282.7	504.8	563.7	578.2	599.6	643.2	667.9	673.9
50°	47.8	58.1	168.3	254.5	481.7	539.0	556.0	578.2	622.7	645.7	653.4
52.5°	44.4	53.0	143.5	226.3	455.3	513.3	533.0	556.0	597.9	620.1	625.2
55°	41.0	48.7	122.1	196.4	427.9	486.0	507.4	529.6	570.6	589.3	592.8
57.5°	39.3	45.3	104.2	168.3	398.9	455.3	479.2	499.7	538.1	552.6	556.0
60°	36.7	42.7	90.5	144.3	367.3	426.2	446.7	467.2	499.7	511.6	514.2
62.5°	34.2	41.0	80.3	121.3	334.8	392.0	412.5	431.3	458.7	467.2	470.6
65°	32.5	39.3	72.6	104.2	301.5	356.2	376.7	392.9	415.1	423.6	425.4
67.5°	30.7	37.6	66.6	89.7	268.2	320.3	335.7	351.0	368.1	376.7	377.5
70°	28.2	35.9	61.5	79.4	234.0	279.3	292.1	308.3	322.0	326.3	328.8
72.5°	26.5	33.3	58.1	71.7	199.0	240.0	252.0	261.4	273.3	277.6	277.6
75°	23.9	29.9	54.7	64.1	163.1	196.4	206.7	216.1	225.5	227.2	224.6
77.5°	21.4	26.5	47.0	53.8	127.3	155.5	164.0	169.1	176.8	178.5	179.4
80°	17.9	23.1	36.7	41.9	92.2	114.5	120.4	124.7	131.5	131.5	133.2
82.5°	13.7	17.9	26.5	29.9	62.4	78.6	83.7	86.3	90.5	90.5	90.5
85°	8.5	11.1	17.1	19.6	37.6	47.8	51.2	52.1	55.5	56.4	56.4
87.5°	4.3	6.0	11.1	12.0	19.6	24.8	24.8	26.5	26.5	25.6	24.8
90°	2.6	4.8	6.9	7.4	11.7	17.3	20.2	17.9	13.4	10.1	10.1
92.5°	10.6	28.6	46.5	51.1	71.8	99.5	113.3	99.3	71.3	50.3	48.3
95°	25.5	58.4	91.4	99.6	176.8	279.7	331.2	295.5	224.2	170.7	164.7
97.5°	44.0	73.0	102.1	109.3	238.1	409.8	495.7	473.1	428.1	394.3	382.7
100°	58.3	84.6	111.0	117.5	260.4	451.0	546.2	547.8	551.2	553.6	539.9
102.5°	70.5	95.1	119.6	125.7	270.7	464.0	560.6	589.3	646.7	689.7	677.9
105°	91.1	111.9	132.7	137.9	278.3	465.4	558.9	623.3	752.1	848.6	842.3
107.5°	112.2	131.7	151.1	156.0	279.7	444.7	527.2	616.9	796.5	931.2	932.7
110°	126.6	144.1	161.7	166.0	277.6	426.3	500.7	601.0	801.8	952.4	958.9



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	140.6	157.3	174.0	178.2	277.7	410.3	476.6	579.4	784.8	938.9	949.0
115°	161.8	177.1	192.6	196.4	280.2	391.9	447.7	546.7	744.6	893.1	907.1
117.5°	182.7	196.7	210.7	214.2	285.4	380.3	427.8	517.2	695.8	829.8	845.3
120°	194.9	208.1	221.2	224.6	289.6	376.5	419.9	501.5	664.8	787.2	802.3
122.5°	206.8	220.1	233.3	236.7	295.7	374.4	413.8	487.3	634.3	744.5	759.5
125°	225.1	237.2	249.3	252.3	304.0	372.8	407.2	469.7	594.6	688.2	701.9
127.5°	239.9	252.1	264.4	267.4	312.2	371.9	401.7	455.3	562.5	642.9	654.5
130°	247.9	261.0	274.2	277.5	318.2	372.4	399.6	447.3	542.7	614.3	625.0
132.5°	256.1	269.2	282.4	285.7	323.0	372.8	397.7	440.4	525.9	589.9	599.5
135°	268.2	280.2	292.2	295.2	328.3	372.5	394.5	430.3	501.9	555.5	563.8
137.5°	280.7	292.5	304.4	307.4	336.3	374.8	394.0	424.2	484.7	530.1	536.8
140°	291.0	301.9	312.9	315.6	341.1	375.1	392.1	418.3	470.5	509.7	516.0
142.5°	298.9	309.0	319.1	321.7	345.2	376.5	392.1	415.1	461.0	495.4	500.9
145°	311.1	320.0	328.8	331.0	350.4	376.5	389.5	408.3	445.8	474.0	478.1
147.5°	323.3	331.8	340.5	342.6	358.2	379.1	389.5	404.3	433.8	455.9	459.4
150°	331.2	339.0	346.8	348.7	362.3	380.4	389.5	402.0	426.9	445.6	448.3
152.5°	339.4	345.3	351.2	352.7	365.0	381.3	389.5	400.2	421.4	437.4	439.4
155°	351.6	356.0	360.3	361.4	370.8	383.2	389.5	397.9	414.8	427.6	428.9
157.5°	360.6	364.9	369.2	370.2	376.6	385.2	389.5	396.1	409.2	419.1	420.1
160°	366.7	370.0	373.3	374.1	379.2	386.1	389.5	395.1	406.5	414.9	415.4
162.5°	372.8	375.3	377.8	378.4	382.1	387.0	389.5	394.3	403.7	410.9	411.4
165°	379.4	381.6	383.8	384.4	386.2	388.4	389.5	392.9	399.7	404.9	405.5
167.5°	385.5	386.5	387.6	387.9	389.3	391.2	392.1	394.4	398.9	402.2	402.5
170°	389.5	390.5	391.6	391.9	392.0	392.0	392.1	394.4	398.9	402.2	402.2
172.5°	391.6	391.9	392.0	392.1	392.1	392.1	392.1	393.9	397.4	400.1	399.9
175°	394.5	394.5	394.5	394.5	393.8	392.6	392.1	393.2	395.5	397.2	397.2
177.5°	394.5	394.5	394.5	394.5	393.9	393.1	392.6	393.5	395.3	396.7	396.4
180°	394.5	394.5	394.5	394.5	394.5	394.5	394.5	394.5	394.5	394.5	394.5



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	265.6	265.6
2.5°	283.6	281.9
5°	364.7	366.4
7.5°	491.1	490.3
10°	610.7	618.4
12.5°	697.8	699.5
15°	750.8	754.2
17.5°	771.3	772.1
20°	772.1	770.4
22.5°	762.7	761.0
25°	751.6	750.8
27.5°	741.4	742.2
30°	737.1	739.7
32.5°	737.1	741.4
35°	738.8	743.1
37.5°	738.0	743.1
40°	734.6	740.5
42.5°	725.2	729.4
45°	710.6	715.8
47.5°	691.8	695.3
50°	667.9	671.3
52.5°	638.0	638.9
55°	602.2	605.6
57.5°	563.7	564.6
60°	521.0	523.6
62.5°	475.7	475.7
65°	427.9	429.6
67.5°	378.4	382.6
70°	328.0	328.8
72.5°	278.4	278.4
75°	227.2	228.1
77.5°	178.5	178.5
80°	132.4	133.2
82.5°	91.4	93.1
85°	57.2	57.2
87.5°	26.5	23.9
90°	10.1	10.1
92.5°	40.3	32.3
95°	140.5	116.2
97.5°	336.6	290.5
100°	485.0	430.0
102.5°	630.9	583.8
105°	817.0	791.7
107.5°	938.9	945.0
110°	985.3	1011.7



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	989.5	1030.0
115°	963.3	1019.4
117.5°	907.6	969.9
120°	862.8	923.2
122.5°	819.1	878.8
125°	756.8	811.8
127.5°	700.8	747.2
130°	667.8	710.6
132.5°	637.9	676.2
135°	596.9	629.9
137.5°	563.9	591.0
140°	541.3	566.6
142.5°	522.6	544.3
145°	494.5	511.0
147.5°	473.0	486.7
150°	459.4	470.5
152.5°	447.8	456.2
155°	434.5	440.0
157.5°	424.0	427.8
160°	417.7	419.9
162.5°	413.6	415.7
165°	407.7	409.9
167.5°	403.4	404.3
170°	402.2	402.2
172.5°	399.0	398.2
175°	397.2	397.2
177.5°	395.5	394.5
180°	394.5	394.5



TEST NUMBER: P937131

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.61	4.46	4.60	5.47	6.81	16.75	17.59	17.74	18.61	19.95
	3H	4.31	5.08	5.32	6.10	7.46	18.57	19.33	19.58	20.35	21.72
	4H	4.61	5.33	5.63	6.36	7.73	19.20	19.93	20.22	20.95	22.32
	6H	4.86	5.53	5.89	6.56	7.94	19.62	20.29	20.65	21.32	22.70
	8H	4.93	5.57	5.96	6.61	7.99	19.74	20.37	20.77	21.41	22.80
	12H	4.95	5.55	5.99	6.59	8.00	19.80	20.40	20.84	21.44	22.84
4H	2H	10.80	11.52	11.82	12.54	13.92	17.02	17.74	18.05	18.77	20.14
	3H	12.37	12.97	13.40	14.02	15.41	19.05	19.66	20.08	20.71	22.09
	4H	12.46	13.02	13.50	14.06	15.47	19.81	20.36	20.85	21.40	22.81
	6H	12.47	12.95	13.52	14.02	15.42	20.33	20.81	21.38	21.88	23.28
	8H	12.45	12.89	13.50	13.95	15.37	20.49	20.93	21.54	21.99	23.41
	12H	12.40	12.81	13.47	13.88	15.31	20.57	20.98	21.64	22.05	23.47
8H	4H	13.89	14.34	14.95	15.40	16.82	19.87	20.31	20.92	21.37	22.79
	6H	14.14	14.51	15.21	15.61	17.02	20.48	20.85	21.56	21.95	23.37
	8H	14.15	14.48	15.24	15.56	17.00	20.69	21.02	21.78	22.10	23.54
	12H	14.12	14.41	15.21	15.49	16.96	20.83	21.12	21.92	22.20	23.67
12H	4H	14.03	14.44	15.10	15.51	16.94	19.82	20.22	20.89	21.30	22.72
	6H	14.39	14.72	15.47	15.80	17.24	20.47	20.79	21.55	21.88	23.31
	8H	14.46	14.75	15.55	15.83	17.30	20.69	20.97	21.78	22.05	23.53