

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521565

Luminaire Tested: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521565
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-37)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7755.7 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521565
CATALOG NUMBER: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P521565

CATALOG NUMBER: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79		63	63	63		48	48	48	42
1	96	91	88	84	87	84	80	77	69	66	64		55	54	52		43	42	41	35
2	87	80	74	68	79	73	68	63	60	56	53		48	46	43		37	36	34	29
3	79	70	63	57	72	64	58	53	53	48	44		43	39	36		33	31	29	24
4	72	62	54	48	66	57	50	44	47	42	38		38	34	31		29	27	25	21
5	66	55	47	41	60	50	43	38	42	36	32		34	30	27		26	24	21	18
6	61	49	41	35	55	45	38	33	38	32	28		30	26	23		24	21	19	16
7	56	44	36	31	51	41	34	29	34	29	25		28	24	21		22	19	17	14
8	52	40	32	27	48	37	30	25	31	26	22		25	21	18		20	17	15	12
9	49	36	29	24	44	34	27	22	28	23	19		23	19	16		18	15	13	11
10	45	33	26	21	41	31	24	20	26	21	17		21	17	15		17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10482	10482	10482
5°	10561	10522	10465
10°	10586	10508	10460
15°	10476	10437	10387
20°	10454	10383	10373
25°	10365	10344	10228
30°	10296	10229	10153
35°	10150	10139	10011
40°	10057	10007	9945
45°	9937	9882	9774
50°	9802	9727	9594
55°	9621	9503	9370
60°	9394	9241	9069
65°	9082	8877	8719
70°	8514	8317	8122
75°	7671	7450	7340
80°	6270	6323	6211
85°	4488	5145	5145

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9937 cd/sqm

TEST NUMBER: P521565

CATALOG NUMBER: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	1.4
10°-20°	307.9	4.0
20°-30°	465.8	6.0
30°-40°	560.3	7.2
40°-50°	581.7	7.5
50°-60°	527.0	6.8
60°-70°	400.9	5.2
70°-80°	222.8	2.9
80°-90°	57.4	0.7
90°-100°	331.9	4.3
100°-110°	944.4	12.2
110°-120°	904.8	11.7
120°-130°	716.1	9.2
130°-140°	574.8	7.4
140°-150°	450.0	5.8
150°-160°	329.3	4.2
160°-170°	203.9	2.6
170°-180°	69.2	0.9
0°-30°	881.4	11.4
0°-40°	1441.6	18.6
0°-60°	2550.3	32.9
0°-90°	3231.4	41.7
90°-120°	2181.1	28.1
90°-150°	3921.9	50.6
90°-180°	4524.0	58.3
0°-180°	7755.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1136	1136	1136	1136	1136	
5°	1140	1130	1136	1131	1130	108
15°	1097	1088	1093	1092	1088	310
25°	1018	1009	1016	1006	1005	469
35°	901	897	900	890	889	565
45°	762	756	757	749	749	588
55°	598	597	591	586	582	534
65°	416	410	407	400	399	410
75°	215	212	209	207	206	228
85°	42	46	49	49	49	52
90°	0	0	0	0	0	3
95°	36	143	642	222	137	41
105°	147	223	962	1700	1616	155
115°	273	330	730	1546	1815	269
125°	385	427	696	1156	1382	345
135°	471	510	688	976	1104	363
145°	555	584	694	845	921	347
155°	634	649	710	764	795	293
165°	701	703	719	734	745	197
175°	734	730	727	723	717	70
180°	728	728	728	728	728	

TEST NUMBER: P521565

CATALOG NUMBER: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1136.1	1136.1	1136.1	1136.1	1136.1
2.5°	1143.6	1133.9	1137.0	1134.4	1132.0
5°	1140.3	1130.1	1136.1	1130.9	1129.9
7.5°	1134.9	1122.9	1125.8	1124.7	1124.7
10°	1129.9	1114.7	1121.6	1116.5	1116.5
12.5°	1116.7	1103.9	1109.2	1106.6	1108.2
15°	1096.8	1087.7	1092.7	1091.5	1087.5
17.5°	1079.6	1068.7	1072.4	1070.5	1068.9
20°	1064.7	1054.6	1057.5	1052.4	1056.5
22.5°	1048.2	1038.1	1043.4	1034.9	1034.9
25°	1018.2	1009.1	1016.1	1005.7	1004.7
27.5°	986.3	980.4	985.1	977.3	974.5
30°	966.4	957.3	960.2	955.0	953.0
32.5°	943.3	934.1	937.0	927.8	929.0
35°	901.2	897.2	900.2	889.8	888.8
37.5°	863.2	855.1	859.9	851.4	850.5
40°	835.0	826.9	830.9	825.7	825.7
42.5°	809.4	800.5	802.7	795.9	793.4
45°	761.6	756.5	757.4	749.1	749.1
47.5°	714.4	710.7	709.2	700.8	702.4
50°	682.9	676.8	677.7	668.4	668.4
52.5°	646.5	646.9	643.0	636.9	632.0
55°	598.1	597.1	590.8	585.6	582.5
57.5°	546.3	541.7	537.2	530.2	529.6
60°	509.1	506.0	500.8	494.5	491.5
62.5°	471.0	468.0	462.7	457.3	456.7
65°	416.0	409.9	406.6	400.4	399.4
67.5°	356.2	351.3	347.3	342.3	341.7
70°	315.6	311.5	308.3	304.1	301.1
72.5°	278.3	271.9	268.6	265.3	263.0
75°	215.2	212.2	209.0	206.9	205.9
77.5°	154.4	154.6	154.6	151.9	150.9
80°	118.0	119.0	119.0	117.9	116.9
82.5°	85.7	87.5	88.4	87.3	87.1
85°	42.4	45.5	48.6	48.6	48.6
87.5°	11.6	15.6	19.0	19.8	19.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.1	58.7	136.3	39.7	29.9
95°	36.0	143.0	642.5	222.4	137.1
97.5°	66.2	167.5	989.5	708.1	485.2
100°	87.2	182.0	1064.8	1078.6	830.8
102.5°	110.5	197.7	1048.2	1380.6	1164.3
105°	146.8	222.6	962.4	1699.9	1616.0
107.5°	183.6	251.6	862.1	1789.9	1864.7
110°	209.1	272.7	804.5	1755.5	1923.4

TEST NUMBER: P521565

CATALOG NUMBER: SQ4-F-100U-075D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	233.5	293.8	765.7	1674.0	1913.4
115°	272.8	329.7	729.7	1545.9	1815.4
117.5°	307.4	360.8	708.4	1405.9	1691.3
120°	335.1	379.8	706.2	1325.8	1599.3
122.5°	357.3	401.9	700.7	1255.6	1509.6
125°	385.0	426.9	696.5	1155.8	1381.9
127.5°	415.1	454.4	694.3	1096.2	1282.5
130°	430.6	469.9	691.0	1054.7	1217.2
132.5°	447.3	485.4	691.0	1022.3	1171.7
135°	470.8	510.1	688.2	976.3	1103.6
137.5°	493.0	531.1	687.9	937.5	1047.4
140°	509.6	548.8	686.8	905.2	1010.8
142.5°	528.4	561.2	690.1	879.5	974.3
145°	555.3	583.7	693.7	845.0	920.8
147.5°	578.3	605.9	699.8	810.2	875.7
150°	598.2	617.2	702.0	798.6	844.7
152.5°	613.7	633.7	704.3	783.1	825.8
155°	634.2	649.1	710.4	763.7	794.8
157.5°	659.7	668.6	711.7	754.9	777.1
160°	673.0	679.7	717.3	748.2	767.1
162.5°	680.7	688.6	718.4	742.5	757.2
165°	700.7	703.4	718.7	734.1	745.0
167.5°	714.2	711.8	725.0	732.1	736.4
170°	718.7	717.3	722.8	724.3	729.7
172.5°	728.6	724.0	726.1	722.1	726.4
175°	733.9	729.8	727.0	722.7	717.3
177.5°	736.1	729.6	726.1	721.7	722.8
180°	728.4	728.4	728.4	728.4	728.4

(END OF REPORT)