

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937135

Luminaire Tested: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937135
REPORT IS A COMBINATION OF REPORTS P933502 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5049.2 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937135
CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2697	2697	2697
5°	2632	3115	3626
10°	2385	4538	6011
15°	2025	5924	7258
20°	1646	6861	7397
25°	1371	7174	7247
30°	1156	7214	7233
35°	1020	7088	7420
40°	887	6927	7614
45°	801	6806	7643
50°	733	6697	7517
55°	701	6540	7183
60°	715	6245	6658
65°	740	5799	5935
70°	782	5047	5014
75°	859	4104	3913
80°	917	2836	2636
85°	770	1497	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7643 cd/sqm



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	0.7
10°-20°	166.7	3.3
20°-30°	291.5	5.8
30°-40°	375.3	7.4
40°-50°	419.1	8.3
50°-60°	401.4	8.0
60°-70°	318.1	6.3
70°-80°	187.1	3.7
80°-90°	53.6	1.1
90°-100°	210.4	4.2
100°-110°	553.3	11.0
110°-120°	573.7	11.4
120°-130°	460.2	9.1
130°-140°	361.1	7.2
140°-150°	277.1	5.5
150°-160°	199.6	4.0
160°-170°	122.1	2.4
170°-180°	41.3	0.8
0°-30°	495.8	9.8
0°-40°	871.0	17.3
0°-60°	1691.6	33.5
0°-90°	2250.5	44.6
90°-120°	1337.4	26.5
90°-150°	2435.8	48.2
90°-180°	2799.0	55.4
0°-180°	5049.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	291	291	291	291	291	
5°	283	304	342	387	401	26
15°	212	392	660	800	825	59
25°	136	444	786	821	822	62
35°	92	424	740	782	813	57
45°	63	338	654	750	783	48
55°	45	215	555	645	663	41
65°	36	114	412	464	470	35
75°	26	70	226	249	250	27
85°	9	22	56	62	63	10
90°	3	8	22	11	11	3
95°	28	109	362	187	127	31
105°	100	151	612	929	866	106
115°	177	215	490	977	1116	175
125°	246	276	446	753	888	219
135°	294	323	432	608	689	227
145°	340	362	426	519	559	213
155°	385	396	426	468	482	177
165°	415	421	426	443	449	117
175°	432	432	429	435	435	41
180°	432	432	432	432	432	



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7
2.5°	290.7	290.7	292.6	293.5	295.4	296.3	298.2	300.0	305.6	306.6	308.5
5°	283.2	287.0	299.1	303.8	316.9	334.6	342.1	354.3	379.5	387.0	391.6
7.5°	272.0	280.4	310.3	317.8	350.5	397.3	416.9	443.1	483.2	502.9	518.8
10°	254.2	272.0	325.3	343.0	396.3	467.4	503.8	540.3	601.0	628.1	638.4
12.5°	234.6	263.6	341.2	365.5	442.1	545.9	589.8	630.0	699.2	735.6	741.2
15°	212.2	251.4	356.1	391.6	490.7	611.3	659.9	709.4	773.9	800.1	806.7
17.5°	192.5	242.1	370.1	407.5	528.1	670.2	719.7	760.9	813.2	831.0	835.6
20°	168.2	227.1	379.5	428.1	567.4	713.2	760.9	792.6	828.1	839.4	841.2
22.5°	150.5	211.2	385.1	435.6	593.5	739.4	779.5	804.8	829.1	832.8	833.8
25°	135.5	193.5	384.2	444.0	616.0	755.2	786.1	804.8	818.8	820.7	820.7
27.5°	121.5	173.9	380.4	445.9	632.8	759.0	783.3	796.4	802.9	806.7	806.7
30°	109.4	155.2	371.1	442.1	640.3	755.2	774.9	781.4	788.0	793.6	796.4
32.5°	100.0	137.4	357.1	434.6	641.2	745.9	759.9	763.7	773.0	786.1	790.8
35°	91.6	119.6	341.2	424.4	635.6	730.9	740.3	744.0	762.7	782.3	788.9
37.5°	83.2	106.6	320.6	406.6	627.2	713.2	719.7	726.3	755.2	778.6	786.1
40°	74.8	95.3	296.3	387.0	614.1	691.7	697.3	707.6	745.9	773.0	780.5
42.5°	68.2	86.0	270.1	366.4	597.3	667.4	675.8	690.7	734.7	763.7	772.1
45°	62.6	76.6	242.1	338.4	575.8	642.1	654.3	674.9	721.6	749.6	757.1
47.5°	57.0	70.1	213.1	309.4	552.4	616.9	632.8	656.2	703.8	730.9	737.5
50°	52.3	63.6	184.1	278.5	527.2	589.8	608.5	632.8	681.4	706.6	715.1
52.5°	48.6	58.0	157.0	247.7	498.2	561.8	583.3	608.5	654.3	678.6	684.2
55°	44.9	53.3	133.7	215.0	468.3	531.8	555.2	579.5	624.4	644.9	648.7
57.5°	43.0	49.5	114.0	184.1	436.5	498.2	524.4	546.8	588.9	604.8	608.5
60°	40.2	46.7	99.1	158.0	401.9	466.4	488.9	511.3	546.8	559.9	562.7
62.5°	37.4	44.9	87.9	132.7	366.4	429.0	451.5	472.0	501.9	511.3	515.0
65°	35.5	43.0	79.5	114.0	330.0	389.8	412.2	430.0	454.3	463.6	465.5
67.5°	33.6	41.1	72.9	98.1	293.5	350.5	367.3	384.2	402.9	412.2	413.1
70°	30.8	39.3	67.3	86.9	256.1	305.6	319.7	337.4	352.4	357.1	359.9
72.5°	29.0	36.5	63.6	78.5	217.8	262.7	275.7	286.0	299.1	303.8	303.8
75°	26.2	32.7	59.8	70.1	178.5	215.0	226.2	236.5	246.8	248.6	245.8
77.5°	23.4	29.0	51.4	58.9	139.3	170.1	179.5	185.1	193.5	195.4	196.3
80°	19.6	25.2	40.2	45.8	100.9	125.3	131.8	136.5	143.9	143.9	145.8
82.5°	15.0	19.6	29.0	32.7	68.2	86.0	91.6	94.4	99.1	99.1	99.1
85°	9.3	12.2	18.7	21.5	41.1	52.3	56.1	57.0	60.8	61.7	61.7
87.5°	4.7	6.5	12.2	13.1	21.5	27.1	27.1	29.0	29.0	28.0	27.1
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.6	14.7	11.0	11.0
92.5°	11.6	31.3	50.9	55.9	78.6	108.9	124.0	108.7	78.0	55.1	52.9
95°	27.9	63.9	100.0	109.0	193.5	306.1	362.5	323.4	245.4	186.8	180.2
97.5°	48.1	79.9	111.7	119.6	260.6	448.5	542.4	517.7	468.5	431.5	418.8
100°	63.7	92.5	121.4	128.6	285.0	493.5	597.7	599.5	603.2	605.9	590.8
102.5°	77.1	104.0	130.9	137.6	296.2	507.7	613.4	644.9	707.7	754.8	741.9
105°	99.6	122.4	145.3	151.0	304.5	509.3	611.7	682.1	823.0	928.6	921.7
107.5°	122.8	144.1	165.3	170.7	306.1	486.6	576.9	675.1	871.6	1019.0	1020.7
110°	138.5	157.7	176.9	181.7	303.8	466.5	547.9	657.8	877.4	1042.2	1049.4



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.9	172.2	190.4	195.0	303.9	449.0	521.6	634.0	858.8	1027.4	1038.6
115°	177.0	193.9	210.8	215.0	306.7	428.8	490.0	598.3	814.9	977.3	992.7
117.5°	199.9	215.3	230.6	234.4	312.4	416.2	468.2	566.0	761.4	908.1	925.1
120°	213.3	227.7	242.1	245.7	317.0	412.0	459.5	548.9	727.5	861.4	878.0
122.5°	226.3	240.9	255.4	259.0	323.6	409.8	452.9	533.2	694.1	814.8	831.1
125°	246.3	259.6	272.8	276.1	332.7	408.0	445.7	514.0	650.6	753.1	768.1
127.5°	262.6	275.9	289.3	292.7	341.6	407.0	439.6	498.3	615.6	703.6	716.3
130°	271.3	285.6	300.0	303.7	348.2	407.5	437.3	489.5	593.9	672.2	683.9
132.5°	280.2	294.6	309.0	312.7	353.5	408.0	435.2	481.9	575.5	645.6	656.1
135°	293.5	306.6	319.8	323.0	359.3	407.6	431.7	470.9	549.2	607.9	617.0
137.5°	307.1	320.1	333.1	336.4	368.0	410.1	431.2	464.3	530.4	580.1	587.5
140°	318.5	330.4	342.4	345.4	373.3	410.5	429.1	457.7	514.8	557.7	564.7
142.5°	327.1	338.2	349.2	352.0	377.7	412.0	429.1	454.3	504.5	542.1	548.1
145°	340.4	350.1	359.8	362.2	383.5	412.0	426.2	446.8	487.8	518.7	523.2
147.5°	353.8	363.1	372.6	374.9	392.0	414.8	426.2	442.4	474.7	498.9	502.7
150°	362.5	371.0	379.5	381.6	396.5	416.3	426.2	439.9	467.2	487.6	490.6
152.5°	371.5	377.9	384.4	385.9	399.4	417.3	426.2	437.9	461.2	478.7	480.9
155°	384.8	389.6	394.3	395.5	405.8	419.4	426.2	435.5	454.0	467.9	469.4
157.5°	394.6	399.3	404.0	405.1	412.1	421.6	426.2	433.4	447.8	458.7	459.7
160°	401.3	404.9	408.5	409.4	415.0	422.5	426.2	432.4	444.8	454.1	454.6
162.5°	408.0	410.7	413.4	414.1	418.1	423.5	426.2	431.5	441.8	449.7	450.2
165°	415.2	417.6	420.1	420.7	422.6	425.0	426.2	430.0	437.4	443.1	443.7
167.5°	421.8	423.0	424.2	424.4	426.0	428.1	429.1	431.6	436.5	440.2	440.4
170°	426.2	427.3	428.6	428.8	428.9	429.0	429.1	431.6	436.5	440.2	440.2
172.5°	428.6	428.8	429.0	429.1	429.1	429.1	429.1	431.1	434.9	437.8	437.6
175°	431.7	431.7	431.7	431.7	430.9	429.7	429.1	430.3	432.8	434.6	434.6
177.5°	431.7	431.7	431.7	431.7	431.1	430.2	429.7	430.6	432.6	434.1	433.8
180°	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	290.7	290.7
2.5°	310.3	308.5
5°	399.1	401.0
7.5°	537.5	536.5
10°	668.3	676.7
12.5°	763.7	765.5
15°	821.6	825.3
17.5°	844.0	845.0
20°	845.0	843.1
22.5°	834.7	832.8
25°	822.5	821.6
27.5°	811.3	812.3
30°	806.7	809.5
32.5°	806.7	811.3
35°	808.5	813.2
37.5°	807.6	813.2
40°	803.8	810.4
42.5°	793.6	798.2
45°	777.7	783.3
47.5°	757.1	760.9
50°	730.9	734.7
52.5°	698.2	699.2
55°	659.0	662.7
57.5°	616.9	617.8
60°	570.2	573.0
62.5°	520.6	520.6
65°	468.3	470.2
67.5°	414.1	418.7
70°	358.9	359.9
72.5°	304.7	304.7
75°	248.6	249.6
77.5°	195.4	195.4
80°	144.9	145.8
82.5°	100.0	101.9
85°	62.6	62.6
87.5°	29.0	26.2
90°	11.0	11.0
92.5°	44.1	35.3
95°	153.8	127.2
97.5°	368.4	317.9
100°	530.7	470.5
102.5°	690.4	638.9
105°	894.0	866.4
107.5°	1027.4	1034.2
110°	1078.3	1107.2



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1082.9	1127.2
115°	1054.2	1115.6
117.5°	993.2	1061.4
120°	944.1	1010.3
122.5°	896.4	961.7
125°	828.2	888.3
127.5°	766.9	817.7
130°	730.8	777.7
132.5°	698.0	740.0
135°	653.2	689.3
137.5°	617.1	646.7
140°	592.4	620.1
142.5°	571.9	595.7
145°	541.2	559.2
147.5°	517.6	532.6
150°	502.8	514.9
152.5°	490.1	499.2
155°	475.5	481.6
157.5°	464.0	468.2
160°	457.1	459.5
162.5°	452.6	454.9
165°	446.1	448.6
167.5°	441.5	442.5
170°	440.2	440.2
172.5°	436.7	435.8
175°	434.6	434.6
177.5°	432.8	431.7
180°	431.7	431.7



TEST NUMBER: P937135

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-4-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.92	4.77	4.91	5.78	7.12	17.06	17.91	18.05	18.92	20.26
	3H	4.63	5.39	5.63	6.41	7.77	18.88	19.64	19.89	20.67	22.03
	4H	4.92	5.65	5.94	6.67	8.04	19.52	20.24	20.54	21.26	22.63
	6H	5.17	5.84	6.20	6.87	8.25	19.94	20.60	20.96	21.63	23.01
	8H	5.24	5.88	6.28	6.92	8.30	20.05	20.68	21.08	21.73	23.11
	12H	5.26	5.86	6.30	6.90	8.31	20.11	20.71	21.15	21.75	23.16
4H	2H	11.11	11.83	12.13	12.86	14.23	17.33	18.06	18.36	19.08	20.45
	3H	12.68	13.28	13.71	14.34	15.72	19.36	19.97	20.40	21.02	22.41
	4H	12.77	13.33	13.81	14.37	15.78	20.12	20.67	21.16	21.72	23.13
	6H	12.78	13.26	13.84	14.33	15.73	20.65	21.12	21.70	22.19	23.59
	8H	12.76	13.21	13.81	14.27	15.69	20.80	21.25	21.85	22.31	23.73
	12H	12.72	13.12	13.79	14.19	15.62	20.89	21.29	21.96	22.36	23.79
8H	4H	14.21	14.65	15.26	15.71	17.13	20.18	20.63	21.23	21.69	23.11
	6H	14.45	14.82	15.52	15.92	17.34	20.80	21.17	21.87	22.27	23.68
	8H	14.47	14.79	15.55	15.88	17.31	21.01	21.33	22.09	22.42	23.85
	12H	14.43	14.72	15.52	15.80	17.28	21.14	21.43	22.23	22.51	23.99
12H	4H	14.35	14.75	15.42	15.82	17.25	20.13	20.54	21.20	21.61	23.03
	6H	14.70	15.03	15.79	16.11	17.55	20.78	21.11	21.86	22.19	23.63
	8H	14.77	15.06	15.86	16.14	17.61	21.00	21.29	22.09	22.37	23.84