

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937146

Luminaire Tested: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937146
REPORT IS A COMBINATION OF REPORTS P933518 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9827.7 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937146
CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2625	2625	2625
5°	2564	3034	3529
10°	2326	4423	5850
15°	1977	5779	7064
20°	1610	6696	7199
25°	1343	7007	7053
30°	1132	7052	7040
35°	1001	6935	7222
40°	872	6783	7410
45°	790	6671	7439
50°	725	6570	7315
55°	694	6424	6992
60°	710	6141	6479
65°	739	5713	5775
70°	787	4982	4879
75°	872	4062	3807
80°	953	2817	2566
85°	848	1495	1313

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7439 cd/sqm



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	0.7
10°-20°	324.4	3.3
20°-30°	567.4	5.8
30°-40°	730.4	7.4
40°-50°	815.9	8.3
50°-60°	781.4	8.0
60°-70°	619.2	6.3
70°-80°	364.1	3.7
80°-90°	104.4	1.1
90°-100°	409.6	4.2
100°-110°	1076.9	11.0
110°-120°	1116.6	11.4
120°-130°	895.6	9.1
130°-140°	702.8	7.2
140°-150°	539.4	5.5
150°-160°	388.5	4.0
160°-170°	237.7	2.4
170°-180°	80.3	0.8
0°-30°	965.0	9.8
0°-40°	1695.4	17.3
0°-60°	3292.7	33.5
0°-90°	4380.4	44.6
90°-120°	2603.1	26.5
90°-150°	4740.9	48.2
90°-180°	5447.0	55.4
0°-180°	9827.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	551	591	666	753	780	51
15°	413	762	1284	1557	1606	115
25°	264	864	1530	1597	1599	122
35°	178	826	1441	1523	1583	111
45°	122	659	1274	1459	1525	94
55°	87	418	1081	1255	1290	80
65°	69	222	802	902	915	69
75°	51	136	440	484	486	53
85°	18	42	109	120	122	19
90°	6	16	43	22	22	6
95°	54	212	706	364	248	60
105°	194	294	1190	1807	1686	206
115°	345	418	954	1902	2171	340
125°	479	537	867	1466	1729	426
135°	571	629	840	1183	1342	442
145°	663	705	830	1010	1088	415
155°	749	770	830	911	937	344
165°	808	819	830	862	873	228
175°	840	840	835	846	846	80
180°	840	840	840	840	840	



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	565.8	565.8	565.8	565.8	565.8	565.8	565.8	565.8	565.8	565.8	565.8
2.5°	565.8	565.8	569.4	571.3	574.9	576.7	580.3	584.0	594.9	596.7	600.4
5°	551.2	558.5	582.2	591.3	616.7	651.3	665.9	689.5	738.6	753.2	762.3
7.5°	529.4	545.8	604.0	618.6	682.2	773.2	811.4	862.3	940.6	978.8	1009.7
10°	494.8	529.4	633.1	667.7	771.4	909.6	980.6	1051.6	1169.9	1222.6	1242.7
12.5°	456.6	513.0	664.0	711.3	860.5	1062.5	1148.1	1226.3	1360.9	1431.9	1442.8
15°	413.0	489.4	693.1	762.3	955.1	1189.9	1284.5	1380.9	1506.4	1557.4	1570.1
17.5°	374.8	471.2	720.4	793.2	1027.9	1304.5	1400.9	1481.0	1582.9	1617.4	1626.5
20°	327.5	442.1	738.6	833.2	1104.4	1388.2	1481.0	1542.8	1612.0	1633.8	1637.4
22.5°	292.9	411.2	749.5	847.8	1155.3	1439.1	1517.4	1566.5	1613.8	1621.1	1622.9
25°	263.8	376.6	747.7	864.2	1199.0	1470.1	1530.1	1566.5	1593.8	1597.4	1597.4
27.5°	236.5	338.4	740.4	867.8	1231.7	1477.3	1524.6	1550.1	1562.8	1570.1	1570.1
30°	212.9	302.0	722.3	860.5	1246.3	1470.1	1508.3	1521.0	1533.7	1544.7	1550.1
32.5°	194.7	267.4	695.0	846.0	1248.1	1451.9	1479.2	1486.4	1504.6	1530.1	1539.2
35°	178.3	232.9	664.0	826.0	1237.2	1422.8	1441.0	1448.2	1484.6	1522.8	1535.6
37.5°	161.9	207.4	624.0	791.4	1220.8	1388.2	1400.9	1413.7	1470.1	1515.5	1530.1
40°	145.5	185.6	576.7	753.2	1195.4	1346.4	1357.3	1377.3	1451.9	1504.6	1519.2
42.5°	132.8	167.4	525.8	713.2	1162.6	1299.1	1315.4	1344.5	1430.0	1486.4	1502.8
45°	121.9	149.2	471.2	658.6	1120.8	1249.9	1273.6	1313.6	1404.6	1459.1	1473.7
47.5°	111.0	136.4	414.8	602.2	1075.3	1200.8	1231.7	1277.2	1370.0	1422.8	1435.5
50°	101.9	123.7	358.4	542.1	1026.1	1148.1	1184.4	1231.7	1326.3	1375.5	1391.8
52.5°	94.6	112.8	305.6	482.1	969.7	1093.5	1135.3	1184.4	1273.6	1320.9	1331.8
55°	87.3	103.7	260.2	418.4	911.5	1035.3	1080.7	1128.0	1215.4	1255.4	1262.7
57.5°	83.7	96.4	222.0	358.4	849.6	969.7	1020.6	1064.4	1146.2	1177.2	1184.4
60°	78.2	91.0	192.8	307.5	782.3	907.8	951.5	995.1	1064.4	1089.8	1095.3
62.5°	72.8	87.3	171.0	258.3	713.2	835.0	878.7	918.7	977.0	995.1	1002.4
65°	69.1	83.7	154.6	222.0	642.2	758.6	802.3	836.9	884.2	902.4	906.0
67.5°	65.5	80.0	141.9	191.0	571.3	682.2	715.0	747.7	784.1	802.3	804.1
70°	60.0	76.4	131.0	169.2	498.5	594.9	622.2	656.8	685.9	695.0	700.4
72.5°	56.4	71.0	123.7	152.8	423.9	511.2	536.7	556.7	582.2	591.3	591.3
75°	50.9	63.7	116.4	136.4	347.5	418.4	440.3	460.3	480.3	483.9	478.5
77.5°	45.5	56.4	100.1	114.6	271.1	331.1	349.3	360.2	376.6	380.2	382.0
80°	38.2	49.1	78.2	89.1	196.5	243.8	256.5	265.6	280.2	280.2	283.8
82.5°	29.1	38.2	56.4	63.7	132.8	167.4	178.3	183.7	192.8	192.8	192.8
85°	18.2	23.7	36.4	41.8	80.0	101.9	109.2	111.0	118.3	120.1	120.1
87.5°	9.1	12.7	23.7	25.5	41.8	52.8	52.8	56.4	56.4	54.6	52.8
90°	5.6	10.2	14.7	15.8	24.8	36.8	42.8	38.1	28.6	21.5	21.5
92.5°	22.6	60.9	99.3	108.9	153.1	211.9	241.4	211.6	151.9	107.2	102.9
95°	54.1	124.3	194.5	212.0	376.5	595.8	705.5	629.6	477.7	363.8	350.8
97.5°	93.6	155.5	217.5	233.0	507.2	872.9	1055.7	1007.7	911.7	839.8	815.2
100°	124.1	180.2	236.4	250.4	554.8	960.6	1163.4	1167.0	1174.0	1179.3	1150.0
102.5°	150.0	202.4	254.8	267.9	576.5	988.1	1193.9	1255.0	1377.4	1469.2	1444.0
105°	194.0	238.4	282.7	293.8	592.7	991.2	1190.5	1327.6	1601.8	1807.4	1794.0
107.5°	239.1	280.5	321.8	332.2	595.7	947.1	1122.9	1314.1	1696.6	1983.5	1986.7
110°	269.6	306.9	344.2	353.6	591.2	908.0	1066.5	1280.2	1707.8	2028.6	2042.6



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	299.5	335.0	370.6	379.5	591.4	873.9	1015.2	1234.0	1671.6	1999.8	2021.4
115°	344.6	377.4	410.2	418.4	596.8	834.7	953.7	1164.4	1586.0	1902.2	1932.2
117.5°	389.1	419.0	448.8	456.3	608.0	810.2	911.4	1101.6	1482.1	1767.4	1800.5
120°	415.1	443.1	471.2	478.2	616.9	801.9	894.4	1068.3	1415.9	1676.6	1708.8
122.5°	440.4	468.8	497.1	504.2	629.9	797.6	881.4	1038.0	1351.1	1585.9	1617.6
125°	479.4	505.2	531.0	537.4	647.4	794.0	867.3	1000.3	1266.2	1465.7	1495.0
127.5°	510.9	537.0	563.1	569.6	664.9	792.0	855.5	969.7	1198.0	1369.3	1393.9
130°	527.9	555.9	584.0	591.0	677.7	793.3	851.1	952.7	1156.0	1308.4	1331.3
132.5°	545.3	573.4	601.5	608.5	688.0	794.0	847.1	938.0	1120.0	1256.5	1276.9
135°	571.3	596.8	622.5	628.8	699.3	793.3	840.3	916.6	1068.9	1183.2	1200.8
137.5°	597.8	623.1	648.4	654.8	716.2	798.2	839.1	903.5	1032.4	1129.0	1143.4
140°	619.8	643.1	666.4	672.2	726.5	799.0	835.2	890.9	1002.1	1085.7	1099.1
142.5°	636.7	658.3	679.9	685.2	735.3	801.9	835.2	884.1	981.9	1055.2	1066.7
145°	662.7	681.5	700.2	705.0	746.5	801.9	829.6	869.6	949.6	1009.5	1018.2
147.5°	688.6	706.9	725.3	729.8	763.1	807.4	829.6	861.1	923.9	971.1	978.4
150°	705.5	722.1	738.6	742.7	771.6	810.3	829.6	856.2	909.3	949.1	955.0
152.5°	723.0	735.5	748.1	751.2	777.3	812.1	829.6	852.2	897.6	931.7	936.1
155°	748.9	758.2	767.5	769.8	789.7	816.3	829.6	847.6	883.7	910.8	913.7
157.5°	768.1	777.1	786.1	788.4	802.1	820.4	829.6	843.6	871.7	892.7	894.8
160°	781.1	788.1	795.1	796.8	807.8	822.3	829.6	841.6	865.7	883.7	884.9
162.5°	794.0	799.3	804.6	805.9	813.9	824.3	829.6	839.8	860.1	875.3	876.3
165°	808.1	812.9	817.7	818.9	822.4	827.2	829.6	836.9	851.4	862.3	863.5
167.5°	821.1	823.4	825.7	826.2	829.2	833.2	835.2	840.0	849.5	856.7	857.2
170°	829.6	831.9	834.1	834.7	834.9	835.1	835.2	840.0	849.5	856.7	856.7
172.5°	834.1	834.6	835.1	835.2	835.2	835.2	835.2	839.0	846.5	852.1	851.7
175°	840.3	840.3	840.3	840.3	838.6	836.3	835.2	837.6	842.4	846.0	846.0
177.5°	840.3	840.3	840.3	840.3	839.0	837.2	836.3	838.2	842.0	844.8	844.3
180°	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	565.8	565.8
2.5°	604.0	600.4
5°	776.8	780.5
7.5°	1046.2	1044.4
10°	1300.9	1317.2
12.5°	1486.4	1490.1
15°	1599.2	1606.5
17.5°	1642.9	1644.7
20°	1644.7	1641.1
22.5°	1624.7	1621.1
25°	1601.1	1599.2
27.5°	1579.2	1581.0
30°	1570.1	1575.6
32.5°	1570.1	1579.2
35°	1573.8	1582.9
37.5°	1571.9	1582.9
40°	1564.7	1577.4
42.5°	1544.7	1553.8
45°	1513.7	1524.6
47.5°	1473.7	1481.0
50°	1422.8	1430.0
52.5°	1359.1	1360.9
55°	1282.7	1290.0
57.5°	1200.8	1202.6
60°	1109.8	1115.3
62.5°	1013.3	1013.3
65°	911.5	915.1
67.5°	805.9	815.0
70°	698.6	700.4
72.5°	593.1	593.1
75°	483.9	485.7
77.5°	380.2	380.2
80°	282.0	283.8
82.5°	194.7	198.3
85°	121.9	121.9
87.5°	56.4	50.9
90°	21.5	21.5
92.5°	85.9	68.8
95°	299.3	247.6
97.5°	716.9	618.6
100°	1033.0	915.9
102.5°	1343.8	1243.6
105°	1740.0	1686.2
107.5°	1999.7	2012.8
110°	2098.8	2154.9



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2107.5	2193.8
115°	2051.7	2171.2
117.5°	1933.2	2065.8
120°	1837.7	1966.5
122.5°	1744.7	1871.8
125°	1612.1	1729.1
127.5°	1492.7	1591.5
130°	1422.4	1513.6
132.5°	1358.6	1440.3
135°	1271.2	1341.6
137.5°	1201.1	1258.8
140°	1153.1	1206.9
142.5°	1113.1	1159.5
145°	1053.4	1088.5
147.5°	1007.4	1036.5
150°	978.6	1002.1
152.5°	953.8	971.7
155°	925.6	937.3
157.5°	903.1	911.4
160°	889.7	894.4
162.5°	880.9	885.4
165°	868.2	873.0
167.5°	859.2	861.2
170°	856.7	856.7
172.5°	850.0	848.2
175°	846.0	846.0
177.5°	842.3	840.3
180°	840.3	840.3



TEST NUMBER: P937146

CATALOG NUMBER: SQ4-FB-075U-075D-92765-1D-UNV-STD-W-8-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.84	4.69	4.84	5.70	7.05	17.02	17.87	18.01	18.88	20.22
	3H	4.55	5.31	5.55	6.33	7.69	18.86	19.62	19.86	20.64	22.00
	4H	4.84	5.57	5.86	6.59	7.96	19.50	20.23	20.52	21.25	22.62
	6H	5.09	5.76	6.12	6.79	8.17	19.93	20.60	20.96	21.63	23.01
	8H	5.16	5.80	6.20	6.84	8.22	20.05	20.69	21.09	21.73	23.11
	12H	5.18	5.78	6.22	6.82	8.23	20.12	20.72	21.16	21.76	23.17
4H	2H	11.06	11.78	12.08	12.80	14.17	17.29	18.02	18.32	19.04	20.41
	3H	12.62	13.23	13.66	14.28	15.66	19.34	19.94	20.37	20.99	22.38
	4H	12.72	13.27	13.76	14.31	15.72	20.10	20.66	21.14	21.70	23.11
	6H	12.73	13.20	13.78	14.27	15.67	20.64	21.12	21.69	22.19	23.59
	8H	12.70	13.15	13.75	14.21	15.63	20.80	21.25	21.86	22.31	23.73
	12H	12.66	13.06	13.73	14.14	15.56	20.90	21.30	21.97	22.37	23.80
8H	4H	14.16	14.61	15.21	15.67	17.08	20.16	20.61	21.21	21.67	23.09
	6H	14.40	14.77	15.48	15.87	17.29	20.79	21.16	21.87	22.26	23.68
	8H	14.42	14.74	15.50	15.83	17.26	21.01	21.34	22.09	22.42	23.86
	12H	14.39	14.67	15.47	15.75	17.23	21.15	21.44	22.24	22.52	24.00
12H	4H	14.30	14.71	15.37	15.78	17.20	20.11	20.52	21.19	21.59	23.02
	6H	14.66	14.99	15.74	16.07	17.51	20.77	21.10	21.86	22.18	23.62
	8H	14.73	15.01	15.82	16.09	17.57	21.00	21.29	22.09	22.37	23.85