

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521626

Luminaire Tested: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521626
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-38)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9182.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521626
CATALOG NUMBER: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P521626

CATALOG NUMBER: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																				
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	44	43	42	36																				
2	87	80	74	69	79	73	68	63	61	57	53	49	46	44	38	36	35	30																				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	29	25																				
4	73	62	54	48	66	57	50	45	47	42	38	38	35	31	30	27	25	21																				
5	67	55	47	41	61	51	43	38	42	37	33	34	30	27	27	24	22	18																				
6	61	49	41	35	56	45	38	33	38	32	28	31	27	24	24	21	19	16																				
7	57	44	36	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14																				
8	52	40	32	27	48	37	30	25	31	26	22	26	21	18	20	17	15	13																				
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	19	16	14	11																				
10	45	33	26	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12711	12711	12711
5°	12812	12733	12697
10°	12799	12710	12674
15°	12739	12666	12639
20°	12681	12625	12550
25°	12583	12535	12398
30°	12475	12445	12292
35°	12349	12306	12177
40°	12226	12180	12029
45°	12084	11984	11846
50°	11879	11796	11659
55°	11712	11543	11403
60°	11440	11210	11051
65°	11071	10756	10590
70°	10426	10092	9911
75°	9414	9176	9037
80°	7778	7778	7678
85°	5473	6277	6479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12084 cd/sqm

TEST NUMBER: P521626

CATALOG NUMBER: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.4	1.4
10°-20°	373.6	4.1
20°-30°	565.0	6.2
30°-40°	680.4	7.4
40°-50°	706.6	7.7
50°-60°	640.5	7.0
60°-70°	487.8	5.3
70°-80°	272.6	3.0
80°-90°	70.7	0.8
90°-100°	385.4	4.2
100°-110°	1096.7	11.9
110°-120°	1050.8	11.4
120°-130°	831.6	9.1
130°-140°	667.5	7.3
140°-150°	522.6	5.7
150°-160°	382.4	4.2
160°-170°	236.8	2.6
170°-180°	80.4	0.9
0°-30°	1069.1	11.6
0°-40°	1749.5	19.1
0°-60°	3096.6	33.7
0°-90°	3927.7	42.8
90°-120°	2532.9	27.6
90°-150°	4554.7	49.6
90°-180°	5254.0	57.2
0°-180°	9182.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1383	1370	1375	1371	1371	131
15°	1334	1322	1326	1323	1323	376
25°	1236	1226	1231	1222	1218	569
35°	1096	1090	1093	1082	1081	686
45°	926	920	918	909	908	713
55°	728	725	718	709	709	649
65°	507	502	493	486	485	500
75°	264	260	257	254	254	279
85°	52	55	59	60	61	64
90°	0	0	0	0	0	4
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P521626

CATALOG NUMBER: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1377.7	1377.7	1377.7	1377.7	1377.7
2.5°	1386.1	1374.9	1378.5	1376.1	1371.6
5°	1383.4	1370.3	1374.8	1371.0	1371.0
7.5°	1373.9	1361.3	1364.3	1362.0	1362.0
10°	1366.2	1352.2	1356.7	1352.8	1352.8
12.5°	1354.0	1341.4	1345.9	1342.1	1341.3
15°	1333.7	1321.5	1326.0	1323.2	1323.2
17.5°	1309.2	1297.6	1303.5	1298.8	1297.3
20°	1291.6	1278.5	1285.9	1278.2	1278.2
22.5°	1270.2	1258.6	1265.2	1256.0	1254.5
25°	1236.1	1225.8	1231.3	1221.7	1217.9
27.5°	1197.8	1186.8	1195.0	1184.2	1182.1
30°	1171.0	1160.8	1168.2	1156.6	1153.8
32.5°	1142.0	1133.2	1138.3	1127.6	1125.5
35°	1096.4	1089.9	1092.6	1082.0	1081.1
37.5°	1048.0	1041.6	1044.2	1032.5	1031.7
40°	1015.1	1009.5	1011.3	998.8	998.8
42.5°	981.4	975.1	975.3	963.6	962.9
45°	926.1	920.5	918.5	908.9	907.9
47.5°	867.4	864.8	861.6	852.1	852.1
50°	827.6	825.7	821.8	812.3	812.3
52.5°	787.0	785.9	780.5	772.4	770.9
55°	728.1	725.3	717.6	708.9	708.9
57.5°	663.6	661.3	652.7	645.8	644.1
60°	620.0	616.2	607.5	599.9	598.9
62.5°	574.8	571.8	562.4	555.4	553.8
65°	507.1	501.5	492.7	486.0	485.1
67.5°	435.5	429.1	421.5	415.9	414.1
70°	386.5	380.9	374.1	369.3	367.4
72.5°	338.3	332.7	326.6	323.4	323.0
75°	264.1	260.3	257.4	253.5	253.5
77.5°	191.5	189.3	187.7	185.8	185.8
80°	146.4	146.4	146.4	144.5	144.5
82.5°	105.0	107.3	108.9	107.7	107.7
85°	51.7	55.4	59.3	60.3	61.2
87.5°	14.5	19.0	23.7	24.5	25.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P521626

CATALOG NUMBER: SQ4-F-125U-100D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)