

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937248

Luminaire Tested: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937248
REPORT IS A COMBINATION OF REPORTS P933519 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11809.0 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 102.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937248
CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3646	3646	3646
5°	3562	4214	4901
10°	3231	6143	8125
15°	2746	8026	9811
20°	2236	9300	9999
25°	1865	9732	9795
30°	1573	9794	9777
35°	1391	9631	10030
40°	1211	9420	10291
45°	1097	9265	10332
50°	1006	9126	10160
55°	963	8921	9710
60°	986	8530	8999
65°	1026	7934	8022
70°	1094	6920	6776
75°	1213	5642	5289
80°	1325	3913	3564
85°	1174	2077	1824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10332 cd/sqm



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	0.9
10°-20°	450.5	3.8
20°-30°	788.1	6.7
30°-40°	1014.5	8.6
40°-50°	1133.1	9.6
50°-60°	1085.3	9.2
60°-70°	860.1	7.3
70°-80°	505.8	4.3
80°-90°	143.9	1.2
90°-100°	430.6	3.6
100°-110°	1132.0	9.6
110°-120°	1173.7	9.9
120°-130°	941.5	8.0
130°-140°	738.7	6.3
140°-150°	567.0	4.8
150°-160°	408.3	3.5
160°-170°	249.8	2.1
170°-180°	84.4	0.7
0°-30°	1340.3	11.3
0°-40°	2354.7	19.9
0°-60°	4573.1	38.7
0°-90°	6082.8	51.5
90°-120°	2736.3	23.2
90°-150°	4983.6	42.2
90°-180°	5726.0	48.5
0°-180°	11809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	766	821	925	1046	1084	71
15°	574	1059	1784	2163	2231	160
25°	366	1200	2125	2219	2221	169
35°	248	1147	2001	2115	2198	155
45°	169	915	1769	2027	2118	131
55°	121	581	1501	1744	1792	111
65°	96	308	1114	1253	1271	95
75°	71	190	612	672	675	74
85°	25	58	152	167	169	27
90°	6	17	45	23	23	7
95°	57	223	742	382	260	63
105°	204	309	1252	1900	1772	216
115°	362	440	1002	2000	2282	358
125°	504	565	912	1541	1818	447
135°	600	661	883	1244	1410	465
145°	697	741	872	1061	1144	436
155°	787	809	872	957	985	362
165°	850	861	872	906	918	240
175°	883	883	878	889	889	84
180°	883	883	883	883	883	



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9
2.5°	785.9	785.9	791.0	793.4	798.5	801.0	806.1	811.1	826.3	828.8	833.9
5°	765.6	775.8	808.7	821.3	856.7	904.7	924.8	957.7	1025.9	1046.2	1058.8
7.5°	735.3	758.1	839.0	859.1	947.6	1073.9	1127.0	1197.7	1306.4	1359.5	1402.4
10°	687.3	735.3	879.4	927.4	1071.4	1263.4	1362.0	1460.6	1624.8	1698.1	1725.8
12.5°	634.2	712.6	922.3	988.0	1195.2	1475.7	1594.5	1703.2	1890.1	1988.7	2003.8
15°	573.6	679.8	962.8	1058.8	1326.6	1652.6	1784.0	1917.9	2092.2	2163.0	2180.7
17.5°	520.6	654.5	1000.7	1101.7	1427.7	1811.8	1945.8	2056.9	2198.4	2246.4	2259.1
20°	454.9	614.1	1025.9	1157.3	1533.8	1928.1	2056.9	2142.8	2238.8	2269.1	2274.2
22.5°	406.9	571.0	1041.1	1177.6	1604.6	1998.8	2107.4	2175.6	2241.4	2251.5	2254.0
25°	366.4	523.0	1038.5	1200.3	1665.2	2041.8	2125.1	2175.6	2213.6	2218.7	2218.7
27.5°	328.5	470.0	1028.5	1205.4	1710.7	2051.9	2117.6	2153.0	2170.7	2180.7	2180.7
30°	295.7	419.5	1003.1	1195.2	1730.9	2041.8	2094.8	2112.5	2130.2	2145.3	2153.0
32.5°	270.4	371.5	965.3	1175.0	1733.5	2016.5	2054.4	2064.5	2089.8	2125.1	2137.8
35°	247.7	323.5	922.3	1147.2	1718.3	1976.1	2001.3	2011.4	2061.9	2115.0	2132.7
37.5°	224.9	288.1	866.7	1099.2	1695.5	1928.1	1945.8	1963.4	2041.8	2104.9	2125.1
40°	202.1	257.8	801.0	1046.2	1660.1	1869.9	1885.0	1912.9	2016.5	2089.8	2109.9
42.5°	184.4	232.5	730.2	990.5	1614.7	1804.2	1827.0	1867.3	1986.1	2064.5	2087.3
45°	169.3	207.2	654.5	914.7	1556.6	1736.0	1768.9	1824.4	1950.7	2026.6	2046.8
47.5°	154.1	189.5	576.1	836.4	1493.4	1667.8	1710.7	1773.9	1902.7	1976.1	1993.8
50°	141.5	171.8	497.8	753.0	1425.2	1594.5	1645.0	1710.7	1842.1	1910.4	1933.0
52.5°	131.4	156.6	424.5	669.6	1346.8	1518.6	1576.8	1645.0	1768.9	1834.6	1849.7
55°	121.2	144.0	361.3	581.2	1266.0	1437.8	1500.9	1566.7	1688.0	1743.5	1753.7
57.5°	116.3	134.0	308.3	497.8	1180.0	1346.8	1417.6	1478.3	1592.0	1634.9	1645.0
60°	108.6	126.3	267.8	427.0	1086.6	1260.9	1321.6	1382.2	1478.3	1513.7	1521.2
62.5°	101.1	121.2	237.5	358.9	990.5	1159.9	1220.5	1276.1	1356.9	1382.2	1392.3
65°	96.0	116.3	214.8	308.3	892.0	1053.7	1114.3	1162.3	1228.0	1253.4	1258.4
67.5°	90.9	111.2	197.1	265.3	793.4	947.6	993.1	1038.5	1089.1	1114.3	1116.9
70°	83.4	106.1	182.0	235.0	692.4	826.3	864.2	912.2	952.7	965.3	972.8
72.5°	78.3	98.6	171.8	212.3	588.7	710.1	745.4	773.3	808.7	821.3	821.3
75°	70.8	88.4	161.7	189.5	482.7	581.2	611.5	639.3	667.1	672.2	664.6
77.5°	63.2	78.3	138.9	159.2	376.5	459.9	485.2	500.3	523.0	528.1	530.7
80°	53.1	68.3	108.6	123.8	272.9	338.6	356.3	368.9	389.2	389.2	394.2
82.5°	40.4	53.1	78.3	88.4	184.4	232.5	247.7	255.2	267.8	267.8	267.8
85°	25.2	32.9	50.6	58.1	111.2	141.5	151.7	154.1	164.3	166.8	166.8
87.5°	12.6	17.7	32.9	35.4	58.1	73.2	73.2	78.3	78.3	75.8	73.2
90°	5.9	10.7	15.5	16.6	26.1	38.7	45.0	40.1	30.0	22.6	22.6
92.5°	23.7	64.1	104.4	114.5	160.9	222.8	253.8	222.4	159.7	112.6	108.1
95°	56.9	130.7	204.4	222.9	395.8	626.3	741.6	661.8	502.1	382.4	368.8
97.5°	98.4	163.5	228.6	244.9	533.2	917.6	1109.8	1059.3	958.4	882.8	856.9
100°	130.4	189.4	248.5	263.2	583.2	1009.7	1223.0	1226.7	1234.1	1239.6	1208.8
102.5°	157.7	212.8	267.8	281.6	606.0	1038.7	1255.0	1319.3	1447.9	1544.3	1518.0
105°	204.0	250.6	297.2	308.9	623.1	1042.0	1251.5	1395.6	1683.8	1900.0	1885.8
107.5°	251.4	294.9	338.3	349.2	626.2	995.6	1180.3	1381.3	1783.4	2085.0	2088.4
110°	283.4	322.6	361.8	371.7	621.4	954.5	1121.0	1345.7	1795.3	2132.4	2147.1



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	314.8	352.2	389.6	398.9	621.6	918.6	1067.1	1297.2	1757.2	2102.2	2124.9
115°	362.2	396.7	431.2	439.8	627.4	877.4	1002.5	1224.0	1667.2	1999.6	2031.0
117.5°	409.1	440.4	471.8	479.6	639.1	851.7	958.0	1157.9	1557.9	1857.9	1892.7
120°	436.3	465.8	495.3	502.7	648.5	843.0	940.2	1123.0	1488.4	1762.5	1796.3
122.5°	463.0	492.8	522.6	530.0	662.2	838.4	926.6	1091.1	1420.2	1667.0	1700.4
125°	503.9	531.1	558.1	564.9	680.5	834.7	911.7	1051.5	1331.0	1540.7	1571.5
127.5°	537.1	564.5	591.9	598.8	699.0	832.6	899.3	1019.3	1259.3	1439.4	1465.3
130°	554.9	584.3	613.9	621.2	712.4	833.9	894.6	1001.4	1215.1	1375.4	1399.4
132.5°	573.2	602.8	632.3	639.7	723.3	834.7	890.4	986.0	1177.4	1320.8	1342.3
135°	600.5	627.4	654.3	661.0	735.1	833.9	883.3	963.5	1123.6	1243.7	1262.3
137.5°	628.4	655.0	681.6	688.3	752.9	839.1	882.1	949.8	1085.3	1186.8	1201.9
140°	651.5	676.0	700.5	706.6	763.7	839.9	878.0	936.5	1053.4	1141.2	1155.4
142.5°	669.3	692.0	714.7	720.3	772.9	843.0	878.0	929.3	1032.1	1109.2	1121.3
145°	696.6	716.4	736.1	741.0	784.7	843.0	872.0	914.1	998.2	1061.2	1070.4
147.5°	723.8	743.1	762.4	767.2	802.2	848.7	872.0	905.1	971.2	1020.8	1028.5
150°	741.6	759.0	776.4	780.7	811.1	851.8	872.0	900.0	955.8	997.7	1003.9
152.5°	760.0	773.2	786.4	789.6	817.1	853.7	872.0	895.9	943.6	979.3	984.0
155°	787.2	797.0	806.7	809.2	830.2	858.1	872.0	891.0	928.9	957.4	960.5
157.5°	807.4	816.9	826.3	828.7	843.2	862.4	872.0	886.8	916.3	938.4	940.6
160°	821.1	828.4	835.8	837.6	849.1	864.4	872.0	884.7	910.0	928.9	930.2
162.5°	834.7	840.2	845.8	847.2	855.5	866.5	872.0	882.8	904.1	920.0	921.2
165°	849.5	854.5	859.5	860.8	864.5	869.6	872.0	879.7	895.0	906.5	907.7
167.5°	863.2	865.5	867.9	868.5	871.7	875.9	878.0	882.9	893.0	900.5	901.0
170°	872.0	874.4	876.8	877.4	877.6	877.9	878.0	882.9	893.0	900.5	900.5
172.5°	876.8	877.3	877.9	878.0	878.0	878.0	878.0	881.9	889.8	895.8	895.3
175°	883.3	883.3	883.3	883.3	881.5	879.1	878.0	880.5	885.5	889.3	889.3
177.5°	883.3	883.3	883.3	883.3	881.9	880.1	879.1	881.1	885.1	888.0	887.5
180°	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	785.9	785.9
2.5°	839.0	833.9
5°	1079.0	1084.0
7.5°	1452.9	1450.4
10°	1806.7	1829.5
12.5°	2064.5	2069.6
15°	2221.1	2231.3
17.5°	2281.8	2284.3
20°	2284.3	2279.3
22.5°	2256.5	2251.5
25°	2223.7	2221.1
27.5°	2193.3	2195.9
30°	2180.7	2188.3
32.5°	2180.7	2193.3
35°	2185.8	2198.4
37.5°	2183.3	2198.4
40°	2173.1	2190.8
42.5°	2145.3	2157.9
45°	2102.4	2117.6
47.5°	2046.8	2056.9
50°	1976.1	1986.1
52.5°	1887.6	1890.1
55°	1781.5	1791.6
57.5°	1667.8	1670.3
60°	1541.4	1549.0
62.5°	1407.5	1407.5
65°	1266.0	1271.1
67.5°	1119.4	1132.0
70°	970.3	972.8
72.5°	823.8	823.8
75°	672.2	674.7
77.5°	528.1	528.1
80°	391.7	394.2
82.5°	270.4	275.5
85°	169.3	169.3
87.5°	78.3	70.8
90°	22.6	22.6
92.5°	90.3	72.3
95°	314.6	260.3
97.5°	753.6	650.3
100°	1085.9	962.8
102.5°	1412.6	1307.2
105°	1829.1	1772.5
107.5°	2102.1	2115.8
110°	2206.2	2265.2



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2215.4	2306.1
115°	2156.7	2282.3
117.5°	2032.1	2171.5
120°	1931.8	2067.2
122.5°	1834.0	1967.6
125°	1694.6	1817.6
127.5°	1569.1	1673.0
130°	1495.2	1591.1
132.5°	1428.2	1514.0
135°	1336.3	1410.3
137.5°	1262.6	1323.2
140°	1212.1	1268.7
142.5°	1170.1	1218.9
145°	1107.3	1144.2
147.5°	1059.0	1089.6
150°	1028.7	1053.4
152.5°	1002.7	1021.4
155°	972.9	985.3
157.5°	949.3	958.0
160°	935.3	940.2
162.5°	926.0	930.8
165°	912.7	917.7
167.5°	903.1	905.2
170°	900.5	900.5
172.5°	893.5	891.6
175°	889.3	889.3
177.5°	885.4	883.3
180°	883.3	883.3



TEST NUMBER: P937248

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.64	6.55	6.57	7.51	8.76	18.82	19.73	19.75	20.69	21.94
	3H	6.35	7.17	7.29	8.14	9.41	20.66	21.48	21.61	22.45	23.72
	4H	6.65	7.43	7.61	8.40	9.68	21.31	22.09	22.27	23.06	24.34
	6H	6.90	7.62	7.87	8.60	9.89	21.74	22.46	22.71	23.44	24.73
	8H	6.97	7.66	7.95	8.65	9.94	21.86	22.55	22.84	23.54	24.83
	12H	6.99	7.64	7.98	8.63	9.95	21.93	22.59	22.92	23.57	24.89
4H	2H	12.86	13.64	13.83	14.61	15.89	19.10	19.88	20.06	20.85	22.13
	3H	14.43	15.08	15.41	16.09	17.38	21.15	21.80	22.12	22.80	24.09
	4H	14.53	15.13	15.52	16.12	17.44	21.92	22.51	22.90	23.51	24.82
	6H	14.54	15.06	15.54	16.08	17.39	22.46	22.98	23.46	23.99	25.31
	8H	14.52	15.00	15.52	16.02	17.34	22.62	23.11	23.62	24.12	25.45
	12H	14.48	14.92	15.50	15.94	17.28	22.72	23.16	23.74	24.18	25.52
8H	4H	15.98	16.46	16.98	17.47	18.80	21.98	22.46	22.98	23.48	24.80
	6H	16.22	16.62	17.25	17.68	19.00	22.61	23.01	23.64	24.07	25.39
	8H	16.24	16.59	17.28	17.63	18.98	22.83	23.19	23.87	24.23	25.57
	12H	16.21	16.52	17.25	17.56	18.95	22.98	23.29	24.02	24.33	25.71
12H	4H	16.12	16.56	17.14	17.59	18.92	21.94	22.37	22.96	23.40	24.74
	6H	16.48	16.84	17.52	17.88	19.22	22.60	22.95	23.63	23.99	25.34
	8H	16.55	16.87	17.59	17.90	19.29	22.83	23.14	23.87	24.18	25.56