

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937547

Luminaire Tested: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937547
REPORT IS A COMBINATION OF REPORTS P933582 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12012.9 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937547
CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37			37
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37	31			31
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30	25			25
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25	21			21
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21	17			17
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18	15			15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13			13
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14	11			11
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12	10			10
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11	9			9
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10	8			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2697	2697	2697
5°	2635	3118	3626
10°	2390	4545	6011
15°	2032	5938	7259
20°	1654	6881	7397
25°	1380	7201	7247
30°	1163	7246	7233
35°	1029	7126	7421
40°	897	6969	7614
45°	812	6855	7644
50°	745	6752	7517
55°	713	6601	7184
60°	730	6311	6658
65°	759	5870	5934
70°	809	5119	5013
75°	896	4174	3912
80°	981	2895	2636
85°	871	1536	1350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7644 cd/sqm



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.2	0.6
10°-20°	333.3	2.8
20°-30°	583.0	4.9
30°-40°	750.5	6.2
40°-50°	838.3	7.0
50°-60°	802.9	6.7
60°-70°	636.3	5.3
70°-80°	374.2	3.1
80°-90°	108.4	0.9
90°-100°	564.8	4.7
100°-110°	1484.7	12.4
110°-120°	1539.5	12.8
120°-130°	1234.9	10.3
130°-140°	968.9	8.1
140°-150°	743.7	6.2
150°-160°	535.6	4.5
160°-170°	327.7	2.7
170°-180°	110.7	0.9
0°-30°	991.6	8.3
0°-40°	1742.1	14.5
0°-60°	3383.4	28.2
0°-90°	4502.2	37.5
90°-120°	3589.0	29.9
90°-150°	6536.6	54.4
90°-180°	7511.0	62.5
0°-180°	12012.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	581	581	581	581	581	
5°	566	608	684	774	802	52
15°	424	783	1320	1600	1651	118
25°	271	888	1572	1641	1643	125
35°	183	849	1481	1565	1626	114
45°	125	677	1309	1499	1567	97
55°	90	430	1110	1290	1326	82
65°	71	228	824	927	940	70
75°	52	140	452	497	499	55
85°	19	43	112	123	125	20
90°	8	22	59	30	30	8
95°	75	292	973	502	341	83
105°	268	405	1641	2492	2325	284
115°	475	577	1315	2623	2994	469
125°	661	741	1196	2021	2384	587
135°	788	867	1159	1631	1850	609
145°	914	972	1144	1392	1501	572
155°	1033	1061	1144	1256	1292	474
165°	1114	1129	1144	1189	1204	314
175°	1159	1159	1152	1166	1166	110
180°	1159	1159	1159	1159	1159	



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4
2.5°	581.4	581.4	585.1	587.0	590.7	592.6	596.3	600.1	611.3	613.2	616.9
5°	566.4	573.9	598.2	607.6	633.7	669.2	684.2	708.5	759.0	773.9	783.3
7.5°	544.0	560.8	620.6	635.6	701.0	794.5	833.8	886.1	966.5	1005.7	1037.5
10°	508.5	544.0	650.6	686.1	792.6	934.7	1007.6	1080.6	1202.1	1256.3	1276.9
12.5°	469.2	527.2	682.3	730.9	884.2	1091.8	1179.7	1260.1	1398.4	1471.3	1482.5
15°	424.4	502.9	712.2	783.3	981.4	1222.7	1319.9	1419.0	1548.0	1600.3	1613.4
17.5°	385.1	484.2	740.3	815.1	1056.2	1340.5	1439.5	1521.8	1626.5	1662.0	1671.3
20°	336.5	454.3	759.0	856.2	1134.8	1426.5	1521.8	1585.4	1656.4	1678.8	1682.6
22.5°	301.0	422.5	770.2	871.1	1187.2	1478.8	1559.2	1609.7	1658.3	1665.7	1667.6
25°	271.1	387.0	768.3	888.0	1232.0	1510.6	1572.3	1609.7	1637.7	1641.4	1641.4
27.5°	243.0	347.7	760.9	891.7	1265.7	1518.1	1566.7	1592.8	1605.9	1613.4	1613.4
30°	218.7	310.3	742.2	884.2	1280.6	1510.6	1549.8	1562.9	1576.0	1587.2	1592.8
32.5°	200.0	274.8	714.1	869.3	1282.5	1491.9	1519.9	1527.4	1546.1	1572.3	1581.6
35°	183.2	239.3	682.3	848.7	1271.3	1462.0	1480.7	1488.1	1525.5	1564.8	1577.9
37.5°	166.4	213.1	641.2	813.2	1254.5	1426.5	1439.5	1452.6	1510.6	1557.3	1572.3
40°	149.6	190.7	592.6	773.9	1228.3	1383.5	1394.7	1415.2	1491.9	1546.1	1561.1
42.5°	136.5	172.0	540.3	732.8	1194.6	1334.9	1351.7	1381.6	1469.5	1527.4	1544.2
45°	125.3	153.3	484.2	676.7	1151.7	1284.4	1308.7	1349.8	1443.3	1499.4	1514.3
47.5°	114.0	140.2	426.2	618.8	1104.9	1233.9	1265.7	1312.4	1407.8	1462.0	1475.1
50°	104.7	127.1	368.3	557.1	1054.3	1179.7	1217.1	1265.7	1362.9	1413.4	1430.2
52.5°	97.2	115.9	314.1	495.4	996.4	1123.6	1166.6	1217.1	1308.7	1357.3	1368.5
55°	89.7	106.6	267.3	430.0	936.6	1063.8	1110.5	1159.1	1248.9	1290.0	1297.5
57.5°	86.0	99.1	228.1	368.3	873.0	996.4	1048.7	1093.7	1177.8	1209.6	1217.1
60°	80.4	93.5	198.2	315.9	803.8	932.8	977.7	1022.6	1093.7	1119.9	1125.5
62.5°	74.8	89.7	175.7	265.5	732.8	858.1	902.9	944.1	1003.9	1022.6	1030.0
65°	71.0	86.0	158.9	228.1	659.9	779.5	824.4	859.9	908.5	927.2	931.0
67.5°	67.3	82.3	145.8	196.3	587.0	701.0	734.7	768.3	805.7	824.4	826.3
70°	61.7	78.5	134.6	173.9	512.2	611.3	639.3	674.9	704.8	714.1	719.7
72.5°	58.0	72.9	127.1	157.0	435.6	525.3	551.5	572.0	598.2	607.6	607.6
75°	52.3	65.4	119.6	140.2	357.1	430.0	452.4	473.0	493.5	497.3	491.7
77.5°	46.7	58.0	102.8	117.8	278.5	340.2	358.9	370.1	387.0	390.7	392.6
80°	39.3	50.5	80.4	91.6	201.9	250.5	263.6	272.9	287.9	287.9	291.6
82.5°	29.9	39.3	58.0	65.4	136.5	172.0	183.2	188.8	198.2	198.2	198.2
85°	18.7	24.3	37.4	43.0	82.3	104.7	112.2	114.0	121.5	123.4	123.4
87.5°	9.3	13.1	24.3	26.2	43.0	54.2	54.2	58.0	58.0	56.1	54.2
90°	7.8	14.0	20.2	21.8	34.2	50.8	59.1	52.5	39.4	29.5	29.5
92.5°	31.1	84.0	136.9	150.1	211.0	292.2	332.8	291.6	209.5	147.8	141.9
95°	74.7	171.4	268.2	292.4	519.1	821.5	972.7	868.1	658.6	501.6	483.8
97.5°	129.1	214.4	299.9	321.2	699.3	1203.5	1455.6	1389.4	1257.1	1157.8	1124.0
100°	171.1	248.4	325.9	345.3	764.9	1324.4	1604.1	1609.0	1618.6	1625.9	1585.5
102.5°	206.9	279.0	351.3	369.3	794.9	1362.3	1646.1	1730.4	1899.1	2025.6	1991.0
105°	267.5	328.6	389.8	405.1	817.2	1366.7	1641.4	1830.4	2208.5	2492.1	2473.5
107.5°	329.7	386.7	443.7	458.0	821.4	1305.9	1548.2	1811.8	2339.2	2734.7	2739.2
110°	371.6	423.1	474.6	487.5	815.2	1251.9	1470.4	1765.2	2354.7	2796.9	2816.3



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	412.9	461.9	511.1	523.3	815.4	1204.9	1399.6	1701.4	2304.7	2757.3	2787.0
115°	475.1	520.4	565.7	577.0	822.9	1150.9	1314.9	1605.5	2186.8	2622.8	2664.0
117.5°	536.5	577.6	618.8	629.1	838.2	1117.1	1256.5	1518.8	2043.5	2436.9	2482.6
120°	572.3	611.0	649.7	659.3	850.7	1105.8	1233.3	1472.9	1952.2	2311.7	2356.1
122.5°	607.3	646.3	685.4	695.1	868.5	1099.7	1215.3	1431.1	1862.8	2186.6	2230.4
125°	660.9	696.5	732.2	741.0	892.6	1094.8	1195.9	1379.3	1745.9	2020.9	2061.3
127.5°	704.5	740.4	776.4	785.3	916.8	1092.0	1179.6	1337.0	1651.8	1887.9	1921.9
130°	727.8	766.5	805.2	814.9	934.3	1093.7	1173.3	1313.4	1593.8	1804.0	1835.4
132.5°	751.9	790.6	829.3	839.0	948.6	1094.8	1167.9	1293.4	1544.2	1732.4	1760.5
135°	787.7	822.9	858.2	867.0	964.2	1093.8	1158.6	1263.6	1473.8	1631.3	1655.6
137.5°	824.2	859.1	894.0	902.7	987.5	1100.5	1157.0	1245.8	1423.5	1556.7	1576.6
140°	854.5	886.7	918.8	926.9	1001.7	1101.6	1151.6	1228.3	1381.8	1496.8	1515.4
142.5°	877.9	907.6	937.3	944.7	1013.7	1105.6	1151.6	1219.0	1353.7	1454.9	1470.9
145°	913.7	939.6	965.6	972.0	1029.3	1105.7	1143.8	1198.9	1309.1	1391.9	1403.9
147.5°	949.4	974.6	999.9	1006.2	1052.1	1113.2	1143.8	1187.2	1273.9	1339.0	1349.0
150°	972.7	995.6	1018.4	1024.1	1064.0	1117.2	1143.8	1180.4	1253.7	1308.7	1316.8
152.5°	996.9	1014.2	1031.4	1035.7	1071.7	1119.8	1143.8	1175.1	1237.6	1284.6	1290.7
155°	1032.6	1045.4	1058.2	1061.4	1088.8	1125.5	1143.8	1168.7	1218.5	1255.8	1259.8
157.5°	1059.0	1071.5	1084.0	1087.1	1105.9	1131.2	1143.8	1163.1	1201.8	1230.9	1233.7
160°	1077.0	1086.7	1096.3	1098.7	1113.8	1133.8	1143.8	1160.4	1193.6	1218.5	1220.2
162.5°	1094.8	1102.1	1109.4	1111.2	1122.0	1136.5	1143.8	1157.8	1185.8	1206.8	1208.4
165°	1114.3	1120.8	1127.3	1129.0	1134.0	1140.5	1143.8	1153.8	1173.9	1188.9	1190.6
167.5°	1132.1	1135.2	1138.4	1139.1	1143.2	1148.8	1151.6	1158.1	1171.3	1181.1	1181.7
170°	1143.8	1146.9	1150.1	1150.8	1151.1	1151.4	1151.6	1158.1	1171.3	1181.1	1181.1
172.5°	1150.1	1150.7	1151.4	1151.6	1151.6	1151.6	1151.6	1156.8	1167.2	1174.9	1174.4
175°	1158.6	1158.6	1158.6	1158.6	1156.2	1153.1	1151.6	1154.8	1161.4	1166.3	1166.3
177.5°	1158.6	1158.6	1158.6	1158.6	1156.8	1154.4	1153.1	1155.8	1160.9	1164.8	1164.2
180°	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6	1158.6



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	581.4	581.4
2.5°	620.6	616.9
5°	798.2	802.0
7.5°	1075.0	1073.1
10°	1336.7	1353.5
12.5°	1527.4	1531.1
15°	1643.3	1650.8
17.5°	1688.2	1690.0
20°	1690.0	1686.3
22.5°	1669.5	1665.7
25°	1645.2	1643.3
27.5°	1622.7	1624.6
30°	1613.4	1619.0
32.5°	1613.4	1622.7
35°	1617.1	1626.5
37.5°	1615.3	1626.5
40°	1607.8	1620.9
42.5°	1587.2	1596.6
45°	1555.4	1566.7
47.5°	1514.3	1521.8
50°	1462.0	1469.5
52.5°	1396.5	1398.4
55°	1318.0	1325.5
57.5°	1233.9	1235.8
60°	1140.4	1146.0
62.5°	1041.3	1041.3
65°	936.6	940.3
67.5°	828.1	837.5
70°	717.9	719.7
72.5°	609.4	609.4
75°	497.3	499.1
77.5°	390.7	390.7
80°	289.8	291.6
82.5°	200.0	203.8
85°	125.3	125.3
87.5°	58.0	52.3
90°	29.5	29.5
92.5°	118.4	94.9
95°	412.6	341.4
97.5°	988.5	853.0
100°	1424.2	1262.8
102.5°	1852.8	1714.5
105°	2399.2	2324.9
107.5°	2757.2	2775.1
110°	2893.7	2971.1



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2905.8	3024.7
115°	2828.8	2993.7
117.5°	2665.4	2848.2
120°	2533.8	2711.4
122.5°	2405.6	2580.7
125°	2222.6	2384.1
127.5°	2058.1	2194.3
130°	1961.2	2087.0
132.5°	1873.2	1985.9
135°	1752.8	1849.9
137.5°	1656.0	1735.6
140°	1589.7	1664.0
142.5°	1534.8	1598.7
145°	1452.3	1500.7
147.5°	1389.1	1429.2
150°	1349.2	1381.8
152.5°	1315.2	1339.7
155°	1276.1	1292.3
157.5°	1245.1	1256.5
160°	1226.7	1233.3
162.5°	1214.6	1220.8
165°	1197.2	1203.7
167.5°	1184.6	1187.4
170°	1181.1	1181.1
172.5°	1171.9	1169.5
175°	1166.3	1166.3
177.5°	1161.4	1158.6
180°	1158.6	1158.6



TEST NUMBER: P937547

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-8-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.19	3.97	4.24	5.03	6.47	16.36	17.15	17.42	18.21	19.65
	3H	3.89	4.59	4.95	5.66	7.11	18.20	18.90	19.26	19.97	21.43
	4H	4.18	4.85	5.25	5.92	7.38	18.84	19.51	19.91	20.58	22.04
	6H	4.43	5.04	5.51	6.12	7.59	19.27	19.88	20.35	20.96	22.43
	8H	4.49	5.08	5.58	6.17	7.64	19.38	19.97	20.47	21.06	22.53
	12H	4.51	5.07	5.60	6.15	7.64	19.45	20.01	20.54	21.09	22.59
4H	2H	10.39	11.06	11.47	12.13	13.59	16.63	17.30	17.71	18.37	19.83
	3H	11.95	12.51	13.04	13.61	15.08	18.67	19.23	19.75	20.32	21.80
	4H	12.04	12.56	13.13	13.65	15.14	19.43	19.95	20.52	21.03	22.53
	6H	12.05	12.49	13.15	13.60	15.09	19.97	20.41	21.07	21.52	23.01
	8H	12.02	12.44	13.12	13.54	15.05	20.13	20.54	21.23	21.64	23.15
	12H	11.98	12.35	13.10	13.47	14.98	20.22	20.59	21.33	21.71	23.22
8H	4H	13.48	13.89	14.58	15.00	16.50	19.48	19.90	20.59	21.00	22.51
	6H	13.72	14.06	14.84	15.21	16.71	20.11	20.45	21.23	21.60	23.10
	8H	13.74	14.04	14.87	15.16	16.68	20.33	20.63	21.46	21.76	23.28
	12H	13.70	13.97	14.84	15.09	16.65	20.47	20.73	21.60	21.86	23.42
12H	4H	13.62	14.00	14.74	15.11	16.62	19.43	19.81	20.55	20.92	22.44
	6H	13.98	14.28	15.11	15.40	16.93	20.09	20.39	21.22	21.52	23.04
	8H	14.04	14.31	15.18	15.43	16.99	20.32	20.58	21.45	21.71	23.26