

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936248

Luminaire Tested: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936248
REPORT IS A COMBINATION OF REPORTS P933453 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4936.9 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936248
CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	29
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1850	1850	1850
5°	1808	2139	2487
10°	1640	3118	4124
15°	1394	4074	4980
20°	1134	4721	5075
25°	947	4940	4972
30°	798	4971	4962
35°	705	4889	5091
40°	615	4781	5224
45°	557	4703	5244
50°	511	4632	5157
55°	490	4528	4928
60°	501	4330	4567
65°	522	4027	4071
70°	556	3512	3440
75°	617	2864	2684
80°	674	1986	1808
85°	596	1054	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5244 cd/sqm



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.0
10°-20°	228.7	4.6
20°-30°	400.0	8.1
30°-40°	514.9	10.4
40°-50°	575.1	11.6
50°-60°	550.8	11.2
60°-70°	436.5	8.8
70°-80°	256.7	5.2
80°-90°	72.4	1.5
90°-100°	139.1	2.8
100°-110°	365.7	7.4
110°-120°	379.2	7.7
120°-130°	304.2	6.2
130°-140°	238.7	4.8
140°-150°	183.2	3.7
150°-160°	131.9	2.7
160°-170°	80.7	1.6
170°-180°	27.3	0.6
0°-30°	680.2	13.8
0°-40°	1195.1	24.2
0°-60°	2321.1	47.0
0°-90°	3086.7	62.5
90°-120°	884.1	17.9
90°-150°	1610.2	32.6
90°-180°	1850.0	37.5
0°-180°	4936.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	399	399	399	399	399	
5°	389	417	469	531	550	36
15°	291	537	906	1098	1132	81
25°	186	609	1079	1126	1127	86
35°	126	582	1016	1074	1116	78
45°	86	464	898	1029	1075	66
55°	62	295	762	885	909	56
65°	49	156	566	636	645	48
75°	36	96	310	341	342	38
85°	13	30	77	85	86	14
90°	2	5	14	7	7	2
95°	18	72	240	124	84	20
105°	66	100	404	614	573	70
115°	117	142	324	646	737	116
125°	163	182	295	498	587	145
135°	194	214	285	402	456	150
145°	225	239	282	343	370	141
155°	254	261	282	309	318	117
165°	274	278	282	293	296	77
175°	285	285	284	287	287	27
180°	285	285	285	285	285	



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	398.8	398.8	398.8	398.8	398.8	398.8	398.8	398.8	398.8	398.8	398.8
2.5°	398.8	398.8	401.4	402.7	405.2	406.6	409.2	411.7	419.4	420.6	423.2
5°	388.6	393.8	410.4	416.8	434.8	459.2	469.4	486.0	520.7	531.0	537.4
7.5°	373.2	384.8	425.8	436.0	481.0	545.0	572.0	607.9	663.0	690.0	711.8
10°	348.8	373.2	446.4	470.7	543.8	641.2	691.3	741.3	824.6	861.8	876.0
12.5°	322.0	361.6	468.2	501.4	606.6	749.0	809.3	864.4	959.3	1009.4	1017.0
15°	291.2	345.0	488.6	537.4	673.4	838.8	905.5	973.4	1061.9	1097.8	1106.8
17.5°	264.2	332.2	507.9	559.2	724.6	919.6	987.6	1044.0	1115.8	1140.2	1146.6
20°	230.8	311.6	520.7	587.4	778.5	978.6	1044.0	1087.6	1136.3	1151.7	1154.3
22.5°	206.4	289.8	528.4	597.6	814.4	1014.5	1069.6	1104.3	1137.6	1142.7	1144.0
25°	186.0	265.4	527.1	609.2	845.2	1036.3	1078.6	1104.3	1123.5	1126.1	1126.1
27.5°	166.8	238.6	522.0	611.8	868.3	1041.4	1074.8	1092.7	1101.7	1106.8	1106.8
30°	150.0	212.9	509.2	606.6	878.6	1036.3	1063.2	1072.2	1081.2	1088.9	1092.7
32.5°	137.2	188.6	490.0	596.4	879.8	1023.4	1042.7	1047.8	1060.6	1078.6	1085.0
35°	125.6	164.2	468.2	582.2	872.1	1003.0	1015.8	1020.9	1046.6	1073.5	1082.4
37.5°	114.2	146.2	439.9	557.9	860.6	978.6	987.6	996.5	1036.3	1068.4	1078.6
40°	102.6	130.8	406.6	531.0	842.6	949.1	956.8	970.9	1023.4	1060.6	1070.9
42.5°	93.6	118.0	370.6	502.8	819.6	915.7	927.3	947.8	1008.1	1047.8	1059.4
45°	86.0	105.2	332.2	464.2	790.0	881.1	897.8	926.0	990.1	1028.6	1038.8
47.5°	78.2	96.2	292.4	424.5	758.0	846.5	868.3	900.4	965.8	1003.0	1011.9
50°	71.8	87.2	252.6	382.2	723.4	809.3	834.9	868.3	935.0	969.6	981.1
52.5°	66.6	79.6	215.4	339.8	683.6	770.8	800.3	834.9	897.8	931.1	938.8
55°	61.6	73.1	183.4	295.0	642.6	729.8	761.8	795.2	856.7	885.0	890.1
57.5°	59.0	68.0	156.4	252.6	599.0	683.6	719.5	750.3	808.0	829.8	834.9
60°	55.2	64.2	136.0	216.8	551.5	640.0	670.8	701.6	750.3	768.2	772.1
62.5°	51.3	61.6	120.6	182.2	502.8	588.7	619.4	647.7	688.7	701.6	706.7
65°	48.8	59.0	109.0	156.4	452.8	534.8	565.6	590.0	623.3	636.2	638.7
67.5°	46.2	56.4	100.0	134.6	402.7	481.0	504.0	527.1	552.8	565.6	566.8
70°	42.4	53.8	92.4	119.2	351.4	419.4	438.6	463.0	483.5	490.0	493.8
72.5°	39.8	50.0	87.2	107.8	298.8	360.4	378.4	392.4	410.4	416.8	416.8
75°	36.0	44.8	82.0	96.2	245.0	295.0	310.4	324.4	338.6	341.2	337.3
77.5°	32.0	39.8	70.6	80.8	191.1	233.4	246.2	254.0	265.4	268.0	269.4
80°	27.0	34.6	55.2	62.8	138.6	171.8	180.8	187.2	197.5	197.5	200.0
82.5°	20.6	27.0	39.8	44.8	93.6	118.0	125.6	129.6	136.0	136.0	136.0
85°	12.8	16.6	25.6	29.5	56.4	71.8	77.0	78.2	83.4	84.6	84.6
87.5°	6.4	9.0	16.6	18.0	29.5	37.2	37.2	39.8	39.8	38.4	37.2
90°	1.9	3.4	5.0	5.4	8.4	12.5	14.5	12.9	9.7	7.3	7.3
92.5°	7.6	20.7	33.8	37.0	52.0	72.0	81.9	71.8	51.6	36.4	35.0
95°	18.4	42.2	66.1	72.0	127.8	202.3	239.6	213.8	162.3	123.5	119.1
97.5°	31.8	52.9	73.8	79.1	172.2	296.4	358.6	342.3	309.7	285.2	276.9
100°	42.2	61.2	80.2	85.0	188.4	326.2	395.1	396.3	398.7	400.5	390.6
102.5°	51.0	68.8	86.5	90.9	195.8	335.6	405.5	426.3	467.8	498.9	490.4
105°	65.9	81.0	96.1	99.8	201.4	336.7	404.4	450.9	544.1	613.9	609.3
107.5°	81.2	95.2	109.3	112.8	202.3	321.7	381.3	446.3	576.2	673.6	674.8
110°	91.6	104.2	116.9	120.1	200.8	308.4	362.2	434.8	580.0	688.9	693.7



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	101.7	113.8	125.8	128.9	200.9	296.8	344.8	419.1	567.7	679.2	686.5
115°	117.0	128.1	139.3	142.1	202.7	283.5	323.9	395.5	538.7	646.1	656.2
117.5°	132.1	142.3	152.4	155.0	206.5	275.2	309.5	374.2	503.3	600.3	611.6
120°	140.9	150.5	160.1	162.5	209.6	272.4	303.8	362.8	480.9	569.4	580.3
122.5°	149.5	159.2	168.9	171.3	214.0	270.9	299.4	352.5	458.9	538.6	549.4
125°	162.8	171.6	180.3	182.5	219.9	269.7	294.6	339.7	430.1	497.8	507.7
127.5°	173.5	182.3	191.2	193.4	225.9	269.0	290.6	329.4	407.0	465.1	473.5
130°	179.3	188.8	198.3	200.7	230.2	269.5	289.1	323.6	392.6	444.3	452.1
132.5°	185.2	194.8	204.2	206.6	233.7	269.7	287.7	318.6	380.4	426.7	433.7
135°	194.0	202.7	211.4	213.6	237.5	269.5	285.4	311.3	363.1	401.9	407.8
137.5°	203.0	211.6	220.2	222.4	243.3	271.1	285.0	306.9	350.6	383.4	388.3
140°	210.5	218.4	226.3	228.3	246.8	271.4	283.7	302.6	340.4	368.7	373.3
142.5°	216.3	223.6	230.9	232.7	249.8	272.4	283.7	300.3	333.5	358.4	362.3
145°	225.1	231.5	237.8	239.4	253.6	272.4	281.8	295.4	322.5	342.9	345.9
147.5°	233.9	240.1	246.3	247.8	259.1	274.2	281.8	292.5	313.8	329.8	332.3
150°	239.6	245.3	250.8	252.2	262.1	275.2	281.8	290.8	308.9	322.3	324.3
152.5°	245.6	249.8	254.1	255.1	264.0	275.9	281.8	289.4	304.8	316.4	317.9
155°	254.3	257.5	260.7	261.4	268.2	277.3	281.8	287.9	300.1	309.3	310.3
157.5°	260.8	263.9	267.0	267.7	272.4	278.6	281.8	286.6	296.0	303.2	303.9
160°	265.2	267.6	270.0	270.6	274.3	279.3	281.8	285.9	294.0	300.1	300.5
162.5°	269.6	271.5	273.2	273.7	276.3	280.0	281.8	285.2	292.1	297.3	297.7
165°	274.5	276.1	277.8	278.2	279.4	281.0	281.8	284.3	289.2	292.9	293.3
167.5°	278.9	279.7	280.5	280.6	281.7	283.0	283.7	285.3	288.6	291.0	291.2
170°	281.8	282.6	283.3	283.5	283.6	283.7	283.7	285.3	288.6	291.0	291.0
172.5°	283.3	283.5	283.7	283.7	283.7	283.7	283.7	284.9	287.5	289.4	289.2
175°	285.4	285.4	285.4	285.4	284.8	284.1	283.7	284.5	286.1	287.3	287.3
177.5°	285.4	285.4	285.4	285.4	284.9	284.4	284.1	284.8	286.0	287.0	286.8
180°	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	398.8	398.8
2.5°	425.8	423.2
5°	547.6	550.2
7.5°	737.4	736.2
10°	917.0	928.6
12.5°	1047.8	1050.4
15°	1127.4	1132.5
17.5°	1158.1	1159.4
20°	1159.4	1156.8
22.5°	1145.3	1142.7
25°	1128.6	1127.4
27.5°	1113.2	1114.5
30°	1106.8	1110.7
32.5°	1106.8	1113.2
35°	1109.4	1115.8
37.5°	1108.1	1115.8
40°	1103.0	1112.0
42.5°	1088.9	1095.3
45°	1067.1	1074.8
47.5°	1038.8	1044.0
50°	1003.0	1008.1
52.5°	958.0	959.3
55°	904.2	909.3
57.5°	846.5	847.8
60°	782.4	786.2
62.5°	714.4	714.4
65°	642.6	645.1
67.5°	568.2	574.6
70°	492.5	493.8
72.5°	418.1	418.1
75°	341.2	342.4
77.5°	268.0	268.0
80°	198.8	200.0
82.5°	137.2	139.8
85°	86.0	86.0
87.5°	39.8	36.0
90°	7.3	7.3
92.5°	29.2	23.3
95°	101.6	84.0
97.5°	243.4	210.1
100°	350.8	311.0
102.5°	456.4	422.4
105°	591.0	572.7
107.5°	679.2	683.6
110°	712.7	731.9



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	715.8	745.1
115°	696.9	737.4
117.5°	656.6	701.7
120°	624.1	667.9
122.5°	592.6	635.7
125°	547.5	587.3
127.5°	507.0	540.5
130°	483.1	514.0
132.5°	461.5	489.2
135°	431.7	455.6
137.5°	407.9	427.5
140°	391.6	409.9
142.5°	378.1	393.8
145°	357.8	369.7
147.5°	342.1	352.1
150°	332.4	340.4
152.5°	324.0	330.0
155°	314.3	318.3
157.5°	306.7	309.5
160°	302.2	303.8
162.5°	299.2	300.7
165°	294.9	296.5
167.5°	291.8	292.5
170°	291.0	291.0
172.5°	288.7	288.1
175°	287.3	287.3
177.5°	286.1	285.4
180°	285.4	285.4



TEST NUMBER: P936248

CATALOG NUMBER: SQ4-FB-025U-050D-92765-1D-UNV-STD-W-8-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.21	5.24	5.04	6.11	7.18	17.39	18.42	18.22	19.29	20.36
	3H	4.92	5.86	5.77	6.73	7.83	19.24	20.17	20.09	21.05	22.15
	4H	5.23	6.12	6.09	6.99	8.11	19.89	20.78	20.75	21.66	22.77
	6H	5.49	6.31	6.37	7.19	8.32	20.33	21.15	21.21	22.04	23.16
	8H	5.56	6.34	6.45	7.25	8.38	20.46	21.24	21.34	22.14	23.27
	12H	5.59	6.33	6.48	7.23	8.38	20.53	21.28	21.42	22.17	23.33
4H	2H	11.45	12.33	12.31	13.21	14.32	17.68	18.57	18.55	19.45	20.56
	3H	13.03	13.77	13.91	14.68	15.81	19.74	20.49	20.62	21.40	22.53
	4H	13.13	13.81	14.02	14.71	15.87	20.52	21.20	21.41	22.10	23.26
	6H	13.15	13.74	14.06	14.67	15.83	21.07	21.66	21.97	22.59	23.74
	8H	13.13	13.68	14.04	14.61	15.78	21.24	21.79	22.14	22.71	23.88
	12H	13.10	13.60	14.03	14.54	15.72	21.34	21.83	22.27	22.78	23.95
8H	4H	14.59	15.14	15.50	16.07	17.24	20.60	21.14	21.50	22.07	23.24
	6H	14.84	15.30	15.78	16.26	17.43	21.23	21.69	22.17	22.65	23.83
	8H	14.86	15.27	15.81	16.22	17.41	21.46	21.86	22.40	22.82	24.00
	12H	14.84	15.20	15.79	16.15	17.38	21.61	21.96	22.56	22.91	24.15
12H	4H	14.74	15.24	15.67	16.18	17.36	20.56	21.05	21.49	22.00	23.17
	6H	15.10	15.51	16.05	16.46	17.65	21.22	21.62	22.16	22.58	23.77
	8H	15.18	15.54	16.13	16.49	17.72	21.46	21.81	22.41	22.76	24.00