

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937633

Luminaire Tested: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

Issue Date: 12/17/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P937633  
REPORT IS A COMBINATION OF REPORTS P933567 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6426.0 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 58  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937633  
CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44	44	44	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36	36	36	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30	30	30	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24	24	24	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20	20	20	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17	17	17	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11	11	11	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10	10	10	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9	9	9	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3404	3404	3404
5°	3322	3931	4575
10°	3009	5726	7585
15°	2555	7476	9158
20°	2078	8657	9333
25°	1731	9052	9145
30°	1458	9103	9127
35°	1287	8944	9364
40°	1119	8740	9607
45°	1011	8588	9645
50°	927	8450	9485
55°	884	8252	9064
60°	902	7880	8401
65°	934	7316	7488
70°	988	6369	6326
75°	1082	5180	4937
80°	1156	3579	3327
85°	977	1890	1702

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 9645 cd/sqm



TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	0.7
10°-20°	210.3	3.3
20°-30°	367.8	5.7
30°-40°	473.5	7.4
40°-50°	528.9	8.2
50°-60°	506.6	7.9
60°-70°	401.4	6.2
70°-80°	236.1	3.7
80°-90°	67.7	1.1
90°-100°	269.7	4.2
100°-110°	709.0	11.0
110°-120°	735.1	11.4
120°-130°	589.6	9.2
130°-140°	462.7	7.2
140°-150°	355.1	5.5
150°-160°	255.7	4.0
160°-170°	156.5	2.4
170°-180°	52.9	0.8
<b>0°-30°</b>	<b>625.6</b>	<b>9.7</b>
<b>0°-40°</b>	<b>1099.1</b>	<b>17.1</b>
<b>0°-60°</b>	<b>2134.5</b>	<b>33.2</b>
<b>0°-90°</b>	<b>2839.7</b>	<b>44.2</b>
<b>90°-120°</b>	<b>1713.7</b>	<b>26.7</b>
<b>90°-150°</b>	<b>3121.1</b>	<b>48.6</b>
<b>90°-180°</b>	<b>3586.0</b>	<b>55.8</b>
<b>0°-180°</b>	<b>6426.0</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	367	367	367	367	367	
5°	357	383	432	488	506	33
15°	268	494	833	1010	1041	75
25°	171	560	992	1036	1037	79
35°	116	536	934	987	1026	72
45°	79	427	826	946	988	61
55°	57	271	701	814	836	52
65°	45	144	520	585	593	44
75°	33	88	286	314	315	35
85°	12	27	71	78	79	12
90°	4	10	28	14	14	4
95°	36	140	464	240	163	40
105°	128	193	784	1190	1110	135
115°	227	276	628	1252	1429	224
125°	316	354	571	965	1138	280
135°	376	414	553	779	883	291
145°	436	464	546	665	717	273
155°	493	507	546	600	617	227
165°	532	539	546	568	575	150
175°	553	553	550	557	557	53
180°	553	553	553	553	553	



TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8
2.5°	366.8	366.8	369.2	370.3	372.7	373.9	376.2	378.6	385.7	386.9	389.2
5°	357.4	362.1	377.4	383.3	399.8	422.2	431.7	447.0	478.9	488.3	494.2
7.5°	343.2	353.8	391.6	401.1	442.3	501.3	526.0	559.0	609.7	634.6	654.6
10°	320.8	343.2	410.4	432.8	500.0	589.8	635.7	681.7	758.4	792.6	805.6
12.5°	296.1	332.6	430.5	461.1	557.9	688.8	744.3	795.0	882.3	928.2	935.3
15°	267.7	317.2	449.3	494.2	619.2	771.4	832.7	895.2	976.6	1009.6	1017.9
17.5°	243.0	305.5	467.0	514.2	666.4	845.7	908.2	960.1	1026.2	1048.6	1054.5
20°	212.3	286.6	478.9	540.2	716.0	899.9	960.1	1000.2	1045.0	1059.2	1061.5
22.5°	189.9	266.5	485.9	549.6	748.9	933.0	983.7	1015.5	1046.2	1050.9	1052.0
25°	171.0	244.1	484.8	560.2	777.3	953.0	991.9	1015.5	1033.2	1035.5	1035.5
27.5°	153.4	219.4	480.1	562.6	798.4	957.7	988.4	1004.9	1013.1	1017.9	1017.9
30°	138.0	195.8	468.3	557.9	807.9	953.0	977.8	986.0	994.3	1001.3	1004.9
32.5°	126.2	173.3	450.6	548.4	809.1	941.2	958.9	963.6	975.4	991.9	997.9
35°	115.6	150.9	430.5	535.5	802.0	922.3	934.1	938.9	962.4	987.2	995.4
37.5°	105.0	134.4	404.5	513.1	791.4	899.9	908.2	916.5	953.0	982.5	991.9
40°	94.3	120.3	373.9	488.3	774.9	872.8	879.9	892.9	941.2	975.4	984.8
42.5°	86.1	108.5	340.9	462.4	753.6	842.1	852.7	871.6	927.1	963.6	974.2
45°	79.0	96.7	305.5	426.9	726.5	810.3	825.6	851.6	910.6	945.9	955.4
47.5°	71.9	88.5	268.9	390.4	697.0	778.5	798.4	828.0	888.2	922.3	930.6
50°	66.1	80.2	232.3	351.5	665.2	744.3	767.8	798.4	859.9	891.6	902.3
52.5°	61.3	73.1	198.2	312.6	628.7	708.8	736.0	767.8	825.6	856.3	863.3
55°	56.6	67.2	168.7	271.3	590.9	671.1	700.6	731.2	787.9	813.8	818.5
57.5°	54.3	62.5	143.9	232.3	550.8	628.7	661.7	690.0	743.0	763.1	767.8
60°	50.7	59.0	125.1	199.3	507.2	588.5	616.9	645.2	690.0	706.5	710.0
62.5°	47.2	56.6	110.9	167.5	462.4	541.4	569.7	595.6	633.4	645.2	649.9
65°	44.8	54.3	100.2	143.9	416.3	491.8	520.1	542.5	573.2	585.0	587.3
67.5°	42.5	51.9	92.0	123.8	370.3	442.3	463.5	484.8	508.3	520.1	521.3
70°	38.9	49.5	84.9	109.7	323.1	385.7	403.4	425.8	444.6	450.6	454.1
72.5°	36.6	46.0	80.2	99.1	274.8	331.4	347.9	360.9	377.4	383.3	383.3
75°	33.0	41.2	75.5	88.5	225.3	271.3	285.5	298.4	311.3	313.8	310.2
77.5°	29.5	36.6	64.9	74.3	175.8	214.7	226.5	233.5	244.1	246.5	247.7
80°	24.7	31.9	50.7	57.8	127.4	158.1	166.3	172.2	181.6	181.6	184.0
82.5°	18.8	24.7	36.6	41.2	86.1	108.5	115.6	119.2	125.1	125.1	125.1
85°	11.8	15.4	23.6	27.1	51.9	66.1	70.8	71.9	76.7	77.8	77.8
87.5°	5.9	8.2	15.4	16.5	27.1	34.2	34.2	36.6	36.6	35.3	34.2
90°	3.7	6.7	9.6	10.4	16.3	24.3	28.2	25.1	18.8	14.1	14.1
92.5°	14.8	40.1	65.3	71.7	100.8	139.5	158.9	139.2	100.0	70.5	67.7
95°	35.6	81.9	128.1	139.6	247.9	392.2	464.4	414.4	314.5	239.5	231.0
97.5°	61.6	102.4	143.2	153.4	333.9	574.7	695.0	663.4	600.2	552.8	536.6
100°	81.7	118.6	155.6	164.9	365.3	632.4	766.0	768.3	772.8	776.3	757.0
102.5°	98.7	133.3	167.7	176.4	379.6	650.5	786.0	826.3	906.8	967.2	950.6
105°	127.7	156.9	186.1	193.4	390.3	652.6	783.8	874.1	1054.5	1190.0	1181.1
107.5°	157.5	184.7	211.9	218.7	392.2	623.5	739.2	865.1	1116.9	1305.8	1308.0
110°	177.5	202.1	226.6	232.8	389.2	597.8	702.0	842.8	1124.3	1335.4	1344.7



TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	197.2	220.6	244.0	249.8	389.4	575.3	668.3	812.4	1100.4	1316.5	1330.7
115°	226.8	248.4	270.0	275.5	392.9	549.6	627.9	766.7	1044.2	1252.3	1272.0
117.5°	256.2	275.8	295.5	300.4	400.3	533.4	600.0	725.3	975.7	1163.6	1185.4
120°	273.2	291.7	310.2	314.8	406.1	528.0	588.9	703.3	932.2	1103.8	1125.1
122.5°	290.0	308.7	327.3	332.0	414.7	525.1	580.3	683.3	889.4	1044.0	1064.9
125°	315.6	332.6	349.5	353.8	426.2	522.7	571.0	658.6	833.6	964.9	984.2
127.5°	336.3	353.5	370.7	375.0	437.7	521.4	563.2	638.4	788.7	901.5	917.7
130°	347.5	366.0	384.5	389.1	446.1	522.3	560.3	627.2	761.0	861.4	876.4
132.5°	359.0	377.5	396.0	400.6	452.9	522.7	557.6	617.5	737.3	827.2	840.7
135°	376.2	392.9	409.8	414.0	460.4	522.3	553.2	603.4	703.7	778.9	790.5
137.5°	393.6	410.2	426.9	431.0	471.5	525.5	552.4	594.8	679.6	743.3	752.7
140°	408.0	423.4	438.7	442.6	478.4	526.0	549.9	586.5	659.7	714.7	723.6
142.5°	419.2	433.4	447.6	451.1	484.1	527.9	549.9	582.0	646.3	694.6	702.3
145°	436.2	448.6	460.9	464.1	491.5	528.0	546.2	572.5	625.1	664.6	670.4
147.5°	453.4	465.4	477.4	480.4	502.4	531.6	546.2	566.9	608.3	639.4	644.2
150°	464.4	475.3	486.2	489.0	508.1	533.5	546.2	563.7	598.6	624.8	628.7
152.5°	475.9	484.2	492.5	494.5	511.7	534.7	546.2	561.1	590.9	613.3	616.3
155°	493.1	499.2	505.3	506.8	520.0	537.4	546.2	558.1	581.8	599.6	601.5
157.5°	505.7	511.6	517.5	519.1	528.1	540.1	546.2	555.4	573.9	587.7	589.0
160°	514.2	518.9	523.4	524.6	531.8	541.4	546.2	554.1	569.9	581.8	582.6
162.5°	522.7	526.2	529.7	530.6	535.8	542.7	546.2	552.9	566.2	576.2	576.9
165°	532.0	535.1	538.2	539.1	541.5	544.6	546.2	551.0	560.6	567.7	568.5
167.5°	540.6	542.1	543.6	544.0	545.9	548.5	549.9	553.0	559.2	564.0	564.3
170°	546.2	547.6	549.1	549.5	549.6	549.8	549.9	553.0	559.2	564.0	564.0
172.5°	549.1	549.5	549.8	549.9	549.9	549.9	549.9	552.4	557.3	561.0	560.7
175°	553.2	553.2	553.2	553.2	552.1	550.6	549.9	551.5	554.6	556.9	556.9
177.5°	553.2	553.2	553.2	553.2	552.4	551.2	550.6	551.8	554.3	556.2	555.8
180°	553.2	553.2	553.2	553.2	553.2	553.2	553.2	553.2	553.2	553.2	553.2



TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	366.8	366.8
2.5°	391.6	389.2
5°	503.6	506.0
7.5°	678.2	677.0
10°	843.3	853.9
12.5°	963.6	966.0
15°	1036.8	1041.4
17.5°	1065.1	1066.2
20°	1066.2	1063.8
22.5°	1053.3	1050.9
25°	1037.9	1036.8
27.5°	1023.7	1024.9
30°	1017.9	1021.4
32.5°	1017.9	1023.7
35°	1020.3	1026.2
37.5°	1019.0	1026.2
40°	1014.4	1022.6
42.5°	1001.3	1007.2
45°	981.3	988.4
47.5°	955.4	960.1
50°	922.3	927.1
52.5°	881.0	882.3
55°	831.5	836.2
57.5°	778.5	779.6
60°	719.5	723.0
62.5°	657.0	657.0
65°	590.9	593.2
67.5°	522.5	528.4
70°	452.9	454.1
72.5°	384.5	384.5
75°	313.8	314.9
77.5°	246.5	246.5
80°	182.8	184.0
82.5°	126.2	128.5
85°	79.0	79.0
87.5°	36.6	33.0
90°	14.1	14.1
92.5°	56.5	45.3
95°	197.0	163.0
97.5°	471.9	407.3
100°	680.0	603.0
102.5°	884.7	818.7
105°	1145.6	1110.2
107.5°	1316.5	1325.1
110°	1381.7	1418.6





TEST NUMBER: P937633

CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1387.5	1444.3
115°	1350.7	1429.4
117.5°	1272.7	1360.0
120°	1209.9	1294.7
122.5°	1148.6	1232.3
125°	1061.2	1138.4
127.5°	982.8	1047.8
130°	936.4	996.5
132.5°	894.4	948.2
135°	836.8	883.2
137.5°	790.8	828.7
140°	759.1	794.5
142.5°	732.8	763.4
145°	693.5	716.6
147.5°	663.3	682.4
150°	644.2	659.7
152.5°	628.0	639.7
155°	609.3	617.1
157.5°	594.6	600.0
160°	585.7	588.9
162.5°	579.9	582.9
165°	571.6	574.8
167.5°	565.6	566.9
170°	564.0	564.0
172.5°	559.6	558.4
175°	556.9	556.9
177.5°	554.6	553.2
180°	553.2	553.2



TEST NUMBER: P937633  
 CATALOG NUMBER: SQ4-FB-100U-100D-92765-1D-UNV-STD-W-4-3500K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.69	5.54	5.69	6.55	7.90	17.83	18.67	18.83	19.69	21.04
	3H	5.40	6.16	6.40	7.18	8.55	19.65	20.41	20.66	21.43	22.80
	4H	5.69	6.41	6.71	7.44	8.82	20.29	21.01	21.31	22.03	23.41
	6H	5.94	6.61	6.98	7.64	9.03	20.71	21.37	21.74	22.40	23.79
	8H	6.01	6.64	7.05	7.69	9.08	20.82	21.45	21.86	22.50	23.88
	12H	6.03	6.63	7.07	7.67	9.08	20.88	21.48	21.92	22.52	23.93
4H	2H	11.88	12.60	12.91	13.63	15.00	18.10	18.82	19.13	19.85	21.23
	3H	13.45	14.05	14.48	15.10	16.49	20.13	20.74	21.17	21.79	23.18
	4H	13.54	14.09	14.59	15.14	16.55	20.89	21.44	21.93	22.49	23.90
	6H	13.55	14.03	14.61	15.10	16.51	21.42	21.89	22.47	22.96	24.37
	8H	13.53	13.97	14.58	15.04	16.46	21.57	22.01	22.62	23.08	24.50
	12H	13.49	13.89	14.56	14.96	16.39	21.65	22.06	22.73	23.13	24.56
8H	4H	14.98	15.42	16.03	16.48	17.91	20.95	21.39	22.00	22.46	23.88
	6H	15.22	15.59	16.30	16.69	18.11	21.56	21.93	22.64	23.04	24.46
	8H	15.24	15.56	16.32	16.65	18.09	21.78	22.10	22.86	23.19	24.63
	12H	15.20	15.49	16.29	16.57	18.05	21.91	22.20	23.00	23.28	24.76
12H	4H	15.12	15.52	16.19	16.59	18.02	20.90	21.30	21.97	22.38	23.81
	6H	15.47	15.80	16.56	16.88	18.32	21.55	21.87	22.63	22.96	24.40
	8H	15.54	15.83	16.63	16.91	18.39	21.77	22.05	22.86	23.14	24.62