

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936439

Luminaire Tested: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936439
REPORT IS A COMBINATION OF REPORTS P933447 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5552.1 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936439
CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63			63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51			51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42			42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35			35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30			30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26			26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22			22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20			20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	19	17			17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16			16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3403	3403	3403
5°	3324	3932	4575
10°	3013	5731	7584
15°	2561	7486	9158
20°	2083	8673	9333
25°	1737	9073	9143
30°	1465	9128	9126
35°	1294	8975	9363
40°	1127	8774	9606
45°	1020	8628	9644
50°	935	8496	9484
55°	894	8302	9063
60°	915	7934	8400
65°	950	7376	7488
70°	1010	6428	6326
75°	1114	5237	4936
80°	1208	3627	3327
85°	1055	1920	1702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9644 cd/sqm



TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.2	1.3
10°-20°	315.4	5.7
20°-30°	551.7	9.9
30°-40°	710.2	12.8
40°-50°	793.3	14.3
50°-60°	759.8	13.7
60°-70°	602.1	10.8
70°-80°	354.1	6.4
80°-90°	99.1	1.8
90°-100°	97.4	1.8
100°-110°	256.1	4.6
110°-120°	265.5	4.8
120°-130°	213.0	3.8
130°-140°	167.1	3.0
140°-150°	128.3	2.3
150°-160°	92.4	1.7
160°-170°	56.5	1.0
170°-180°	19.1	0.3
0°-30°	938.3	16.9
0°-40°	1648.5	29.7
0°-60°	3201.5	57.7
0°-90°	4256.8	76.7
90°-120°	619.0	11.1
90°-150°	1127.3	20.3
90°-180°	1295.0	23.3
0°-180°	5552.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	550	550	550	550	550	
5°	536	575	647	732	759	49
15°	402	741	1249	1514	1562	112
25°	256	840	1488	1553	1555	118
35°	173	803	1401	1481	1539	108
45°	118	640	1238	1419	1482	92
55°	85	407	1051	1221	1254	77
65°	67	216	780	877	890	67
75°	50	133	428	471	472	52
85°	18	41	106	117	118	19
90°	1	4	10	5	5	2
95°	13	50	168	86	59	14
105°	46	70	283	430	401	49
115°	82	100	227	452	516	81
125°	114	128	206	349	411	101
135°	136	150	200	281	319	105
145°	158	168	197	240	259	99
155°	178	183	197	216	223	82
165°	192	195	197	205	208	54
175°	200	200	199	201	201	19
180°	200	200	200	200	200	



TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	550.1	550.1	550.1	550.1	550.1	550.1	550.1	550.1	550.1	550.1	550.1
2.5°	550.1	550.1	553.7	555.5	559.0	560.7	564.3	567.9	578.4	580.2	583.8
5°	536.0	543.1	566.1	574.9	599.7	633.3	647.4	670.4	718.2	732.4	741.2
7.5°	514.8	530.7	587.3	601.4	663.4	751.9	789.0	838.5	914.6	951.7	981.8
10°	481.1	514.8	615.6	649.2	750.1	884.5	953.5	1022.5	1137.5	1188.8	1208.3
12.5°	444.0	498.9	645.7	691.7	836.7	1033.1	1116.2	1192.3	1323.2	1392.2	1402.8
15°	401.6	475.9	674.0	741.2	928.7	1156.9	1249.0	1342.7	1464.7	1514.2	1526.6
17.5°	364.5	458.2	700.5	771.3	999.5	1268.4	1362.1	1440.0	1539.1	1572.6	1581.5
20°	318.4	429.9	718.2	810.2	1073.8	1349.7	1440.0	1500.1	1567.4	1588.6	1592.1
22.5°	284.8	399.8	728.8	824.3	1123.3	1399.3	1475.3	1523.1	1569.1	1576.2	1578.0
25°	256.5	366.2	727.0	840.3	1165.8	1429.4	1487.7	1523.1	1549.7	1553.2	1553.2
27.5°	229.9	329.0	720.0	843.8	1197.6	1436.4	1482.4	1507.2	1519.6	1526.6	1526.6
30°	207.0	293.7	702.3	836.7	1211.7	1429.4	1466.5	1478.9	1491.3	1501.8	1507.2
32.5°	189.3	260.0	675.7	822.5	1213.5	1411.7	1438.2	1445.2	1462.9	1487.7	1496.6
35°	173.3	226.5	645.7	803.1	1202.9	1383.4	1401.1	1408.1	1443.5	1480.7	1493.0
37.5°	157.5	201.6	606.8	769.5	1187.0	1349.7	1362.1	1374.5	1429.4	1473.5	1487.7
40°	141.5	180.4	560.7	732.4	1162.2	1309.0	1319.6	1339.1	1411.7	1462.9	1477.1
42.5°	129.2	162.7	511.2	693.5	1130.4	1263.1	1278.9	1307.2	1390.4	1445.2	1461.2
45°	118.5	145.1	458.2	640.4	1089.7	1215.3	1238.3	1277.2	1365.6	1418.7	1432.9
47.5°	107.9	132.6	403.4	585.6	1045.4	1167.5	1197.6	1241.8	1332.1	1383.4	1395.7
50°	99.1	120.3	348.5	527.2	997.7	1116.2	1151.7	1197.6	1289.6	1337.3	1353.3
52.5°	92.0	109.7	297.2	468.8	942.9	1063.2	1103.8	1151.7	1238.3	1284.3	1294.9
55°	84.9	100.9	253.0	406.9	886.3	1006.5	1050.8	1096.8	1181.7	1220.6	1227.7
57.5°	81.4	93.7	215.8	348.5	826.1	942.9	992.4	1034.9	1114.4	1144.5	1151.7
60°	76.1	88.5	187.5	298.9	760.7	882.7	925.2	967.6	1034.9	1059.6	1064.9
62.5°	70.8	84.9	166.3	251.2	693.5	811.9	854.4	893.3	949.9	967.6	974.7
65°	67.2	81.4	150.4	215.8	624.5	737.7	780.1	813.7	859.8	877.4	880.9
67.5°	63.6	77.8	138.0	185.8	555.5	663.4	695.2	727.0	762.5	780.1	781.9
70°	58.4	74.3	127.4	164.5	484.7	578.4	605.0	638.6	666.9	675.7	681.1
72.5°	54.8	69.0	120.3	148.6	412.2	497.1	521.8	541.3	566.1	574.9	574.9
75°	49.5	61.9	113.2	132.6	337.9	406.9	428.1	447.6	467.0	470.6	465.2
77.5°	44.2	54.8	97.3	111.5	263.6	322.0	339.6	350.3	366.2	369.7	371.5
80°	37.1	47.8	76.1	86.7	191.0	237.1	249.4	258.2	272.4	272.4	276.0
82.5°	28.3	37.1	54.8	61.9	129.2	162.7	173.3	178.7	187.5	187.5	187.5
85°	17.7	23.0	35.3	40.7	77.8	99.1	106.1	107.9	115.0	116.8	116.8
87.5°	8.8	12.4	23.0	24.7	40.7	51.3	51.3	54.8	54.8	53.1	51.3
90°	1.3	2.4	3.5	3.7	5.9	8.7	10.2	9.0	6.8	5.1	5.1
92.5°	5.4	14.5	23.6	25.9	36.4	50.4	57.4	50.3	36.1	25.4	24.5
95°	12.9	29.5	46.2	50.4	89.5	141.7	167.7	149.7	113.5	86.5	83.5
97.5°	22.2	37.0	51.7	55.3	120.6	207.5	251.0	239.6	216.8	199.7	193.9
100°	29.5	42.8	56.2	59.5	131.9	228.4	276.6	277.4	279.1	280.4	273.4
102.5°	35.7	48.2	60.6	63.7	137.1	234.9	283.9	298.4	327.5	349.4	343.4
105°	46.1	56.7	67.2	69.9	140.9	235.7	283.0	315.6	380.9	429.8	426.6
107.5°	56.9	66.7	76.5	79.0	141.7	225.2	267.0	312.5	403.5	471.7	472.5
110°	64.1	73.0	81.9	84.1	140.6	215.9	253.6	304.5	406.1	482.4	485.7



TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	71.2	79.7	88.1	90.2	140.6	207.8	241.4	293.4	397.5	475.5	480.6
115°	81.9	89.8	97.6	99.5	141.9	198.4	226.7	276.9	377.1	452.3	459.4
117.5°	92.6	99.6	106.7	108.5	144.5	192.6	216.7	262.0	352.4	420.2	428.1
120°	98.7	105.4	112.0	113.7	146.7	190.8	212.7	254.0	336.7	398.7	406.4
122.5°	104.7	111.5	118.2	119.9	149.8	189.7	209.6	246.8	321.3	377.1	384.7
125°	114.0	120.1	126.3	127.8	154.0	188.9	206.3	237.9	301.2	348.6	355.5
127.5°	121.5	127.6	133.9	135.4	158.1	188.3	203.4	230.6	284.9	325.6	331.5
130°	125.5	132.2	138.8	140.5	161.1	188.6	202.4	226.5	274.8	311.1	316.5
132.5°	129.7	136.4	143.0	144.7	163.6	188.9	201.5	223.1	266.4	298.8	303.6
135°	135.9	141.9	148.0	149.5	166.3	188.7	199.9	218.0	254.2	281.4	285.5
137.5°	142.2	148.2	154.2	155.7	170.3	189.9	199.6	214.9	245.6	268.5	271.9
140°	147.4	152.9	158.4	159.9	172.8	190.0	198.6	211.8	238.3	258.1	261.4
142.5°	151.4	156.5	161.7	162.9	174.8	190.7	198.6	210.2	233.5	250.9	253.7
145°	157.5	162.0	166.5	167.6	177.5	190.7	197.3	206.7	225.7	240.0	242.1
147.5°	163.7	168.1	172.5	173.5	181.5	192.0	197.3	204.8	219.7	230.9	232.6
150°	167.7	171.7	175.7	176.6	183.5	192.7	197.3	203.6	216.2	225.7	227.1
152.5°	171.9	174.9	177.9	178.6	184.9	193.2	197.3	202.6	213.4	221.5	222.6
155°	178.1	180.3	182.5	183.1	187.8	194.1	197.3	201.6	210.1	216.5	217.3
157.5°	182.6	184.8	186.9	187.5	190.8	195.1	197.3	200.6	207.3	212.3	212.8
160°	185.8	187.5	189.1	189.5	192.1	195.6	197.3	200.1	205.8	210.1	210.4
162.5°	188.8	190.0	191.3	191.6	193.5	196.0	197.3	199.7	204.5	208.2	208.4
165°	192.2	193.3	194.4	194.7	195.6	196.7	197.3	199.0	202.4	205.0	205.3
167.5°	195.2	195.8	196.3	196.5	197.2	198.2	198.6	199.8	202.0	203.7	203.8
170°	197.3	197.8	198.3	198.4	198.5	198.6	198.6	199.8	202.0	203.7	203.7
172.5°	198.3	198.4	198.6	198.6	198.6	198.6	198.6	199.5	201.3	202.6	202.5
175°	199.9	199.9	199.9	199.9	199.4	198.9	198.6	199.1	200.3	201.2	201.2
177.5°	199.9	199.9	199.9	199.9	199.5	199.1	198.9	199.3	200.2	200.9	200.8
180°	199.9	199.9	199.9	199.9	199.9	199.9	199.9	199.9	199.9	199.9	199.9



TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	550.1	550.1
2.5°	587.3	583.8
5°	755.3	758.9
7.5°	1017.1	1015.4
10°	1264.8	1280.7
12.5°	1445.2	1448.8
15°	1554.9	1562.0
17.5°	1597.4	1599.1
20°	1599.1	1595.6
22.5°	1579.7	1576.2
25°	1556.7	1554.9
27.5°	1535.5	1537.3
30°	1526.6	1531.9
32.5°	1526.6	1535.5
35°	1530.2	1539.1
37.5°	1528.4	1539.1
40°	1521.3	1533.7
42.5°	1501.8	1510.8
45°	1471.8	1482.4
47.5°	1432.9	1440.0
50°	1383.4	1390.4
52.5°	1321.4	1323.2
55°	1247.2	1254.2
57.5°	1167.5	1169.3
60°	1079.1	1084.4
62.5°	985.4	985.4
65°	886.3	889.8
67.5°	783.6	792.5
70°	679.3	681.1
72.5°	576.7	576.7
75°	470.6	472.3
77.5°	369.7	369.7
80°	274.2	276.0
82.5°	189.3	192.8
85°	118.5	118.5
87.5°	54.8	49.5
90°	5.1	5.1
92.5°	20.4	16.3
95°	71.1	58.9
97.5°	170.5	147.1
100°	245.6	217.8
102.5°	319.6	295.7
105°	413.8	401.0
107.5°	475.5	478.6
110°	499.1	512.5



TEST NUMBER: P936439
CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	501.1	521.6
115°	487.8	516.3
117.5°	459.7	491.2
120°	437.0	467.6
122.5°	414.9	445.1
125°	383.3	411.1
127.5°	355.0	378.5
130°	338.2	359.9
132.5°	323.0	342.5
135°	302.2	319.0
137.5°	285.6	299.3
140°	274.1	287.0
142.5°	264.7	275.7
145°	250.5	258.9
147.5°	239.6	246.5
150°	232.7	238.3
152.5°	226.8	231.1
155°	220.0	222.9
157.5°	214.8	216.7
160°	211.6	212.7
162.5°	209.5	210.6
165°	206.5	207.6
167.5°	204.3	204.8
170°	203.7	203.7
172.5°	202.1	201.7
175°	201.2	201.2
177.5°	200.3	199.9
180°	199.9	199.9



TEST NUMBER: P936439

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.39	8.62	8.07	9.33	10.15	20.55	21.79	21.23	22.49	23.32
	3H	8.12	9.23	8.81	9.95	10.81	22.41	23.53	23.11	24.24	25.10
	4H	8.43	9.49	9.15	10.21	11.08	23.07	24.12	23.78	24.85	25.72
	6H	8.70	9.68	9.43	10.41	11.30	23.52	24.49	24.24	25.23	26.12
	8H	8.78	9.71	9.52	10.47	11.36	23.65	24.58	24.38	25.33	26.22
	12H	8.81	9.70	9.56	10.45	11.37	23.72	24.61	24.47	25.36	26.28
4H	2H	14.64	15.69	15.35	16.42	17.29	20.87	21.92	21.59	22.65	23.52
	3H	16.24	17.12	16.97	17.89	18.78	22.94	23.83	23.67	24.59	25.48
	4H	16.35	17.16	17.09	17.92	18.84	23.72	24.53	24.47	25.29	26.21
	6H	16.38	17.08	17.15	17.87	18.80	24.28	24.98	25.04	25.77	26.70
	8H	16.37	17.03	17.14	17.81	18.75	24.45	25.11	25.22	25.89	26.83
	12H	16.34	16.94	17.13	17.74	18.69	24.56	25.15	25.35	25.96	26.91
8H	4H	17.82	18.48	18.59	19.26	20.20	23.82	24.47	24.58	25.26	26.20
	6H	18.08	18.63	18.88	19.45	20.40	24.46	25.01	25.26	25.83	26.77
	8H	18.11	18.59	18.92	19.42	20.38	24.68	25.17	25.49	25.99	26.95
	12H	18.09	18.52	18.91	19.34	20.35	24.84	25.27	25.65	26.09	27.10
12H	4H	17.98	18.58	18.77	19.38	20.33	23.79	24.38	24.58	25.19	26.13
	6H	18.34	18.83	19.15	19.66	20.62	24.45	24.93	25.26	25.76	26.72
	8H	18.43	18.86	19.25	19.68	20.69	24.69	25.12	25.51	25.94	26.95