

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936445

Luminaire Tested: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936445
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7403.4 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936445
CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66				63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55				51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45				42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38				35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33				30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28				26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25				22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22				20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20				17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3404	3404	3404
5°	3325	3934	4575
10°	3016	5734	7585
15°	2564	7492	9159
20°	2087	8682	9334
25°	1741	9085	9144
30°	1468	9143	9127
35°	1298	8991	9363
40°	1131	8793	9607
45°	1025	8649	9645
50°	939	8519	9485
55°	900	8328	9065
60°	921	7963	8401
65°	958	7407	7489
70°	1020	6459	6326
75°	1132	5266	4937
80°	1235	3653	3327
85°	1099	1939	1703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9645 cd/sqm



TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	1.3
10°-20°	420.6	5.7
20°-30°	735.7	9.9
30°-40°	947.0	12.8
40°-50°	1057.8	14.3
50°-60°	1013.1	13.7
60°-70°	802.9	10.8
70°-80°	472.1	6.4
80°-90°	132.2	1.8
90°-100°	129.9	1.8
100°-110°	341.4	4.6
110°-120°	354.0	4.8
120°-130°	284.0	3.8
130°-140°	222.8	3.0
140°-150°	171.0	2.3
150°-160°	123.2	1.7
160°-170°	75.4	1.0
170°-180°	25.5	0.3
0°-30°	1251.2	16.9
0°-40°	2198.2	29.7
0°-60°	4269.1	57.7
0°-90°	5676.3	76.7
90°-120°	825.3	11.1
90°-150°	1503.1	20.3
90°-180°	1727.0	23.3
0°-180°	7403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	715	767	863	977	1012	66
15°	536	988	1665	2019	2083	149
25°	342	1120	1984	2071	2074	158
35°	231	1071	1868	1974	2052	144
45°	158	854	1651	1892	1977	122
55°	113	542	1401	1628	1672	103
65°	90	288	1040	1170	1187	89
75°	66	177	571	628	630	69
85°	24	54	142	156	158	25
90°	2	5	14	7	7	3
95°	17	67	224	115	78	19
105°	62	93	378	573	535	65
115°	109	133	302	603	688	108
125°	152	170	275	465	548	135
135°	181	199	266	375	425	140
145°	210	224	263	320	345	132
155°	237	244	263	289	297	109
165°	256	260	263	273	277	72
175°	266	266	265	268	268	25
180°	266	266	266	266	266	



TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	733.6	733.6	733.6	733.6	733.6	733.6	733.6	733.6	733.6	733.6	733.6
2.5°	733.6	733.6	738.4	740.7	745.4	747.7	752.5	757.2	771.4	773.7	778.5
5°	714.7	724.2	754.9	766.7	799.7	844.5	863.3	894.0	957.7	976.6	988.4
7.5°	686.4	707.7	783.2	802.0	884.6	1002.5	1052.0	1118.1	1219.6	1269.1	1309.2
10°	641.6	686.4	820.9	865.8	1000.2	1179.4	1271.4	1363.5	1516.7	1585.2	1611.1
12.5°	592.1	665.2	861.0	922.3	1115.8	1377.6	1488.4	1589.9	1764.4	1856.5	1870.6
15°	535.5	634.6	898.8	988.4	1238.4	1542.7	1665.4	1790.4	1953.1	2019.2	2035.7
17.5°	485.9	611.0	934.1	1028.5	1332.8	1691.3	1816.4	1920.1	2052.2	2097.0	2108.9
20°	424.6	573.2	957.7	1080.3	1431.9	1799.9	1920.1	2000.4	2090.0	2118.3	2123.0
22.5°	379.8	533.1	971.9	1099.3	1497.9	1865.9	1967.3	2031.0	2092.4	2101.8	2104.2
25°	342.1	488.3	969.5	1120.5	1554.5	1906.0	1983.8	2031.0	2066.4	2071.1	2071.1
27.5°	306.6	438.7	960.1	1125.2	1597.0	1915.5	1976.8	2009.8	2026.3	2035.7	2035.7
30°	276.0	391.6	936.4	1115.8	1615.8	1906.0	1955.6	1972.1	1988.6	2002.7	2009.8
32.5°	252.4	346.8	901.1	1096.9	1618.2	1882.4	1917.8	1927.3	1950.8	1983.8	1995.6
35°	231.2	302.0	861.0	1071.0	1604.0	1844.7	1868.3	1877.7	1924.8	1974.4	1990.9
37.5°	209.9	268.9	809.1	1026.2	1582.8	1799.9	1816.4	1832.9	1906.0	1964.9	1983.8
40°	188.7	240.7	747.7	976.6	1549.8	1745.6	1759.7	1785.7	1882.4	1950.8	1969.7
42.5°	172.2	217.0	681.7	924.7	1507.4	1684.3	1705.5	1743.2	1854.1	1927.3	1948.5
45°	158.1	193.4	611.0	853.9	1453.1	1620.6	1651.3	1703.1	1821.0	1891.8	1910.7
47.5°	143.9	176.9	537.8	780.8	1394.1	1556.9	1597.0	1656.0	1776.2	1844.7	1861.2
50°	132.1	160.4	464.7	702.9	1330.5	1488.4	1535.7	1597.0	1719.6	1783.4	1804.5
52.5°	122.6	146.2	396.3	625.1	1257.3	1417.7	1471.9	1535.7	1651.3	1712.6	1726.7
55°	113.2	134.4	337.3	542.5	1181.8	1342.2	1401.1	1462.6	1575.7	1627.6	1637.1
57.5°	108.5	125.1	287.8	464.7	1101.6	1257.3	1323.3	1380.0	1486.1	1526.2	1535.7
60°	101.4	117.9	250.0	398.6	1014.4	1177.1	1233.7	1290.3	1380.0	1413.0	1420.1
62.5°	94.3	113.2	221.7	335.0	924.7	1082.7	1139.3	1191.3	1266.7	1290.3	1299.7
65°	89.6	108.5	200.5	287.8	832.7	983.7	1040.3	1085.1	1146.4	1170.0	1174.8
67.5°	84.9	103.8	184.0	247.7	740.7	884.6	927.1	969.5	1016.7	1040.3	1042.7
70°	77.8	99.1	169.9	219.4	646.3	771.4	806.7	851.6	889.3	901.1	908.2
72.5°	73.1	92.0	160.4	198.2	549.6	662.9	695.9	721.9	754.9	766.7	766.7
75°	66.1	82.6	150.9	176.9	450.6	542.5	570.8	596.8	622.8	627.5	620.4
77.5°	59.0	73.1	129.7	148.6	351.5	429.4	452.9	467.0	488.3	493.0	495.4
80°	49.5	63.7	101.4	115.6	254.8	316.1	332.6	344.4	363.3	363.3	368.0
82.5°	37.8	49.5	73.1	82.6	172.2	217.0	231.2	238.2	250.0	250.0	250.0
85°	23.6	30.7	47.2	54.3	103.8	132.1	141.6	143.9	153.4	155.7	155.7
87.5°	11.8	16.5	30.7	33.0	54.3	68.4	68.4	73.1	73.1	70.8	68.4
90°	1.8	3.2	4.6	5.0	7.9	11.7	13.6	12.1	9.0	6.8	6.8
92.5°	7.1	19.3	31.5	34.5	48.6	67.2	76.5	67.0	48.2	34.0	32.7
95°	17.1	39.4	61.7	67.2	119.3	188.9	223.7	199.6	151.5	115.3	111.2
97.5°	29.7	49.4	68.9	73.8	160.8	276.7	334.7	319.6	289.1	266.3	258.5
100°	39.4	57.1	74.9	79.4	175.8	304.5	368.8	370.0	372.2	373.9	364.6
102.5°	47.6	64.2	80.8	84.9	182.8	313.3	378.6	397.9	436.7	465.8	457.8
105°	61.5	75.6	89.7	93.2	188.0	314.3	377.5	421.0	507.9	573.1	568.8
107.5°	75.8	88.9	102.0	105.3	188.9	300.3	356.0	416.6	537.9	628.9	629.9
110°	85.5	97.3	109.2	112.1	187.5	287.9	338.1	405.9	541.5	643.1	647.6



TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	95.0	106.2	117.5	120.3	187.5	277.1	321.9	391.2	529.9	634.0	640.9
115°	109.3	119.6	130.1	132.6	189.2	264.7	302.3	369.2	502.9	603.1	612.6
117.5°	123.4	132.8	142.3	144.7	192.8	256.9	288.9	349.3	469.9	560.4	570.9
120°	131.6	140.5	149.4	151.7	195.7	254.3	283.6	338.7	448.9	531.6	541.7
122.5°	139.6	148.6	157.6	159.9	199.8	252.9	279.5	329.1	428.4	502.8	512.9
125°	152.0	160.2	168.3	170.4	205.3	251.8	275.0	317.1	401.5	464.7	474.0
127.5°	162.0	170.2	178.5	180.6	210.8	251.1	271.3	307.5	379.9	434.2	442.0
130°	167.4	176.3	185.1	187.4	214.9	251.5	269.8	302.1	366.5	414.8	422.0
132.5°	172.9	181.8	190.7	192.9	218.2	251.8	268.6	297.4	355.1	398.4	404.9
135°	181.1	189.2	197.4	199.4	221.7	251.5	266.4	290.6	338.9	375.2	380.7
137.5°	189.5	197.5	205.6	207.6	227.1	253.1	266.1	286.5	327.3	357.9	362.5
140°	196.5	203.9	211.3	213.2	230.4	253.3	264.8	282.5	317.8	344.2	348.5
142.5°	201.9	208.7	215.6	217.3	233.2	254.3	264.8	280.4	311.3	334.6	338.2
145°	210.1	216.1	222.0	223.5	236.7	254.3	263.1	275.7	301.1	320.1	322.9
147.5°	218.3	224.1	229.9	231.4	241.9	256.0	263.1	273.1	293.0	307.9	310.2
150°	223.7	229.0	234.1	235.5	244.7	256.9	263.1	271.4	288.3	300.9	302.8
152.5°	229.2	233.2	237.2	238.2	246.5	257.5	263.1	270.2	284.6	295.4	296.8
155°	237.4	240.4	243.3	244.0	250.4	258.9	263.1	268.8	280.2	288.8	289.7
157.5°	243.5	246.4	249.2	249.9	254.3	260.1	263.1	267.5	276.4	283.0	283.7
160°	247.6	249.8	252.1	252.6	256.1	260.7	263.1	266.9	274.5	280.2	280.6
162.5°	251.7	253.4	255.0	255.5	258.0	261.4	263.1	266.3	272.7	277.5	277.9
165°	256.3	257.8	259.3	259.7	260.8	262.3	263.1	265.4	269.9	273.4	273.8
167.5°	260.4	261.1	261.8	262.0	263.0	264.2	264.8	266.4	269.4	271.6	271.8
170°	263.1	263.8	264.5	264.7	264.8	264.8	264.8	266.4	269.4	271.6	271.6
172.5°	264.5	264.7	264.8	264.8	264.8	264.8	264.8	266.0	268.4	270.2	270.0
175°	266.4	266.4	266.4	266.4	265.9	265.2	264.8	265.6	267.1	268.2	268.2
177.5°	266.4	266.4	266.4	266.4	266.0	265.5	265.2	265.8	267.0	267.9	267.7
180°	266.4	266.4	266.4	266.4	266.4	266.4	266.4	266.4	266.4	266.4	266.4



TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	733.6	733.6
2.5°	783.2	778.5
5°	1007.2	1012.0
7.5°	1356.3	1354.0
10°	1686.6	1707.8
12.5°	1927.3	1932.0
15°	2073.5	2082.9
17.5°	2130.1	2132.5
20°	2132.5	2127.7
22.5°	2106.5	2101.8
25°	2075.9	2073.5
27.5°	2047.5	2049.9
30°	2035.7	2042.9
32.5°	2035.7	2047.5
35°	2040.4	2052.2
37.5°	2038.1	2052.2
40°	2028.7	2045.2
42.5°	2002.7	2014.5
45°	1962.6	1976.8
47.5°	1910.7	1920.1
50°	1844.7	1854.1
52.5°	1762.1	1764.4
55°	1663.0	1672.5
57.5°	1556.9	1559.2
60°	1438.9	1446.0
62.5°	1313.9	1313.9
65°	1181.8	1186.6
67.5°	1045.0	1056.8
70°	905.8	908.2
72.5°	769.0	769.0
75°	627.5	629.8
77.5°	493.0	493.0
80°	365.6	368.0
82.5°	252.4	257.2
85°	158.1	158.1
87.5°	73.1	66.1
90°	6.8	6.8
92.5°	27.2	21.8
95°	94.9	78.5
97.5°	227.3	196.1
100°	327.5	290.4
102.5°	426.0	394.3
105°	551.7	534.6
107.5°	634.0	638.1
110°	665.4	683.2



TEST NUMBER: P936445
CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	668.2	695.5
115°	650.5	688.4
117.5°	613.0	655.0
120°	582.6	623.5
122.5°	553.2	593.4
125°	511.1	548.2
127.5°	473.3	504.6
130°	451.0	479.9
132.5°	430.8	456.7
135°	403.0	425.3
137.5°	380.8	399.1
140°	365.5	382.7
142.5°	352.9	367.6
145°	334.0	345.1
147.5°	319.4	328.7
150°	310.3	317.8
152.5°	302.4	308.0
155°	293.4	297.2
157.5°	286.4	288.9
160°	282.1	283.6
162.5°	279.3	280.7
165°	275.3	276.8
167.5°	272.4	273.1
170°	271.6	271.6
172.5°	269.5	268.9
175°	268.2	268.2
177.5°	267.1	266.4
180°	266.4	266.4



TEST NUMBER: P936445

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.39	8.63	8.07	9.33	10.16	20.57	21.80	21.25	22.51	23.34
	3H	8.12	9.24	8.82	9.95	10.81	22.44	23.55	23.13	24.27	25.13
	4H	8.44	9.49	9.15	10.22	11.09	23.10	24.15	23.81	24.88	25.75
	6H	8.71	9.68	9.44	10.42	11.31	23.55	24.52	24.27	25.26	26.15
	8H	8.79	9.72	9.52	10.48	11.37	23.68	24.61	24.42	25.37	26.26
	12H	8.82	9.71	9.56	10.46	11.38	23.76	24.65	24.50	25.40	26.32
4H	2H	14.65	15.70	15.37	16.43	17.30	20.89	21.94	21.60	22.67	23.54
	3H	16.25	17.14	16.98	17.90	18.79	22.97	23.85	23.70	24.61	25.51
	4H	16.36	17.17	17.11	17.93	18.85	23.75	24.56	24.50	25.32	26.24
	6H	16.39	17.10	17.16	17.88	18.81	24.31	25.01	25.07	25.80	26.73
	8H	16.38	17.04	17.15	17.82	18.76	24.48	25.14	25.25	25.92	26.87
	12H	16.36	16.95	17.15	17.76	18.70	24.60	25.19	25.39	26.00	26.94
8H	4H	17.84	18.50	18.61	19.28	20.22	23.84	24.50	24.61	25.28	26.22
	6H	18.10	18.65	18.90	19.47	20.41	24.49	25.04	25.29	25.86	26.80
	8H	18.12	18.61	18.93	19.43	20.39	24.71	25.20	25.52	26.03	26.98
	12H	18.11	18.54	18.92	19.35	20.37	24.88	25.31	25.69	26.12	27.14
12H	4H	18.00	18.59	18.79	19.40	20.35	23.81	24.41	24.60	25.21	26.16
	6H	18.36	18.85	19.17	19.67	20.63	24.48	24.97	25.29	25.79	26.75
	8H	18.45	18.88	19.26	19.70	20.71	24.73	25.16	25.54	25.97	26.99