

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936448

Luminaire Tested: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936448
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7930.7 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936448
CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66				63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55				51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45				42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38				35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33				30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28				26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25				22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22				20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20				17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3646	3646	3646
5°	3562	4214	4901
10°	3231	6143	8125
15°	2746	8026	9811
20°	2236	9300	9999
25°	1865	9732	9795
30°	1573	9794	9777
35°	1391	9631	10030
40°	1211	9420	10291
45°	1097	9265	10332
50°	1006	9126	10160
55°	963	8921	9710
60°	986	8530	8999
65°	1026	7934	8022
70°	1094	6920	6776
75°	1213	5642	5289
80°	1325	3913	3564
85°	1174	2077	1824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10332 cd/sqm



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	1.3
10°-20°	450.5	5.7
20°-30°	788.1	9.9
30°-40°	1014.5	12.8
40°-50°	1133.1	14.3
50°-60°	1085.3	13.7
60°-70°	860.1	10.8
70°-80°	505.8	6.4
80°-90°	141.6	1.8
90°-100°	139.1	1.8
100°-110°	365.7	4.6
110°-120°	379.2	4.8
120°-130°	304.2	3.8
130°-140°	238.7	3.0
140°-150°	183.2	2.3
150°-160°	131.9	1.7
160°-170°	80.7	1.0
170°-180°	27.3	0.3
0°-30°	1340.3	16.9
0°-40°	2354.7	29.7
0°-60°	4573.1	57.7
0°-90°	6080.6	76.7
90°-120°	884.1	11.1
90°-150°	1610.2	20.3
90°-180°	1850.0	23.3
0°-180°	7930.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	766	821	925	1046	1084	71
15°	574	1059	1784	2163	2231	160
25°	366	1200	2125	2219	2221	169
35°	248	1147	2001	2115	2198	155
45°	169	915	1769	2027	2118	131
55°	121	581	1501	1744	1792	111
65°	96	308	1114	1253	1271	95
75°	71	190	612	672	675	74
85°	25	58	152	167	169	27
90°	2	5	14	7	7	3
95°	18	72	240	124	84	20
105°	66	100	404	614	573	70
115°	117	142	324	646	737	116
125°	163	182	295	498	587	145
135°	194	214	285	402	456	150
145°	225	239	282	343	370	141
155°	254	261	282	309	318	117
165°	274	278	282	293	296	77
175°	285	285	284	287	287	27
180°	285	285	285	285	285	



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9	785.9
2.5°	785.9	785.9	791.0	793.4	798.5	801.0	806.1	811.1	826.3	828.8	833.9
5°	765.6	775.8	808.7	821.3	856.7	904.7	924.8	957.7	1025.9	1046.2	1058.8
7.5°	735.3	758.1	839.0	859.1	947.6	1073.9	1127.0	1197.7	1306.4	1359.5	1402.4
10°	687.3	735.3	879.4	927.4	1071.4	1263.4	1362.0	1460.6	1624.8	1698.1	1725.8
12.5°	634.2	712.6	922.3	988.0	1195.2	1475.7	1594.5	1703.2	1890.1	1988.7	2003.8
15°	573.6	679.8	962.8	1058.8	1326.6	1652.6	1784.0	1917.9	2092.2	2163.0	2180.7
17.5°	520.6	654.5	1000.7	1101.7	1427.7	1811.8	1945.8	2056.9	2198.4	2246.4	2259.1
20°	454.9	614.1	1025.9	1157.3	1533.8	1928.1	2056.9	2142.8	2238.8	2269.1	2274.2
22.5°	406.9	571.0	1041.1	1177.6	1604.6	1998.8	2107.4	2175.6	2241.4	2251.5	2254.0
25°	366.4	523.0	1038.5	1200.3	1665.2	2041.8	2125.1	2175.6	2213.6	2218.7	2218.7
27.5°	328.5	470.0	1028.5	1205.4	1710.7	2051.9	2117.6	2153.0	2170.7	2180.7	2180.7
30°	295.7	419.5	1003.1	1195.2	1730.9	2041.8	2094.8	2112.5	2130.2	2145.3	2153.0
32.5°	270.4	371.5	965.3	1175.0	1733.5	2016.5	2054.4	2064.5	2089.8	2125.1	2137.8
35°	247.7	323.5	922.3	1147.2	1718.3	1976.1	2001.3	2011.4	2061.9	2115.0	2132.7
37.5°	224.9	288.1	866.7	1099.2	1695.5	1928.1	1945.8	1963.4	2041.8	2104.9	2125.1
40°	202.1	257.8	801.0	1046.2	1660.1	1869.9	1885.0	1912.9	2016.5	2089.8	2109.9
42.5°	184.4	232.5	730.2	990.5	1614.7	1804.2	1827.0	1867.3	1986.1	2064.5	2087.3
45°	169.3	207.2	654.5	914.7	1556.6	1736.0	1768.9	1824.4	1950.7	2026.6	2046.8
47.5°	154.1	189.5	576.1	836.4	1493.4	1667.8	1710.7	1773.9	1902.7	1976.1	1993.8
50°	141.5	171.8	497.8	753.0	1425.2	1594.5	1645.0	1710.7	1842.1	1910.4	1933.0
52.5°	131.4	156.6	424.5	669.6	1346.8	1518.6	1576.8	1645.0	1768.9	1834.6	1849.7
55°	121.2	144.0	361.3	581.2	1266.0	1437.8	1500.9	1566.7	1688.0	1743.5	1753.7
57.5°	116.3	134.0	308.3	497.8	1180.0	1346.8	1417.6	1478.3	1592.0	1634.9	1645.0
60°	108.6	126.3	267.8	427.0	1086.6	1260.9	1321.6	1382.2	1478.3	1513.7	1521.2
62.5°	101.1	121.2	237.5	358.9	990.5	1159.9	1220.5	1276.1	1356.9	1382.2	1392.3
65°	96.0	116.3	214.8	308.3	892.0	1053.7	1114.3	1162.3	1228.0	1253.4	1258.4
67.5°	90.9	111.2	197.1	265.3	793.4	947.6	993.1	1038.5	1089.1	1114.3	1116.9
70°	83.4	106.1	182.0	235.0	692.4	826.3	864.2	912.2	952.7	965.3	972.8
72.5°	78.3	98.6	171.8	212.3	588.7	710.1	745.4	773.3	808.7	821.3	821.3
75°	70.8	88.4	161.7	189.5	482.7	581.2	611.5	639.3	667.1	672.2	664.6
77.5°	63.2	78.3	138.9	159.2	376.5	459.9	485.2	500.3	523.0	528.1	530.7
80°	53.1	68.3	108.6	123.8	272.9	338.6	356.3	368.9	389.2	389.2	394.2
82.5°	40.4	53.1	78.3	88.4	184.4	232.5	247.7	255.2	267.8	267.8	267.8
85°	25.2	32.9	50.6	58.1	111.2	141.5	151.7	154.1	164.3	166.8	166.8
87.5°	12.6	17.7	32.9	35.4	58.1	73.2	73.2	78.3	78.3	75.8	73.2
90°	1.9	3.4	5.0	5.4	8.4	12.5	14.5	12.9	9.7	7.3	7.3
92.5°	7.6	20.7	33.8	37.0	52.0	72.0	81.9	71.8	51.6	36.4	35.0
95°	18.4	42.2	66.1	72.0	127.8	202.3	239.6	213.8	162.3	123.5	119.1
97.5°	31.8	52.9	73.8	79.1	172.2	296.4	358.6	342.3	309.7	285.2	276.9
100°	42.2	61.2	80.2	85.0	188.4	326.2	395.1	396.3	398.7	400.5	390.6
102.5°	51.0	68.8	86.5	90.9	195.8	335.6	405.5	426.3	467.8	498.9	490.4
105°	65.9	81.0	96.1	99.8	201.4	336.7	404.4	450.9	544.1	613.9	609.3
107.5°	81.2	95.2	109.3	112.8	202.3	321.7	381.3	446.3	576.2	673.6	674.8
110°	91.6	104.2	116.9	120.1	200.8	308.4	362.2	434.8	580.0	688.9	693.7



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	101.7	113.8	125.8	128.9	200.9	296.8	344.8	419.1	567.7	679.2	686.5
115°	117.0	128.1	139.3	142.1	202.7	283.5	323.9	395.5	538.7	646.1	656.2
117.5°	132.1	142.3	152.4	155.0	206.5	275.2	309.5	374.2	503.3	600.3	611.6
120°	140.9	150.5	160.1	162.5	209.6	272.4	303.8	362.8	480.9	569.4	580.3
122.5°	149.5	159.2	168.9	171.3	214.0	270.9	299.4	352.5	458.9	538.6	549.4
125°	162.8	171.6	180.3	182.5	219.9	269.7	294.6	339.7	430.1	497.8	507.7
127.5°	173.5	182.3	191.2	193.4	225.9	269.0	290.6	329.4	407.0	465.1	473.5
130°	179.3	188.8	198.3	200.7	230.2	269.5	289.1	323.6	392.6	444.3	452.1
132.5°	185.2	194.8	204.2	206.6	233.7	269.7	287.7	318.6	380.4	426.7	433.7
135°	194.0	202.7	211.4	213.6	237.5	269.5	285.4	311.3	363.1	401.9	407.8
137.5°	203.0	211.6	220.2	222.4	243.3	271.1	285.0	306.9	350.6	383.4	388.3
140°	210.5	218.4	226.3	228.3	246.8	271.4	283.7	302.6	340.4	368.7	373.3
142.5°	216.3	223.6	230.9	232.7	249.8	272.4	283.7	300.3	333.5	358.4	362.3
145°	225.1	231.5	237.8	239.4	253.6	272.4	281.8	295.4	322.5	342.9	345.9
147.5°	233.9	240.1	246.3	247.8	259.1	274.2	281.8	292.5	313.8	329.8	332.3
150°	239.6	245.3	250.8	252.2	262.1	275.2	281.8	290.8	308.9	322.3	324.3
152.5°	245.6	249.8	254.1	255.1	264.0	275.9	281.8	289.4	304.8	316.4	317.9
155°	254.3	257.5	260.7	261.4	268.2	277.3	281.8	287.9	300.1	309.3	310.3
157.5°	260.8	263.9	267.0	267.7	272.4	278.6	281.8	286.6	296.0	303.2	303.9
160°	265.2	267.6	270.0	270.6	274.3	279.3	281.8	285.9	294.0	300.1	300.5
162.5°	269.6	271.5	273.2	273.7	276.3	280.0	281.8	285.2	292.1	297.3	297.7
165°	274.5	276.1	277.8	278.2	279.4	281.0	281.8	284.3	289.2	292.9	293.3
167.5°	278.9	279.7	280.5	280.6	281.7	283.0	283.7	285.3	288.6	291.0	291.2
170°	281.8	282.6	283.3	283.5	283.6	283.7	283.7	285.3	288.6	291.0	291.0
172.5°	283.3	283.5	283.7	283.7	283.7	283.7	283.7	284.9	287.5	289.4	289.2
175°	285.4	285.4	285.4	285.4	284.8	284.1	283.7	284.5	286.1	287.3	287.3
177.5°	285.4	285.4	285.4	285.4	284.9	284.4	284.1	284.8	286.0	287.0	286.8
180°	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	785.9	785.9
2.5°	839.0	833.9
5°	1079.0	1084.0
7.5°	1452.9	1450.4
10°	1806.7	1829.5
12.5°	2064.5	2069.6
15°	2221.1	2231.3
17.5°	2281.8	2284.3
20°	2284.3	2279.3
22.5°	2256.5	2251.5
25°	2223.7	2221.1
27.5°	2193.3	2195.9
30°	2180.7	2188.3
32.5°	2180.7	2193.3
35°	2185.8	2198.4
37.5°	2183.3	2198.4
40°	2173.1	2190.8
42.5°	2145.3	2157.9
45°	2102.4	2117.6
47.5°	2046.8	2056.9
50°	1976.1	1986.1
52.5°	1887.6	1890.1
55°	1781.5	1791.6
57.5°	1667.8	1670.3
60°	1541.4	1549.0
62.5°	1407.5	1407.5
65°	1266.0	1271.1
67.5°	1119.4	1132.0
70°	970.3	972.8
72.5°	823.8	823.8
75°	672.2	674.7
77.5°	528.1	528.1
80°	391.7	394.2
82.5°	270.4	275.5
85°	169.3	169.3
87.5°	78.3	70.8
90°	7.3	7.3
92.5°	29.2	23.3
95°	101.6	84.0
97.5°	243.4	210.1
100°	350.8	311.0
102.5°	456.4	422.4
105°	591.0	572.7
107.5°	679.2	683.6
110°	712.7	731.9



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	715.8	745.1
115°	696.9	737.4
117.5°	656.6	701.7
120°	624.1	667.9
122.5°	592.6	635.7
125°	547.5	587.3
127.5°	507.0	540.5
130°	483.1	514.0
132.5°	461.5	489.2
135°	431.7	455.6
137.5°	407.9	427.5
140°	391.6	409.9
142.5°	378.1	393.8
145°	357.8	369.7
147.5°	342.1	352.1
150°	332.4	340.4
152.5°	324.0	330.0
155°	314.3	318.3
157.5°	306.7	309.5
160°	302.2	303.8
162.5°	299.2	300.7
165°	294.9	296.5
167.5°	291.8	292.5
170°	291.0	291.0
172.5°	288.7	288.1
175°	287.3	287.3
177.5°	286.1	285.4
180°	285.4	285.4



TEST NUMBER: P936448

CATALOG NUMBER: SQ4-FB-025U-100D-92765-1D-UNV-STD-W-8-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.63	8.87	8.31	9.57	10.40	20.81	22.04	21.49	22.75	23.58
	3H	8.36	9.48	9.06	10.19	11.05	22.68	23.79	23.37	24.50	25.37
	4H	8.68	9.73	9.39	10.46	11.33	23.34	24.39	24.05	25.12	25.99
	6H	8.95	9.92	9.67	10.66	11.55	23.79	24.76	24.51	25.50	26.39
	8H	9.03	9.96	9.76	10.71	11.60	23.92	24.85	24.66	25.61	26.50
	12H	9.06	9.95	9.80	10.70	11.62	24.00	24.89	24.74	25.64	26.56
4H	2H	14.89	15.94	15.60	16.67	17.54	21.13	22.18	21.84	22.91	23.78
	3H	16.49	17.38	17.22	18.14	19.03	23.21	24.09	23.94	24.85	25.74
	4H	16.60	17.41	17.35	18.17	19.09	23.99	24.80	24.73	25.56	26.48
	6H	16.63	17.34	17.40	18.12	19.05	24.55	25.25	25.31	26.04	26.97
	8H	16.62	17.28	17.39	18.06	19.00	24.72	25.38	25.49	26.16	27.10
	12H	16.60	17.19	17.39	18.00	18.94	24.83	25.43	25.62	26.23	27.18
8H	4H	18.08	18.73	18.85	19.52	20.46	24.08	24.74	24.85	25.52	26.46
	6H	18.34	18.88	19.14	19.71	20.65	24.73	25.27	25.53	26.10	27.04
	8H	18.36	18.85	19.17	19.67	20.63	24.95	25.44	25.76	26.27	27.22
	12H	18.35	18.78	19.16	19.59	20.61	25.12	25.55	25.93	26.36	27.38
12H	4H	18.24	18.83	19.03	19.64	20.59	24.05	24.65	24.84	25.45	26.40
	6H	18.60	19.09	19.41	19.91	20.87	24.72	25.20	25.53	26.03	26.99
	8H	18.69	19.12	19.50	19.93	20.95	24.96	25.39	25.78	26.21	27.23