

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936640

Luminaire Tested: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936640
REPORT IS A COMBINATION OF REPORTS P933477 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4919.3 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936640
CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	43	42	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	39	37	35	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	24	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13
8	51	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1760	1760	1760
5°	1719	2034	2366
10°	1559	2964	3922
15°	1324	3871	4736
20°	1078	4486	4827
25°	899	4693	4729
30°	758	4721	4720
35°	670	4641	4842
40°	583	4539	4969
45°	527	4463	4988
50°	483	4394	4906
55°	462	4294	4689
60°	474	4104	4345
65°	490	3815	3873
70°	522	3325	3272
75°	578	2708	2553
80°	625	1876	1720
85°	549	994	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4988 cd/sqm



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.8	0.7
10°-20°	163.1	3.3
20°-30°	285.4	5.8
30°-40°	367.3	7.5
40°-50°	410.3	8.3
50°-60°	393.0	8.0
60°-70°	311.4	6.3
70°-80°	183.1	3.7
80°-90°	52.5	1.1
90°-100°	204.3	4.2
100°-110°	537.0	10.9
110°-120°	556.8	11.3
120°-130°	446.6	9.1
130°-140°	350.4	7.1
140°-150°	269.0	5.5
150°-160°	193.7	3.9
160°-170°	118.5	2.4
170°-180°	40.0	0.8
0°-30°	485.3	9.9
0°-40°	852.6	17.3
0°-60°	1655.9	33.7
0°-90°	2202.9	44.8
90°-120°	1298.1	26.4
90°-150°	2364.1	48.1
90°-180°	2716.0	55.2
0°-180°	4919.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	284	284	284	284	284	
5°	277	297	335	379	392	26
15°	208	383	646	783	808	58
25°	133	435	770	803	804	61
35°	90	415	725	766	796	56
45°	61	331	640	734	767	47
55°	44	210	544	631	649	40
65°	35	112	404	454	460	34
75°	26	69	221	243	244	27
85°	9	21	55	60	61	10
90°	3	8	21	11	11	3
95°	27	106	352	181	123	30
105°	97	146	594	901	841	103
115°	172	209	476	949	1083	170
125°	239	268	432	731	862	212
135°	285	314	419	590	669	220
145°	330	352	414	503	543	207
155°	374	384	414	454	467	172
165°	403	408	414	430	435	114
175°	419	419	416	422	422	40
180°	419	419	419	419	419	



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5
2.5°	284.5	284.5	286.4	287.3	289.2	290.1	291.9	293.7	299.2	300.1	301.9
5°	277.3	280.9	292.8	297.4	310.2	327.6	334.8	346.8	371.5	378.8	383.4
7.5°	266.3	274.5	303.7	311.1	343.1	388.9	408.1	433.7	473.0	492.3	507.9
10°	248.9	266.3	318.4	335.8	388.0	457.5	493.2	528.9	588.4	614.8	624.9
12.5°	229.7	258.1	333.9	357.8	432.8	534.3	577.3	616.7	684.4	720.1	725.5
15°	207.7	246.1	348.6	383.4	480.4	598.4	645.9	694.5	757.6	783.2	789.7
17.5°	188.5	237.0	362.3	399.0	516.9	656.0	704.5	744.8	796.0	813.4	817.9
20°	164.7	222.3	371.5	419.1	555.4	698.1	744.8	775.9	810.7	821.7	823.5
22.5°	147.3	206.8	377.0	426.3	581.0	723.7	763.1	787.7	811.6	815.2	816.1
25°	132.7	189.4	376.0	434.6	603.0	739.3	769.5	787.7	801.5	803.3	803.3
27.5°	119.0	170.2	372.4	436.4	619.5	743.0	766.7	779.6	785.9	789.7	789.7
30°	107.1	151.9	363.2	432.8	626.7	739.3	758.5	764.9	771.3	776.8	779.6
32.5°	97.9	134.5	349.5	425.4	627.6	730.2	743.9	747.5	756.6	769.5	774.1
35°	89.7	117.2	333.9	415.4	622.2	715.5	724.6	728.3	746.6	765.8	772.2
37.5°	81.4	104.3	313.8	398.1	613.9	698.1	704.5	711.0	739.3	762.2	769.5
40°	73.2	93.3	290.1	378.8	601.2	677.0	682.6	692.6	730.2	756.6	764.0
42.5°	66.8	84.1	264.4	358.7	584.6	653.3	661.5	676.1	719.2	747.5	755.7
45°	61.3	75.0	237.0	331.2	563.6	628.6	640.5	660.6	706.3	733.8	741.1
47.5°	55.9	68.6	208.6	302.8	540.8	603.9	619.5	642.3	689.0	715.5	721.9
50°	51.2	62.2	180.3	272.6	516.0	577.3	595.6	619.5	667.0	691.7	700.0
52.5°	47.6	56.8	153.7	242.5	487.7	549.9	571.0	595.6	640.5	664.3	669.8
55°	43.9	52.1	130.8	210.4	458.4	520.6	543.5	567.2	611.2	631.3	635.0
57.5°	42.1	48.5	111.6	180.3	427.3	487.7	513.3	535.2	576.4	592.0	595.6
60°	39.4	45.8	97.0	154.6	393.4	456.5	478.6	500.5	535.2	548.1	550.8
62.5°	36.6	43.9	86.1	129.9	358.7	420.0	441.9	462.1	491.3	500.5	504.1
65°	34.7	42.1	77.8	111.6	323.0	381.5	403.5	420.9	444.6	453.8	455.6
67.5°	32.9	40.3	71.4	96.1	287.3	343.1	359.6	376.0	394.3	403.5	404.4
70°	30.2	38.4	65.9	85.1	250.7	299.2	312.9	330.3	344.9	349.5	352.3
72.5°	28.4	35.7	62.2	76.9	213.2	257.1	269.9	280.0	292.8	297.4	297.4
75°	25.7	32.0	58.6	68.6	174.7	210.4	221.4	231.5	241.5	243.4	240.6
77.5°	22.8	28.4	50.3	57.7	136.4	166.6	175.7	181.2	189.4	191.2	192.1
80°	19.2	24.7	39.4	44.8	98.8	122.6	129.0	133.6	140.9	140.9	142.7
82.5°	14.6	19.2	28.4	32.0	66.8	84.1	89.7	92.4	97.0	97.0	97.0
85°	9.2	11.9	18.3	21.0	40.3	51.2	54.9	55.9	59.5	60.4	60.4
87.5°	4.5	6.4	11.9	12.8	21.0	26.6	26.6	28.4	28.4	27.5	26.6
90°	2.8	5.1	7.4	7.9	12.4	18.4	21.4	19.0	14.2	10.6	10.6
92.5°	11.3	30.4	49.5	54.3	76.3	105.7	120.3	105.4	75.7	53.4	51.3
95°	27.0	61.9	97.0	105.7	187.7	297.2	351.8	314.0	238.2	181.4	174.9
97.5°	46.7	77.6	108.4	116.2	253.0	435.4	526.5	502.6	454.6	418.7	406.4
100°	61.9	89.9	117.9	124.9	276.6	479.0	580.2	581.9	585.4	588.1	573.5
102.5°	74.8	101.0	127.1	133.6	287.5	492.8	595.4	625.8	686.9	732.6	720.2
105°	96.8	118.9	141.0	146.5	295.5	494.3	593.6	662.0	798.8	901.4	894.6
107.5°	119.3	139.9	160.5	165.6	297.1	472.3	559.9	655.2	846.0	989.0	990.7
110°	134.4	153.0	171.6	176.3	294.8	452.8	531.8	638.4	851.7	1011.6	1018.6



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.4	167.1	184.8	189.3	294.9	435.8	506.2	615.4	833.6	997.2	1008.0
115°	171.8	188.2	204.6	208.7	297.6	416.2	475.6	580.7	790.9	948.6	963.5
117.5°	194.0	208.9	223.8	227.5	303.2	404.1	454.5	549.3	739.1	881.3	897.9
120°	206.9	221.0	235.0	238.5	307.6	399.9	446.0	532.7	706.1	836.0	852.1
122.5°	219.7	233.8	247.9	251.4	314.1	397.7	439.5	517.6	673.8	790.8	806.7
125°	239.1	251.9	264.8	268.0	322.8	396.0	432.5	498.8	631.5	730.9	745.4
127.5°	254.8	267.8	280.8	284.1	331.6	395.0	426.6	483.6	597.4	682.8	695.1
130°	263.2	277.3	291.3	294.7	337.9	395.5	424.3	475.0	576.4	652.5	663.9
132.5°	272.0	286.0	300.0	303.5	343.1	396.0	422.4	467.8	558.5	626.6	636.7
135°	284.9	297.6	310.4	313.6	348.8	395.6	419.1	457.1	533.0	590.0	598.8
137.5°	298.1	310.7	323.3	326.5	357.1	398.0	418.4	450.5	514.8	563.0	570.2
140°	309.1	320.7	332.3	335.2	362.3	398.4	416.5	444.3	499.8	541.3	548.1
142.5°	317.5	328.2	338.9	341.7	366.6	399.9	416.5	440.9	489.6	526.1	532.0
145°	330.5	339.8	349.2	351.6	372.3	399.9	413.7	433.6	473.5	503.4	507.8
147.5°	343.4	352.5	361.7	363.9	380.5	402.6	413.7	429.3	460.7	484.3	487.9
150°	351.8	360.1	368.3	370.4	384.9	404.1	413.7	427.0	453.5	473.3	476.2
152.5°	360.5	366.8	373.0	374.6	387.6	405.0	413.7	425.0	447.6	464.6	466.7
155°	373.5	378.1	382.7	383.9	393.8	407.1	413.7	422.7	440.7	454.2	455.6
157.5°	383.0	387.5	392.1	393.1	400.0	409.2	413.7	420.7	434.7	445.2	446.2
160°	389.5	393.0	396.4	397.3	402.8	410.1	413.7	419.7	431.7	440.7	441.3
162.5°	396.0	398.6	401.2	401.9	405.8	411.1	413.7	418.8	428.9	436.4	437.0
165°	403.0	405.3	407.7	408.3	410.2	412.5	413.7	417.3	424.5	430.0	430.6
167.5°	409.4	410.5	411.7	412.0	413.5	415.5	416.5	418.9	423.6	427.2	427.4
170°	413.7	414.8	416.0	416.2	416.3	416.4	416.5	418.9	423.6	427.2	427.2
172.5°	416.0	416.2	416.4	416.5	416.5	416.5	416.5	418.3	422.1	424.9	424.7
175°	419.1	419.1	419.1	419.1	418.3	417.1	416.5	417.7	420.1	421.8	421.8
177.5°	419.1	419.1	419.1	419.1	418.4	417.5	417.1	418.0	419.9	421.3	421.0
180°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.1



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	284.5	284.5
2.5°	303.7	301.9
5°	390.7	392.5
7.5°	526.1	525.2
10°	654.2	662.4
12.5°	747.5	749.4
15°	804.3	807.9
17.5°	826.2	827.1
20°	827.1	825.3
22.5°	817.0	815.2
25°	805.2	804.3
27.5°	794.2	795.1
30°	789.7	792.4
32.5°	789.7	794.2
35°	791.5	796.0
37.5°	790.6	796.0
40°	786.8	793.3
42.5°	776.8	781.4
45°	761.3	766.7
47.5°	741.1	744.8
50°	715.5	719.2
52.5°	683.5	684.4
55°	645.0	648.8
57.5°	603.9	604.8
60°	558.2	560.9
62.5°	509.7	509.7
65°	458.4	460.2
67.5°	405.3	409.9
70°	351.4	352.3
72.5°	298.3	298.3
75°	243.4	244.3
77.5°	191.2	191.2
80°	141.8	142.7
82.5°	97.9	99.7
85°	61.3	61.3
87.5°	28.4	25.7
90°	10.6	10.6
92.5°	42.8	34.3
95°	149.2	123.4
97.5°	357.5	308.5
100°	515.1	456.7
102.5°	670.1	620.1
105°	867.8	840.9
107.5°	997.1	1003.7
110°	1046.5	1074.6



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1051.0	1093.9
115°	1023.1	1082.7
117.5°	964.0	1030.2
120°	916.4	980.7
122.5°	870.1	933.4
125°	803.8	862.2
127.5°	744.4	793.7
130°	709.3	754.8
132.5°	677.5	718.2
135°	633.9	669.0
137.5°	599.0	627.7
140°	574.9	601.8
142.5°	555.1	578.2
145°	525.3	542.8
147.5°	502.4	516.9
150°	488.0	499.8
152.5°	475.6	484.6
155°	461.5	467.4
157.5°	450.4	454.5
160°	443.6	446.0
162.5°	439.3	441.5
165°	433.0	435.4
167.5°	428.4	429.4
170°	427.2	427.2
172.5°	423.8	423.0
175°	421.8	421.8
177.5°	420.1	419.1
180°	419.1	419.1



TEST NUMBER: P936640

CATALOG NUMBER: SQ4-FB-050U-050D-92765-1D-UNV-STD-W-6-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.47	3.32	3.46	4.33	5.67	15.63	16.48	16.63	17.49	18.83
	3H	3.17	3.94	4.18	4.96	6.32	17.47	18.23	18.47	19.25	20.61
	4H	3.47	4.20	4.49	5.22	6.59	18.11	18.83	19.13	19.85	21.22
	6H	3.72	4.39	4.75	5.41	6.80	18.53	19.20	19.56	20.23	21.61
	8H	3.79	4.42	4.82	5.47	6.85	18.65	19.29	19.69	20.33	21.71
	12H	3.81	4.41	4.84	5.45	6.85	18.72	19.32	19.76	20.36	21.76
4H	2H	9.67	10.40	10.70	11.42	12.79	15.91	16.63	16.93	17.65	19.02
	3H	11.24	11.85	12.27	12.90	14.28	17.95	18.55	18.98	19.60	20.99
	4H	11.34	11.89	12.38	12.93	14.34	18.71	19.27	19.75	20.31	21.71
	6H	11.35	11.83	12.40	12.89	14.29	19.24	19.72	20.29	20.79	22.19
	8H	11.32	11.77	12.37	12.83	14.25	19.40	19.85	20.45	20.91	22.33
	12H	11.28	11.68	12.35	12.76	14.18	19.49	19.90	20.56	20.97	22.39
8H	4H	12.78	13.22	13.83	14.28	15.70	18.77	19.22	19.82	20.28	21.69
	6H	13.02	13.39	14.09	14.49	15.90	19.39	19.76	20.47	20.86	22.28
	8H	13.04	13.36	14.12	14.45	15.88	19.61	19.94	20.69	21.02	22.45
	12H	13.00	13.29	14.09	14.37	15.84	19.75	20.04	20.84	21.12	22.59
12H	4H	12.92	13.32	13.99	14.40	15.82	18.72	19.13	19.79	20.20	21.62
	6H	13.28	13.60	14.36	14.69	16.12	19.38	19.70	20.46	20.79	22.22
	8H	13.34	13.63	14.43	14.71	16.18	19.60	19.89	20.69	20.97	22.44