

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937928

Luminaire Tested: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937928
REPORT IS A COMBINATION OF REPORTS P933590 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20221.2 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 166.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937928
CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P937928

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2625	2625	2625
5°	2566	3035	3529
10°	2328	4425	5850
15°	1979	5783	7064
20°	1612	6703	7199
25°	1345	7016	7053
30°	1135	7062	7039
35°	1004	6947	7221
40°	875	6796	7410
45°	793	6686	7439
50°	728	6588	7315
55°	698	6444	6991
60°	715	6164	6479
65°	746	5736	5776
70°	797	5006	4879
75°	885	4085	3807
80°	975	2837	2566
85°	885	1507	1313

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7439 cd/sqm



TEST NUMBER: P937928

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.8	0.5
10°-20°	486.6	2.4
20°-30°	851.1	4.2
30°-40°	1095.6	5.4
40°-50°	1223.8	6.1
50°-60°	1172.1	5.8
60°-70°	928.9	4.6
70°-80°	546.2	2.7
80°-90°	159.8	0.8
90°-100°	1026.2	5.1
100°-110°	2697.9	13.3
110°-120°	2797.5	13.8
120°-130°	2243.9	11.1
130°-140°	1760.7	8.7
140°-150°	1351.4	6.7
150°-160°	973.2	4.8
160°-170°	595.5	2.9
170°-180°	201.2	1.0
0°-30°	1447.5	7.2
0°-40°	2543.1	12.6
0°-60°	4938.9	24.4
0°-90°	6573.8	32.5
90°-120°	6521.6	32.3
90°-150°	11877.6	58.7
90°-180°	13647.0	67.5
0°-180°	20221.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	849	849	849	849	849	
5°	827	887	999	1130	1171	76
15°	620	1144	1927	2336	2410	172
25°	396	1296	2295	2396	2399	182
35°	267	1239	2161	2284	2374	167
45°	183	988	1910	2189	2287	141
55°	131	628	1621	1883	1935	119
65°	104	333	1204	1354	1373	103
75°	76	205	660	726	729	80
85°	27	63	164	180	183	29
90°	14	40	107	54	54	13
95°	136	531	1768	911	620	151
105°	486	736	2983	4528	4225	515
115°	863	1048	2389	4766	5440	853
125°	1201	1346	2173	3672	4332	1066
135°	1431	1575	2105	2964	3361	1107
145°	1660	1766	2078	2529	2727	1040
155°	1876	1929	2078	2282	2348	862
165°	2025	2052	2078	2160	2187	571
175°	2105	2105	2092	2119	2119	200
180°	2105	2105	2105	2105	2105	



TEST NUMBER: P937928
 CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7
2.5°	848.7	848.7	854.1	856.9	862.3	865.1	870.5	876.0	892.4	895.1	900.5
5°	826.9	837.8	873.3	886.9	925.1	977.0	998.8	1034.3	1108.0	1129.9	1143.5
7.5°	794.1	818.7	906.0	927.8	1023.3	1159.9	1217.2	1293.6	1410.9	1468.2	1514.6
10°	742.3	794.1	949.7	1001.5	1157.1	1364.5	1471.0	1577.4	1754.8	1833.9	1863.9
12.5°	685.0	769.6	996.1	1067.1	1290.9	1593.8	1722.0	1839.4	2041.3	2147.7	2164.1
15°	619.5	734.1	1039.8	1143.5	1432.8	1784.8	1926.7	2071.3	2259.6	2336.0	2355.1
17.5°	562.2	706.8	1080.7	1189.9	1541.9	1956.7	2101.4	2221.4	2374.2	2426.1	2439.7
20°	491.2	663.1	1108.0	1249.9	1656.5	2082.3	2221.4	2314.2	2417.9	2450.7	2456.1
22.5°	439.4	616.7	1124.4	1271.8	1732.9	2158.7	2276.0	2349.7	2420.6	2431.6	2434.3
25°	395.7	564.9	1121.7	1296.3	1798.4	2205.1	2295.1	2349.7	2390.6	2396.1	2396.1
27.5°	354.8	507.6	1110.8	1301.8	1847.6	2216.0	2286.9	2325.1	2344.2	2355.1	2355.1
30°	319.3	453.0	1083.5	1290.9	1869.4	2205.1	2262.4	2281.5	2300.6	2316.9	2325.1
32.5°	292.0	401.1	1042.5	1269.0	1872.1	2177.8	2218.7	2229.6	2256.9	2295.1	2308.7
35°	267.4	349.3	996.1	1239.0	1855.8	2134.1	2161.4	2172.3	2226.9	2284.2	2303.3
37.5°	242.9	311.1	936.0	1187.2	1831.2	2082.3	2101.4	2120.5	2205.1	2273.3	2295.1
40°	218.3	278.3	865.1	1129.9	1793.0	2019.5	2035.9	2065.9	2177.8	2256.9	2278.7
42.5°	199.2	251.1	788.7	1069.8	1743.9	1948.5	1973.1	2016.8	2145.0	2229.6	2254.2
45°	182.8	223.8	706.8	987.9	1681.1	1874.9	1910.3	1970.4	2106.8	2188.7	2210.5
47.5°	166.5	204.7	622.2	903.3	1612.9	1801.2	1847.6	1915.8	2055.0	2134.1	2153.2
50°	152.8	185.6	537.6	813.2	1539.2	1722.0	1776.6	1847.6	1989.5	2063.1	2087.7
52.5°	141.9	169.2	458.5	723.2	1454.6	1640.2	1702.9	1776.6	1910.3	1981.3	1997.7
55°	131.0	155.5	390.2	627.6	1367.3	1552.8	1621.1	1692.0	1823.0	1883.0	1894.0
57.5°	125.5	144.6	332.9	537.6	1274.5	1454.6	1531.0	1596.5	1719.3	1765.7	1776.6
60°	117.3	136.4	289.3	461.2	1173.5	1361.8	1427.3	1492.8	1596.5	1634.7	1642.9
62.5°	109.2	131.0	256.5	387.5	1069.8	1252.7	1318.2	1378.2	1465.5	1492.8	1503.7
65°	103.7	125.5	232.0	332.9	963.3	1138.0	1203.5	1255.4	1326.3	1353.6	1359.1
67.5°	98.2	120.1	212.9	286.5	856.9	1023.3	1072.6	1121.7	1176.3	1203.5	1206.3
70°	90.1	114.6	196.5	253.8	747.7	892.4	933.3	985.1	1028.8	1042.5	1050.7
72.5°	84.6	106.4	185.6	229.2	635.8	766.8	805.0	835.0	873.3	886.9	886.9
75°	76.4	95.5	174.7	204.7	521.2	627.6	660.4	690.4	720.4	725.9	717.7
77.5°	68.2	84.6	150.1	171.9	406.6	496.7	524.0	540.3	564.9	570.3	573.1
80°	57.3	73.7	117.3	133.7	294.7	365.7	384.8	398.4	420.3	420.3	425.7
82.5°	43.7	57.3	84.6	95.5	199.2	251.1	267.4	275.6	289.3	289.3	289.3
85°	27.3	35.5	54.6	62.8	120.1	152.8	163.7	166.5	177.4	180.1	180.1
87.5°	13.6	19.1	35.5	38.2	62.8	79.1	79.1	84.6	84.6	81.9	79.1
90°	14.1	25.4	36.7	39.6	62.1	92.2	107.3	95.4	71.6	53.7	53.7
92.5°	56.5	152.5	248.7	272.7	383.4	531.0	604.7	530.0	380.5	268.4	257.8
95°	135.6	311.5	487.3	531.2	943.3	1492.8	1767.5	1577.2	1196.7	911.4	879.0
97.5°	234.5	389.6	544.8	583.5	1270.7	2186.9	2645.0	2524.7	2284.2	2103.8	2042.2
100°	310.8	451.5	592.2	627.4	1389.8	2406.5	2914.8	2923.7	2941.2	2954.4	2881.1
102.5°	375.9	507.1	638.3	671.1	1444.5	2475.6	2991.2	3144.3	3450.8	3680.7	3617.9
105°	486.0	597.2	708.3	736.2	1485.0	2483.4	2982.6	3326.1	4013.1	4528.4	4494.6
107.5°	599.1	702.7	806.3	832.2	1492.5	2373.0	2813.1	3292.2	4250.5	4969.2	4977.4
110°	675.4	768.9	862.5	885.9	1481.2	2274.9	2671.8	3207.5	4278.8	5082.2	5117.4



TEST NUMBER: P937928

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	750.3	839.4	928.6	950.8	1481.6	2189.4	2543.3	3091.5	4187.9	5010.2	5064.2
115°	863.2	945.5	1027.8	1048.4	1495.4	2091.3	2389.3	2917.4	3973.6	4765.8	4840.6
117.5°	974.9	1049.6	1124.4	1143.0	1523.1	2029.9	2283.3	2759.9	3713.1	4428.0	4511.1
120°	1039.9	1110.2	1180.6	1198.2	1545.7	2009.2	2240.9	2676.4	3547.4	4200.6	4281.3
122.5°	1103.5	1174.4	1245.4	1263.1	1578.2	1998.4	2208.4	2600.6	3384.9	3973.1	4052.7
125°	1201.0	1265.7	1330.3	1346.5	1622.1	1989.4	2173.0	2506.1	3172.5	3672.1	3745.4
127.5°	1280.1	1345.4	1410.8	1427.0	1665.8	1984.2	2143.4	2429.4	3001.4	3430.5	3492.4
130°	1322.5	1392.8	1463.2	1480.7	1697.8	1987.4	2132.1	2386.7	2896.0	3278.0	3335.1
132.5°	1366.3	1436.6	1507.0	1524.6	1723.8	1989.4	2122.2	2350.1	2806.0	3148.0	3199.2
135°	1431.3	1495.4	1559.4	1575.4	1752.1	1987.6	2105.3	2296.2	2678.0	2964.3	3008.4
137.5°	1497.7	1561.1	1624.5	1640.3	1794.3	1999.7	2102.4	2263.8	2586.6	2828.6	2864.7
140°	1552.8	1611.1	1669.5	1684.2	1820.3	2001.7	2092.5	2231.9	2510.7	2719.8	2753.6
142.5°	1595.1	1649.2	1703.2	1716.7	1841.9	2009.0	2092.5	2215.0	2459.9	2643.6	2672.6
145°	1660.2	1707.3	1754.4	1766.2	1870.2	2009.0	2078.4	2178.6	2378.9	2529.1	2551.1
147.5°	1725.1	1771.0	1816.8	1828.3	1911.7	2022.9	2078.4	2157.2	2314.8	2433.0	2451.2
150°	1767.5	1809.0	1850.5	1860.8	1933.3	2030.0	2078.4	2145.0	2278.1	2377.9	2392.6
152.5°	1811.4	1842.7	1874.2	1882.0	1947.5	2034.8	2078.4	2135.3	2248.9	2334.1	2345.3
155°	1876.3	1899.6	1922.8	1928.6	1978.6	2045.1	2078.4	2123.6	2214.1	2281.8	2289.2
157.5°	1924.4	1947.0	1969.6	1975.3	2009.7	2055.5	2078.4	2113.5	2183.9	2236.6	2241.8
160°	1956.9	1974.5	1992.1	1996.5	2023.8	2060.2	2078.4	2108.5	2168.8	2214.1	2217.1
162.5°	1989.4	2002.6	2015.8	2019.0	2038.9	2065.2	2078.4	2103.9	2154.7	2192.9	2195.7
165°	2024.7	2036.6	2048.5	2051.5	2060.5	2072.4	2078.4	2096.6	2133.0	2160.3	2163.3
167.5°	2057.2	2062.9	2068.5	2069.9	2077.4	2087.5	2092.5	2104.4	2128.3	2146.2	2147.5
170°	2078.4	2084.1	2089.7	2091.1	2091.5	2092.2	2092.5	2104.4	2128.3	2146.2	2146.2
172.5°	2089.7	2091.0	2092.3	2092.5	2092.5	2092.5	2092.5	2102.0	2120.8	2134.9	2133.8
175°	2105.3	2105.3	2105.3	2105.3	2101.0	2095.3	2092.5	2098.5	2110.4	2119.4	2119.4
177.5°	2105.3	2105.3	2105.3	2105.3	2102.0	2097.5	2095.3	2100.1	2109.4	2116.5	2115.3
180°	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3	2105.3



TEST NUMBER: P937928

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	848.7	848.7
2.5°	906.0	900.5
5°	1165.3	1170.8
7.5°	1569.2	1566.5
10°	1951.3	1975.8
12.5°	2229.6	2235.1
15°	2398.8	2409.7
17.5°	2464.3	2467.0
20°	2467.0	2461.6
22.5°	2437.0	2431.6
25°	2401.5	2398.8
27.5°	2368.8	2371.5
30°	2355.1	2363.3
32.5°	2355.1	2368.8
35°	2360.6	2374.2
37.5°	2357.9	2374.2
40°	2347.0	2366.1
42.5°	2316.9	2330.6
45°	2270.5	2286.9
47.5°	2210.5	2221.4
50°	2134.1	2145.0
52.5°	2038.6	2041.3
55°	1924.0	1934.9
57.5°	1801.2	1803.9
60°	1664.7	1672.9
62.5°	1520.1	1520.1
65°	1367.3	1372.7
67.5°	1209.0	1222.6
70°	1048.0	1050.7
72.5°	889.6	889.6
75°	725.9	728.6
77.5°	570.3	570.3
80°	423.0	425.7
82.5°	292.0	297.5
85°	182.8	182.8
87.5°	84.6	76.4
90°	53.7	53.7
92.5°	215.0	172.4
95°	749.6	620.3
97.5°	1796.1	1549.9
100°	2587.8	2294.6
102.5°	3366.7	3115.5
105°	4359.6	4224.6
107.5°	5010.0	5042.7
110°	5258.1	5398.7



TEST NUMBER: P937928

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5280.2	5496.2
115°	5140.2	5439.7
117.5°	4843.3	5175.5
120°	4604.0	4926.8
122.5°	4371.1	4689.5
125°	4038.7	4332.0
127.5°	3739.8	3987.2
130°	3563.7	3792.3
132.5°	3403.9	3608.5
135°	3184.8	3361.3
137.5°	3009.2	3153.6
140°	2888.6	3023.6
142.5°	2788.8	2904.9
145°	2638.9	2726.9
147.5°	2524.1	2596.9
150°	2451.7	2510.8
152.5°	2389.9	2434.5
155°	2318.8	2348.2
157.5°	2262.5	2283.3
160°	2229.0	2240.9
162.5°	2207.0	2218.2
165°	2175.2	2187.2
167.5°	2152.5	2157.5
170°	2146.2	2146.2
172.5°	2129.4	2125.0
175°	2119.4	2119.4
177.5°	2110.3	2105.3
180°	2105.3	2105.3



TEST NUMBER: P937928
 CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.50	3.25	3.59	4.34	5.84	15.69	16.44	16.78	17.53	19.03
	3H	3.20	3.87	4.29	4.97	6.48	17.53	18.20	18.63	19.30	20.81
	4H	3.49	4.12	4.60	5.23	6.75	18.17	18.81	19.28	19.91	21.43
	6H	3.73	4.32	4.85	5.42	6.96	18.60	19.19	19.72	20.29	21.82
	8H	3.80	4.36	4.92	5.47	7.00	18.72	19.28	19.84	20.40	21.92
	12H	3.81	4.34	4.94	5.45	7.00	18.79	19.32	19.91	20.43	21.98
4H	2H	9.71	10.35	10.82	11.45	12.97	15.95	16.59	17.07	17.69	19.21
	3H	11.27	11.80	12.39	12.92	14.46	17.99	18.52	19.11	19.65	21.18
	4H	11.36	11.84	12.48	12.96	14.51	18.76	19.25	19.88	20.36	21.92
	6H	11.36	11.78	12.49	12.92	14.46	19.29	19.71	20.43	20.85	22.40
	8H	11.33	11.72	12.46	12.86	14.42	19.46	19.85	20.59	20.98	22.54
	12H	11.28	11.64	12.43	12.78	14.35	19.55	19.90	20.70	21.05	22.61
8H	4H	12.79	13.19	13.93	14.32	15.88	18.81	19.20	19.94	20.33	21.89
	6H	13.03	13.35	14.18	14.53	16.09	19.44	19.76	20.59	20.93	22.49
	8H	13.05	13.33	14.21	14.48	16.06	19.66	19.94	20.82	21.09	22.67
	12H	13.01	13.26	14.17	14.41	16.02	19.80	20.05	20.96	21.20	22.81
12H	4H	12.93	13.29	14.08	14.43	16.00	18.75	19.11	19.90	20.25	21.82
	6H	13.29	13.57	14.45	14.73	16.30	19.42	19.70	20.58	20.85	22.43
	8H	13.35	13.60	14.52	14.75	16.37	19.64	19.89	20.81	21.04	22.66