

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937933

Luminaire Tested: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937933
REPORT IS A COMBINATION OF REPORTS P933598 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.2 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937933
CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33			33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	27			27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	22			22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	18			18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	15			15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	13			13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11			11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	10			10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	8			8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	7			7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	7			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2576	2576	2576
5°	2514	2975	3462
10°	2278	4333	5741
15°	1933	5658	6931
20°	1573	6551	7064
25°	1310	6851	6920
30°	1103	6889	6907
35°	974	6769	7086
40°	847	6615	7271
45°	766	6499	7299
50°	701	6396	7178
55°	669	6245	6860
60°	683	5962	6358
65°	706	5537	5667
70°	749	4820	4788
75°	820	3919	3736
80°	875	2709	2517
85°	737	1431	1288

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7299 cd/sqm



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	0.5
10°-20°	159.2	2.4
20°-30°	278.4	4.2
30°-40°	358.4	5.4
40°-50°	400.3	6.1
50°-60°	383.4	5.8
60°-70°	303.8	4.6
70°-80°	178.7	2.7
80°-90°	52.3	0.8
90°-100°	335.7	5.1
100°-110°	882.5	13.3
110°-120°	915.0	13.8
120°-130°	734.0	11.1
130°-140°	575.9	8.7
140°-150°	442.0	6.7
150°-160°	318.3	4.8
160°-170°	194.8	2.9
170°-180°	65.8	1.0
0°-30°	473.4	7.2
0°-40°	831.8	12.6
0°-60°	1615.4	24.4
0°-90°	2150.2	32.5
90°-120°	2133.2	32.3
90°-150°	3885.1	58.7
90°-180°	4464.0	67.5
0°-180°	6614.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	278	278	278	278	278	
5°	270	290	327	370	383	25
15°	203	374	630	764	788	56
25°	129	424	751	784	785	60
35°	88	405	707	747	777	55
45°	60	323	625	716	748	46
55°	43	205	530	616	633	39
65°	34	109	394	443	449	34
75°	25	67	216	237	238	26
85°	9	20	54	59	60	9
90°	5	13	35	18	18	4
95°	44	174	578	298	203	49
105°	159	241	976	1481	1382	169
115°	282	343	782	1559	1779	279
125°	393	440	711	1201	1417	349
135°	468	515	689	970	1099	362
145°	543	578	680	827	892	340
155°	614	631	680	746	768	282
165°	662	671	680	707	715	187
175°	689	689	684	693	693	65
180°	689	689	689	689	689	



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	277.6	277.6	277.6	277.6	277.6	277.6	277.6	277.6	277.6	277.6	277.6
2.5°	277.6	277.6	279.4	280.3	282.1	283.0	284.7	286.5	291.9	292.8	294.6
5°	270.5	274.0	285.6	290.1	302.6	319.6	326.7	338.3	362.4	369.5	374.0
7.5°	259.8	267.8	296.3	303.5	334.7	379.4	398.1	423.1	461.5	480.2	495.4
10°	242.8	259.8	310.6	327.6	378.5	446.3	481.1	515.9	574.0	599.8	609.7
12.5°	224.0	251.7	325.8	349.0	422.2	521.3	563.2	601.6	667.7	702.5	707.8
15°	202.6	240.1	340.1	374.0	468.6	583.8	630.2	677.5	739.1	764.1	770.3
17.5°	183.9	231.2	353.5	389.2	504.3	640.0	687.3	726.6	776.6	793.5	798.0
20°	160.7	216.9	362.4	408.8	541.8	681.1	726.6	756.9	790.9	801.6	803.4
22.5°	143.7	201.7	367.8	416.0	566.8	706.1	744.4	768.5	791.8	795.3	796.2
25°	129.4	184.8	366.9	424.0	588.2	721.2	750.7	768.5	781.9	783.7	783.7
27.5°	116.0	166.0	363.3	425.8	604.3	724.8	748.0	760.5	766.8	770.3	770.3
30°	104.4	148.2	354.4	422.2	611.4	721.2	740.0	746.2	752.5	757.8	760.5
32.5°	95.5	131.2	341.0	415.1	612.3	712.3	725.7	729.3	738.2	750.7	755.2
35°	87.5	114.3	325.8	405.2	607.0	698.0	707.0	710.5	728.4	747.1	753.4
37.5°	79.4	101.8	306.2	388.3	598.9	681.1	687.3	693.6	721.2	743.6	750.7
40°	71.4	91.0	283.0	369.5	586.5	660.5	665.9	675.7	712.3	738.2	745.3
42.5°	65.2	82.1	258.0	349.9	570.4	637.3	645.4	659.6	701.6	729.3	737.3
45°	59.8	73.2	231.2	323.1	549.9	613.2	624.8	644.5	689.1	715.9	723.0
47.5°	54.4	66.9	203.5	295.5	527.5	589.1	604.3	626.6	672.1	698.0	704.3
50°	50.0	60.7	175.8	266.0	503.4	563.2	581.1	604.3	650.7	674.8	682.9
52.5°	46.4	55.3	150.0	236.5	475.8	536.5	557.0	581.1	624.8	648.0	653.4
55°	42.8	50.9	127.6	205.3	447.2	507.9	530.2	553.4	596.3	615.9	619.5
57.5°	41.1	47.3	108.9	175.8	416.9	475.8	500.8	522.2	562.4	577.5	581.1
60°	38.4	44.6	94.6	150.9	383.8	445.4	466.8	488.3	522.2	534.7	537.4
62.5°	35.7	42.8	83.9	126.8	349.9	409.7	431.1	450.8	479.3	488.3	491.8
65°	33.9	41.1	75.9	108.9	315.1	372.2	393.6	410.6	433.8	442.7	444.5
67.5°	32.1	39.3	69.6	93.7	280.3	334.7	350.8	366.9	384.7	393.6	394.5
70°	29.5	37.5	64.3	83.0	244.6	291.9	305.3	322.2	336.5	341.0	343.7
72.5°	27.7	34.8	60.7	75.0	208.0	250.8	263.3	273.1	285.6	290.1	290.1
75°	25.0	31.2	57.1	66.9	170.5	205.3	216.0	225.8	235.7	237.4	234.8
77.5°	22.3	27.7	49.1	56.2	133.0	162.5	171.4	176.7	184.8	186.6	187.5
80°	18.7	24.1	38.4	43.7	96.4	119.6	125.9	130.3	137.5	137.5	139.2
82.5°	14.3	18.7	27.7	31.2	65.2	82.1	87.5	90.2	94.6	94.6	94.6
85°	8.9	11.6	17.9	20.5	39.3	50.0	53.6	54.4	58.0	58.9	58.9
87.5°	4.5	6.2	11.6	12.5	20.5	25.9	25.9	27.7	27.7	26.8	25.9
90°	4.6	8.3	12.1	12.9	20.4	30.2	35.1	31.2	23.4	17.6	17.6
92.5°	18.5	49.9	81.3	89.2	125.4	173.7	197.8	173.3	124.5	87.8	84.4
95°	44.4	101.8	159.4	173.8	308.6	488.3	578.1	515.9	391.5	298.1	287.5
97.5°	76.7	127.4	178.2	190.8	415.6	715.3	865.1	825.8	747.1	688.1	668.0
100°	101.7	147.7	193.7	205.2	454.6	787.1	953.4	956.3	962.1	966.4	942.3
102.5°	122.9	165.8	208.8	219.5	472.5	809.8	978.4	1028.6	1128.8	1204.0	1183.4
105°	159.0	195.4	231.7	240.8	485.8	812.4	975.6	1088.0	1312.7	1481.2	1470.1
107.5°	195.9	229.8	263.8	272.2	488.3	776.2	920.2	1076.9	1390.3	1625.4	1628.0
110°	220.9	251.5	282.1	289.7	484.5	744.2	874.0	1049.2	1399.6	1662.4	1673.9



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	245.4	274.6	303.7	311.0	484.6	716.1	831.9	1011.2	1369.9	1638.9	1656.5
115°	282.3	309.3	336.2	342.9	489.2	684.0	781.5	954.2	1299.7	1558.9	1583.3
117.5°	318.9	343.4	367.8	373.9	498.3	664.0	746.9	902.7	1214.5	1448.4	1475.5
120°	340.2	363.2	386.2	391.9	505.7	657.2	733.0	875.5	1160.3	1374.0	1400.4
122.5°	361.0	384.2	407.4	413.2	516.3	653.7	722.4	850.7	1107.2	1299.6	1325.6
125°	392.8	414.0	435.2	440.4	530.6	650.7	710.8	819.8	1037.7	1201.1	1225.1
127.5°	418.7	440.1	461.4	466.8	544.9	649.0	701.1	794.6	981.8	1122.1	1142.4
130°	432.6	455.6	478.6	484.3	555.4	650.1	697.4	780.7	947.2	1072.2	1090.9
132.5°	446.9	470.0	493.0	498.7	563.9	650.7	694.2	768.7	917.9	1029.7	1046.4
135°	468.2	489.2	510.0	515.3	573.1	650.1	688.7	751.1	876.0	969.7	984.1
137.5°	489.9	510.6	531.4	536.6	586.9	654.1	687.7	740.4	846.0	925.2	937.0
140°	507.9	527.0	546.1	550.9	595.5	654.8	684.5	730.1	821.3	889.7	900.7
142.5°	521.7	539.4	557.1	561.5	602.5	657.1	684.5	724.5	804.6	864.7	874.1
145°	543.1	558.4	573.9	577.7	611.7	657.1	679.8	712.6	778.1	827.3	834.5
147.5°	564.3	579.3	594.3	598.1	625.3	661.6	679.8	705.6	757.2	795.9	801.8
150°	578.1	591.7	605.3	608.7	632.4	664.0	679.8	701.6	745.2	777.8	782.6
152.5°	592.5	602.8	613.1	615.6	637.1	665.5	679.8	698.4	735.6	763.5	767.1
155°	613.8	621.4	628.9	630.8	647.1	668.9	679.8	694.6	724.2	746.4	748.8
157.5°	629.5	636.9	644.2	646.1	657.3	672.3	679.8	691.3	714.4	731.6	733.3
160°	640.1	645.8	651.6	653.0	662.0	673.8	679.8	689.6	709.4	724.2	725.2
162.5°	650.7	655.0	659.4	660.4	666.9	675.5	679.8	688.1	704.8	717.3	718.2
165°	662.2	666.2	670.1	671.1	674.0	677.9	679.8	685.8	697.7	706.6	707.6
167.5°	672.9	674.7	676.6	677.1	679.6	682.9	684.5	688.4	696.2	702.0	702.5
170°	679.8	681.7	683.6	684.0	684.2	684.4	684.5	688.4	696.2	702.0	702.0
172.5°	683.6	683.9	684.4	684.5	684.5	684.5	684.5	687.5	693.7	698.3	697.9
175°	688.7	688.7	688.7	688.7	687.2	685.4	684.5	686.4	690.3	693.2	693.2
177.5°	688.7	688.7	688.7	688.7	687.6	686.1	685.4	686.9	690.0	692.3	691.9
180°	688.7	688.7	688.7	688.7	688.7	688.7	688.7	688.7	688.7	688.7	688.7



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	277.6	277.6
2.5°	296.3	294.6
5°	381.1	382.9
7.5°	513.3	512.4
10°	638.2	646.3
12.5°	729.3	731.1
15°	784.6	788.2
17.5°	806.0	806.9
20°	806.9	805.1
22.5°	797.1	795.3
25°	785.5	784.6
27.5°	774.8	775.7
30°	770.3	773.0
32.5°	770.3	774.8
35°	772.1	776.6
37.5°	771.2	776.6
40°	767.7	773.9
42.5°	757.8	762.3
45°	742.7	748.0
47.5°	723.0	726.6
50°	698.0	701.6
52.5°	666.8	667.7
55°	629.3	632.9
57.5°	589.1	590.0
60°	544.5	547.2
62.5°	497.2	497.2
65°	447.2	449.0
67.5°	395.4	399.9
70°	342.8	343.7
72.5°	291.0	291.0
75°	237.4	238.3
77.5°	186.6	186.6
80°	138.4	139.2
82.5°	95.5	97.3
85°	59.8	59.8
87.5°	27.7	25.0
90°	17.6	17.6
92.5°	70.3	56.4
95°	245.2	202.9
97.5°	587.5	507.0
100°	846.5	750.5
102.5°	1101.2	1019.1
105°	1426.0	1381.9
107.5°	1638.8	1649.5
110°	1719.9	1765.9



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1727.1	1797.8
115°	1681.3	1779.3
117.5°	1584.2	1692.9
120°	1505.9	1611.5
122.5°	1429.7	1533.9
125°	1321.0	1416.9
127.5°	1223.2	1304.2
130°	1165.7	1240.5
132.5°	1113.4	1180.3
135°	1041.8	1099.4
137.5°	984.3	1031.5
140°	944.8	989.0
142.5°	912.2	950.2
145°	863.3	892.0
147.5°	825.6	849.4
150°	802.0	821.3
152.5°	781.7	796.3
155°	758.5	768.1
157.5°	740.1	746.9
160°	729.1	733.0
162.5°	722.0	725.6
165°	711.5	715.4
167.5°	704.1	705.7
170°	702.0	702.0
172.5°	696.5	695.1
175°	693.2	693.2
177.5°	690.3	688.7
180°	688.7	688.7



TEST NUMBER: P937933

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.42	3.16	3.50	4.25	5.75	15.55	16.30	16.64	17.39	18.89
	3H	3.11	3.78	4.21	4.88	6.40	17.37	18.04	18.47	19.14	20.65
	4H	3.41	4.04	4.51	5.14	6.66	18.00	18.63	19.11	19.74	21.26
	6H	3.65	4.24	4.77	5.34	6.87	18.41	19.00	19.53	20.10	21.63
	8H	3.72	4.27	4.84	5.39	6.92	18.52	19.08	19.64	20.20	21.73
	12H	3.73	4.26	4.85	5.37	6.92	18.58	19.11	19.70	20.22	21.77
4H	2H	9.59	10.23	10.71	11.33	12.85	15.82	16.45	16.93	17.55	19.07
	3H	11.15	11.68	12.27	12.81	14.34	17.84	18.37	18.96	19.49	21.03
	4H	11.24	11.73	12.37	12.85	14.40	18.59	19.08	19.71	20.19	21.75
	6H	11.25	11.67	12.38	12.80	14.35	19.11	19.53	20.24	20.67	22.21
	8H	11.22	11.61	12.35	12.74	14.31	19.26	19.65	20.39	20.78	22.35
	12H	11.17	11.53	12.32	12.67	14.24	19.34	19.69	20.49	20.84	22.41
8H	4H	12.67	13.06	13.80	14.19	15.75	18.64	19.03	19.77	20.16	21.72
	6H	12.90	13.23	14.06	14.40	15.96	19.25	19.57	20.40	20.75	22.31
	8H	12.92	13.20	14.08	14.36	15.93	19.46	19.74	20.62	20.90	22.48
	12H	12.88	13.13	14.05	14.28	15.90	19.59	19.84	20.75	20.99	22.60
12H	4H	12.80	13.16	13.95	14.30	15.87	18.59	18.94	19.73	20.08	21.65
	6H	13.16	13.44	14.32	14.59	16.17	19.23	19.52	20.39	20.67	22.25
	8H	13.22	13.47	14.38	14.62	16.23	19.45	19.70	20.61	20.85	22.46