

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937226

Luminaire Tested: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937226
REPORT IS A COMBINATION OF REPORTS P933495 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16153.6 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 153.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937226
CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3325	3325	3325
5°	3249	3844	4469
10°	2948	5605	7409
15°	2507	7324	8946
20°	2042	8489	9118
25°	1704	8886	8933
30°	1437	8944	8916
35°	1271	8798	9146
40°	1109	8607	9385
45°	1005	8469	9421
50°	922	8344	9265
55°	884	8161	8855
60°	906	7806	8206
65°	944	7265	7315
70°	1009	6340	6180
75°	1122	5174	4823
80°	1235	3593	3250
85°	1118	1910	1663

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9421 cd/sqm



TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.0	0.9
10°-20°	616.3	3.8
20°-30°	1077.9	6.7
30°-40°	1387.6	8.6
40°-50°	1549.9	9.6
50°-60°	1484.5	9.2
60°-70°	1176.4	7.3
70°-80°	691.8	4.3
80°-90°	196.8	1.2
90°-100°	589.0	3.6
100°-110°	1548.5	9.6
110°-120°	1605.7	9.9
120°-130°	1287.9	8.0
130°-140°	1010.6	6.3
140°-150°	775.7	4.8
150°-160°	558.6	3.5
160°-170°	341.8	2.1
170°-180°	115.5	0.7
0°-30°	1833.3	11.3
0°-40°	3220.9	19.9
0°-60°	6255.3	38.7
0°-90°	8320.3	51.5
90°-120°	3743.2	23.2
90°-150°	6817.4	42.2
90°-180°	7833.0	48.5
0°-180°	16153.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1075	1075	1075	1075	1075	
5°	1047	1123	1265	1431	1483	97
15°	785	1448	2440	2959	3052	218
25°	501	1642	2907	3035	3038	231
35°	339	1569	2738	2893	3007	212
45°	232	1251	2420	2772	2896	179
55°	166	795	2053	2385	2451	151
65°	131	422	1524	1714	1739	130
75°	97	259	836	919	923	101
85°	34	80	207	228	232	37
90°	8	23	62	31	31	9
95°	78	305	1014	523	356	86
105°	279	422	1712	2599	2425	296
115°	496	602	1371	2735	3122	489
125°	689	773	1247	2108	2486	612
135°	822	904	1208	1701	1929	636
145°	953	1014	1193	1452	1565	597
155°	1077	1107	1193	1310	1348	495
165°	1162	1178	1193	1240	1255	328
175°	1208	1208	1201	1216	1216	115
180°	1208	1208	1208	1208	1208	



TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0	1075.0
2.5°	1075.0	1075.0	1081.8	1085.3	1092.2	1095.7	1102.6	1109.5	1130.2	1133.7	1140.6
5°	1047.3	1061.1	1106.1	1123.4	1171.8	1237.4	1265.1	1310.0	1403.3	1430.9	1448.2
7.5°	1005.8	1036.9	1147.5	1175.2	1296.1	1468.9	1541.6	1638.3	1787.0	1859.5	1918.3
10°	940.1	1005.8	1202.8	1268.5	1465.5	1728.2	1863.0	1997.8	2222.5	2322.7	2360.7
12.5°	867.6	974.7	1261.6	1351.5	1634.9	2018.5	2181.0	2329.6	2585.4	2720.2	2740.9
15°	784.6	929.8	1316.9	1448.2	1814.6	2260.5	2440.2	2623.4	2861.9	2958.6	2982.9
17.5°	712.0	895.2	1368.7	1507.0	1952.8	2478.2	2661.4	2813.5	3007.0	3072.7	3090.1
20°	622.1	839.9	1403.3	1583.0	2098.0	2637.2	2813.5	2931.0	3062.3	3103.8	3110.7
22.5°	556.4	781.2	1424.0	1610.6	2194.8	2734.0	2882.6	2976.0	3065.8	3079.7	3083.1
25°	501.2	715.5	1420.5	1641.8	2277.8	2792.8	2906.8	2976.0	3027.8	3034.7	3034.7
27.5°	449.4	642.9	1406.8	1648.7	2340.0	2806.6	2896.5	2944.9	2969.0	2982.9	2982.9
30°	404.4	573.8	1372.1	1634.9	2367.7	2792.8	2865.3	2889.6	2913.7	2934.5	2944.9
32.5°	369.8	508.0	1320.3	1607.2	2371.1	2758.2	2810.0	2823.9	2858.4	2906.8	2924.1
35°	338.7	442.4	1261.6	1569.2	2350.3	2702.9	2737.5	2751.3	2820.4	2893.0	2917.2
37.5°	307.7	394.1	1185.5	1503.6	2319.3	2637.2	2661.4	2685.6	2792.8	2879.2	2906.8
40°	276.5	352.6	1095.7	1430.9	2270.9	2557.8	2578.4	2616.5	2758.2	2858.4	2886.1
42.5°	252.3	318.0	998.9	1354.9	2208.6	2467.9	2499.0	2554.3	2716.7	2823.9	2855.0
45°	231.6	283.4	895.2	1251.2	2129.2	2374.5	2419.5	2495.5	2668.3	2772.0	2799.7
47.5°	210.9	259.3	788.1	1144.1	2042.7	2281.2	2340.0	2426.3	2602.7	2702.9	2727.1
50°	193.6	235.0	680.9	1030.0	1949.4	2181.0	2250.1	2340.0	2519.7	2613.0	2644.2
52.5°	179.7	214.3	580.7	916.0	1842.3	2077.3	2156.8	2250.1	2419.5	2509.4	2530.1
55°	165.9	197.0	494.3	794.9	1731.7	1966.7	2053.1	2142.9	2308.9	2384.9	2398.7
57.5°	159.0	183.2	421.7	680.9	1614.1	1842.3	1939.1	2022.0	2177.6	2236.2	2250.1
60°	148.6	172.8	366.3	584.1	1486.2	1724.7	1807.7	1890.7	2022.0	2070.4	2080.8
62.5°	138.2	165.9	324.9	490.8	1354.9	1586.5	1669.4	1745.5	1856.1	1890.7	1904.4
65°	131.3	159.0	293.8	421.7	1220.1	1441.3	1524.2	1590.0	1679.8	1714.3	1721.3
67.5°	124.4	152.1	269.6	362.9	1085.3	1296.1	1358.4	1420.5	1489.7	1524.2	1527.7
70°	114.1	145.2	248.9	321.4	947.0	1130.2	1182.1	1247.8	1303.1	1320.3	1330.7
72.5°	107.2	134.8	235.0	290.3	805.3	971.3	1019.7	1057.7	1106.1	1123.4	1123.4
75°	96.8	121.0	221.2	259.3	660.1	794.9	836.5	874.5	912.5	919.4	909.0
77.5°	86.4	107.2	190.1	217.7	515.0	629.1	663.6	684.4	715.5	722.4	725.9
80°	72.6	93.3	148.6	169.3	373.3	463.1	487.4	504.6	532.3	532.3	539.2
82.5°	55.3	72.6	107.2	121.0	252.3	318.0	338.7	349.1	366.3	366.3	366.3
85°	34.5	44.9	69.2	79.5	152.1	193.6	207.4	210.9	224.6	228.1	228.1
87.5°	17.3	24.2	44.9	48.4	79.5	100.2	100.2	107.2	107.2	103.7	100.2
90°	8.1	14.6	21.0	22.7	35.7	53.0	61.7	54.8	41.1	30.8	30.8
92.5°	32.4	87.6	142.8	156.5	220.0	304.7	347.1	304.2	218.4	154.1	148.0
95°	77.9	178.8	279.7	305.0	541.4	856.9	1014.5	905.3	686.9	523.0	504.5
97.5°	134.6	223.7	312.7	334.9	729.4	1255.2	1518.1	1449.1	1311.0	1207.5	1172.2
100°	178.4	259.2	339.9	360.1	797.7	1381.2	1673.0	1678.1	1688.2	1695.8	1653.6
102.5°	215.7	291.1	366.3	385.2	829.0	1420.9	1716.9	1804.8	1980.7	2112.6	2076.6
105°	279.0	342.8	406.5	422.5	852.3	1425.4	1712.0	1909.1	2303.5	2599.2	2579.8
107.5°	343.8	403.3	462.8	477.7	856.7	1362.0	1614.7	1889.7	2439.7	2852.2	2856.9
110°	387.6	441.3	495.1	508.5	850.1	1305.8	1533.6	1841.0	2455.9	2917.0	2937.2



TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	430.6	481.8	533.0	545.8	850.5	1256.7	1459.8	1774.4	2403.8	2875.7	2906.7
115°	495.5	542.7	589.9	601.7	858.3	1200.4	1371.4	1674.5	2280.7	2735.4	2778.4
117.5°	559.6	602.5	645.3	656.0	874.2	1165.0	1310.5	1584.0	2131.2	2541.5	2589.2
120°	596.9	637.3	677.6	687.7	887.2	1153.2	1286.2	1536.1	2036.0	2411.0	2457.3
122.5°	633.4	674.1	714.8	725.0	905.9	1147.0	1267.5	1492.6	1942.8	2280.5	2326.2
125°	689.3	726.5	763.6	772.9	931.0	1141.8	1247.3	1438.5	1820.9	2107.7	2149.8
127.5°	734.8	772.3	809.8	819.1	956.2	1138.9	1230.3	1394.5	1722.8	1969.1	2004.5
130°	759.1	799.5	839.8	849.9	974.5	1140.6	1223.7	1369.9	1662.2	1881.4	1914.2
132.5°	784.2	824.6	864.9	875.0	989.3	1141.8	1218.1	1348.9	1610.6	1806.9	1836.2
135°	821.5	858.3	895.1	904.2	1005.6	1140.8	1208.4	1317.9	1537.0	1701.4	1726.7
137.5°	859.7	896.0	932.5	941.5	1030.0	1147.8	1206.7	1299.3	1484.6	1623.6	1644.3
140°	891.2	924.7	958.3	966.6	1044.8	1149.0	1201.1	1281.1	1441.1	1561.1	1580.5
142.5°	915.5	946.6	977.6	985.3	1057.3	1153.1	1201.1	1271.3	1411.9	1517.3	1534.0
145°	952.9	979.9	1006.9	1013.7	1073.5	1153.1	1192.9	1250.4	1365.4	1451.7	1464.3
147.5°	990.2	1016.5	1042.9	1049.4	1097.3	1161.0	1192.9	1238.2	1328.6	1396.5	1406.9
150°	1014.5	1038.3	1062.1	1068.1	1109.7	1165.2	1192.9	1231.1	1307.5	1364.8	1373.3
152.5°	1039.6	1057.7	1075.7	1080.2	1117.8	1167.9	1192.9	1225.6	1290.8	1339.7	1346.1
155°	1077.0	1090.3	1103.6	1107.0	1135.6	1173.8	1192.9	1218.9	1270.8	1309.7	1314.0
157.5°	1104.5	1117.5	1130.5	1133.7	1153.4	1179.8	1192.9	1213.1	1253.5	1283.7	1286.7
160°	1123.2	1133.3	1143.4	1145.9	1161.6	1182.5	1192.9	1210.2	1244.8	1270.8	1272.6
162.5°	1141.8	1149.4	1156.9	1158.8	1170.2	1185.4	1192.9	1207.5	1236.7	1258.6	1260.3
165°	1162.2	1169.0	1175.8	1177.5	1182.7	1189.5	1192.9	1203.4	1224.2	1239.9	1241.7
167.5°	1180.7	1184.0	1187.3	1188.1	1192.4	1198.2	1201.1	1207.9	1221.5	1231.8	1232.5
170°	1192.9	1196.2	1199.5	1200.3	1200.5	1200.9	1201.1	1207.9	1221.5	1231.8	1231.8
172.5°	1199.4	1200.1	1200.9	1201.1	1201.1	1201.1	1201.1	1206.5	1217.3	1225.4	1224.8
175°	1208.4	1208.4	1208.4	1208.4	1205.9	1202.7	1201.1	1204.5	1211.3	1216.5	1216.5
177.5°	1208.4	1208.4	1208.4	1208.4	1206.5	1203.9	1202.7	1205.4	1210.8	1214.8	1214.1
180°	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4	1208.4



TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1075.0	1075.0
2.5°	1147.5	1140.6
5°	1475.9	1482.8
7.5°	1987.5	1984.0
10°	2471.3	2502.4
12.5°	2823.9	2830.8
15°	3038.2	3052.0
17.5°	3121.1	3124.6
20°	3124.6	3117.7
22.5°	3086.6	3079.7
25°	3041.7	3038.2
27.5°	3000.1	3003.6
30°	2982.9	2993.3
32.5°	2982.9	3000.1
35°	2989.8	3007.0
37.5°	2986.3	3007.0
40°	2972.5	2996.7
42.5°	2934.5	2951.7
45°	2875.7	2896.5
47.5°	2799.7	2813.5
50°	2702.9	2716.7
52.5°	2581.9	2585.4
55°	2436.7	2450.6
57.5°	2281.2	2284.6
60°	2108.4	2118.8
62.5°	1925.2	1925.2
65°	1731.7	1738.6
67.5°	1531.2	1548.5
70°	1327.2	1330.7
72.5°	1126.8	1126.8
75°	919.4	922.9
77.5°	722.4	722.4
80°	535.8	539.2
82.5°	369.8	376.7
85°	231.6	231.6
87.5°	107.2	96.8
90°	30.8	30.8
92.5°	123.5	99.0
95°	430.3	356.1
97.5°	1030.9	889.6
100°	1485.3	1317.0
102.5°	1932.3	1788.2
105°	2502.3	2424.8
107.5°	2875.6	2894.4
110°	3017.9	3098.7



TEST NUMBER: P937226

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3030.7	3154.7
115°	2950.3	3122.2
117.5°	2779.9	2970.6
120°	2642.6	2827.8
122.5°	2508.8	2691.6
125°	2318.1	2486.4
127.5°	2146.6	2288.6
130°	2045.4	2176.7
132.5°	1953.7	2071.3
135°	1828.0	1929.3
137.5°	1727.2	1810.1
140°	1658.0	1735.4
142.5°	1600.7	1667.3
145°	1514.7	1565.1
147.5°	1448.7	1490.6
150°	1407.2	1441.1
152.5°	1371.7	1397.3
155°	1330.9	1347.8
157.5°	1298.6	1310.5
160°	1279.4	1286.2
162.5°	1266.7	1273.3
165°	1248.5	1255.4
167.5°	1235.5	1238.4
170°	1231.8	1231.8
172.5°	1222.2	1219.7
175°	1216.5	1216.5
177.5°	1211.3	1208.4
180°	1208.4	1208.4



TEST NUMBER: P937226
 CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-12-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.32	6.24	6.26	7.20	8.44	18.51	19.43	19.45	20.39	21.63
	3H	6.03	6.85	6.98	7.82	9.09	20.36	21.18	21.31	22.15	23.42
	4H	6.33	7.11	7.29	8.08	9.36	21.01	21.79	21.97	22.77	24.04
	6H	6.59	7.30	7.56	8.28	9.57	21.45	22.17	22.42	23.15	24.44
	8H	6.65	7.34	7.63	8.34	9.62	21.58	22.26	22.56	23.26	24.54
	12H	6.67	7.33	7.66	8.32	9.63	21.65	22.30	22.63	23.29	24.60
4H	2H	12.55	13.33	13.52	14.30	15.58	18.79	19.57	19.76	20.55	21.82
	3H	14.12	14.78	15.10	15.78	17.07	20.85	21.50	21.83	22.50	23.80
	4H	14.22	14.82	15.21	15.81	17.13	21.62	22.22	22.61	23.21	24.53
	6H	14.23	14.75	15.23	15.77	17.08	22.17	22.69	23.17	23.70	25.02
	8H	14.21	14.69	15.21	15.71	17.04	22.34	22.82	23.34	23.83	25.16
	12H	14.17	14.61	15.19	15.64	16.97	22.43	22.87	23.45	23.90	25.23
8H	4H	15.67	16.16	16.67	17.17	18.50	21.69	22.17	22.69	23.18	24.51
	6H	15.92	16.32	16.94	17.37	18.70	22.32	22.72	23.35	23.78	25.10
	8H	15.94	16.29	16.97	17.33	18.67	22.55	22.90	23.58	23.94	25.28
	12H	15.91	16.22	16.95	17.25	18.64	22.70	23.01	23.74	24.04	25.43
12H	4H	15.82	16.26	16.84	17.28	18.62	21.64	22.08	22.66	23.11	24.44
	6H	16.18	16.53	17.21	17.57	18.92	22.31	22.66	23.34	23.70	25.05
	8H	16.25	16.56	17.29	17.60	18.98	22.54	22.85	23.58	23.89	25.28