

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938047

Luminaire Tested: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938047  
REPORT IS A COMBINATION OF REPORTS P933615 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15297.4 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 128.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938047  
CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38	32		
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31	26		
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26	21		
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22	18		
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19	15		
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13		
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14	11		
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13	10		
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11	9		
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10	8		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3564	3564	3564
5°	3482	4119	4791
10°	3158	6005	7943
15°	2684	7845	9590
20°	2185	9091	9774
25°	1823	9514	9575
30°	1537	9574	9558
35°	1359	9415	9804
40°	1184	9208	10060
45°	1073	9057	10100
50°	984	8921	9932
55°	942	8721	9492
60°	965	8339	8797
65°	1003	7756	7842
70°	1069	6764	6625
75°	1185	5514	5170
80°	1295	3825	3484
85°	1150	2029	1783

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10100 cd/sqm



TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.4	0.6
10°-20°	440.4	2.9
20°-30°	770.4	5.0
30°-40°	991.7	6.5
40°-50°	1107.7	7.2
50°-60°	1060.9	6.9
60°-70°	840.8	5.5
70°-80°	494.4	3.2
80°-90°	142.9	0.9
90°-100°	703.0	4.6
100°-110°	1848.2	12.1
110°-120°	1916.4	12.5
120°-130°	1537.2	10.0
130°-140°	1206.1	7.9
140°-150°	925.8	6.1
150°-160°	666.7	4.4
160°-170°	407.9	2.7
170°-180°	137.8	0.9
0°-30°	1310.1	8.6
0°-40°	2301.8	15.0
0°-60°	4470.4	29.2
0°-90°	5948.4	38.9
90°-120°	4467.6	29.2
90°-150°	8136.6	53.2
90°-180°	9349.0	61.1
0°-180°	15297.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	768	768	768	768	768	
5°	748	803	904	1023	1060	69
15°	561	1035	1744	2114	2181	156
25°	358	1173	2077	2169	2171	165
35°	242	1122	1956	2068	2149	151
45°	166	894	1729	1981	2070	128
55°	118	568	1467	1704	1751	108
65°	94	301	1089	1225	1242	93
75°	69	185	598	657	660	72
85°	25	57	148	163	166	26
90°	10	27	74	37	37	10
95°	93	364	1211	624	425	103
105°	333	504	2043	3102	2894	353
115°	591	718	1637	3265	3726	584
125°	823	922	1489	2516	2968	730
135°	980	1079	1442	2031	2303	759
145°	1137	1210	1424	1733	1868	712
155°	1285	1321	1424	1563	1609	591
165°	1387	1405	1424	1480	1498	391
175°	1442	1442	1434	1452	1452	137
180°	1442	1442	1442	1442	1442	



TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	768.2	768.2	768.2	768.2	768.2	768.2	768.2	768.2	768.2	768.2	768.2
2.5°	768.2	768.2	773.2	775.6	780.6	783.0	788.0	792.9	807.8	810.2	815.2
5°	748.4	758.3	790.5	802.8	837.4	884.3	904.0	936.2	1002.8	1022.7	1035.0
7.5°	718.8	741.0	820.1	839.8	926.3	1049.8	1101.6	1170.8	1277.1	1329.0	1370.9
10°	671.9	718.8	859.6	906.6	1047.3	1235.0	1331.4	1427.8	1588.3	1659.9	1687.1
12.5°	620.0	696.5	901.6	965.8	1168.4	1442.5	1558.6	1664.9	1847.6	1944.0	1958.8
15°	560.7	664.5	941.2	1035.0	1296.8	1615.5	1743.9	1874.8	2045.2	2114.4	2131.7
17.5°	508.9	639.8	978.2	1077.0	1395.6	1771.1	1902.0	2010.6	2149.0	2195.9	2208.3
20°	444.6	600.3	1002.8	1131.3	1499.4	1884.7	2010.6	2094.7	2188.5	2218.2	2223.1
22.5°	397.7	558.2	1017.7	1151.1	1568.5	1953.9	2060.1	2126.7	2191.0	2200.9	2203.4
25°	358.2	511.3	1015.2	1173.3	1627.8	1995.9	2077.4	2126.7	2163.8	2168.8	2168.8
27.5°	321.1	459.4	1005.4	1178.3	1672.3	2005.8	2070.0	2104.6	2121.9	2131.7	2131.7
30°	289.0	410.1	980.6	1168.4	1692.0	1995.9	2047.8	2065.0	2082.3	2097.1	2104.6
32.5°	264.3	363.1	943.6	1148.6	1694.5	1971.2	2008.2	2018.1	2042.8	2077.4	2089.7
35°	242.1	316.2	901.6	1121.5	1679.7	1931.7	1956.3	1966.2	2015.6	2067.5	2084.8
37.5°	219.8	281.6	847.2	1074.5	1657.4	1884.7	1902.0	1919.3	1995.9	2057.6	2077.4
40°	197.6	252.0	783.0	1022.7	1622.8	1827.9	1842.7	1869.9	1971.2	2042.8	2062.5
42.5°	180.3	227.2	713.8	968.3	1578.4	1763.7	1785.9	1825.4	1941.5	2018.1	2040.4
45°	165.5	202.6	639.8	894.1	1521.6	1697.0	1729.1	1783.4	1906.9	1981.0	2000.8
47.5°	150.7	185.3	563.2	817.6	1459.8	1630.3	1672.3	1734.1	1860.0	1931.7	1949.0
50°	138.3	168.0	486.6	736.1	1393.2	1558.6	1608.1	1672.3	1800.7	1867.4	1889.6
52.5°	128.4	153.1	415.0	654.6	1316.5	1484.5	1541.3	1608.1	1729.1	1793.3	1808.1
55°	118.5	140.8	353.2	568.1	1237.6	1405.5	1467.2	1531.5	1650.0	1704.3	1714.3
57.5°	113.7	131.0	301.3	486.6	1153.5	1316.5	1385.7	1445.1	1556.2	1598.2	1608.1
60°	106.2	123.5	261.8	417.4	1062.2	1232.6	1291.9	1351.1	1445.1	1479.6	1487.0
62.5°	98.8	118.5	232.2	350.8	968.3	1133.8	1193.1	1247.5	1326.4	1351.1	1361.0
65°	93.8	113.7	209.9	301.3	872.0	1030.0	1089.3	1136.2	1200.4	1225.2	1230.2
67.5°	88.9	108.7	192.6	259.4	775.6	926.3	970.8	1015.2	1064.6	1089.3	1091.8
70°	81.5	103.8	177.9	229.8	676.8	807.8	844.8	891.7	931.2	943.6	951.0
72.5°	76.6	96.4	168.0	207.5	575.5	694.1	728.7	755.9	790.5	802.8	802.8
75°	69.2	86.5	158.1	185.3	471.8	568.1	597.7	624.9	652.1	657.1	649.6
77.5°	61.8	76.6	135.8	155.6	368.1	449.6	474.3	489.0	511.3	516.2	518.8
80°	51.9	66.7	106.2	121.0	266.8	331.0	348.3	360.6	380.4	380.4	385.4
82.5°	39.5	51.9	76.6	86.5	180.3	227.2	242.1	249.5	261.8	261.8	261.8
85°	24.7	32.2	49.4	56.8	108.7	138.3	148.2	150.7	160.6	163.0	163.0
87.5°	12.3	17.3	32.2	34.6	56.8	71.6	71.6	76.6	76.6	74.1	71.6
90°	9.7	17.5	25.1	27.1	42.6	63.3	73.6	65.3	49.0	36.7	36.7
92.5°	38.7	104.5	170.4	186.8	262.7	363.7	414.3	363.0	260.7	183.9	176.6
95°	92.9	213.4	333.9	364.0	646.3	1022.7	1210.8	1080.5	819.8	624.3	602.1
97.5°	160.7	267.0	373.2	399.8	870.5	1498.1	1811.9	1729.6	1564.8	1441.2	1399.1
100°	212.9	309.3	405.7	429.8	952.1	1648.5	1996.8	2002.8	2014.9	2023.9	1973.7
102.5°	257.4	347.3	437.3	459.8	989.6	1695.9	2049.1	2154.0	2364.0	2521.4	2478.4
105°	332.9	409.1	485.2	504.3	1017.2	1701.3	2043.3	2278.5	2749.2	3102.1	3079.0
107.5°	410.4	481.4	552.3	570.1	1022.4	1625.5	1927.1	2255.4	2911.8	3404.1	3409.7
110°	462.7	526.8	590.9	606.9	1014.7	1558.4	1830.3	2197.3	2931.1	3481.5	3505.6



TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	514.0	575.0	636.2	651.4	1015.0	1499.8	1742.2	2117.8	2868.8	3432.1	3469.2
115°	591.4	647.8	704.0	718.1	1024.3	1432.6	1636.8	1998.5	2722.1	3264.7	3316.1
117.5°	667.8	719.1	770.2	783.0	1043.4	1390.6	1564.1	1890.6	2543.6	3033.4	3090.3
120°	712.3	760.6	808.7	820.8	1058.8	1376.4	1535.1	1833.4	2430.0	2877.6	2932.8
122.5°	755.9	804.5	853.1	865.3	1081.1	1368.9	1512.8	1781.5	2318.8	2721.8	2776.3
125°	822.7	867.0	911.3	922.4	1111.1	1362.8	1488.6	1716.9	2173.3	2515.6	2565.8
127.5°	876.9	921.7	966.4	977.6	1141.2	1359.2	1468.3	1664.2	2056.2	2350.0	2392.4
130°	905.9	954.1	1002.3	1014.3	1163.1	1361.4	1460.6	1635.0	1983.9	2245.5	2284.7
132.5°	935.9	984.2	1032.3	1044.3	1180.8	1362.8	1453.7	1609.9	1922.2	2156.5	2191.5
135°	980.5	1024.3	1068.3	1079.2	1200.2	1361.5	1442.2	1572.9	1834.5	2030.6	2060.8
137.5°	1025.9	1069.4	1112.9	1123.7	1229.2	1369.9	1440.2	1550.8	1771.9	1937.7	1962.5
140°	1063.7	1103.7	1143.7	1153.7	1247.0	1371.3	1433.5	1529.0	1720.0	1863.2	1886.3
142.5°	1092.8	1129.8	1166.7	1176.0	1261.8	1376.3	1433.5	1517.3	1685.1	1810.9	1830.8
145°	1137.3	1169.5	1201.8	1209.9	1281.2	1376.3	1423.7	1492.4	1629.7	1732.6	1747.6
147.5°	1181.8	1213.2	1244.7	1252.5	1309.6	1385.7	1423.7	1477.8	1585.7	1666.8	1679.2
150°	1210.8	1239.2	1267.6	1274.8	1324.4	1390.7	1423.7	1469.4	1560.6	1629.0	1639.1
152.5°	1240.8	1262.3	1283.8	1289.2	1334.1	1393.8	1423.7	1462.7	1540.6	1599.0	1606.7
155°	1285.4	1301.3	1317.2	1321.2	1355.4	1400.9	1423.7	1454.8	1516.7	1563.2	1568.2
157.5°	1318.3	1333.7	1349.2	1353.1	1376.6	1408.0	1423.7	1447.9	1496.0	1532.2	1535.7
160°	1340.6	1352.6	1364.7	1367.7	1386.4	1411.3	1423.7	1444.4	1485.7	1516.7	1518.7
162.5°	1362.8	1371.8	1380.8	1383.1	1396.6	1414.7	1423.7	1441.1	1476.0	1502.2	1504.1
165°	1387.0	1395.2	1403.4	1405.4	1411.5	1419.6	1423.7	1436.3	1461.2	1479.9	1482.0
167.5°	1409.3	1413.1	1417.0	1417.9	1423.1	1430.0	1433.5	1441.6	1458.0	1470.2	1471.0
170°	1423.7	1427.7	1431.6	1432.5	1432.8	1433.3	1433.5	1441.6	1458.0	1470.2	1470.2
172.5°	1431.5	1432.3	1433.3	1433.5	1433.5	1433.5	1433.5	1439.9	1452.8	1462.5	1461.8
175°	1442.2	1442.2	1442.2	1442.2	1439.3	1435.4	1433.5	1437.6	1445.7	1451.9	1451.9
177.5°	1442.2	1442.2	1442.2	1442.2	1439.9	1436.9	1435.4	1438.6	1445.1	1449.9	1449.1
180°	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2



TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	768.2	768.2
2.5°	820.1	815.2
5°	1054.7	1059.7
7.5°	1420.3	1417.9
10°	1766.1	1788.4
12.5°	2018.1	2023.1
15°	2171.2	2181.1
17.5°	2230.5	2233.0
20°	2233.0	2228.1
22.5°	2205.8	2200.9
25°	2173.8	2171.2
27.5°	2144.0	2146.6
30°	2131.7	2139.2
32.5°	2131.7	2144.0
35°	2136.6	2149.0
37.5°	2134.2	2149.0
40°	2124.3	2141.6
42.5°	2097.1	2109.4
45°	2055.1	2070.0
47.5°	2000.8	2010.6
50°	1931.7	1941.5
52.5°	1845.2	1847.6
55°	1741.5	1751.4
57.5°	1630.3	1632.7
60°	1506.7	1514.2
62.5°	1375.9	1375.9
65°	1237.6	1242.5
67.5°	1094.3	1106.6
70°	948.5	951.0
72.5°	805.2	805.2
75°	657.1	659.5
77.5°	516.2	516.2
80°	382.9	385.4
82.5°	264.3	269.3
85°	165.5	165.5
87.5°	76.6	69.2
90°	36.7	36.7
92.5°	147.3	118.1
95°	513.5	424.9
97.5°	1230.4	1061.8
100°	1772.8	1571.9
102.5°	2306.3	2134.2
105°	2986.5	2894.0
107.5°	3432.1	3454.4
110°	3602.0	3698.4





TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	3617.1	3765.1
115°	3521.2	3726.4
117.5°	3317.8	3545.4
120°	3154.0	3375.0
122.5°	2994.4	3212.5
125°	2766.7	2967.6
127.5°	2561.9	2731.4
130°	2441.3	2597.8
132.5°	2331.8	2472.0
135°	2181.8	2302.6
137.5°	2061.4	2160.4
140°	1978.9	2071.3
142.5°	1910.4	1990.0
145°	1807.8	1868.0
147.5°	1729.1	1779.0
150°	1679.6	1720.0
152.5°	1637.1	1667.7
155°	1588.4	1608.6
157.5°	1549.9	1564.1
160°	1526.8	1535.1
162.5°	1511.9	1519.6
165°	1490.1	1498.3
167.5°	1474.5	1478.0
170°	1470.2	1470.2
172.5°	1458.7	1455.7
175°	1451.9	1451.9
177.5°	1445.6	1442.2
180°	1442.2	1442.2



TEST NUMBER: P938047

CATALOG NUMBER: SQ4-FB-125U-100D-92765-1D-UNV-STD-W-8-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.31	5.11	5.35	6.16	7.58	17.49	18.29	18.53	19.34	20.76
	3H	5.01	5.73	6.06	6.79	8.22	19.32	20.04	20.37	21.10	22.54
	4H	5.31	5.99	6.37	7.05	8.49	19.97	20.65	21.03	21.71	23.15
	6H	5.55	6.18	6.63	7.24	8.70	20.39	21.02	21.46	22.08	23.54
	8H	5.62	6.22	6.70	7.30	8.75	20.51	21.11	21.59	22.19	23.64
	12H	5.64	6.20	6.72	7.28	8.75	20.58	21.14	21.66	22.22	23.70
4H	2H	11.52	12.20	12.59	13.26	14.70	17.76	18.43	18.82	19.50	20.94
	3H	13.08	13.65	14.16	14.74	16.19	19.80	20.36	20.87	21.45	22.91
	4H	13.17	13.69	14.25	14.77	16.25	20.56	21.08	21.64	22.16	23.64
	6H	13.18	13.63	14.27	14.73	16.20	21.09	21.54	22.19	22.65	24.12
	8H	13.15	13.57	14.24	14.67	16.16	21.26	21.67	22.35	22.77	24.26
	12H	13.11	13.49	14.22	14.59	16.09	21.35	21.73	22.45	22.83	24.33
8H	4H	14.61	15.03	15.70	16.12	17.61	20.61	21.03	21.71	22.13	23.62
	6H	14.85	15.20	15.96	16.33	17.82	21.24	21.59	22.35	22.72	24.21
	8H	14.87	15.17	15.99	16.29	17.80	21.46	21.76	22.58	22.88	24.39
	12H	14.83	15.10	15.96	16.21	17.76	21.60	21.87	22.73	22.98	24.53
12H	4H	14.75	15.13	15.86	16.24	17.73	20.56	20.94	21.67	22.05	23.55
	6H	15.11	15.41	16.23	16.53	18.04	21.22	21.53	22.34	22.65	24.15
	8H	15.17	15.44	16.30	16.56	18.10	21.45	21.72	22.57	22.83	24.37