

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937243

Luminaire Tested: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937243
REPORT IS A COMBINATION OF REPORTS P933519 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10548.5 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 102.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937243
CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3257	3257	3257
5°	3182	3764	4378
10°	2886	5487	7258
15°	2453	7169	8764
20°	1997	8307	8932
25°	1666	8694	8750
30°	1405	8748	8734
35°	1242	8603	8959
40°	1082	8414	9193
45°	980	8276	9229
50°	899	8152	9076
55°	861	7969	8674
60°	881	7620	8039
65°	917	7087	7166
70°	977	6181	6053
75°	1082	5039	4724
80°	1183	3494	3184
85°	1048	1855	1630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9229 cd/sqm



TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	0.9
10°-20°	402.4	3.8
20°-30°	703.9	6.7
30°-40°	906.2	8.6
40°-50°	1012.2	9.6
50°-60°	969.4	9.2
60°-70°	768.3	7.3
70°-80°	451.8	4.3
80°-90°	128.5	1.2
90°-100°	384.6	3.6
100°-110°	1011.1	9.6
110°-120°	1048.5	9.9
120°-130°	841.0	8.0
130°-140°	659.9	6.3
140°-150°	506.5	4.8
150°-160°	364.8	3.5
160°-170°	223.2	2.1
170°-180°	75.4	0.7
0°-30°	1197.2	11.3
0°-40°	2103.4	19.9
0°-60°	4085.0	38.7
0°-90°	5433.6	51.5
90°-120°	2444.2	23.2
90°-150°	4451.6	42.2
90°-180°	5115.0	48.5
0°-180°	10548.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	702	702	702	702	702	
5°	684	734	826	934	968	63
15°	512	946	1594	1932	1993	143
25°	327	1072	1898	1982	1984	151
35°	221	1025	1788	1889	1964	138
45°	151	817	1580	1810	1892	117
55°	108	519	1341	1557	1600	99
65°	86	275	995	1120	1135	85
75°	63	169	546	600	603	66
85°	22	52	136	149	151	24
90°	5	15	40	20	20	6
95°	51	199	662	342	232	56
105°	182	276	1118	1697	1583	193
115°	324	393	896	1786	2039	320
125°	450	505	814	1376	1624	400
135°	536	590	789	1111	1260	415
145°	622	662	779	948	1022	390
155°	703	723	779	855	880	323
165°	759	769	779	810	820	214
175°	789	789	784	794	794	75
180°	789	789	789	789	789	



TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	702.0	702.0	702.0	702.0	702.0	702.0	702.0	702.0	702.0	702.0	702.0
2.5°	702.0	702.0	706.5	708.8	713.3	715.5	720.0	724.6	738.1	740.4	744.9
5°	683.9	693.0	722.3	733.6	765.2	808.1	826.1	855.5	916.4	934.5	945.8
7.5°	656.8	677.2	749.4	767.4	846.4	959.3	1006.7	1069.9	1167.0	1214.4	1252.7
10°	613.9	656.8	785.5	828.4	957.1	1128.6	1216.6	1304.7	1451.3	1516.8	1541.6
12.5°	566.5	636.5	823.9	882.6	1067.7	1318.2	1424.3	1521.4	1688.4	1776.4	1789.9
15°	512.4	607.2	860.0	945.8	1185.0	1476.2	1593.5	1713.2	1868.9	1932.1	1947.9
17.5°	465.0	584.7	893.8	984.1	1275.3	1618.4	1738.1	1837.3	1963.7	2006.6	2018.0
20°	406.3	548.5	916.4	1033.8	1370.1	1722.3	1837.3	1914.1	1999.9	2026.9	2031.5
22.5°	363.4	510.1	930.0	1051.9	1433.3	1785.5	1882.5	1943.4	2002.2	2011.1	2013.4
25°	327.3	467.2	927.7	1072.2	1487.5	1823.8	1898.3	1943.4	1977.3	1981.8	1981.8
27.5°	293.4	419.8	918.7	1076.7	1528.1	1832.9	1891.6	1923.2	1939.0	1947.9	1947.9
30°	264.1	374.7	896.1	1067.7	1546.1	1823.8	1871.2	1887.0	1902.8	1916.3	1923.2
32.5°	241.5	331.8	862.2	1049.6	1548.4	1801.3	1835.1	1844.1	1866.7	1898.3	1909.6
35°	221.2	289.0	823.9	1024.8	1534.9	1765.1	1787.7	1796.7	1841.8	1889.2	1905.0
37.5°	200.9	257.3	774.2	981.9	1514.5	1722.3	1738.1	1753.9	1823.8	1880.2	1898.3
40°	180.6	230.3	715.5	934.5	1482.9	1670.3	1683.8	1708.7	1801.3	1866.7	1884.7
42.5°	164.8	207.6	652.3	884.8	1442.4	1611.7	1632.0	1668.0	1774.1	1844.1	1864.5
45°	151.3	185.1	584.7	817.1	1390.4	1550.7	1580.1	1629.7	1742.5	1810.2	1828.3
47.5°	137.7	169.3	514.6	747.1	1334.0	1489.8	1528.1	1584.6	1699.6	1765.1	1780.9
50°	126.4	153.5	444.7	672.6	1273.1	1424.3	1469.4	1528.1	1645.5	1706.5	1726.7
52.5°	117.4	139.9	379.2	598.1	1203.0	1356.5	1408.5	1469.4	1580.1	1638.7	1652.2
55°	108.3	128.6	322.8	519.1	1130.9	1284.4	1340.7	1399.5	1507.8	1557.4	1566.5
57.5°	103.9	119.7	275.4	444.7	1054.1	1203.0	1266.2	1320.5	1422.0	1460.4	1469.4
60°	97.0	112.8	239.2	381.5	970.6	1126.3	1180.5	1234.6	1320.5	1352.1	1358.8
62.5°	90.3	108.3	212.2	320.6	884.8	1036.1	1090.2	1139.9	1212.1	1234.6	1243.7
65°	85.8	103.9	191.8	275.4	796.8	941.2	995.4	1038.3	1097.0	1119.6	1124.1
67.5°	81.2	99.3	176.0	237.0	708.8	846.4	887.1	927.7	972.9	995.4	997.7
70°	74.5	94.8	162.5	209.9	618.5	738.1	772.0	814.8	851.0	862.2	869.0
72.5°	70.0	88.1	153.5	189.6	525.9	634.3	665.9	690.7	722.3	733.6	733.6
75°	63.2	79.0	144.4	169.3	431.2	519.1	546.2	571.1	595.9	600.5	593.6
77.5°	56.5	70.0	124.1	142.2	336.4	410.8	433.4	446.9	467.2	471.7	474.0
80°	47.4	61.0	97.0	110.6	243.8	302.4	318.2	329.5	347.6	347.6	352.2
82.5°	36.1	47.4	70.0	79.0	164.8	207.6	221.2	228.0	239.2	239.2	239.2
85°	22.5	29.4	45.2	51.9	99.3	126.4	135.5	137.7	146.7	149.0	149.0
87.5°	11.3	15.8	29.4	31.6	51.9	65.4	65.4	70.0	70.0	67.7	65.4
90°	5.3	9.6	13.8	14.9	23.3	34.6	40.2	35.8	26.8	20.2	20.2
92.5°	21.2	57.2	93.3	102.2	143.7	199.0	226.7	198.7	142.6	100.6	96.6
95°	50.8	116.8	182.6	199.1	353.5	559.5	662.5	591.1	448.5	341.6	329.4
97.5°	87.9	146.1	204.2	218.7	476.3	819.6	991.3	946.2	856.1	788.5	765.5
100°	116.5	169.2	222.0	235.1	520.9	902.0	1092.4	1095.8	1102.3	1107.3	1079.8
102.5°	140.8	190.0	239.2	251.5	541.3	927.8	1121.0	1178.4	1293.3	1379.5	1355.9
105°	182.2	223.9	265.5	275.9	556.5	930.7	1117.9	1246.6	1504.0	1697.2	1684.5
107.5°	224.6	263.4	302.2	311.9	559.4	889.3	1054.3	1233.9	1593.0	1862.4	1865.5
110°	253.2	288.2	323.2	332.0	555.1	852.6	1001.4	1202.1	1603.6	1904.8	1917.9



TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	281.2	314.6	348.0	356.3	555.3	820.6	953.2	1158.7	1569.6	1877.8	1898.0
115°	323.5	354.4	385.2	392.9	560.4	783.7	895.5	1093.4	1489.3	1786.2	1814.3
117.5°	365.4	393.4	421.4	428.4	570.9	760.8	855.8	1034.3	1391.6	1659.6	1690.7
120°	389.7	416.0	442.4	449.0	579.3	753.0	839.9	1003.1	1329.5	1574.3	1604.6
122.5°	413.6	440.2	466.8	473.4	591.5	748.9	827.7	974.6	1268.6	1489.1	1518.9
125°	450.1	474.4	498.6	504.6	607.9	745.6	814.4	939.3	1188.9	1376.3	1403.8
127.5°	479.8	504.3	528.7	534.9	624.4	743.7	803.3	910.5	1124.9	1285.7	1308.9
130°	495.7	522.0	548.4	554.9	636.3	744.9	799.1	894.5	1085.4	1228.6	1250.0
132.5°	512.0	538.4	564.8	571.4	646.1	745.6	795.4	880.8	1051.7	1179.8	1199.0
135°	536.4	560.4	584.5	590.5	656.7	744.9	789.0	860.6	1003.7	1111.0	1127.5
137.5°	561.3	585.1	608.8	614.8	672.5	749.5	787.9	848.4	969.4	1060.1	1073.6
140°	582.0	603.9	625.7	631.2	682.2	750.3	784.3	836.5	941.0	1019.4	1032.0
142.5°	597.9	618.1	638.4	643.4	690.4	753.0	784.3	830.1	921.9	990.8	1001.6
145°	622.2	639.9	657.5	661.9	701.0	753.0	779.0	816.5	891.6	947.9	956.1
147.5°	646.6	663.7	681.0	685.3	716.5	758.1	779.0	808.5	867.5	911.9	918.7
150°	662.5	678.0	693.6	697.4	724.6	760.9	779.0	803.9	853.8	891.2	896.7
152.5°	678.9	690.6	702.4	705.3	729.9	762.6	779.0	800.2	842.9	874.8	879.0
155°	703.2	711.9	720.6	722.8	741.6	766.5	779.0	795.9	829.8	855.2	858.0
157.5°	721.2	729.7	738.1	740.3	753.2	770.3	779.0	792.1	818.5	838.2	840.2
160°	733.4	740.0	746.6	748.2	758.5	772.1	779.0	790.2	812.9	829.8	830.9
162.5°	745.6	750.5	755.5	756.8	764.2	774.0	779.0	788.5	807.6	821.8	822.9
165°	758.8	763.2	767.8	768.9	772.2	776.7	779.0	785.8	799.5	809.7	810.8
167.5°	771.0	773.2	775.3	775.8	778.6	782.4	784.3	788.7	797.7	804.4	804.8
170°	779.0	781.1	783.2	783.7	783.9	784.2	784.3	788.7	797.7	804.4	804.4
172.5°	783.2	783.7	784.2	784.3	784.3	784.3	784.3	787.8	794.9	800.1	799.7
175°	789.0	789.0	789.0	789.0	787.4	785.3	784.3	786.5	791.0	794.3	794.3
177.5°	789.0	789.0	789.0	789.0	787.8	786.1	785.3	787.1	790.6	793.2	792.8
180°	789.0	789.0	789.0	789.0	789.0	789.0	789.0	789.0	789.0	789.0	789.0



TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	702.0	702.0
2.5°	749.4	744.9
5°	963.8	968.3
7.5°	1297.8	1295.6
10°	1613.9	1634.2
12.5°	1844.1	1848.7
15°	1984.1	1993.1
17.5°	2038.2	2040.5
20°	2040.5	2036.0
22.5°	2015.7	2011.1
25°	1986.4	1984.1
27.5°	1959.2	1961.5
30°	1947.9	1954.8
32.5°	1947.9	1959.2
35°	1952.5	1963.7
37.5°	1950.2	1963.7
40°	1941.2	1957.0
42.5°	1916.3	1927.6
45°	1878.0	1891.6
47.5°	1828.3	1837.3
50°	1765.1	1774.1
52.5°	1686.1	1688.4
55°	1591.3	1600.4
57.5°	1489.8	1492.0
60°	1376.9	1383.7
62.5°	1257.3	1257.3
65°	1130.9	1135.4
67.5°	999.9	1011.2
70°	866.8	869.0
72.5°	735.8	735.8
75°	600.5	602.7
77.5°	471.7	471.7
80°	349.9	352.2
82.5°	241.5	246.1
85°	151.3	151.3
87.5°	70.0	63.2
90°	20.2	20.2
92.5°	80.6	64.6
95°	281.0	232.5
97.5°	673.1	580.9
100°	969.9	860.0
102.5°	1261.8	1167.7
105°	1633.9	1583.3
107.5°	1877.7	1889.9
110°	1970.7	2023.4



TEST NUMBER: P937243

CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1978.9	2059.9
115°	1926.5	2038.7
117.5°	1815.2	1939.7
120°	1725.6	1846.5
122.5°	1638.2	1757.5
125°	1513.7	1623.6
127.5°	1401.6	1494.4
130°	1335.6	1421.3
132.5°	1275.7	1352.4
135°	1193.6	1259.8
137.5°	1127.8	1181.9
140°	1082.7	1133.3
142.5°	1045.2	1088.8
145°	989.1	1022.0
147.5°	945.9	973.3
150°	918.9	941.0
152.5°	895.6	912.4
155°	869.1	880.1
157.5°	848.0	855.8
160°	835.4	839.9
162.5°	827.1	831.4
165°	815.3	819.7
167.5°	806.7	808.6
170°	804.4	804.4
172.5°	798.1	796.5
175°	794.3	794.3
177.5°	790.9	789.0
180°	789.0	789.0



TEST NUMBER: P937243
 CATALOG NUMBER: SQ4-FB-075U-100D-92765-1D-UNV-STD-W-8-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.25	6.16	6.18	7.12	8.37	18.42	19.34	19.36	20.30	21.54
	3H	5.96	6.78	6.90	7.75	9.01	20.27	21.09	21.21	22.06	23.33
	4H	6.26	7.04	7.22	8.01	9.28	20.91	21.69	21.88	22.67	23.94
	6H	6.51	7.23	7.48	8.21	9.50	21.35	22.07	22.32	23.04	24.34
	8H	6.58	7.26	7.56	8.26	9.55	21.47	22.16	22.45	23.15	24.44
	12H	6.60	7.25	7.58	8.24	9.55	21.54	22.19	22.53	23.18	24.50
4H	2H	12.47	13.25	13.43	14.22	15.50	18.70	19.48	19.67	20.46	21.73
	3H	14.04	14.69	15.02	15.69	16.99	20.75	21.41	21.73	22.41	23.70
	4H	14.14	14.73	15.12	15.73	17.04	21.52	22.12	22.51	23.12	24.43
	6H	14.15	14.67	15.15	15.69	17.00	22.07	22.58	23.07	23.60	24.91
	8H	14.13	14.61	15.13	15.62	16.95	22.23	22.71	23.23	23.73	25.05
	12H	14.09	14.52	15.11	15.55	16.89	22.33	22.76	23.35	23.79	25.13
8H	4H	15.59	16.07	16.59	17.08	18.41	21.59	22.07	22.59	23.08	24.41
	6H	15.83	16.23	16.86	17.28	18.61	22.22	22.62	23.25	23.67	25.00
	8H	15.85	16.20	16.88	17.24	18.59	22.44	22.80	23.48	23.83	25.18
	12H	15.82	16.13	16.86	17.17	18.55	22.59	22.90	23.63	23.93	25.32
12H	4H	15.73	16.17	16.75	17.20	18.53	21.54	21.98	22.56	23.01	24.34
	6H	16.09	16.44	17.12	17.48	18.83	22.21	22.56	23.24	23.60	24.94
	8H	16.16	16.47	17.20	17.51	18.90	22.44	22.75	23.48	23.78	25.17