

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937335

Luminaire Tested: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P937335  
REPORT IS A COMBINATION OF REPORTS P933504 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6605.6 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 62  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937335  
CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58			58
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52	47			47
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43	38			38
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36	32			32
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30	27			27
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26	23			23
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22	19			19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17			17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15			15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15	13			13
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14	12			12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4564	4564	4564
5°	4454	5272	6135
10°	4036	7679	10171
15°	3426	10024	12281
20°	2786	11609	12516
25°	2322	12139	12263
30°	1955	12205	12239
35°	1726	11993	12556
40°	1502	11721	12882
45°	1357	11518	12933
50°	1242	11333	12720
55°	1186	11066	12156
60°	1210	10566	11266
65°	1252	9812	10041
70°	1325	8539	8484
75°	1453	6946	6620
80°	1554	4799	4462
85°	1308	2533	2284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 12933 cd/sqm



TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.6	1.0
10°-20°	282.0	4.3
20°-30°	493.3	7.5
30°-40°	635.0	9.6
40°-50°	709.2	10.7
50°-60°	679.3	10.3
60°-70°	538.3	8.1
70°-80°	316.6	4.8
80°-90°	89.6	1.4
90°-100°	210.4	3.2
100°-110°	553.3	8.4
110°-120°	573.7	8.7
120°-130°	460.2	7.0
130°-140°	361.1	5.5
140°-150°	277.1	4.2
150°-160°	199.6	3.0
160°-170°	122.1	1.8
170°-180°	41.3	0.6
0°-30°	838.9	12.7
0°-40°	1473.9	22.3
0°-60°	2862.4	43.3
0°-90°	3806.9	57.6
90°-120°	1337.4	20.2
90°-150°	2435.8	36.9
90°-180°	2799.0	42.4
0°-180°	6605.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	492	492	492	492	492	
5°	479	514	579	655	678	44
15°	359	663	1117	1354	1396	100
25°	229	751	1330	1389	1390	106
35°	155	718	1253	1324	1376	97
45°	106	572	1107	1268	1325	82
55°	76	364	940	1091	1121	69
65°	60	193	698	784	796	60
75°	44	119	383	421	422	46
85°	16	36	95	104	106	17
90°	3	8	22	11	11	3
95°	28	109	362	187	127	31
105°	100	151	612	929	866	106
115°	177	215	490	977	1116	175
125°	246	276	446	753	888	219
135°	294	323	432	608	689	227
145°	340	362	426	519	559	213
155°	385	396	426	468	482	177
165°	415	421	426	443	449	117
175°	432	432	429	435	435	41
180°	432	432	432	432	432	



TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8
2.5°	491.8	491.8	495.0	496.6	499.8	501.4	504.6	507.7	517.2	518.8	521.9
5°	479.2	485.6	506.1	514.0	536.1	566.2	578.9	599.4	642.1	654.8	662.7
7.5°	460.2	474.5	525.1	537.7	593.1	672.1	705.4	749.7	817.7	850.9	877.8
10°	430.2	460.2	550.4	580.5	670.6	790.8	852.5	914.1	1017.0	1062.9	1080.2
12.5°	397.0	446.0	577.3	618.4	748.1	923.7	998.0	1066.0	1183.1	1244.7	1254.2
15°	359.0	425.5	602.6	662.7	830.3	1034.3	1116.6	1200.4	1309.6	1353.8	1365.0
17.5°	325.8	409.7	626.3	689.6	893.6	1134.0	1217.8	1287.5	1376.0	1406.1	1413.9
20°	284.7	384.4	642.1	724.4	960.0	1206.8	1287.5	1341.2	1401.3	1420.3	1423.5
22.5°	254.6	357.4	651.6	737.0	1004.3	1251.0	1319.1	1361.8	1402.9	1409.3	1410.8
25°	229.4	327.4	650.1	751.2	1042.3	1277.9	1330.2	1361.8	1385.5	1388.7	1388.7
27.5°	205.6	294.2	643.7	754.4	1070.7	1284.3	1325.4	1347.6	1358.6	1365.0	1365.0
30°	185.1	262.6	627.9	748.1	1083.4	1277.9	1311.1	1322.2	1333.3	1342.8	1347.6
32.5°	169.3	232.5	604.2	735.4	1085.0	1262.1	1285.9	1292.1	1308.0	1330.2	1338.0
35°	155.0	202.5	577.3	718.0	1075.5	1236.8	1252.6	1259.0	1290.5	1323.8	1334.9
37.5°	140.8	180.3	542.5	688.0	1061.3	1206.8	1217.8	1229.0	1277.9	1317.5	1330.2
40°	126.6	161.3	501.4	654.8	1039.1	1170.3	1179.9	1197.3	1262.1	1308.0	1320.6
42.5°	115.4	145.5	457.1	620.0	1010.6	1129.3	1143.5	1168.8	1243.2	1292.1	1306.4
45°	106.0	129.7	409.7	572.5	974.2	1086.6	1107.2	1141.9	1221.0	1268.5	1281.1
47.5°	96.5	118.6	360.6	523.5	934.7	1043.9	1070.7	1110.3	1190.9	1236.8	1247.9
50°	88.6	107.6	311.5	471.3	892.0	998.0	1029.7	1070.7	1153.0	1195.7	1210.0
52.5°	82.3	98.1	265.7	419.1	843.0	950.5	987.0	1029.7	1107.2	1148.3	1157.7
55°	75.9	90.1	226.2	363.8	792.4	899.9	939.5	980.6	1056.5	1091.3	1097.6
57.5°	72.7	83.8	192.9	311.5	738.6	843.0	887.3	925.3	996.4	1023.3	1029.7
60°	68.0	79.1	167.7	267.3	680.1	789.3	827.2	865.2	925.3	947.4	952.1
62.5°	63.3	75.9	148.7	224.6	620.0	726.0	763.9	798.7	849.4	865.2	871.4
65°	60.1	72.7	134.4	192.9	558.3	659.5	697.5	727.6	768.7	784.5	787.7
67.5°	56.9	69.6	123.4	166.1	496.6	593.1	621.6	650.1	681.7	697.5	699.1
70°	52.2	66.5	113.8	147.1	433.3	517.2	540.9	570.9	596.2	604.2	609.0
72.5°	49.1	61.7	107.6	132.8	368.6	444.5	466.6	484.0	506.1	514.0	514.0
75°	44.3	55.3	101.2	118.6	302.1	363.8	382.8	400.1	417.5	420.7	415.9
77.5°	39.5	49.1	87.0	99.6	235.6	287.9	303.7	313.1	327.4	330.5	332.1
80°	33.2	42.7	68.0	77.5	170.8	211.9	223.0	230.9	243.6	243.6	246.8
82.5°	25.3	33.2	49.1	55.3	115.4	145.5	155.0	159.7	167.7	167.7	167.7
85°	15.8	20.6	31.6	36.4	69.6	88.6	94.9	96.5	102.8	104.4	104.4
87.5°	7.9	11.0	20.6	22.2	36.4	45.9	45.9	49.1	49.1	47.5	45.9
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.6	14.7	11.0	11.0
92.5°	11.6	31.3	50.9	55.9	78.6	108.9	124.0	108.7	78.0	55.1	52.9
95°	27.9	63.9	100.0	109.0	193.5	306.1	362.5	323.4	245.4	186.8	180.2
97.5°	48.1	79.9	111.7	119.6	260.6	448.5	542.4	517.7	468.5	431.5	418.8
100°	63.7	92.5	121.4	128.6	285.0	493.5	597.7	599.5	603.2	605.9	590.8
102.5°	77.1	104.0	130.9	137.6	296.2	507.7	613.4	644.9	707.7	754.8	741.9
105°	99.6	122.4	145.3	151.0	304.5	509.3	611.7	682.1	823.0	928.6	921.7
107.5°	122.8	144.1	165.3	170.7	306.1	486.6	576.9	675.1	871.6	1019.0	1020.7
110°	138.5	157.7	176.9	181.7	303.8	466.5	547.9	657.8	877.4	1042.2	1049.4



TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.9	172.2	190.4	195.0	303.9	449.0	521.6	634.0	858.8	1027.4	1038.6
115°	177.0	193.9	210.8	215.0	306.7	428.8	490.0	598.3	814.9	977.3	992.7
117.5°	199.9	215.3	230.6	234.4	312.4	416.2	468.2	566.0	761.4	908.1	925.1
120°	213.3	227.7	242.1	245.7	317.0	412.0	459.5	548.9	727.5	861.4	878.0
122.5°	226.3	240.9	255.4	259.0	323.6	409.8	452.9	533.2	694.1	814.8	831.1
125°	246.3	259.6	272.8	276.1	332.7	408.0	445.7	514.0	650.6	753.1	768.1
127.5°	262.6	275.9	289.3	292.7	341.6	407.0	439.6	498.3	615.6	703.6	716.3
130°	271.3	285.6	300.0	303.7	348.2	407.5	437.3	489.5	593.9	672.2	683.9
132.5°	280.2	294.6	309.0	312.7	353.5	408.0	435.2	481.9	575.5	645.6	656.1
135°	293.5	306.6	319.8	323.0	359.3	407.6	431.7	470.9	549.2	607.9	617.0
137.5°	307.1	320.1	333.1	336.4	368.0	410.1	431.2	464.3	530.4	580.1	587.5
140°	318.5	330.4	342.4	345.4	373.3	410.5	429.1	457.7	514.8	557.7	564.7
142.5°	327.1	338.2	349.2	352.0	377.7	412.0	429.1	454.3	504.5	542.1	548.1
145°	340.4	350.1	359.8	362.2	383.5	412.0	426.2	446.8	487.8	518.7	523.2
147.5°	353.8	363.1	372.6	374.9	392.0	414.8	426.2	442.4	474.7	498.9	502.7
150°	362.5	371.0	379.5	381.6	396.5	416.3	426.2	439.9	467.2	487.6	490.6
152.5°	371.5	377.9	384.4	385.9	399.4	417.3	426.2	437.9	461.2	478.7	480.9
155°	384.8	389.6	394.3	395.5	405.8	419.4	426.2	435.5	454.0	467.9	469.4
157.5°	394.6	399.3	404.0	405.1	412.1	421.6	426.2	433.4	447.8	458.7	459.7
160°	401.3	404.9	408.5	409.4	415.0	422.5	426.2	432.4	444.8	454.1	454.6
162.5°	408.0	410.7	413.4	414.1	418.1	423.5	426.2	431.5	441.8	449.7	450.2
165°	415.2	417.6	420.1	420.7	422.6	425.0	426.2	430.0	437.4	443.1	443.7
167.5°	421.8	423.0	424.2	424.4	426.0	428.1	429.1	431.6	436.5	440.2	440.4
170°	426.2	427.3	428.6	428.8	428.9	429.0	429.1	431.6	436.5	440.2	440.2
172.5°	428.6	428.8	429.0	429.1	429.1	429.1	429.1	431.1	434.9	437.8	437.6
175°	431.7	431.7	431.7	431.7	430.9	429.7	429.1	430.3	432.8	434.6	434.6
177.5°	431.7	431.7	431.7	431.7	431.1	430.2	429.7	430.6	432.6	434.1	433.8
180°	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7	431.7



TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	491.8	491.8
2.5°	525.1	521.9
5°	675.3	678.5
7.5°	909.5	907.9
10°	1130.8	1145.1
12.5°	1292.1	1295.3
15°	1390.3	1396.5
17.5°	1428.2	1429.8
20°	1429.8	1426.6
22.5°	1412.3	1409.3
25°	1391.8	1390.3
27.5°	1372.8	1374.4
30°	1365.0	1369.7
32.5°	1365.0	1372.8
35°	1368.1	1376.0
37.5°	1366.5	1376.0
40°	1360.2	1371.2
42.5°	1342.8	1350.7
45°	1315.9	1325.4
47.5°	1281.1	1287.5
50°	1236.8	1243.2
52.5°	1181.5	1183.1
55°	1115.0	1121.4
57.5°	1043.9	1045.5
60°	964.8	969.6
62.5°	881.0	881.0
65°	792.4	795.5
67.5°	700.7	708.6
70°	607.4	609.0
72.5°	515.6	515.6
75°	420.7	422.3
77.5°	330.5	330.5
80°	245.2	246.8
82.5°	169.3	172.4
85°	106.0	106.0
87.5°	49.1	44.3
90°	11.0	11.0
92.5°	44.1	35.3
95°	153.8	127.2
97.5°	368.4	317.9
100°	530.7	470.5
102.5°	690.4	638.9
105°	894.0	866.4
107.5°	1027.4	1034.2
110°	1078.3	1107.2





TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	1082.9	1127.2
115°	1054.2	1115.6
117.5°	993.2	1061.4
120°	944.1	1010.3
122.5°	896.4	961.7
125°	828.2	888.3
127.5°	766.9	817.7
130°	730.8	777.7
132.5°	698.0	740.0
135°	653.2	689.3
137.5°	617.1	646.7
140°	592.4	620.1
142.5°	571.9	595.7
145°	541.2	559.2
147.5°	517.6	532.6
150°	502.8	514.9
152.5°	490.1	499.2
155°	475.5	481.6
157.5°	464.0	468.2
160°	457.1	459.5
162.5°	452.6	454.9
165°	446.1	448.6
167.5°	441.5	442.5
170°	440.2	440.2
172.5°	436.7	435.8
175°	434.6	434.6
177.5°	432.8	431.7
180°	431.7	431.7



TEST NUMBER: P937335

CATALOG NUMBER: SQ4-FB-075U-125D-92765-1D-UNV-STD-W-4-5000K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.93	7.91	7.81	8.82	9.97	20.07	21.05	20.95	21.96	23.11
	3H	7.65	8.53	8.54	9.45	10.62	21.90	22.79	22.80	23.70	24.88
	4H	7.95	8.79	8.86	9.71	10.90	22.55	23.38	23.45	24.30	25.49
	6H	8.21	8.98	9.13	9.91	11.11	22.97	23.74	23.89	24.67	25.87
	8H	8.28	9.02	9.21	9.96	11.16	23.09	23.82	24.01	24.77	25.97
	12H	8.30	9.00	9.24	9.94	11.17	23.15	23.85	24.09	24.79	26.02
4H	2H	14.14	14.97	15.05	15.90	17.08	20.36	21.20	21.27	22.12	23.31
	3H	15.72	16.42	16.64	17.37	18.58	22.40	23.10	23.33	24.06	25.26
	4H	15.82	16.46	16.75	17.41	18.64	23.17	23.81	24.10	24.75	25.98
	6H	15.84	16.39	16.79	17.36	18.59	23.70	24.25	24.65	25.22	26.45
	8H	15.82	16.34	16.77	17.30	18.54	23.86	24.38	24.81	25.34	26.58
	12H	15.78	16.25	16.75	17.23	18.48	23.95	24.42	24.92	25.40	26.65
8H	4H	17.26	17.78	18.21	18.75	19.99	23.24	23.75	24.19	24.72	25.96
	6H	17.51	17.94	18.49	18.95	20.19	23.86	24.29	24.84	25.30	26.54
	8H	17.53	17.91	18.52	18.91	20.17	24.07	24.45	25.06	25.45	26.71
	12H	17.51	17.84	18.50	18.83	20.14	24.22	24.55	25.21	25.54	26.85
12H	4H	17.41	17.88	18.38	18.86	20.11	23.20	23.66	24.17	24.65	25.90
	6H	17.77	18.15	18.75	19.14	20.40	23.84	24.23	24.83	25.22	26.48
	8H	17.84	18.18	18.83	19.17	20.47	24.07	24.41	25.06	25.40	26.70