

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938244

Luminaire Tested: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938244
REPORT IS A COMBINATION OF REPORTS P933645 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13327.3 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 111.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938244
CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	17
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	12
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	10
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	8
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	7
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	6
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	5
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	9	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1687	1687	1687
5°	1649	1951	2269
10°	1495	2844	3761
15°	1271	3715	4541
20°	1035	4305	4628
25°	863	4505	4534
30°	728	4533	4526
35°	643	4458	4643
40°	561	4360	4764
45°	508	4289	4782
50°	466	4224	4703
55°	447	4129	4495
60°	457	3948	4165
65°	476	3673	3714
70°	506	3203	3137
75°	562	2612	2448
80°	614	1811	1649
85°	545	961	845

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4782 cd/sqm



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.1	0.4
10°-20°	208.5	1.6
20°-30°	364.8	2.7
30°-40°	469.6	3.5
40°-50°	524.5	3.9
50°-60°	502.4	3.8
60°-70°	398.1	3.0
70°-80°	234.1	1.8
80°-90°	71.2	0.5
90°-100°	790.1	5.9
100°-110°	2077.1	15.6
110°-120°	2153.8	16.2
120°-130°	1727.6	13.0
130°-140°	1355.5	10.2
140°-150°	1040.4	7.8
150°-160°	749.3	5.6
160°-170°	458.4	3.4
170°-180°	154.9	1.2
0°-30°	620.4	4.7
0°-40°	1090.0	8.2
0°-60°	2116.8	15.9
0°-90°	2820.3	21.2
90°-120°	5020.9	37.7
90°-150°	9144.4	68.6
90°-180°	10507.0	78.8
0°-180°	13327.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	364	364	364	364	364	
5°	354	380	428	484	502	33
15°	266	490	826	1001	1033	74
25°	170	556	984	1027	1028	78
35°	115	531	926	979	1018	72
45°	78	423	819	938	980	61
55°	56	269	695	807	829	51
65°	44	143	516	580	588	44
75°	33	88	283	311	312	34
85°	12	27	70	77	78	12
90°	11	30	83	41	41	10
95°	104	409	1361	702	478	116
105°	374	567	2296	3486	3252	397
115°	665	807	1840	3669	4188	656
125°	925	1037	1673	2827	3335	821
135°	1102	1213	1621	2282	2588	853
145°	1278	1360	1600	1947	2099	801
155°	1445	1485	1600	1757	1808	664
165°	1559	1579	1600	1663	1684	440
175°	1621	1621	1611	1632	1632	154
180°	1621	1621	1621	1621	1621	



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	363.7	363.7	363.7	363.7	363.7	363.7	363.7	363.7	363.7	363.7	363.7
2.5°	363.7	363.7	366.1	367.3	369.6	370.8	373.1	375.5	382.5	383.6	386.0
5°	354.4	359.1	374.3	380.1	396.5	418.8	428.1	443.3	474.9	484.2	490.1
7.5°	340.4	350.9	388.3	397.6	438.6	497.1	521.7	554.4	604.7	629.3	649.1
10°	318.1	340.4	407.1	429.3	495.9	584.8	630.5	676.1	752.0	786.0	798.9
12.5°	293.6	329.8	426.9	457.3	553.2	683.1	738.1	788.3	874.9	920.5	927.5
15°	265.5	314.6	445.6	490.1	614.1	764.9	825.8	887.7	968.5	1001.2	1009.4
17.5°	240.9	302.9	463.2	510.0	660.8	838.6	900.6	952.1	1017.6	1039.8	1045.7
20°	210.5	284.2	474.9	535.7	710.0	892.4	952.1	991.9	1036.3	1050.4	1052.7
22.5°	188.3	264.3	481.9	545.0	742.7	925.2	975.5	1007.1	1037.5	1042.2	1043.3
25°	169.6	242.1	480.8	555.6	770.8	945.1	983.7	1007.1	1024.6	1027.0	1027.0
27.5°	152.1	217.6	476.0	557.9	791.9	949.7	980.2	996.6	1004.8	1009.4	1009.4
30°	136.8	194.2	464.4	553.2	801.2	945.1	969.6	977.8	986.0	993.1	996.6
32.5°	125.1	172.0	446.8	543.9	802.4	933.3	951.0	955.6	967.3	983.7	989.5
35°	114.6	149.7	426.9	531.0	795.4	914.7	926.4	931.1	954.4	979.0	987.1
37.5°	104.1	133.3	401.2	508.8	784.8	892.4	900.6	908.8	945.1	974.3	983.7
40°	93.6	119.3	370.8	484.2	768.4	865.6	872.6	885.5	933.3	967.3	976.7
42.5°	85.4	107.6	338.0	458.5	747.4	835.1	845.7	864.4	919.4	955.6	966.1
45°	78.4	95.9	302.9	423.4	720.5	803.6	818.8	844.5	903.0	938.0	947.4
47.5°	71.3	87.7	266.7	387.2	691.3	772.0	791.9	821.1	880.8	914.7	922.9
50°	65.5	79.5	230.4	348.6	659.7	738.1	761.5	791.9	852.7	884.2	894.8
52.5°	60.8	72.6	196.5	309.9	623.4	702.9	729.9	761.5	818.8	849.2	856.2
55°	56.2	66.7	167.3	269.0	586.0	665.5	694.7	725.2	781.3	807.1	811.8
57.5°	53.8	62.0	142.7	230.4	546.2	623.4	656.2	684.3	736.9	756.8	761.5
60°	50.3	58.5	124.0	197.7	503.0	583.7	611.7	639.8	684.3	700.6	704.2
62.5°	46.8	56.2	110.0	166.1	458.5	536.9	564.9	590.7	628.1	639.8	644.5
65°	44.5	53.8	99.4	142.7	412.9	487.7	515.8	538.0	568.5	580.2	582.5
67.5°	42.1	51.5	91.2	122.8	367.3	438.6	459.6	480.8	504.1	515.8	516.9
70°	38.6	49.1	84.2	108.7	320.5	382.5	400.0	422.2	441.0	446.8	450.3
72.5°	36.3	45.6	79.5	98.3	272.5	328.7	345.1	357.9	374.3	380.1	380.1
75°	32.8	40.9	74.8	87.7	223.4	269.0	283.1	295.9	308.8	311.1	307.7
77.5°	29.2	36.3	64.4	73.7	174.3	212.9	224.5	231.6	242.1	244.4	245.7
80°	24.6	31.6	50.3	57.3	126.4	156.7	164.9	170.7	180.2	180.2	182.4
82.5°	18.7	24.6	36.3	40.9	85.4	107.6	114.6	118.2	124.0	124.0	124.0
85°	11.7	15.2	23.4	26.9	51.5	65.5	70.2	71.3	76.0	77.2	77.2
87.5°	5.8	8.2	15.2	16.4	26.9	33.9	33.9	36.3	36.3	35.1	33.9
90°	10.9	19.6	28.3	30.4	47.9	71.1	82.7	73.5	55.1	41.3	41.3
92.5°	43.5	117.5	191.5	210.0	295.2	408.8	465.6	408.0	293.0	206.7	198.5
95°	104.5	239.8	375.1	409.0	726.2	1149.3	1360.8	1214.3	921.4	701.6	676.7
97.5°	180.6	300.0	419.4	449.3	978.3	1683.7	2036.4	1943.8	1758.6	1619.7	1572.4
100°	239.3	347.6	455.9	483.0	1070.1	1852.7	2244.1	2250.9	2264.4	2274.5	2218.1
102.5°	289.3	390.4	491.4	516.7	1112.1	1905.9	2302.9	2420.9	2656.7	2833.7	2785.4
105°	374.2	459.7	545.4	566.7	1143.2	1911.9	2296.3	2560.8	3089.7	3486.4	3460.4
107.5°	461.2	541.0	620.7	640.7	1149.1	1826.9	2165.8	2534.7	3272.5	3825.8	3832.1
110°	520.0	592.0	664.1	682.0	1140.4	1751.5	2057.0	2469.4	3294.2	3912.8	3939.8



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	577.6	646.3	714.9	732.1	1140.7	1685.6	1958.0	2380.0	3224.2	3857.3	3898.9
115°	664.7	728.0	791.3	807.2	1151.3	1610.0	1839.5	2246.0	3059.2	3669.1	3726.7
117.5°	750.6	808.1	865.7	880.1	1172.6	1562.8	1757.8	2124.8	2858.7	3409.1	3473.0
120°	800.6	854.8	908.9	922.4	1190.1	1546.8	1725.2	2060.5	2731.1	3234.0	3296.1
122.5°	849.5	904.2	958.8	972.5	1215.1	1538.5	1700.2	2002.1	2606.0	3058.8	3120.1
125°	924.6	974.4	1024.2	1036.7	1248.8	1531.6	1673.0	1929.5	2442.4	2827.1	2883.6
127.5°	985.6	1035.8	1086.1	1098.7	1282.5	1527.6	1650.1	1870.3	2310.8	2641.1	2688.7
130°	1018.2	1072.3	1126.5	1140.0	1307.2	1530.0	1641.4	1837.5	2229.6	2523.7	2567.7
132.5°	1051.9	1106.1	1160.2	1173.8	1327.1	1531.6	1633.8	1809.3	2160.3	2423.6	2463.0
135°	1101.9	1151.3	1200.6	1212.9	1348.9	1530.2	1620.8	1767.8	2061.7	2282.2	2316.1
137.5°	1153.1	1201.9	1250.7	1262.9	1381.5	1539.6	1618.7	1742.9	1991.4	2177.7	2205.5
140°	1195.5	1240.5	1285.4	1296.6	1401.4	1541.1	1611.0	1718.3	1933.0	2094.0	2120.0
142.5°	1228.1	1269.7	1311.3	1321.7	1418.1	1546.7	1611.0	1705.3	1893.8	2035.2	2057.6
145°	1278.1	1314.4	1350.7	1359.8	1439.9	1546.7	1600.1	1677.2	1831.4	1947.2	1964.1
147.5°	1328.2	1363.5	1398.8	1407.6	1471.8	1557.4	1600.1	1660.8	1782.1	1873.1	1887.2
150°	1360.8	1392.7	1424.6	1432.6	1488.4	1562.9	1600.1	1651.4	1753.8	1830.7	1842.1
152.5°	1394.6	1418.7	1443.0	1449.0	1499.4	1566.5	1600.1	1643.9	1731.3	1797.0	1805.5
155°	1444.6	1462.5	1480.4	1484.8	1523.3	1574.5	1600.1	1634.9	1704.6	1756.8	1762.5
157.5°	1481.6	1499.0	1516.4	1520.7	1547.2	1582.5	1600.1	1627.2	1681.4	1722.0	1726.0
160°	1506.6	1520.1	1533.6	1537.0	1558.1	1586.1	1600.1	1623.3	1669.8	1704.6	1706.8
162.5°	1531.6	1541.8	1552.0	1554.5	1569.7	1590.0	1600.1	1619.7	1658.9	1688.3	1690.4
165°	1558.8	1567.9	1577.2	1579.4	1586.3	1595.5	1600.1	1614.1	1642.2	1663.2	1665.5
167.5°	1583.8	1588.1	1592.5	1593.6	1599.4	1607.2	1611.0	1620.2	1638.6	1652.3	1653.3
170°	1600.1	1604.5	1608.8	1609.9	1610.3	1610.7	1611.0	1620.2	1638.6	1652.3	1652.3
172.5°	1608.8	1609.8	1610.7	1611.0	1611.0	1611.0	1611.0	1618.2	1632.7	1643.6	1642.7
175°	1620.8	1620.8	1620.8	1620.8	1617.5	1613.2	1611.0	1615.6	1624.8	1631.7	1631.7
177.5°	1620.8	1620.8	1620.8	1620.8	1618.2	1614.8	1613.2	1616.8	1624.1	1629.5	1628.5
180°	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8	1620.8



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	363.7	363.7
2.5°	388.3	386.0
5°	499.4	501.8
7.5°	672.5	671.4
10°	836.3	846.8
12.5°	955.6	957.9
15°	1028.1	1032.8
17.5°	1056.2	1057.3
20°	1057.3	1055.0
22.5°	1044.5	1042.2
25°	1029.3	1028.1
27.5°	1015.2	1016.4
30°	1009.4	1013.0
32.5°	1009.4	1015.2
35°	1011.7	1017.6
37.5°	1010.6	1017.6
40°	1005.9	1014.1
42.5°	993.1	998.9
45°	973.2	980.2
47.5°	947.4	952.1
50°	914.7	919.4
52.5°	873.7	874.9
55°	824.6	829.3
57.5°	772.0	773.1
60°	713.5	717.0
62.5°	651.5	651.5
65°	586.0	588.4
67.5°	518.2	524.0
70°	449.2	450.3
72.5°	381.3	381.3
75°	311.1	312.3
77.5°	244.4	244.4
80°	181.3	182.4
82.5°	125.1	127.5
85°	78.4	78.4
87.5°	36.3	32.8
90°	41.3	41.3
92.5°	165.6	132.7
95°	577.1	477.5
97.5°	1382.8	1193.3
100°	1992.3	1766.6
102.5°	2591.9	2398.6
105°	3356.5	3252.5
107.5°	3857.2	3882.3
110°	4048.2	4156.5



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4065.2	4231.5
115°	3957.4	4187.9
117.5°	3728.8	3984.6
120°	3544.6	3793.1
122.5°	3365.3	3610.4
125°	3109.4	3335.2
127.5°	2879.3	3069.7
130°	2743.7	2919.7
132.5°	2620.5	2778.2
135°	2452.0	2587.8
137.5°	2316.7	2427.9
140°	2223.9	2327.9
142.5°	2147.0	2236.5
145°	2031.8	2099.4
147.5°	1943.2	1999.3
150°	1887.6	1933.0
152.5°	1839.9	1874.3
155°	1785.2	1807.9
157.5°	1741.9	1757.8
160°	1716.1	1725.2
162.5°	1699.1	1707.8
165°	1674.7	1683.9
167.5°	1657.2	1661.1
170°	1652.3	1652.3
172.5°	1639.4	1636.0
175°	1631.7	1631.7
177.5°	1624.6	1620.8
180°	1620.8	1620.8



TEST NUMBER: P938244

CATALOG NUMBER: SQ4-FB-150U-050D-92765-1D-UNV-STD-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.42	1.07	2.70	12.43	13.09	13.59	14.25	15.88
	3H	0.00	0.53	1.11	1.70	3.34	14.25	14.85	15.43	16.01	17.65
	4H	0.23	0.79	1.41	1.96	3.60	14.89	15.45	16.07	16.62	18.26
	6H	0.47	0.99	1.66	2.15	3.81	15.31	15.83	16.50	16.99	18.65
	8H	0.53	1.03	1.72	2.20	3.86	15.42	15.92	16.61	17.10	18.75
	12H	0.54	1.01	1.74	2.18	3.86	15.48	15.95	16.68	17.13	18.80
4H	2H	6.44	7.01	7.63	8.17	9.82	12.68	13.24	13.87	14.41	16.05
	3H	7.99	8.46	9.18	9.65	11.31	14.70	15.18	15.90	16.36	18.02
	4H	8.07	8.51	9.27	9.68	11.36	15.46	15.90	16.66	17.07	18.75
	6H	8.07	8.45	9.27	9.64	11.31	15.99	16.36	17.19	17.56	19.23
	8H	8.04	8.39	9.24	9.58	11.27	16.15	16.49	17.34	17.68	19.37
	12H	7.99	8.31	9.20	9.51	11.20	16.23	16.55	17.44	17.74	19.43
8H	4H	9.50	9.85	10.70	11.04	12.72	15.50	15.85	16.70	17.04	18.73
	6H	9.73	10.02	10.95	11.25	12.93	16.12	16.41	17.34	17.64	19.32
	8H	9.75	10.00	10.97	11.21	12.91	16.34	16.59	17.56	17.80	19.50
	12H	9.71	9.93	10.93	11.13	12.86	16.48	16.70	17.70	17.90	19.63
12H	4H	9.63	9.95	10.85	11.15	12.84	15.45	15.76	16.66	16.96	18.65
	6H	9.99	10.24	11.21	11.45	13.15	16.11	16.36	17.33	17.56	19.26
	8H	10.05	10.27	11.28	11.48	13.21	16.33	16.55	17.55	17.75	19.48