

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937430

Luminaire Tested: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937430
REPORT IS A COMBINATION OF REPORTS P933557 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16160.6 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937430
CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9	7
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1851	1851	1851
5°	1809	2139	2488
10°	1641	3120	4124
15°	1396	4077	4980
20°	1136	4725	5076
25°	948	4946	4972
30°	800	4979	4963
35°	708	4897	5091
40°	617	4791	5224
45°	559	4714	5244
50°	514	4645	5157
55°	492	4543	4929
60°	504	4346	4568
65°	526	4044	4072
70°	561	3530	3440
75°	624	2880	2684
80°	687	2000	1809
85°	622	1063	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5244 cd/sqm



TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	0.5
10°-20°	343.0	2.1
20°-30°	600.0	3.7
30°-40°	772.4	4.8
40°-50°	862.8	5.3
50°-60°	826.3	5.1
60°-70°	654.9	4.1
70°-80°	385.1	2.4
80°-90°	113.8	0.7
90°-100°	866.6	5.4
100°-110°	2278.3	14.1
110°-120°	2362.4	14.6
120°-130°	1894.9	11.7
130°-140°	1486.8	9.2
140°-150°	1141.2	7.1
150°-160°	821.9	5.1
160°-170°	502.9	3.1
170°-180°	169.9	1.1
0°-30°	1020.5	6.3
0°-40°	1792.9	11.1
0°-60°	3482.0	21.5
0°-90°	4635.7	28.7
90°-120°	5507.3	34.1
90°-150°	10030.3	62.1
90°-180°	11525.0	71.3
0°-180°	16160.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	583	625	704	796	825	54
15°	437	806	1358	1647	1699	122
25°	279	914	1618	1689	1691	129
35°	189	874	1524	1610	1674	118
45°	129	696	1347	1543	1612	100
55°	92	442	1143	1328	1364	84
65°	73	235	848	954	968	72
75°	54	144	466	512	514	56
85°	19	44	115	127	129	20
90°	12	33	91	45	45	11
95°	115	449	1493	770	524	127
105°	410	622	2519	3824	3568	435
115°	729	885	2018	4024	4594	720
125°	1014	1137	1835	3101	3658	900
135°	1209	1330	1778	2503	2839	935
145°	1402	1492	1755	2136	2303	878
155°	1584	1629	1755	1927	1983	728
165°	1710	1732	1755	1824	1847	483
175°	1778	1778	1767	1790	1790	169
180°	1778	1778	1778	1778	1778	



TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	598.4	598.4	598.4	598.4	598.4	598.4	598.4	598.4	598.4	598.4	598.4
2.5°	598.4	598.4	602.2	604.1	607.9	609.9	613.8	617.6	629.2	631.1	634.9
5°	583.0	590.6	615.7	625.3	652.2	688.7	704.1	729.2	781.1	796.5	806.2
7.5°	559.9	577.2	638.7	654.1	721.5	817.7	858.1	912.0	994.7	1035.1	1067.8
10°	523.3	559.9	669.5	706.1	815.7	962.0	1037.0	1112.1	1237.1	1293.0	1314.1
12.5°	482.9	542.5	702.2	752.2	910.0	1123.6	1214.1	1296.8	1439.2	1514.2	1525.7
15°	436.8	517.6	733.0	806.2	1010.1	1258.3	1358.4	1460.3	1593.1	1646.9	1660.4
17.5°	396.3	498.3	761.9	838.9	1087.1	1379.5	1481.4	1566.1	1673.9	1710.4	1720.1
20°	346.3	467.6	781.1	881.2	1167.9	1468.0	1566.1	1631.6	1704.7	1727.7	1731.6
22.5°	309.8	434.8	792.7	896.6	1221.7	1521.9	1604.6	1656.6	1706.6	1714.3	1716.2
25°	279.0	398.3	790.8	913.9	1267.9	1554.6	1618.1	1656.6	1685.4	1689.3	1689.3
27.5°	250.1	357.9	783.0	917.8	1302.5	1562.3	1612.3	1639.2	1652.7	1660.4	1660.4
30°	225.1	319.4	763.8	910.0	1317.9	1554.6	1595.0	1608.5	1621.9	1633.5	1639.2
32.5°	205.9	282.8	734.9	894.6	1319.8	1535.4	1564.2	1571.9	1591.1	1618.1	1627.7
35°	188.6	246.3	702.2	873.5	1308.4	1504.6	1523.8	1531.5	1570.0	1610.4	1623.8
37.5°	171.3	219.4	660.0	837.0	1291.0	1468.0	1481.4	1494.9	1554.6	1602.7	1618.1
40°	153.9	196.2	609.9	796.5	1264.1	1423.8	1435.3	1456.5	1535.4	1591.1	1606.5
42.5°	140.5	177.0	556.0	754.2	1229.5	1373.8	1391.1	1421.9	1512.2	1571.9	1589.2
45°	128.9	157.8	498.3	696.5	1185.2	1321.7	1346.8	1389.2	1485.4	1543.0	1558.4
47.5°	117.3	144.3	438.7	636.8	1137.1	1269.8	1302.5	1350.6	1448.7	1504.6	1518.1
50°	107.8	130.8	379.0	573.3	1085.1	1214.1	1252.5	1302.5	1402.6	1454.6	1471.9
52.5°	100.0	119.3	323.2	509.8	1025.5	1156.3	1200.6	1252.5	1346.8	1396.8	1408.4
55°	92.4	109.7	275.1	442.5	963.9	1094.7	1142.8	1192.9	1285.2	1327.6	1335.2
57.5°	88.5	101.9	234.7	379.0	898.5	1025.5	1079.4	1125.5	1212.1	1244.9	1252.5
60°	82.7	96.2	204.0	325.2	827.3	960.1	1006.3	1052.4	1125.5	1152.5	1158.2
62.5°	77.0	92.4	180.8	273.2	754.2	883.1	929.3	971.6	1033.2	1052.4	1060.1
65°	73.1	88.5	163.5	234.7	679.2	802.3	848.5	885.1	935.1	954.3	958.1
67.5°	69.2	84.6	150.0	202.0	604.1	721.5	756.2	790.8	829.2	848.5	850.4
70°	63.5	80.8	138.6	178.9	527.1	629.2	658.1	694.6	725.4	734.9	740.8
72.5°	59.7	75.1	130.8	161.6	448.3	540.6	567.6	588.7	615.7	625.3	625.3
75°	53.8	67.3	123.2	144.3	367.5	442.5	465.6	486.8	507.9	511.8	506.0
77.5°	48.1	59.7	105.9	121.2	286.7	350.2	369.4	380.9	398.3	402.1	404.0
80°	40.4	51.9	82.7	94.3	207.8	257.8	271.3	280.9	296.3	296.3	300.1
82.5°	30.8	40.4	59.7	67.3	140.5	177.0	188.6	194.3	204.0	204.0	204.0
85°	19.2	25.1	38.4	44.3	84.6	107.8	115.4	117.3	125.1	127.0	127.0
87.5°	9.7	13.5	25.1	27.0	44.3	55.8	55.8	59.7	59.7	57.8	55.8
90°	12.0	21.5	31.0	33.4	52.5	77.9	90.6	80.6	60.4	45.3	45.3
92.5°	47.7	128.8	210.0	230.3	323.8	448.4	510.7	447.6	321.4	226.7	217.7
95°	114.6	263.0	411.5	448.6	796.6	1260.6	1492.6	1332.0	1010.6	769.5	742.2
97.5°	198.0	329.0	460.0	492.8	1073.0	1846.7	2233.6	2132.0	1928.9	1776.6	1724.7
100°	262.5	381.2	500.0	529.7	1173.6	2032.2	2461.5	2469.0	2483.8	2494.9	2433.0
102.5°	317.4	428.2	539.0	566.7	1219.8	2090.6	2526.0	2655.3	2914.1	3108.2	3055.1
105°	410.5	504.3	598.2	621.6	1254.0	2097.2	2518.8	2808.9	3389.0	3824.1	3795.6
107.5°	505.9	593.4	680.9	702.8	1260.4	2003.8	2375.6	2780.2	3589.5	4196.3	4203.2
110°	570.4	649.4	728.3	748.1	1250.8	1921.1	2256.2	2708.6	3613.3	4291.8	4321.5



TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	633.6	708.9	784.2	803.0	1251.3	1848.9	2147.7	2610.7	3536.6	4231.0	4276.6
115°	729.0	798.5	867.9	885.3	1262.7	1766.0	2017.7	2463.6	3355.6	4024.5	4087.7
117.5°	823.3	886.4	949.5	965.3	1286.3	1714.2	1928.2	2330.6	3135.6	3739.4	3809.5
120°	878.2	937.5	997.0	1011.8	1305.4	1696.8	1892.4	2260.2	2995.7	3547.3	3615.5
122.5°	931.9	991.9	1051.7	1066.7	1332.8	1687.6	1865.0	2196.1	2858.4	3355.2	3422.4
125°	1014.2	1068.8	1123.4	1137.1	1369.7	1680.0	1835.1	2116.4	2679.1	3101.0	3162.9
127.5°	1081.0	1136.1	1191.3	1205.1	1406.8	1675.6	1810.1	2051.6	2534.7	2897.0	2949.2
130°	1116.8	1176.2	1235.6	1250.4	1433.8	1678.3	1800.5	2015.6	2445.7	2768.2	2816.5
132.5°	1153.8	1213.2	1272.6	1287.4	1455.6	1679.9	1792.1	1984.6	2369.6	2658.4	2701.6
135°	1208.7	1262.7	1316.9	1330.4	1479.5	1678.4	1777.8	1939.1	2261.4	2503.2	2540.5
137.5°	1264.8	1318.3	1371.9	1385.2	1515.3	1688.7	1775.5	1911.7	2184.3	2388.8	2419.3
140°	1311.3	1360.7	1409.9	1422.2	1537.2	1690.5	1767.0	1884.8	2120.3	2296.9	2325.4
142.5°	1347.1	1392.7	1438.3	1449.7	1555.4	1696.5	1767.0	1870.5	2077.3	2232.4	2256.9
145°	1402.0	1441.7	1481.5	1491.5	1579.3	1696.6	1755.2	1839.7	2008.9	2135.8	2154.3
147.5°	1456.9	1495.6	1534.3	1544.0	1614.3	1708.2	1755.2	1821.7	1954.8	2054.7	2070.1
150°	1492.6	1527.6	1562.6	1571.4	1632.7	1714.4	1755.2	1811.4	1923.8	2008.1	2020.5
152.5°	1529.6	1556.1	1582.7	1589.3	1644.6	1718.3	1755.2	1803.2	1899.1	1971.1	1980.5
155°	1584.5	1604.1	1623.8	1628.7	1670.9	1727.1	1755.2	1793.3	1869.6	1926.9	1933.1
157.5°	1625.1	1644.2	1663.3	1668.1	1697.1	1735.9	1755.2	1784.8	1844.2	1888.8	1893.2
160°	1652.5	1667.4	1682.2	1686.0	1709.0	1739.8	1755.2	1780.6	1831.5	1869.6	1872.1
162.5°	1679.9	1691.0	1702.2	1705.0	1721.7	1744.0	1755.2	1776.6	1819.5	1851.8	1854.2
165°	1709.8	1719.8	1729.9	1732.4	1740.0	1750.1	1755.2	1770.6	1801.3	1824.3	1826.8
167.5°	1737.2	1742.0	1746.8	1748.0	1754.3	1762.8	1767.0	1777.2	1797.4	1812.5	1813.5
170°	1755.2	1760.0	1764.7	1765.9	1766.3	1766.8	1767.0	1777.2	1797.4	1812.5	1812.5
172.5°	1764.7	1765.7	1766.8	1767.0	1767.0	1767.0	1767.0	1775.0	1790.9	1802.9	1801.9
175°	1777.8	1777.8	1777.8	1777.8	1774.2	1769.4	1767.0	1772.1	1782.2	1789.7	1789.7
177.5°	1777.8	1777.8	1777.8	1777.8	1775.1	1771.3	1769.4	1773.5	1781.4	1787.3	1786.3
180°	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8	1777.8



TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	598.4	598.4
2.5°	638.7	634.9
5°	821.6	825.4
7.5°	1106.3	1104.4
10°	1375.7	1393.0
12.5°	1571.9	1575.7
15°	1691.2	1698.9
17.5°	1737.4	1739.3
20°	1739.3	1735.5
22.5°	1718.1	1714.3
25°	1693.1	1691.2
27.5°	1670.0	1672.0
30°	1660.4	1666.2
32.5°	1660.4	1670.0
35°	1664.3	1673.9
37.5°	1662.3	1673.9
40°	1654.6	1668.1
42.5°	1633.5	1643.1
45°	1600.8	1612.3
47.5°	1558.4	1566.1
50°	1504.6	1512.2
52.5°	1437.3	1439.2
55°	1356.5	1364.1
57.5°	1269.8	1271.7
60°	1173.6	1179.4
62.5°	1071.7	1071.7
65°	963.9	967.8
67.5°	852.4	861.9
70°	738.9	740.8
72.5°	627.3	627.3
75°	511.8	513.7
77.5°	402.1	402.1
80°	298.2	300.1
82.5°	205.9	209.7
85°	128.9	128.9
87.5°	59.7	53.8
90°	45.3	45.3
92.5°	181.6	145.5
95°	633.0	523.8
97.5°	1516.8	1308.9
100°	2185.4	1937.7
102.5°	2843.0	2631.0
105°	3681.5	3567.6
107.5°	4230.9	4258.4
110°	4440.3	4559.1



TEST NUMBER: P937430

CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4459.0	4641.5
115°	4340.7	4593.6
117.5°	4090.0	4370.6
120°	3888.0	4160.6
122.5°	3691.2	3960.1
125°	3410.5	3658.2
127.5°	3158.2	3367.1
130°	3009.4	3202.5
132.5°	2874.5	3047.4
135°	2689.5	2838.6
137.5°	2541.2	2663.2
140°	2439.4	2553.4
142.5°	2355.0	2453.1
145°	2228.6	2302.8
147.5°	2131.5	2193.0
150°	2070.4	2120.3
152.5°	2018.1	2055.8
155°	1958.1	1983.0
157.5°	1910.7	1928.2
160°	1882.3	1892.4
162.5°	1863.7	1873.3
165°	1836.9	1847.0
167.5°	1817.7	1821.9
170°	1812.5	1812.5
172.5°	1798.2	1794.5
175°	1789.7	1789.7
177.5°	1782.1	1777.8
180°	1777.8	1777.8



TEST NUMBER: P937430
 CATALOG NUMBER: SQ4-FB-100U-050D-92765-1D-UNV-STD-W-12-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.78	1.49	1.89	2.61	4.15	13.97	14.68	15.08	15.80	17.34
	3H	1.47	2.11	2.59	3.23	4.79	15.80	16.44	16.93	17.57	19.13
	4H	1.76	2.37	2.89	3.49	5.06	16.44	17.05	17.58	18.18	19.74
	6H	2.00	2.57	3.14	3.69	5.27	16.87	17.43	18.01	18.56	20.14
	8H	2.07	2.60	3.21	3.74	5.31	16.99	17.53	18.13	18.67	20.24
	12H	2.08	2.59	3.23	3.72	5.32	17.06	17.56	18.20	18.70	20.29
4H	2H	7.98	8.59	9.12	9.72	11.28	14.22	14.83	15.36	15.96	17.52
	3H	9.53	10.05	10.68	11.19	12.77	16.26	16.77	17.41	17.92	19.50
	4H	9.62	10.09	10.77	11.23	12.83	17.02	17.50	18.18	18.63	20.23
	6H	9.62	10.03	10.78	11.19	12.78	17.56	17.96	18.72	19.12	20.71
	8H	9.60	9.97	10.75	11.13	12.73	17.72	18.10	18.88	19.25	20.85
	12H	9.55	9.89	10.72	11.05	12.66	17.81	18.15	18.98	19.31	20.92
8H	4H	11.06	11.44	12.21	12.59	14.19	17.07	17.45	18.23	18.60	20.21
	6H	11.29	11.61	12.47	12.80	14.40	17.70	18.01	18.88	19.20	20.81
	8H	11.31	11.58	12.49	12.75	14.38	17.92	18.19	19.10	19.36	20.99
	12H	11.27	11.51	12.46	12.68	14.33	18.06	18.30	19.25	19.47	21.12
12H	4H	11.20	11.54	12.37	12.70	14.31	17.02	17.36	18.19	18.52	20.13
	6H	11.55	11.82	12.73	13.00	14.62	17.68	17.95	18.86	19.12	20.75
	8H	11.61	11.85	12.80	13.02	14.68	17.91	18.14	19.09	19.31	20.97