

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937542

Luminaire Tested: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937542
REPORT IS A COMBINATION OF REPORTS P933574 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9216.7 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 73.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937542
CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P937542

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37	31
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30	25
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25	21
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21	17
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18	15
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16	13
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14	11
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12	10
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11	9
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2760	2760	2760
5°	2695	3188	3709
10°	2443	4647	6149
15°	2076	6069	7426
20°	1690	7032	7568
25°	1409	7357	7414
30°	1187	7402	7400
35°	1050	7277	7591
40°	913	7115	7789
45°	827	6995	7819
50°	758	6888	7690
55°	725	6732	7349
60°	742	6433	6810
65°	770	5980	6071
70°	818	5212	5129
75°	905	4246	4003
80°	980	2941	2696
85°	853	1558	1380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7819 cd/sqm



TEST NUMBER: P937542

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	0.6
10°-20°	255.7	2.8
20°-30°	447.3	4.9
30°-40°	575.9	6.2
40°-50°	643.2	7.0
50°-60°	616.0	6.7
60°-70°	488.2	5.3
70°-80°	287.1	3.1
80°-90°	83.1	0.9
90°-100°	433.3	4.7
100°-110°	1139.2	12.4
110°-120°	1181.2	12.8
120°-130°	947.5	10.3
130°-140°	743.4	8.1
140°-150°	570.6	6.2
150°-160°	410.9	4.5
160°-170°	251.4	2.7
170°-180°	84.9	0.9
0°-30°	760.8	8.3
0°-40°	1336.6	14.5
0°-60°	2595.8	28.2
0°-90°	3454.3	37.5
90°-120°	2753.7	29.9
90°-150°	5015.2	54.4
90°-180°	5762.0	62.5
0°-180°	9216.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	446	446	446	446	446	
5°	435	466	525	594	615	40
15°	326	601	1013	1228	1267	91
25°	208	681	1206	1259	1261	96
35°	141	651	1136	1201	1248	88
45°	96	519	1004	1150	1202	74
55°	69	330	852	990	1017	63
65°	54	175	632	711	721	54
75°	40	108	347	382	383	42
85°	14	33	86	95	96	15
90°	6	17	45	23	23	6
95°	57	224	746	385	262	64
105°	205	311	1259	1912	1784	218
115°	364	443	1009	2012	2297	360
125°	507	569	918	1551	1829	450
135°	604	665	889	1252	1419	468
145°	701	746	878	1068	1151	439
155°	792	814	878	964	992	364
165°	855	866	878	912	924	241
175°	889	889	884	895	895	84
180°	889	889	889	889	889	



TEST NUMBER: P937542
 CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	446.1	446.1	446.1	446.1	446.1	446.1	446.1	446.1	446.1	446.1	446.1
2.5°	446.1	446.1	448.9	450.4	453.2	454.7	457.5	460.4	469.0	470.4	473.3
5°	434.6	440.3	459.0	466.1	486.2	513.5	524.9	543.6	582.3	593.8	601.0
7.5°	417.4	430.3	476.2	487.7	537.9	609.6	639.7	679.9	741.5	771.6	796.0
10°	390.1	417.4	499.1	526.4	608.1	717.1	773.1	829.0	922.2	963.8	979.6
12.5°	360.0	404.5	523.5	560.8	678.4	837.6	905.0	966.7	1072.8	1128.9	1137.5
15°	325.6	385.8	546.5	601.0	753.0	938.0	1012.6	1088.7	1187.7	1227.8	1237.9
17.5°	295.5	371.5	568.0	625.4	810.4	1028.4	1104.5	1167.6	1247.9	1275.2	1282.4
20°	258.2	348.5	582.3	656.9	870.6	1094.5	1167.6	1216.4	1270.9	1288.1	1291.0
22.5°	230.9	324.1	590.9	668.4	910.8	1134.6	1196.3	1235.0	1272.3	1278.0	1279.5
25°	208.0	296.9	589.5	681.3	945.2	1159.0	1206.3	1235.0	1256.5	1259.4	1259.4
27.5°	186.5	266.8	583.8	684.2	971.0	1164.7	1202.0	1222.1	1232.2	1237.9	1237.9
30°	167.8	238.1	569.4	678.4	982.5	1159.0	1189.1	1199.2	1209.2	1217.8	1222.1
32.5°	153.5	210.8	547.9	666.9	983.9	1144.7	1166.2	1171.9	1186.3	1206.3	1213.5
35°	140.6	183.6	523.5	651.2	975.3	1121.7	1136.1	1141.8	1170.5	1200.6	1210.6
37.5°	127.7	163.5	492.0	623.9	962.4	1094.5	1104.5	1114.5	1159.0	1194.9	1206.3
40°	114.7	146.3	454.7	593.8	942.3	1061.4	1070.0	1085.8	1144.7	1186.3	1197.7
42.5°	104.7	132.0	414.5	562.2	916.5	1024.1	1037.0	1059.9	1127.4	1171.9	1184.8
45°	96.1	117.6	371.5	519.2	883.5	985.4	1004.0	1035.6	1107.4	1150.4	1161.9
47.5°	87.5	107.6	327.0	474.7	847.7	946.6	971.0	1006.9	1080.0	1121.7	1131.8
50°	80.3	97.5	282.6	427.4	808.9	905.0	933.7	971.0	1045.6	1084.3	1097.3
52.5°	74.6	88.9	241.0	380.1	764.5	862.0	895.0	933.7	1004.0	1041.3	1049.9
55°	68.8	81.8	205.1	329.9	718.6	816.1	852.0	889.3	958.1	989.7	995.4
57.5°	66.0	76.0	175.0	282.6	669.8	764.5	804.6	839.1	903.6	928.0	933.7
60°	61.7	71.7	152.0	242.4	616.7	715.7	750.1	784.6	839.1	859.1	863.4
62.5°	57.4	68.8	134.8	203.7	562.2	658.3	692.8	724.3	770.2	784.6	790.3
65°	54.5	66.0	121.9	175.0	506.3	598.1	632.5	659.8	697.1	711.4	714.3
67.5°	51.6	63.1	111.9	150.6	450.4	537.9	563.7	589.5	618.2	632.5	634.0
70°	47.3	60.2	103.3	133.4	393.0	469.0	490.5	517.8	540.7	547.9	552.2
72.5°	44.5	55.9	97.5	120.5	334.2	403.0	423.1	438.9	459.0	466.1	466.1
75°	40.2	50.2	91.8	107.6	273.9	329.9	347.1	362.9	378.7	381.5	377.2
77.5°	35.9	44.5	78.9	90.4	213.7	261.0	275.4	284.0	296.9	299.8	301.2
80°	30.1	38.7	61.7	70.3	154.9	192.2	202.2	209.4	220.9	220.9	223.7
82.5°	22.9	30.1	44.5	50.2	104.7	132.0	140.6	144.9	152.0	152.0	152.0
85°	14.3	18.6	28.7	33.0	63.1	80.3	86.1	87.5	93.2	94.7	94.7
87.5°	7.2	10.0	18.6	20.1	33.0	41.6	41.6	44.5	44.5	43.0	41.6
90°	5.9	10.7	15.5	16.7	26.3	39.0	45.3	40.3	30.2	22.7	22.7
92.5°	23.9	64.4	105.0	115.1	161.9	224.1	255.3	223.7	160.6	113.3	108.8
95°	57.3	131.5	205.8	224.3	398.4	630.3	746.3	666.0	505.3	384.8	371.1
97.5°	99.1	164.6	230.1	246.4	536.5	923.4	1116.8	1066.1	964.5	888.3	862.3
100°	131.3	190.7	250.0	264.9	586.8	1016.1	1230.7	1234.4	1241.9	1247.4	1216.5
102.5°	158.7	214.2	269.6	283.4	610.0	1045.3	1262.9	1327.7	1457.0	1554.1	1527.6
105°	205.2	252.1	299.1	310.9	627.1	1048.7	1259.4	1404.5	1694.5	1912.0	1897.8
107.5°	252.9	296.7	340.5	351.4	630.2	1001.9	1187.8	1390.1	1794.7	2098.2	2101.6
110°	285.1	324.6	364.2	374.1	625.4	960.6	1128.1	1354.3	1806.6	2145.9	2160.7



TEST NUMBER: P937542

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	316.8	354.5	392.1	401.5	625.6	924.4	1073.8	1305.3	1768.3	2115.5	2138.2
115°	364.5	399.2	433.9	442.6	631.4	882.9	1008.8	1231.8	1677.8	2012.3	2044.0
117.5°	411.6	443.2	474.7	482.6	643.0	857.0	964.0	1165.3	1567.8	1869.6	1904.7
120°	439.1	468.8	498.5	505.9	652.7	848.3	946.2	1130.0	1497.8	1773.6	1807.7
122.5°	466.0	495.9	525.9	533.4	666.4	843.7	932.5	1098.1	1429.2	1677.5	1711.2
125°	507.1	534.4	561.8	568.6	684.9	840.0	917.6	1058.2	1339.5	1550.6	1581.5
127.5°	540.5	568.1	595.7	602.6	703.4	837.8	905.0	1025.8	1267.3	1448.5	1474.6
130°	558.4	588.2	617.8	625.3	717.0	839.2	900.3	1007.7	1222.8	1384.1	1408.2
132.5°	576.9	606.6	636.3	643.7	727.9	840.0	896.0	992.3	1184.8	1329.2	1350.8
135°	604.3	631.4	658.4	665.2	739.8	839.2	888.9	969.5	1130.7	1251.7	1270.3
137.5°	632.3	659.1	686.0	692.7	757.7	844.4	887.7	955.9	1092.2	1194.4	1209.6
140°	655.7	680.3	705.0	711.1	768.6	845.2	883.5	942.4	1060.1	1148.4	1162.6
142.5°	673.5	696.4	719.2	724.9	777.8	848.2	883.5	935.3	1038.6	1116.2	1128.4
145°	701.0	720.9	740.8	745.7	789.7	848.3	877.6	919.9	1004.5	1067.9	1077.2
147.5°	728.4	747.7	767.1	771.9	807.1	854.1	877.6	910.9	977.4	1027.3	1035.0
150°	746.3	763.8	781.3	785.7	816.3	857.1	877.6	905.7	961.8	1004.0	1010.2
152.5°	764.9	778.1	791.3	794.7	822.3	859.1	877.6	901.6	949.6	985.5	990.2
155°	792.3	802.1	811.8	814.3	835.4	863.5	877.6	896.7	934.9	963.5	966.6
157.5°	812.6	822.1	831.6	834.0	848.5	867.9	877.6	892.4	922.2	944.4	946.6
160°	826.2	833.7	841.2	843.0	854.5	869.9	877.6	890.3	915.7	934.9	936.1
162.5°	840.0	845.6	851.1	852.5	860.9	872.0	877.6	888.3	909.8	925.9	927.0
165°	854.9	859.9	865.0	866.2	870.0	875.1	877.6	885.2	900.6	912.2	913.5
167.5°	868.6	871.0	873.4	874.0	877.1	881.4	883.5	888.6	898.6	906.2	906.8
170°	877.6	880.0	882.4	882.9	883.1	883.4	883.5	888.6	898.6	906.2	906.2
172.5°	882.4	882.9	883.4	883.5	883.5	883.5	883.5	887.5	895.5	901.4	900.9
175°	888.9	888.9	888.9	888.9	887.1	884.7	883.5	886.0	891.1	894.9	894.9
177.5°	888.9	888.9	888.9	888.9	887.5	885.7	884.8	886.8	890.7	893.7	893.1
180°	888.9	888.9	888.9	888.9	888.9	888.9	888.9	888.9	888.9	888.9	888.9



TEST NUMBER: P937542

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	446.1	446.1
2.5°	476.2	473.3
5°	612.4	615.3
7.5°	824.7	823.3
10°	1025.5	1038.4
12.5°	1171.9	1174.8
15°	1260.8	1266.6
17.5°	1295.3	1296.7
20°	1296.7	1293.8
22.5°	1280.9	1278.0
25°	1262.3	1260.8
27.5°	1245.1	1246.5
30°	1237.9	1242.2
32.5°	1237.9	1245.1
35°	1240.8	1247.9
37.5°	1239.3	1247.9
40°	1233.6	1243.6
42.5°	1217.8	1225.0
45°	1193.4	1202.0
47.5°	1161.9	1167.6
50°	1121.7	1127.4
52.5°	1071.4	1072.8
55°	1011.2	1016.9
57.5°	946.6	948.1
60°	874.9	879.2
62.5°	798.9	798.9
65°	718.6	721.4
67.5°	635.4	642.6
70°	550.8	552.2
72.5°	467.6	467.6
75°	381.5	383.0
77.5°	299.8	299.8
80°	222.3	223.7
82.5°	153.5	156.3
85°	96.1	96.1
87.5°	44.5	40.2
90°	22.7	22.7
92.5°	90.7	72.8
95°	316.5	261.9
97.5°	758.4	654.4
100°	1092.6	968.8
102.5°	1421.5	1315.4
105°	1840.8	1783.8
107.5°	2115.5	2129.3
110°	2220.2	2279.6



TEST NUMBER: P937542

CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2229.5	2320.7
115°	2170.4	2296.9
117.5°	2045.0	2185.3
120°	1944.0	2080.3
122.5°	1845.6	1980.1
125°	1705.3	1829.1
127.5°	1579.2	1683.6
130°	1504.8	1601.2
132.5°	1437.3	1523.7
135°	1344.8	1419.3
137.5°	1270.6	1331.6
140°	1219.7	1276.7
142.5°	1177.6	1226.6
145°	1114.3	1151.4
147.5°	1065.8	1096.6
150°	1035.2	1060.1
152.5°	1009.1	1027.9
155°	979.0	991.5
157.5°	955.3	964.0
160°	941.2	946.2
162.5°	931.8	936.6
165°	918.5	923.5
167.5°	908.9	911.0
170°	906.2	906.2
172.5°	899.1	897.3
175°	894.9	894.9
177.5°	891.0	888.9
180°	888.9	888.9



TEST NUMBER: P937542
 CATALOG NUMBER: SQ4-FB-100U-075D-92765-1D-UNV-STD-W-6-6500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.26	4.05	4.31	5.11	6.54	16.42	17.21	17.48	18.27	19.71
	3H	3.96	4.66	5.02	5.73	7.19	18.25	18.96	19.31	20.03	21.48
	4H	4.25	4.92	5.33	5.99	7.46	18.89	19.56	19.96	20.63	22.09
	6H	4.50	5.12	5.58	6.19	7.67	19.31	19.93	20.40	21.00	22.48
	8H	4.57	5.15	5.65	6.24	7.71	19.43	20.02	20.52	21.11	22.58
	12H	4.58	5.14	5.67	6.22	7.72	19.49	20.05	20.58	21.14	22.63
4H	2H	10.46	11.13	11.54	12.20	13.66	16.69	17.36	17.77	18.43	19.89
	3H	12.02	12.58	13.10	13.68	15.15	18.72	19.28	19.81	20.38	21.86
	4H	12.11	12.62	13.20	13.71	15.21	19.48	20.00	20.58	21.09	22.58
	6H	12.12	12.56	13.22	13.67	15.16	20.01	20.46	21.11	21.57	23.06
	8H	12.09	12.50	13.19	13.61	15.11	20.17	20.58	21.27	21.69	23.19
	12H	12.04	12.42	13.16	13.53	15.05	20.26	20.63	21.38	21.75	23.26
8H	4H	13.54	13.96	14.65	15.06	16.57	19.54	19.95	20.64	21.05	22.56
	6H	13.78	14.13	14.91	15.27	16.77	20.16	20.50	21.28	21.65	23.15
	8H	13.80	14.10	14.93	15.23	16.75	20.38	20.68	21.50	21.80	23.32
	12H	13.76	14.03	14.90	15.15	16.71	20.51	20.78	21.65	21.90	23.46
12H	4H	13.68	14.06	14.80	15.17	16.68	19.49	19.86	20.60	20.98	22.49
	6H	14.04	14.34	15.17	15.47	16.99	20.14	20.44	21.27	21.57	23.09
	8H	14.11	14.37	15.24	15.49	17.05	20.36	20.63	21.50	21.75	23.31