

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561471

Luminaire Tested: **SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561471
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4467.6 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 36.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561471

CATALOG NUMBER: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561471

CATALOG NUMBER: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7273	7273	7273
5°	7329	7280	7254
10°	7310	7277	7256
15°	7272	7272	7265
20°	7224	7246	7246
25°	7156	7207	7186
30°	7069	7154	7123
35°	6964	7070	7021
40°	6848	6946	6875
45°	6724	6772	6667
50°	6548	6548	6443
55°	6341	6259	6164
60°	6034	5912	5818
65°	5578	5466	5418
70°	4883	4923	4904
75°	3928	4345	4370
80°	2795	3682	3725
85°	1704	3091	3091



TEST NUMBER: P561471

CATALOG NUMBER: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.7
10°-20°	214.1	4.8
20°-30°	324.2	7.3
30°-40°	388.7	8.7
40°-50°	396.4	8.9
50°-60°	346.0	7.7
60°-70°	247.7	5.5
70°-80°	127.6	2.9
80°-90°	32.3	0.7
90°-100°	169.9	3.8
100°-110°	483.4	10.8
110°-120°	463.2	10.4
120°-130°	366.6	8.2
130°-140°	294.2	6.6
140°-150°	230.4	5.2
150°-160°	168.5	3.8
160°-170°	104.4	2.3
170°-180°	35.4	0.8
0°-30°	612.9	13.7
0°-40°	1001.6	22.4
0°-60°	1744.0	39.0
0°-90°	2151.5	48.2
90°-120°	1116.5	25.0
90°-150°	2007.7	44.9
90°-180°	2316.0	51.8
0°-180°	4467.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	788	788	788	788	788	
5°	791	783	786	784	783	75
15°	761	755	761	761	761	215
25°	703	698	708	706	706	323
35°	618	617	628	623	623	387
45°	515	514	519	512	511	397
55°	394	389	389	383	383	351
65°	256	250	250	248	248	253
75°	110	115	122	123	123	119
85°	16	25	29	30	29	22
90°	0	0	0	0	0	1
95°	18	73	329	114	70	21
105°	75	114	493	870	827	79
115°	140	169	374	791	929	137
125°	197	218	356	592	707	176
135°	241	261	352	500	565	186
145°	284	299	355	433	471	178
155°	325	332	364	391	407	150
165°	359	360	368	376	381	101
175°	376	374	372	370	367	36
180°	373	373	373	373	373	



TEST NUMBER: P561471

CATALOG NUMBER: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.3	788.3	788.3	788.3	788.3
2.5°	793.0	786.2	788.3	786.5	783.7
5°	791.3	783.4	786.1	783.9	783.2
7.5°	785.6	777.7	781.3	779.9	779.1
10°	780.3	772.5	776.7	775.2	774.5
12.5°	773.3	766.0	770.8	769.4	769.2
15°	761.3	754.9	761.3	761.3	760.6
17.5°	746.3	740.4	747.3	747.7	747.3
20°	735.8	729.4	738.0	737.3	738.0
22.5°	722.9	717.7	726.9	725.0	725.7
25°	702.9	697.9	708.0	705.9	705.9
27.5°	679.3	675.7	686.7	684.4	684.4
30°	663.5	659.9	671.5	668.6	668.6
32.5°	646.0	643.6	654.6	651.1	651.1
35°	618.3	616.8	627.7	623.4	623.4
37.5°	589.6	588.4	598.3	593.0	591.3
40°	568.6	567.9	576.7	570.8	570.8
42.5°	547.6	546.9	554.5	547.5	547.5
45°	515.3	513.9	519.0	512.4	511.0
47.5°	480.2	478.7	481.9	474.7	474.0
50°	456.2	454.8	456.2	449.6	448.9
52.5°	431.7	429.1	429.4	422.8	422.6
55°	394.2	389.2	389.1	383.2	383.2
57.5°	354.5	347.9	348.5	343.5	342.8
60°	327.0	319.9	320.4	316.0	315.3
62.5°	300.2	291.9	293.6	288.6	288.5
65°	255.5	249.8	250.4	248.2	248.2
67.5°	212.6	207.3	211.1	209.3	209.2
70°	181.0	177.5	182.5	182.5	181.8
72.5°	151.8	151.7	158.0	158.0	158.4
75°	110.2	115.2	121.9	122.6	122.6
77.5°	73.6	82.4	89.8	90.1	89.9
80°	52.6	62.5	69.3	70.8	70.1
82.5°	35.6	46.2	51.8	53.3	52.6
85°	16.1	24.6	29.2	29.9	29.2
87.5°	4.7	9.8	11.7	11.7	10.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.1	69.8	20.3	15.3
95°	18.4	73.2	328.9	113.8	70.2
97.5°	33.9	85.7	506.5	362.5	248.4
100°	44.7	93.2	545.1	552.1	425.3
102.5°	56.6	101.2	536.6	706.7	596.0
105°	75.1	114.0	492.6	870.2	827.2
107.5°	94.0	128.8	441.3	916.3	954.5
110°	107.0	139.6	411.8	898.6	984.6



TEST NUMBER: P561471

CATALOG NUMBER: SQ4-PC3-050U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	119.5	150.4	392.0	856.9	979.5
115°	139.6	168.8	373.6	791.4	929.3
117.5°	157.4	184.7	362.6	719.7	865.8
120°	171.5	194.4	361.5	678.7	818.7
122.5°	182.9	205.8	358.7	642.8	772.8
125°	197.1	218.5	356.5	591.7	707.4
127.5°	212.5	232.6	355.4	561.2	656.5
130°	220.4	240.5	353.7	539.9	623.1
132.5°	229.0	248.5	353.7	523.3	599.8
135°	241.0	261.1	352.3	499.8	564.9
137.5°	252.3	271.9	352.2	479.9	536.2
140°	260.9	281.0	351.6	463.4	517.5
142.5°	270.5	287.3	353.3	450.2	498.7
145°	284.2	298.8	355.1	432.6	471.4
147.5°	296.0	310.2	358.2	414.7	448.3
150°	306.2	315.9	359.4	408.8	432.4
152.5°	314.2	324.4	360.5	400.9	422.8
155°	324.6	332.3	363.6	390.9	406.9
157.5°	337.7	342.3	364.3	386.4	397.8
160°	344.5	348.0	367.2	383.0	392.7
162.5°	348.5	352.5	367.7	380.1	387.6
165°	358.7	360.1	367.9	375.8	381.4
167.5°	365.6	364.4	371.1	374.7	377.0
170°	367.9	367.2	370.0	370.8	373.6
172.5°	373.0	370.6	371.7	369.6	371.9
175°	375.7	373.6	372.1	370.0	367.2
177.5°	376.8	373.5	371.7	369.5	370.0
180°	372.9	372.9	372.9	372.9	372.9

(END OF REPORT)