

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561485

Luminaire Tested: **SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561485
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5590.8 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 47.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561485
CATALOG NUMBER: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561485

CATALOG NUMBER: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	86	83	77	75	72	66	65	63	56	55	54	49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10996	10996	10996
5°	11079	11007	10966
10°	11052	11001	10970
15°	10994	10994	10983
20°	10922	10954	10954
25°	10818	10897	10863
30°	10687	10816	10769
35°	10528	10690	10614
40°	10354	10500	10394
45°	10166	10237	10079
50°	9900	9900	9742
55°	9585	9461	9320
60°	9123	8940	8796
65°	8431	8263	8191
70°	7383	7443	7413
75°	5939	6570	6609
80°	4224	5568	5627
85°	2572	4668	4668



TEST NUMBER: P561485

CATALOG NUMBER: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	2.0
10°-20°	323.7	5.8
20°-30°	490.2	8.8
30°-40°	587.7	10.5
40°-50°	599.2	10.7
50°-60°	523.1	9.4
60°-70°	374.5	6.7
70°-80°	192.9	3.4
80°-90°	48.8	0.9
90°-100°	171.5	3.1
100°-110°	488.0	8.7
110°-120°	467.6	8.4
120°-130°	370.1	6.6
130°-140°	297.0	5.3
140°-150°	232.5	4.2
150°-160°	170.1	3.0
160°-170°	105.4	1.9
170°-180°	35.8	0.6
0°-30°	926.7	16.6
0°-40°	1514.3	27.1
0°-60°	2636.6	47.2
0°-90°	3252.8	58.2
90°-120°	1127.1	20.2
90°-150°	2026.7	36.3
90°-180°	2338.0	41.8
0°-180°	5590.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1192	1192	1192	1192	1192	
5°	1196	1184	1188	1185	1184	114
15°	1151	1141	1151	1151	1150	325
25°	1063	1055	1070	1067	1067	489
35°	935	932	949	942	942	585
45°	779	777	785	775	772	600
55°	596	588	588	579	579	531
65°	386	378	378	375	375	382
75°	167	174	184	185	185	180
85°	24	37	44	45	44	33
90°	0	0	0	0	0	2
95°	19	74	332	115	71	21
105°	76	115	497	878	835	80
115°	141	170	377	799	938	139
125°	199	221	360	597	714	178
135°	243	264	356	504	570	188
145°	287	302	358	437	476	179
155°	328	335	367	395	411	151
165°	362	364	371	379	385	102
175°	379	377	376	374	371	36
180°	376	376	376	376	376	

TEST NUMBER: P561485

CATALOG NUMBER: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1191.8	1191.8	1191.8	1191.8	1191.8
2.5°	1198.9	1188.5	1191.8	1189.1	1184.8
5°	1196.2	1184.4	1188.5	1185.2	1184.1
7.5°	1187.6	1175.8	1181.2	1179.0	1177.9
10°	1179.7	1167.8	1174.2	1171.9	1170.9
12.5°	1169.1	1158.1	1165.3	1163.1	1162.9
15°	1151.0	1141.3	1151.0	1151.0	1149.9
17.5°	1128.3	1119.4	1129.8	1130.5	1129.8
20°	1112.4	1102.7	1115.7	1114.6	1115.7
22.5°	1093.0	1085.0	1098.9	1096.1	1097.1
25°	1062.7	1055.2	1070.4	1067.1	1067.1
27.5°	1027.0	1021.6	1038.2	1034.7	1034.7
30°	1003.1	997.7	1015.3	1010.8	1010.8
32.5°	976.6	973.0	989.7	984.4	984.4
35°	934.7	932.5	949.1	942.4	942.4
37.5°	891.4	889.5	904.5	896.5	893.9
40°	859.7	858.6	871.8	863.0	863.0
42.5°	827.9	826.8	838.3	827.7	827.7
45°	779.1	776.9	784.6	774.6	772.5
47.5°	725.9	723.8	728.6	717.7	716.6
50°	689.7	687.6	689.7	679.8	678.7
52.5°	652.6	648.8	649.1	639.2	639.0
55°	595.9	588.4	588.2	579.4	579.4
57.5°	535.9	526.0	526.8	519.3	518.2
60°	494.4	483.6	484.5	477.8	476.7
62.5°	453.8	441.3	443.8	436.3	436.1
65°	386.2	377.6	378.5	375.2	375.2
67.5°	321.4	313.4	319.1	316.5	316.3
70°	273.7	268.3	275.9	275.9	274.8
72.5°	229.5	229.3	238.8	238.8	239.5
75°	166.6	174.2	184.3	185.4	185.4
77.5°	111.2	124.6	135.7	136.2	136.0
80°	79.5	94.6	104.8	107.0	105.9
82.5°	53.9	69.8	78.4	80.5	79.5
85°	24.3	37.2	44.1	45.2	44.1
87.5°	7.1	14.8	17.7	17.6	15.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.4	70.4	20.5	15.5
95°	18.6	73.9	332.0	114.9	70.8
97.5°	34.2	86.5	511.3	365.9	250.7
100°	45.1	94.1	550.3	557.4	429.3
102.5°	57.1	102.2	541.7	713.5	601.6
105°	75.8	115.0	497.3	878.4	835.1
107.5°	94.9	130.0	445.5	925.0	963.6
110°	108.1	140.9	415.7	907.2	993.9

TEST NUMBER: P561485

CATALOG NUMBER: SQ4-PC3-050U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	151.8	395.7	865.1	988.8
115°	141.0	170.4	377.1	798.9	938.1
117.5°	158.9	186.4	366.1	726.5	874.0
120°	173.2	196.3	364.9	685.1	826.5
122.5°	184.6	207.7	362.1	648.9	780.1
125°	198.9	220.6	359.9	597.3	714.1
127.5°	214.5	234.8	358.8	566.5	662.8
130°	222.5	242.8	357.1	545.0	629.0
132.5°	231.1	250.9	357.1	528.3	605.5
135°	243.3	263.6	355.6	504.5	570.3
137.5°	254.7	274.5	355.5	484.4	541.3
140°	263.3	283.6	354.9	467.8	522.4
142.5°	273.1	290.0	356.6	454.5	503.5
145°	286.9	301.6	358.5	436.7	475.8
147.5°	298.8	313.1	361.6	418.7	452.5
150°	309.1	318.9	362.8	412.7	436.5
152.5°	317.1	327.5	363.9	404.7	426.8
155°	327.7	335.4	367.1	394.6	410.7
157.5°	340.9	345.5	367.8	390.1	401.6
160°	347.8	351.3	370.7	386.6	396.4
162.5°	351.8	355.8	371.2	383.7	391.3
165°	362.1	363.5	371.4	379.4	385.0
167.5°	369.1	367.8	374.7	378.3	380.5
170°	371.4	370.7	373.5	374.3	377.1
172.5°	376.5	374.2	375.2	373.1	375.4
175°	379.2	377.1	375.7	373.5	370.7
177.5°	380.4	377.0	375.2	373.0	373.5
180°	376.4	376.4	376.4	376.4	376.4

(END OF REPORT)