

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561494

Luminaire Tested: **SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561494  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6287.7 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 58.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561494

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561494

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	89	95	91	88	85	80	78	75	71	69	67	62	60	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13742	13742	13742
5°	13846	13756	13705
10°	13812	13747	13709
15°	13739	13739	13727
20°	13649	13690	13690
25°	13520	13619	13576
30°	13355	13517	13459
35°	13156	13359	13266
40°	12939	13122	12989
45°	12705	12795	12596
50°	12373	12373	12175
55°	11979	11824	11646
60°	11402	11171	10994
65°	10538	10326	10237
70°	9226	9301	9263
75°	7422	8210	8259
80°	5276	6960	7035
85°	3208	5843	5843



TEST NUMBER: P561494

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.0	2.2
10°-20°	404.5	6.4
20°-30°	612.6	9.7
30°-40°	734.4	11.7
40°-50°	748.9	11.9
50°-60°	653.7	10.4
60°-70°	468.0	7.4
70°-80°	241.0	3.8
80°-90°	60.9	1.0
90°-100°	163.0	2.6
100°-110°	463.9	7.4
110°-120°	444.5	7.1
120°-130°	351.8	5.6
130°-140°	282.4	4.5
140°-150°	221.1	3.5
150°-160°	161.8	2.6
160°-170°	100.2	1.6
170°-180°	34.0	0.5
0°-30°	1158.1	18.4
0°-40°	1892.5	30.1
0°-60°	3295.0	52.4
0°-90°	4065.0	64.7
90°-120°	1071.5	17.0
90°-150°	1926.7	30.6
90°-180°	2223.0	35.4
0°-180°	6287.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1495	1480	1485	1481	1480	142
15°	1438	1426	1438	1438	1437	406
25°	1328	1319	1338	1334	1334	611
35°	1168	1165	1186	1178	1178	731
45°	974	971	981	968	965	749
55°	745	735	735	724	724	664
65°	483	472	473	469	469	477
75°	208	218	230	232	232	225
85°	30	46	55	56	55	41
90°	0	0	0	0	0	2
95°	18	70	316	109	67	20
105°	72	109	473	835	794	76
115°	134	162	358	760	892	132
125°	189	210	342	568	679	169
135°	231	251	338	480	542	178
145°	273	287	341	415	452	170
155°	312	319	349	375	390	144
165°	344	346	353	361	366	97
175°	360	358	357	355	352	34
180°	358	358	358	358	358	

TEST NUMBER: P561494

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1489.5	1489.5	1489.5	1489.5	1489.5
2.5°	1498.3	1485.3	1489.5	1486.0	1480.6
5°	1495.0	1480.1	1485.3	1481.2	1479.8
7.5°	1484.2	1469.4	1476.2	1473.4	1472.1
10°	1474.3	1459.5	1467.4	1464.6	1463.3
12.5°	1461.1	1447.3	1456.4	1453.6	1453.3
15°	1438.4	1426.3	1438.4	1438.4	1437.1
17.5°	1410.0	1399.0	1412.0	1412.8	1412.0
20°	1390.2	1378.0	1394.3	1393.0	1394.3
22.5°	1365.9	1355.9	1373.3	1369.8	1371.1
25°	1328.1	1318.7	1337.8	1333.6	1333.6
27.5°	1283.4	1276.7	1297.5	1293.1	1293.1
30°	1253.6	1246.9	1268.8	1263.3	1263.3
32.5°	1220.5	1215.9	1236.8	1230.2	1230.2
35°	1168.1	1165.4	1186.1	1177.8	1177.8
37.5°	1114.1	1111.6	1130.3	1120.3	1117.1
40°	1074.3	1073.0	1089.5	1078.5	1078.5
42.5°	1034.6	1033.3	1047.6	1034.3	1034.3
45°	973.7	971.0	980.6	968.1	965.4
47.5°	907.2	904.5	910.5	897.0	895.6
50°	862.0	859.3	862.0	849.5	848.2
52.5°	815.6	810.8	811.2	798.8	798.5
55°	744.7	735.3	735.1	724.0	724.0
57.5°	669.7	657.3	658.4	649.0	647.6
60°	617.9	604.4	605.4	597.1	595.8
62.5°	567.1	551.5	554.7	545.3	545.0
65°	482.7	471.9	473.0	468.9	468.9
67.5°	401.6	391.6	398.8	395.5	395.3
70°	342.0	335.3	344.8	344.8	343.4
72.5°	286.9	286.6	298.4	298.5	299.3
75°	208.2	217.7	230.3	231.7	231.7
77.5°	139.0	155.7	169.6	170.2	169.9
80°	99.3	118.2	131.0	133.7	132.4
82.5°	67.3	87.3	97.9	100.6	99.3
85°	30.3	46.5	55.2	56.5	55.2
87.5°	8.8	18.5	22.1	22.0	19.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	28.9	66.9	19.5	14.7
95°	17.7	70.2	315.6	109.3	67.3
97.5°	32.5	82.3	486.1	347.8	238.4
100°	42.9	89.4	523.1	529.9	408.2
102.5°	54.3	97.1	515.0	678.3	572.0
105°	72.1	109.4	472.8	835.1	793.9
107.5°	90.2	123.6	423.5	879.3	916.0
110°	102.7	134.0	395.2	862.4	944.9

TEST NUMBER: P561494

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	114.7	144.4	376.2	822.4	940.0
115°	134.0	161.9	358.5	759.5	891.8
117.5°	151.0	177.2	348.0	690.7	830.9
120°	164.6	186.6	346.9	651.3	785.7
122.5°	175.5	197.5	344.2	616.8	741.6
125°	189.1	209.7	342.2	567.8	678.9
127.5°	203.9	223.2	341.1	538.5	630.1
130°	211.6	230.9	339.5	518.1	598.0
132.5°	219.7	238.5	339.5	502.2	575.6
135°	231.3	250.6	338.1	479.6	542.2
137.5°	242.2	260.9	338.0	460.5	514.6
140°	250.3	269.6	337.4	444.7	496.6
142.5°	259.6	275.7	339.0	432.1	478.6
145°	272.8	286.8	340.8	415.1	452.4
147.5°	284.1	297.6	343.8	398.0	430.2
150°	293.9	303.2	344.9	392.3	415.0
152.5°	301.5	311.3	346.0	384.7	405.7
155°	311.6	318.9	349.0	375.2	390.5
157.5°	324.1	328.5	349.7	370.9	381.8
160°	330.6	333.9	352.4	367.6	376.9
162.5°	334.4	338.3	352.9	364.8	372.0
165°	344.2	345.5	353.1	360.7	366.0
167.5°	350.9	349.7	356.2	359.6	361.8
170°	353.1	352.4	355.1	355.8	358.5
172.5°	358.0	355.7	356.7	354.7	356.9
175°	360.5	358.5	357.1	355.0	352.4
177.5°	361.6	358.4	356.7	354.6	355.1
180°	357.8	357.8	357.8	357.8	357.8

(END OF REPORT)