

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561508

Luminaire Tested: **SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561508
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7488.2 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 71.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561508
CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561508

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	86	79	74	88	81	75	71	73	68	65	65	62	59	58	55	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	46	43	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	24
8	57	44	36	30	53	42	35	29	38	32	27	35	29	26	31	27	24	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	19
10	49	37	29	24	47	35	28	24	32	26	22	30	24	21	27	23	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17679	17679	17679
5°	17813	17698	17632
10°	17769	17686	17636
15°	17675	17675	17659
20°	17559	17612	17612
25°	17394	17520	17466
30°	17182	17390	17314
35°	16926	17185	17066
40°	16646	16882	16711
45°	16344	16460	16205
50°	15917	15917	15662
55°	15411	15212	14984
60°	14668	14373	14144
65°	13557	13286	13168
70°	11869	11966	11918
75°	9550	10562	10626
80°	6785	8958	9048
85°	4128	7516	7516



TEST NUMBER: P561508

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.3	2.4
10°-20°	520.4	6.9
20°-30°	788.1	10.5
30°-40°	944.8	12.6
40°-50°	963.4	12.9
50°-60°	841.0	11.2
60°-70°	602.1	8.0
70°-80°	310.1	4.1
80°-90°	78.4	1.0
90°-100°	165.7	2.2
100°-110°	471.4	6.3
110°-120°	451.7	6.0
120°-130°	357.5	4.8
130°-140°	286.9	3.8
140°-150°	224.6	3.0
150°-160°	164.4	2.2
160°-170°	101.8	1.4
170°-180°	34.5	0.5
0°-30°	1489.9	19.9
0°-40°	2434.7	32.5
0°-60°	4239.0	56.6
0°-90°	5229.6	69.8
90°-120°	1088.8	14.5
90°-150°	1957.8	26.1
90°-180°	2259.0	30.2
0°-180°	7488.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1916	1916	1916	1916	1916	
5°	1923	1904	1911	1906	1904	183
15°	1850	1835	1850	1850	1849	522
25°	1709	1696	1721	1716	1716	786
35°	1503	1499	1526	1515	1515	940
45°	1253	1249	1262	1245	1242	964
55°	958	946	946	932	932	854
65°	621	607	609	603	603	614
75°	268	280	296	298	298	289
85°	39	60	71	73	71	53
90°	0	0	0	0	0	2
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	



TEST NUMBER: P561508

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1916.2	1916.2	1916.2	1916.2	1916.2
2.5°	1927.5	1910.9	1916.2	1911.8	1904.8
5°	1923.3	1904.2	1910.9	1905.5	1903.8
7.5°	1909.4	1890.4	1899.2	1895.6	1893.8
10°	1896.7	1877.6	1887.8	1884.2	1882.5
12.5°	1879.6	1861.9	1873.6	1870.0	1869.7
15°	1850.5	1834.9	1850.5	1850.5	1848.8
17.5°	1814.0	1799.8	1816.5	1817.5	1816.5
20°	1788.4	1772.8	1793.8	1792.0	1793.8
22.5°	1757.2	1744.4	1766.8	1762.2	1764.0
25°	1708.6	1696.5	1721.0	1715.7	1715.7
27.5°	1651.1	1642.4	1669.2	1663.5	1663.5
30°	1612.8	1604.1	1632.3	1625.2	1625.2
32.5°	1570.2	1564.3	1591.1	1582.6	1582.6
35°	1502.8	1499.3	1525.8	1515.2	1515.2
37.5°	1433.2	1430.1	1454.2	1441.3	1437.1
40°	1382.1	1380.4	1401.7	1387.5	1387.5
42.5°	1331.0	1329.3	1347.7	1330.7	1330.7
45°	1252.6	1249.1	1261.5	1245.4	1242.0
47.5°	1167.1	1163.6	1171.4	1153.9	1152.2
50°	1108.9	1105.4	1108.9	1092.9	1091.2
52.5°	1049.3	1043.0	1043.6	1027.6	1027.3
55°	958.1	945.9	945.7	931.5	931.5
57.5°	861.6	845.6	847.0	834.9	833.2
60°	794.9	777.5	778.9	768.2	766.5
62.5°	729.6	709.4	713.6	701.5	701.2
65°	621.0	607.1	608.6	603.2	603.2
67.5°	516.7	503.8	513.1	508.8	508.5
70°	440.0	431.3	443.6	443.5	441.8
72.5°	369.0	368.7	383.9	384.0	385.0
75°	267.9	280.1	296.3	298.1	298.1
77.5°	178.8	200.4	218.2	218.9	218.6
80°	127.7	152.0	168.6	172.1	170.3
82.5°	86.6	112.3	126.0	129.5	127.7
85°	39.0	59.9	71.0	72.7	71.0
87.5°	11.4	23.8	28.4	28.3	25.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P561508

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	<i>116.5</i>	146.7	382.3	835.7	955.2
115°	<i>136.2</i>	164.6	364.3	771.7	906.2
117.5°	<i>153.5</i>	180.1	353.6	701.8	844.3
120°	<i>167.3</i>	189.6	352.5	661.9	798.4
122.5°	<i>178.3</i>	200.6	349.8	626.8	753.6
125°	<i>192.2</i>	213.1	347.7	577.0	689.9
127.5°	<i>207.2</i>	226.8	346.6	547.2	640.2
130°	<i>215.0</i>	234.6	344.9	526.5	607.6
132.5°	<i>223.3</i>	242.3	344.9	510.3	584.9
135°	<i>235.0</i>	254.6	343.5	487.4	550.9
137.5°	<i>246.1</i>	265.1	343.4	468.0	522.9
140°	<i>254.4</i>	274.0	342.9	451.9	504.6
142.5°	<i>263.8</i>	280.1	344.5	439.0	486.4
145°	<i>277.2</i>	291.4	346.3	421.8	459.7
147.5°	<i>288.7</i>	302.4	349.4	404.4	437.1
150°	<i>298.6</i>	308.1	350.5	398.7	421.7
152.5°	<i>306.4</i>	316.4	351.6	390.9	412.3
155°	<i>316.6</i>	324.0	354.6	381.2	396.8
157.5°	<i>329.3</i>	333.8	355.3	376.8	387.9
160°	<i>335.9</i>	339.3	358.1	373.5	382.9
162.5°	<i>339.8</i>	343.7	358.6	370.7	378.0
165°	<i>349.8</i>	351.1	358.8	366.5	371.9
167.5°	<i>356.5</i>	355.3	361.9	365.4	367.6
170°	<i>358.8</i>	358.1	360.8	361.6	364.3
172.5°	<i>363.7</i>	361.4	362.5	360.5	362.6
175°	<i>366.4</i>	364.3	362.9	360.8	358.1
177.5°	<i>367.5</i>	364.2	362.5	360.3	360.8
180°	<i>363.6</i>	363.6	363.6	363.6	363.6

(END OF REPORT)