

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937947

Luminaire Tested: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937947
REPORT IS A COMBINATION OF REPORTS P933614 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13852.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 111.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937947
CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	40	40	40	33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	33	33	33	27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	27	27	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	23	23	23	18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	19	19	19	15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	16	16	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	14	14	14	11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	12	12	12	10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	11	11	11	8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	10	10	10	7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2697	2697	2697
5°	2635	3118	3626
10°	2390	4545	6011
15°	2032	5938	7259
20°	1654	6881	7397
25°	1380	7201	7247
30°	1163	7246	7233
35°	1029	7126	7421
40°	897	6969	7614
45°	812	6855	7644
50°	745	6752	7517
55°	713	6601	7184
60°	730	6311	6658
65°	759	5870	5934
70°	809	5119	5013
75°	896	4174	3912
80°	981	2895	2636
85°	871	1536	1350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7644 cd/sqm



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.2	0.5
10°-20°	333.3	2.4
20°-30°	583.0	4.2
30°-40°	750.5	5.4
40°-50°	838.3	6.1
50°-60°	802.9	5.8
60°-70°	636.3	4.6
70°-80°	374.2	2.7
80°-90°	109.5	0.8
90°-100°	703.0	5.1
100°-110°	1848.2	13.3
110°-120°	1916.4	13.8
120°-130°	1537.2	11.1
130°-140°	1206.1	8.7
140°-150°	925.8	6.7
150°-160°	666.7	4.8
160°-170°	407.9	2.9
170°-180°	137.8	1.0
0°-30°	991.6	7.2
0°-40°	1742.1	12.6
0°-60°	3383.4	24.4
0°-90°	4503.3	32.5
90°-120°	4467.6	32.3
90°-150°	8136.6	58.7
90°-180°	9349.0	67.5
0°-180°	13852.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	581	581	581	581	581	
5°	566	608	684	774	802	52
15°	424	783	1320	1600	1651	118
25°	271	888	1572	1641	1643	125
35°	183	849	1481	1565	1626	114
45°	125	677	1309	1499	1567	97
55°	90	430	1110	1290	1326	82
65°	71	228	824	927	940	70
75°	52	140	452	497	499	55
85°	19	43	112	123	125	20
90°	10	27	74	37	37	9
95°	93	364	1211	624	425	103
105°	333	504	2043	3102	2894	353
115°	591	718	1637	3265	3726	584
125°	823	922	1489	2516	2968	730
135°	980	1079	1442	2031	2303	759
145°	1137	1210	1424	1733	1868	712
155°	1285	1321	1424	1563	1609	591
165°	1387	1405	1424	1480	1498	391
175°	1442	1442	1434	1452	1452	137
180°	1442	1442	1442	1442	1442	



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4	581.4
2.5°	581.4	581.4	585.1	587.0	590.7	592.6	596.3	600.1	611.3	613.2	616.9
5°	566.4	573.9	598.2	607.6	633.7	669.2	684.2	708.5	759.0	773.9	783.3
7.5°	544.0	560.8	620.6	635.6	701.0	794.5	833.8	886.1	966.5	1005.7	1037.5
10°	508.5	544.0	650.6	686.1	792.6	934.7	1007.6	1080.6	1202.1	1256.3	1276.9
12.5°	469.2	527.2	682.3	730.9	884.2	1091.8	1179.7	1260.1	1398.4	1471.3	1482.5
15°	424.4	502.9	712.2	783.3	981.4	1222.7	1319.9	1419.0	1548.0	1600.3	1613.4
17.5°	385.1	484.2	740.3	815.1	1056.2	1340.5	1439.5	1521.8	1626.5	1662.0	1671.3
20°	336.5	454.3	759.0	856.2	1134.8	1426.5	1521.8	1585.4	1656.4	1678.8	1682.6
22.5°	301.0	422.5	770.2	871.1	1187.2	1478.8	1559.2	1609.7	1658.3	1665.7	1667.6
25°	271.1	387.0	768.3	888.0	1232.0	1510.6	1572.3	1609.7	1637.7	1641.4	1641.4
27.5°	243.0	347.7	760.9	891.7	1265.7	1518.1	1566.7	1592.8	1605.9	1613.4	1613.4
30°	218.7	310.3	742.2	884.2	1280.6	1510.6	1549.8	1562.9	1576.0	1587.2	1592.8
32.5°	200.0	274.8	714.1	869.3	1282.5	1491.9	1519.9	1527.4	1546.1	1572.3	1581.6
35°	183.2	239.3	682.3	848.7	1271.3	1462.0	1480.7	1488.1	1525.5	1564.8	1577.9
37.5°	166.4	213.1	641.2	813.2	1254.5	1426.5	1439.5	1452.6	1510.6	1557.3	1572.3
40°	149.6	190.7	592.6	773.9	1228.3	1383.5	1394.7	1415.2	1491.9	1546.1	1561.1
42.5°	136.5	172.0	540.3	732.8	1194.6	1334.9	1351.7	1381.6	1469.5	1527.4	1544.2
45°	125.3	153.3	484.2	676.7	1151.7	1284.4	1308.7	1349.8	1443.3	1499.4	1514.3
47.5°	114.0	140.2	426.2	618.8	1104.9	1233.9	1265.7	1312.4	1407.8	1462.0	1475.1
50°	104.7	127.1	368.3	557.1	1054.3	1179.7	1217.1	1265.7	1362.9	1413.4	1430.2
52.5°	97.2	115.9	314.1	495.4	996.4	1123.6	1166.6	1217.1	1308.7	1357.3	1368.5
55°	89.7	106.6	267.3	430.0	936.6	1063.8	1110.5	1159.1	1248.9	1290.0	1297.5
57.5°	86.0	99.1	228.1	368.3	873.0	996.4	1048.7	1093.7	1177.8	1209.6	1217.1
60°	80.4	93.5	198.2	315.9	803.8	932.8	977.7	1022.6	1093.7	1119.9	1125.5
62.5°	74.8	89.7	175.7	265.5	732.8	858.1	902.9	944.1	1003.9	1022.6	1030.0
65°	71.0	86.0	158.9	228.1	659.9	779.5	824.4	859.9	908.5	927.2	931.0
67.5°	67.3	82.3	145.8	196.3	587.0	701.0	734.7	768.3	805.7	824.4	826.3
70°	61.7	78.5	134.6	173.9	512.2	611.3	639.3	674.9	704.8	714.1	719.7
72.5°	58.0	72.9	127.1	157.0	435.6	525.3	551.5	572.0	598.2	607.6	607.6
75°	52.3	65.4	119.6	140.2	357.1	430.0	452.4	473.0	493.5	497.3	491.7
77.5°	46.7	58.0	102.8	117.8	278.5	340.2	358.9	370.1	387.0	390.7	392.6
80°	39.3	50.5	80.4	91.6	201.9	250.5	263.6	272.9	287.9	287.9	291.6
82.5°	29.9	39.3	58.0	65.4	136.5	172.0	183.2	188.8	198.2	198.2	198.2
85°	18.7	24.3	37.4	43.0	82.3	104.7	112.2	114.0	121.5	123.4	123.4
87.5°	9.3	13.1	24.3	26.2	43.0	54.2	54.2	58.0	58.0	56.1	54.2
90°	9.7	17.5	25.1	27.1	42.6	63.3	73.6	65.3	49.0	36.7	36.7
92.5°	38.7	104.5	170.4	186.8	262.7	363.7	414.3	363.0	260.7	183.9	176.6
95°	92.9	213.4	333.9	364.0	646.3	1022.7	1210.8	1080.5	819.8	624.3	602.1
97.5°	160.7	267.0	373.2	399.8	870.5	1498.1	1811.9	1729.6	1564.8	1441.2	1399.1
100°	212.9	309.3	405.7	429.8	952.1	1648.5	1996.8	2002.8	2014.9	2023.9	1973.7
102.5°	257.4	347.3	437.3	459.8	989.6	1695.9	2049.1	2154.0	2364.0	2521.4	2478.4
105°	332.9	409.1	485.2	504.3	1017.2	1701.3	2043.3	2278.5	2749.2	3102.1	3079.0
107.5°	410.4	481.4	552.3	570.1	1022.4	1625.5	1927.1	2255.4	2911.8	3404.1	3409.7
110°	462.7	526.8	590.9	606.9	1014.7	1558.4	1830.3	2197.3	2931.1	3481.5	3505.6



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	514.0	575.0	636.2	651.4	1015.0	1499.8	1742.2	2117.8	2868.8	3432.1	3469.2
115°	591.4	647.8	704.0	718.1	1024.3	1432.6	1636.8	1998.5	2722.1	3264.7	3316.1
117.5°	667.8	719.1	770.2	783.0	1043.4	1390.6	1564.1	1890.6	2543.6	3033.4	3090.3
120°	712.3	760.6	808.7	820.8	1058.8	1376.4	1535.1	1833.4	2430.0	2877.6	2932.8
122.5°	755.9	804.5	853.1	865.3	1081.1	1368.9	1512.8	1781.5	2318.8	2721.8	2776.3
125°	822.7	867.0	911.3	922.4	1111.1	1362.8	1488.6	1716.9	2173.3	2515.6	2565.8
127.5°	876.9	921.7	966.4	977.6	1141.2	1359.2	1468.3	1664.2	2056.2	2350.0	2392.4
130°	905.9	954.1	1002.3	1014.3	1163.1	1361.4	1460.6	1635.0	1983.9	2245.5	2284.7
132.5°	935.9	984.2	1032.3	1044.3	1180.8	1362.8	1453.7	1609.9	1922.2	2156.5	2191.5
135°	980.5	1024.3	1068.3	1079.2	1200.2	1361.5	1442.2	1572.9	1834.5	2030.6	2060.8
137.5°	1025.9	1069.4	1112.9	1123.7	1229.2	1369.9	1440.2	1550.8	1771.9	1937.7	1962.5
140°	1063.7	1103.7	1143.7	1153.7	1247.0	1371.3	1433.5	1529.0	1720.0	1863.2	1886.3
142.5°	1092.8	1129.8	1166.7	1176.0	1261.8	1376.3	1433.5	1517.3	1685.1	1810.9	1830.8
145°	1137.3	1169.5	1201.8	1209.9	1281.2	1376.3	1423.7	1492.4	1629.7	1732.6	1747.6
147.5°	1181.8	1213.2	1244.7	1252.5	1309.6	1385.7	1423.7	1477.8	1585.7	1666.8	1679.2
150°	1210.8	1239.2	1267.6	1274.8	1324.4	1390.7	1423.7	1469.4	1560.6	1629.0	1639.1
152.5°	1240.8	1262.3	1283.8	1289.2	1334.1	1393.8	1423.7	1462.7	1540.6	1599.0	1606.7
155°	1285.4	1301.3	1317.2	1321.2	1355.4	1400.9	1423.7	1454.8	1516.7	1563.2	1568.2
157.5°	1318.3	1333.7	1349.2	1353.1	1376.6	1408.0	1423.7	1447.9	1496.0	1532.2	1535.7
160°	1340.6	1352.6	1364.7	1367.7	1386.4	1411.3	1423.7	1444.4	1485.7	1516.7	1518.7
162.5°	1362.8	1371.8	1380.8	1383.1	1396.6	1414.7	1423.7	1441.1	1476.0	1502.2	1504.1
165°	1387.0	1395.2	1403.4	1405.4	1411.5	1419.6	1423.7	1436.3	1461.2	1479.9	1482.0
167.5°	1409.3	1413.1	1417.0	1417.9	1423.1	1430.0	1433.5	1441.6	1458.0	1470.2	1471.0
170°	1423.7	1427.7	1431.6	1432.5	1432.8	1433.3	1433.5	1441.6	1458.0	1470.2	1470.2
172.5°	1431.5	1432.3	1433.3	1433.5	1433.5	1433.5	1433.5	1439.9	1452.8	1462.5	1461.8
175°	1442.2	1442.2	1442.2	1442.2	1439.3	1435.4	1433.5	1437.6	1445.7	1451.9	1451.9
177.5°	1442.2	1442.2	1442.2	1442.2	1439.9	1436.9	1435.4	1438.6	1445.1	1449.9	1449.1
180°	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	581.4	581.4
2.5°	620.6	616.9
5°	798.2	802.0
7.5°	1075.0	1073.1
10°	1336.7	1353.5
12.5°	1527.4	1531.1
15°	1643.3	1650.8
17.5°	1688.2	1690.0
20°	1690.0	1686.3
22.5°	1669.5	1665.7
25°	1645.2	1643.3
27.5°	1622.7	1624.6
30°	1613.4	1619.0
32.5°	1613.4	1622.7
35°	1617.1	1626.5
37.5°	1615.3	1626.5
40°	1607.8	1620.9
42.5°	1587.2	1596.6
45°	1555.4	1566.7
47.5°	1514.3	1521.8
50°	1462.0	1469.5
52.5°	1396.5	1398.4
55°	1318.0	1325.5
57.5°	1233.9	1235.8
60°	1140.4	1146.0
62.5°	1041.3	1041.3
65°	936.6	940.3
67.5°	828.1	837.5
70°	717.9	719.7
72.5°	609.4	609.4
75°	497.3	499.1
77.5°	390.7	390.7
80°	289.8	291.6
82.5°	200.0	203.8
85°	125.3	125.3
87.5°	58.0	52.3
90°	36.7	36.7
92.5°	147.3	118.1
95°	513.5	424.9
97.5°	1230.4	1061.8
100°	1772.8	1571.9
102.5°	2306.3	2134.2
105°	2986.5	2894.0
107.5°	3432.1	3454.4
110°	3602.0	3698.4



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3617.1	3765.1
115°	3521.2	3726.4
117.5°	3317.8	3545.4
120°	3154.0	3375.0
122.5°	2994.4	3212.5
125°	2766.7	2967.6
127.5°	2561.9	2731.4
130°	2441.3	2597.8
132.5°	2331.8	2472.0
135°	2181.8	2302.6
137.5°	2061.4	2160.4
140°	1978.9	2071.3
142.5°	1910.4	1990.0
145°	1807.8	1868.0
147.5°	1729.1	1779.0
150°	1679.6	1720.0
152.5°	1637.1	1667.7
155°	1588.4	1608.6
157.5°	1549.9	1564.1
160°	1526.8	1535.1
162.5°	1511.9	1519.6
165°	1490.1	1498.3
167.5°	1474.5	1478.0
170°	1470.2	1470.2
172.5°	1458.7	1455.7
175°	1451.9	1451.9
177.5°	1445.6	1442.2
180°	1442.2	1442.2



TEST NUMBER: P937947

CATALOG NUMBER: SQ4-FB-125U-075D-92765-1D-UNV-STD-W-8-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.59	3.34	3.68	4.43	5.93	15.77	16.52	16.86	17.61	19.10
	3H	3.29	3.96	4.38	5.06	6.57	17.60	18.27	18.70	19.37	20.88
	4H	3.58	4.22	4.69	5.32	6.84	18.24	18.88	19.35	19.98	21.50
	6H	3.82	4.41	4.94	5.51	7.05	18.66	19.25	19.78	20.35	21.89
	8H	3.89	4.45	5.01	5.57	7.09	18.78	19.34	19.90	20.46	21.98
	12H	3.90	4.43	5.03	5.55	7.10	18.85	19.37	19.97	20.49	22.04
4H	2H	9.79	10.43	10.91	11.53	13.05	16.03	16.66	17.14	17.77	19.29
	3H	11.35	11.88	12.47	13.01	14.54	18.06	18.60	19.19	19.72	21.26
	4H	11.44	11.93	12.56	13.04	14.60	18.83	19.31	19.95	20.43	21.98
	6H	11.44	11.86	12.57	13.00	14.55	19.36	19.78	20.49	20.92	22.46
	8H	11.42	11.81	12.55	12.94	14.50	19.52	19.91	20.65	21.04	22.60
	12H	11.37	11.72	12.52	12.86	14.43	19.60	19.96	20.75	21.10	22.67
8H	4H	12.87	13.26	14.00	14.40	15.96	18.88	19.27	20.01	20.40	21.96
	6H	13.11	13.43	14.26	14.61	16.17	19.50	19.82	20.65	21.00	22.56
	8H	13.13	13.41	14.28	14.56	16.14	19.72	20.00	20.88	21.15	22.73
	12H	13.09	13.34	14.25	14.49	16.10	19.86	20.11	21.02	21.26	22.87
12H	4H	13.01	13.37	14.16	14.51	16.08	18.82	19.18	19.97	20.32	21.89
	6H	13.37	13.65	14.53	14.80	16.38	19.48	19.77	20.64	20.92	22.50
	8H	13.43	13.68	14.59	14.83	16.44	19.71	19.95	20.87	21.10	22.72