

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561544

Luminaire Tested: **SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561544
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7089.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561544

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561544

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55		
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	46		
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39		
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33		
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28		
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24		
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21		
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19		
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17		
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	24	20	17	15		
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13179	13179	13179
5°	13278	13193	13144
10°	13246	13184	13147
15°	13177	13177	13164
20°	13090	13129	13129
25°	12966	13060	13020
30°	12809	12963	12907
35°	12618	12811	12722
40°	12409	12585	12457
45°	12184	12270	12080
50°	11865	11865	11675
55°	11488	11340	11170
60°	10933	10713	10544
65°	10106	9905	9817
70°	8848	8921	8883
75°	7119	7874	7921
80°	5058	6673	6748
85°	3080	5600	5600



TEST NUMBER: P561544

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.2	1.9
10°-20°	387.9	5.5
20°-30°	587.5	8.3
30°-40°	704.3	9.9
40°-50°	718.2	10.1
50°-60°	626.9	8.8
60°-70°	448.8	6.3
70°-80°	231.2	3.3
80°-90°	58.5	0.8
90°-100°	234.1	3.3
100°-110°	666.0	9.4
110°-120°	638.1	9.0
120°-130°	505.0	7.1
130°-140°	405.4	5.7
140°-150°	317.4	4.5
150°-160°	232.2	3.3
160°-170°	143.8	2.0
170°-180°	48.8	0.7
0°-30°	1110.6	15.7
0°-40°	1814.9	25.6
0°-60°	3160.0	44.6
0°-90°	3898.5	55.0
90°-120°	1538.2	21.7
90°-150°	2766.0	39.0
90°-180°	3191.0	45.0
0°-180°	7089.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1428	1428	1428	1428	1428	
5°	1434	1420	1424	1420	1419	136
15°	1380	1368	1380	1380	1378	389
25°	1274	1265	1283	1279	1279	586
35°	1120	1118	1137	1130	1130	701
45°	934	931	940	928	926	719
55°	714	705	705	694	694	637
65°	463	453	454	450	450	458
75°	200	209	221	222	222	216
85°	29	45	53	54	53	40
90°	0	0	0	0	0	2
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	

TEST NUMBER: P561544

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1428.4	1428.4	1428.4	1428.4	1428.4
2.5°	1436.9	1424.5	1428.4	1425.1	1420.0
5°	1433.7	1419.5	1424.5	1420.5	1419.2
7.5°	1423.4	1409.2	1415.7	1413.1	1411.8
10°	1413.9	1399.7	1407.3	1404.6	1403.3
12.5°	1401.2	1388.0	1396.7	1394.0	1393.8
15°	1379.5	1367.8	1379.5	1379.5	1378.2
17.5°	1352.2	1341.6	1354.1	1354.9	1354.1
20°	1333.2	1321.6	1337.2	1335.9	1337.2
22.5°	1309.9	1300.3	1317.1	1313.7	1314.9
25°	1273.7	1264.6	1282.9	1279.0	1279.0
27.5°	1230.8	1224.4	1244.3	1240.1	1240.1
30°	1202.3	1195.8	1216.8	1211.5	1211.5
32.5°	1170.5	1166.1	1186.1	1179.8	1179.8
35°	1120.3	1117.7	1137.4	1129.5	1129.5
37.5°	1068.4	1066.1	1084.0	1074.4	1071.3
40°	1030.3	1029.0	1044.9	1034.3	1034.3
42.5°	992.2	990.9	1004.7	992.0	992.0
45°	933.8	931.2	940.4	928.4	925.8
47.5°	870.0	867.4	873.2	860.2	858.9
50°	826.6	824.0	826.6	814.7	813.4
52.5°	782.2	777.5	778.0	766.1	765.8
55°	714.2	705.2	705.0	694.4	694.4
57.5°	642.3	630.4	631.4	622.4	621.1
60°	592.5	579.6	580.6	572.7	571.4
62.5°	543.9	528.9	532.0	523.0	522.7
65°	462.9	452.6	453.7	449.7	449.7
67.5°	385.1	375.6	382.5	379.3	379.1
70°	328.0	321.5	330.7	330.6	329.3
72.5°	275.1	274.8	286.2	286.2	287.0
75°	199.7	208.8	220.9	222.2	222.2
77.5°	133.3	149.4	162.7	163.2	162.9
80°	95.2	113.3	125.6	128.3	127.0
82.5°	64.5	83.7	93.9	96.5	95.2
85°	29.1	44.6	52.9	54.2	52.9
87.5°	8.5	17.8	21.2	21.1	19.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5

TEST NUMBER: P561544

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)